

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331817-840

Luminaire Tested: **S122RDIW-S675D1240U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331817-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7571.2 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	30				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	72	64	58	54	52	48	44	41	38	36	30	29	27	22				
4	73	63	55	50	66	57	51	46	46	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18				
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	35	31	34	30	26	28	24	22	21	19	17	14				
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	13				
9	50	38	31	26	45	35	29	24	29	24	21	23	20	18	18	16	14	12				
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23954	23954	23954	23954
5°	26752	24104	21371	24104
10°	29681	23935	18525	23935
15°	31141	23584	14596	23584
20°	26996	23063	12631	23063
25°	17706	22352	11277	22352
30°	11917	21490	10206	21490
35°	9652	20402	9207	20402
40°	8585	19220	8517	19220
45°	7768	17831	7606	17831
50°	7068	16458	7043	16458
55°	6646	14933	6559	14933
60°	5561	13533	5493	13533
65°	4688	12287	5318	12287
70°	4334	10976	5013	10976
75°	4049	9551	4629	9551
80°	3738	7857	4119	7857
85°	3446	6206	3631	6206



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	1.9
10°-20°	391.9	5.2
20°-30°	505.0	6.7
30°-40°	479.9	6.3
40°-50°	411.1	5.4
50°-60°	313.0	4.1
60°-70°	197.9	2.6
70°-80°	98.8	1.3
80°-90°	29.9	0.4
90°-100°	56.9	0.8
100°-110°	208.8	2.8
110°-120°	558.2	7.4
120°-130°	921.5	12.2
130°-140°	980.0	12.9
140°-150°	910.9	12.0
150°-160°	732.3	9.7
160°-170°	471.9	6.2
170°-180°	162.4	2.1
0°-30°	1037.5	13.7
0°-40°	1517.4	20.0
0°-60°	2241.5	29.6
0°-90°	2568.1	33.9
90°-120°	824.0	10.9
90°-150°	3636.4	48.0
90°-180°	5003.0	66.1
0°-180°	7571.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1484	1484	1484	1484	1484	
5°	1651	1487	1319	1487	1651	163
15°	1863	1411	873	1411	1863	503
25°	994	1255	633	1255	994	472
35°	490	1035	467	1035	490	313
45°	340	781	333	781	340	263
55°	236	530	233	530	236	207
65°	123	322	139	322	123	125
75°	65	153	74	153	65	69
85°	19	34	20	34	19	21
90°	33	1	33	1	33	15
95°	53	80	53	80	53	50
105°	94	376	94	376	94	98
115°	101	710	101	710	101	254
125°	1056	1004	1056	1004	1056	914
135°	1284	1243	1284	1243	1284	989
145°	1464	1442	1464	1442	1464	915
155°	1589	1587	1589	1587	1589	733
165°	1669	1673	1669	1673	1669	471
175°	1701	1711	1701	1711	1701	162
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1543.8	1545.0	1546.3	1543.4	1543.4	1540.9	1535.5	1531.5	1519.8	1518.2	1518.2
5°	1650.6	1649.5	1651.6	1645.0	1635.7	1633.6	1623.8	1610.9	1597.5	1582.6	1579.4
7.5°	1756.8	1755.2	1751.1	1750.0	1742.8	1727.3	1711.5	1694.8	1672.4	1650.7	1639.8
10°	1810.4	1827.5	1817.1	1799.1	1802.7	1778.5	1765.5	1743.4	1724.8	1692.3	1685.2
12.5°	1863.2	1869.9	1866.6	1856.3	1851.7	1834.9	1817.6	1798.3	1764.0	1734.8	1709.5
15°	1863.0	1872.8	1875.3	1872.3	1874.8	1873.8	1864.5	1848.6	1818.7	1786.7	1758.9
17.5°	1725.5	1732.2	1749.2	1760.6	1775.0	1805.5	1820.6	1826.4	1822.0	1803.8	1784.2
20°	1571.2	1559.8	1607.3	1631.5	1652.1	1703.6	1748.0	1765.0	1792.3	1791.8	1786.7
22.5°	1352.6	1355.3	1400.3	1429.1	1489.2	1540.8	1591.3	1655.4	1708.2	1743.1	1763.6
25°	993.9	1013.5	1058.3	1097.5	1164.5	1260.4	1347.5	1448.6	1543.9	1619.1	1690.8
27.5°	746.4	747.9	783.5	819.6	859.4	938.0	1047.6	1168.3	1304.2	1416.4	1545.5
30°	639.2	636.1	651.1	673.3	707.2	768.1	850.5	969.2	1104.7	1273.7	1424.3
32.5°	563.3	563.5	574.8	591.2	619.5	660.5	716.9	813.2	941.4	1107.6	1284.0
35°	489.7	489.2	497.5	509.3	521.2	547.4	586.1	636.6	724.8	879.9	1060.4
37.5°	437.0	439.2	443.2	450.6	463.7	478.4	501.6	535.5	598.2	690.0	841.7
40°	407.3	408.3	413.9	420.1	427.9	439.2	458.3	485.5	531.5	604.7	715.5
42.5°	380.0	381.0	385.1	390.8	396.9	408.3	424.0	447.7	484.8	542.0	633.4
45°	340.2	340.2	343.9	346.4	353.1	363.5	376.3	395.9	421.7	463.9	524.7
47.5°	302.9	303.0	305.4	309.8	314.1	322.0	334.8	350.7	369.5	402.2	454.1
50°	281.4	282.0	283.5	287.1	289.7	296.9	306.7	320.6	340.2	365.5	408.8
52.5°	264.2	263.8	265.8	267.3	269.1	274.3	281.6	293.9	311.3	333.4	369.2
55°	236.1	234.0	237.1	239.7	241.3	243.3	247.4	255.2	270.1	288.7	315.5
57.5°	201.1	200.3	202.4	204.8	209.6	215.2	218.6	223.6	231.4	244.7	271.2
60°	172.2	172.2	176.8	178.3	184.0	191.3	198.4	202.6	210.4	219.0	238.6
62.5°	146.6	147.0	149.2	150.8	153.9	162.8	172.9	182.0	189.2	197.6	210.7
65°	122.7	123.7	123.7	124.7	126.8	128.9	133.0	140.2	153.1	164.9	174.7
67.5°	104.1	104.4	104.7	105.7	106.3	108.6	110.2	113.4	116.4	127.6	139.8
70°	91.8	93.3	92.8	93.8	94.3	95.3	97.5	99.0	103.6	106.2	113.4
72.5°	80.2	81.3	81.2	81.9	83.2	83.4	85.0	86.6	89.6	91.8	95.6
75°	64.9	64.4	64.9	65.9	66.4	67.1	67.1	69.1	70.6	72.7	75.2
77.5°	50.1	50.6	50.5	50.6	50.7	51.6	51.5	52.5	54.0	55.0	56.2
80°	40.2	40.7	40.2	40.7	41.2	41.7	41.2	41.7	43.3	44.3	44.3
82.5°	31.1	31.2	31.5	31.6	31.7	31.8	32.6	32.7	33.8	33.6	34.0
85°	18.6	18.1	18.1	18.1	18.6	19.1	18.6	18.6	19.1	19.1	19.1
87.5°	13.2	13.5	13.4	13.3	13.2	13.0	12.8	12.9	12.2	12.3	11.5
90°	33.3	32.8	32.2	31.7	31.2	30.2	28.8	27.5	26.1	24.7	22.5
92.5°	33.3	33.0	32.7	32.3	32.0	31.5	30.8	30.1	29.4	28.7	27.6
95°	53.1	53.4	53.6	53.9	54.2	53.6	52.3	50.9	49.6	48.2	46.3
97.5°	70.9	70.6	70.3	69.9	69.6	68.9	67.8	66.7	65.5	64.5	60.1
100°	82.8	82.2	81.7	81.1	80.6	79.2	77.0	74.8	72.6	70.4	65.7
102.5°	88.7	88.0	87.2	86.3	85.6	83.8	81.0	78.1	75.2	72.4	111.4
105°	93.9	92.8	91.7	90.6	89.5	87.5	84.4	81.4	78.4	75.3	150.3
107.5°	96.6	95.5	94.4	93.3	92.2	93.2	96.2	99.4	102.4	105.5	195.4
110°	97.6	96.5	95.4	94.3	93.2	106.3	133.8	161.3	188.7	216.2	295.5



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.6	97.7	96.8	95.9	95.0	144.7	244.9	345.0	445.1	545.2	564.9
115°	101.3	121.1	140.9	160.6	180.4	253.8	380.9	508.0	635.1	762.2	755.4
117.5°	413.5	478.6	543.5	608.4	673.4	721.2	751.9	782.7	813.4	844.2	839.5
120°	753.6	790.6	827.7	864.7	901.8	918.7	915.3	912.1	908.8	905.4	900.6
122.5°	940.3	947.6	954.7	961.9	969.1	971.7	969.8	967.8	965.7	963.8	958.5
125°	1056.2	1055.4	1054.6	1053.7	1052.9	1051.6	1049.7	1047.7	1045.8	1043.9	1038.6
127.5°	1129.3	1129.1	1129.0	1128.8	1128.7	1127.2	1124.4	1121.6	1118.8	1116.0	1112.1
130°	1174.8	1175.1	1175.4	1175.6	1175.9	1174.5	1171.5	1168.5	1165.5	1162.5	1159.4
132.5°	1219.3	1219.5	1219.8	1220.1	1220.3	1219.2	1216.6	1214.1	1211.4	1208.9	1205.9
135°	1283.5	1284.0	1284.6	1285.2	1285.7	1284.6	1281.8	1279.1	1276.4	1273.6	1271.1
137.5°	1342.0	1343.0	1343.9	1344.8	1345.7	1344.9	1342.2	1339.5	1336.9	1334.1	1331.3
140°	1378.7	1380.0	1381.4	1382.7	1384.1	1383.6	1381.1	1378.7	1376.1	1373.7	1370.7
142.5°	1414.2	1415.5	1416.9	1418.4	1419.7	1419.3	1417.0	1414.7	1412.5	1410.3	1406.7
145°	1463.9	1465.2	1466.6	1467.9	1469.4	1469.1	1467.1	1465.2	1463.3	1461.4	1456.7
147.5°	1507.6	1508.7	1509.8	1511.1	1512.2	1512.1	1510.7	1509.2	1507.8	1506.3	1501.8
150°	1534.3	1535.6	1537.0	1538.4	1539.7	1539.6	1538.0	1536.3	1534.7	1533.1	1528.6
152.5°	1557.0	1558.8	1560.6	1562.5	1564.3	1564.4	1562.7	1561.0	1559.4	1557.7	1553.6
155°	1588.6	1590.8	1593.1	1595.2	1597.4	1597.7	1596.1	1594.4	1592.8	1591.1	1587.8
157.5°	1617.5	1619.7	1621.8	1624.0	1626.1	1626.3	1624.4	1622.6	1620.6	1618.8	1616.5
160°	1634.4	1636.3	1638.2	1640.1	1642.0	1642.1	1640.5	1638.9	1637.2	1635.6	1634.0
162.5°	1648.2	1650.5	1652.8	1655.3	1657.6	1657.9	1656.0	1654.2	1652.2	1650.4	1649.0
165°	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9	1668.1
167.5°	1682.0	1684.5	1687.0	1689.4	1691.9	1692.1	1690.2	1688.3	1686.4	1684.5	1683.7
170°	1689.9	1692.4	1694.9	1697.4	1699.8	1700.1	1698.2	1696.3	1694.4	1692.4	1691.8
172.5°	1695.9	1698.3	1700.8	1703.2	1705.8	1706.0	1704.0	1702.1	1700.2	1698.3	1697.8
175°	1701.0	1703.7	1706.6	1709.3	1712.0	1712.4	1710.5	1708.6	1706.7	1704.8	1704.2
177.5°	1704.2	1706.3	1708.2	1710.2	1712.1	1712.4	1710.8	1709.3	1707.8	1706.3	1706.0
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1519.0	1515.7	1512.9	1505.4	1501.8	1493.5	1492.3	1491.9	1481.1	1470.8	1467.9
5°	1571.2	1563.0	1550.5	1536.1	1521.2	1505.7	1495.4	1487.2	1466.5	1446.9	1435.6
7.5°	1623.8	1606.1	1584.7	1557.4	1534.6	1509.0	1490.1	1473.1	1443.8	1415.7	1396.8
10°	1662.9	1634.1	1605.8	1568.1	1538.7	1509.8	1483.1	1459.9	1426.8	1389.8	1363.4
12.5°	1687.3	1655.6	1616.5	1579.6	1541.7	1504.9	1469.1	1439.3	1400.5	1362.1	1330.9
15°	1720.2	1686.2	1638.7	1586.2	1537.2	1489.2	1448.0	1410.9	1360.4	1314.5	1276.4
17.5°	1747.1	1700.3	1649.3	1588.5	1531.9	1470.9	1417.7	1370.4	1314.1	1258.8	1213.9
20°	1755.8	1709.4	1650.6	1589.7	1522.8	1451.1	1393.9	1342.3	1282.0	1221.7	1170.1
22.5°	1750.4	1714.3	1648.9	1576.2	1507.5	1432.5	1367.9	1308.1	1241.2	1179.6	1119.8
25°	1714.0	1701.6	1639.8	1560.3	1482.1	1394.9	1320.2	1254.7	1178.4	1112.5	1047.4
27.5°	1629.1	1655.9	1617.5	1533.0	1445.8	1352.4	1268.4	1193.9	1114.7	1040.5	975.7
30°	1547.5	1608.8	1592.4	1514.0	1416.5	1324.8	1230.5	1152.7	1068.1	991.8	927.9
32.5°	1435.7	1537.1	1553.2	1487.6	1386.8	1286.1	1187.2	1109.7	1021.5	941.1	878.8
35°	1257.8	1409.4	1478.9	1437.1	1336.2	1227.4	1125.3	1035.1	946.4	867.1	805.2
37.5°	1045.5	1251.9	1367.9	1370.9	1278.1	1165.0	1053.9	964.3	873.5	795.6	728.7
40°	907.8	1131.5	1282.5	1316.1	1237.7	1115.5	1003.1	911.9	823.2	746.9	670.1
42.5°	784.1	1006.9	1192.7	1250.9	1188.6	1067.2	954.5	859.1	773.0	700.7	622.3
45°	634.1	828.9	1033.6	1137.7	1103.2	990.8	871.7	780.9	700.0	637.6	562.4
47.5°	534.8	672.2	870.2	1011.1	1010.5	907.9	790.7	703.9	628.8	570.4	509.4
50°	478.4	597.9	765.5	925.3	938.7	852.6	741.2	655.2	585.1	523.7	474.7
52.5°	427.7	526.2	676.8	830.0	868.2	793.7	685.6	606.1	538.1	481.7	439.7
55°	361.3	437.7	552.1	695.4	753.2	700.5	604.7	530.5	475.2	427.9	391.7
57.5°	305.7	362.9	454.7	570.2	637.3	604.3	525.1	464.8	417.7	374.8	346.3
60°	270.6	317.5	395.4	491.8	566.0	542.8	475.2	419.1	378.9	341.7	315.0
62.5°	237.6	277.9	344.7	422.9	491.0	481.4	426.2	379.1	343.9	310.0	287.3
65°	191.3	220.7	272.7	334.1	388.7	393.3	353.7	321.6	290.2	263.4	243.3
67.5°	152.3	171.5	208.1	259.8	300.7	315.4	291.1	266.7	241.8	221.1	203.6
70°	128.4	143.8	170.7	212.4	250.0	265.5	251.6	232.5	210.9	193.8	178.8
72.5°	104.0	119.1	138.9	169.5	201.8	218.4	213.6	200.0	182.4	168.2	154.1
75°	78.4	83.0	96.4	117.0	142.3	156.7	160.4	153.1	139.2	128.4	120.1
77.5°	58.0	60.7	67.2	78.0	94.4	107.3	112.6	111.8	102.2	95.8	88.2
80°	46.4	48.0	51.0	55.6	68.1	80.9	84.5	84.5	77.9	75.2	67.6
82.5°	35.2	36.4	38.3	40.8	46.6	57.9	61.9	62.7	58.5	55.0	49.0
85°	20.1	19.6	20.6	22.1	23.2	26.3	32.5	33.5	32.5	28.4	26.8
87.5°	11.1	11.0	10.6	9.7	9.5	9.3	10.7	12.2	11.2	10.5	10.3
90°	20.3	18.1	16.0	13.3	10.3	7.3	4.2	1.2	4.2	7.3	10.3
92.5°	26.5	25.3	24.2	23.8	24.1	24.4	24.6	24.9	24.6	24.4	24.1
95°	44.3	42.4	40.5	44.0	53.1	62.2	71.2	80.3	71.2	62.2	53.1
97.5°	55.5	51.1	46.7	57.3	82.8	108.3	133.8	159.4	133.8	108.3	82.8
100°	61.1	56.5	51.7	68.3	105.8	143.4	181.1	218.6	181.1	143.4	105.8
102.5°	150.5	189.5	228.5	252.1	260.0	267.9	275.9	283.9	275.9	267.9	260.0
105°	225.2	300.2	375.2	408.5	400.2	392.0	383.7	375.6	383.7	392.0	400.2
107.5°	285.3	375.2	465.0	506.6	500.0	493.3	486.7	480.1	486.7	493.3	500.0
110°	374.9	454.2	533.5	570.3	564.5	558.8	553.0	547.2	553.0	558.8	564.5



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	584.5	604.1	623.7	631.0	625.8	620.7	615.6	610.5	615.6	620.7	625.8
115°	748.5	741.6	734.8	729.0	724.3	719.6	715.0	710.3	715.0	719.6	724.3
117.5°	834.8	830.0	825.4	820.4	815.2	809.9	804.8	799.5	804.8	809.9	815.2
120°	895.6	890.7	885.8	881.2	877.1	872.9	868.9	864.7	868.9	872.9	877.1
122.5°	953.0	947.7	942.3	937.5	933.1	928.8	924.4	920.1	924.4	928.8	933.1
125°	1033.4	1028.2	1023.0	1018.5	1015.0	1011.5	1007.8	1004.3	1007.8	1011.5	1015.0
127.5°	1108.2	1104.3	1100.4	1096.5	1092.6	1088.5	1084.6	1080.7	1084.6	1088.5	1092.6
130°	1156.4	1153.4	1150.3	1146.7	1142.3	1137.9	1133.5	1129.1	1133.5	1137.9	1142.3
132.5°	1202.9	1199.8	1196.8	1193.5	1189.7	1186.0	1182.2	1178.5	1182.2	1186.0	1189.7
135°	1268.7	1266.2	1263.7	1260.3	1255.9	1251.5	1247.1	1242.7	1247.1	1251.5	1255.9
137.5°	1328.6	1325.8	1322.9	1320.0	1317.0	1313.8	1310.8	1307.7	1310.8	1313.8	1317.0
140°	1367.7	1364.6	1361.6	1359.0	1356.8	1354.6	1352.4	1350.2	1352.4	1354.6	1356.8
142.5°	1403.3	1399.9	1396.4	1393.7	1391.7	1389.8	1387.8	1385.8	1387.8	1389.8	1391.7
145°	1452.1	1447.4	1442.7	1440.6	1440.8	1441.1	1441.4	1441.6	1441.4	1441.1	1440.8
147.5°	1497.1	1492.5	1487.9	1486.1	1487.1	1488.2	1489.2	1490.3	1489.2	1488.2	1487.1
150°	1524.3	1519.8	1515.5	1514.2	1516.1	1518.1	1520.0	1522.0	1520.0	1518.1	1516.1
152.5°	1549.4	1545.2	1541.1	1540.0	1542.2	1544.3	1546.5	1548.6	1546.5	1544.3	1542.2
155°	1584.5	1581.2	1577.9	1577.5	1579.9	1582.5	1584.9	1587.4	1584.9	1582.5	1579.9
157.5°	1614.2	1611.8	1609.5	1609.4	1611.5	1613.6	1615.7	1617.8	1615.7	1613.6	1611.5
160°	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1634.0	1632.2	1630.6
162.5°	1647.5	1646.1	1644.7	1644.8	1646.5	1648.1	1649.7	1651.4	1649.7	1648.1	1646.5
165°	1667.3	1666.5	1665.7	1666.1	1667.7	1669.3	1671.0	1672.6	1671.0	1669.3	1667.7
167.5°	1682.9	1682.2	1681.4	1681.8	1683.5	1685.2	1686.8	1688.5	1686.8	1685.2	1683.5
170°	1691.3	1690.7	1690.2	1690.7	1692.4	1694.0	1695.7	1697.4	1695.7	1694.0	1692.4
172.5°	1697.2	1696.7	1696.2	1696.7	1698.3	1700.0	1701.6	1703.2	1701.6	1700.0	1698.3
175°	1703.6	1703.1	1702.5	1703.2	1705.2	1707.1	1709.0	1710.9	1709.0	1707.1	1705.2
177.5°	1705.8	1705.6	1705.4	1706.0	1707.6	1709.1	1710.6	1712.1	1710.6	1709.1	1707.6
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1462.6	1459.7	1454.3	1446.0	1441.1	1432.4	1426.6	1430.0	1430.8	1430.0	1429.2
5°	1423.3	1412.4	1397.5	1383.0	1369.7	1355.2	1347.0	1343.3	1336.2	1332.0	1330.0
7.5°	1375.7	1357.1	1336.0	1310.8	1289.4	1267.1	1255.7	1249.9	1235.2	1227.2	1220.1
10°	1340.3	1310.9	1289.8	1256.8	1236.7	1207.3	1187.2	1187.7	1167.6	1156.2	1148.0
12.5°	1301.1	1268.8	1233.7	1204.0	1176.0	1152.5	1128.2	1118.4	1097.0	1086.1	1063.9
15°	1236.2	1198.5	1161.4	1121.2	1092.9	1056.2	1021.2	978.4	943.8	913.9	905.7
17.5°	1165.2	1118.6	1081.4	1034.2	985.6	924.0	883.4	858.6	837.8	822.0	810.2
20°	1116.5	1069.1	1029.5	958.3	892.8	851.1	821.2	802.1	780.4	763.5	754.2
22.5°	1065.4	1015.9	961.8	882.4	831.4	797.9	771.2	749.3	734.7	721.3	713.0
25°	992.8	938.7	849.5	794.9	753.7	718.6	700.0	686.6	671.2	653.1	644.9
27.5°	916.1	830.0	766.0	725.4	686.0	663.2	646.5	626.5	612.7	604.6	596.0
30°	858.8	772.7	722.8	678.4	650.6	625.3	605.7	594.4	581.0	567.0	561.4
32.5°	794.9	726.1	678.2	641.3	613.0	591.5	576.0	557.6	548.0	539.4	527.6
35°	715.5	663.5	619.7	589.8	562.9	545.4	527.4	516.5	499.0	491.8	487.2
37.5°	648.2	603.1	570.5	538.9	517.7	498.3	487.3	470.0	462.4	452.4	442.6
40°	610.4	566.0	534.5	508.8	485.0	470.6	456.8	442.8	431.4	426.9	415.0
42.5°	571.6	535.5	504.0	475.7	459.9	444.6	427.1	416.9	405.1	397.6	390.2
45°	518.1	486.1	459.3	436.1	418.6	402.6	391.2	374.3	367.6	352.5	346.4
47.5°	471.1	441.3	415.8	393.7	376.6	366.2	349.6	336.3	325.6	316.4	308.5
50°	437.7	412.9	388.2	368.6	353.1	338.2	321.1	314.5	297.9	293.3	288.7
52.5°	407.2	383.6	360.9	341.7	326.3	311.7	296.8	288.0	276.9	272.3	268.9
55°	364.5	341.7	320.1	303.1	287.6	272.7	263.4	252.6	247.4	243.8	239.7
57.5°	321.5	301.1	284.6	267.3	251.8	239.9	229.1	222.7	217.3	212.6	207.6
60°	294.4	274.8	259.8	243.8	227.8	218.0	209.8	202.1	195.9	188.6	186.6
62.5°	265.5	248.3	234.7	219.0	205.2	196.2	188.3	181.1	173.6	163.1	160.2
65°	225.8	212.4	197.9	185.1	172.7	163.9	152.6	144.3	141.3	140.2	139.7
67.5°	190.0	177.2	164.8	151.7	140.4	132.3	126.5	125.2	123.1	122.5	121.1
70°	166.0	154.1	141.8	129.4	118.6	117.0	114.9	112.9	110.3	109.3	108.3
72.5°	144.5	132.3	119.9	110.0	105.3	103.4	101.4	99.3	97.6	96.5	95.8
75°	110.8	99.5	91.3	87.7	85.0	83.5	80.4	78.9	77.9	76.2	75.7
77.5°	79.8	73.4	69.6	67.4	64.6	63.0	61.2	59.7	58.6	58.3	57.5
80°	60.8	57.8	55.1	52.1	51.0	49.0	48.5	47.0	47.5	45.8	45.8
82.5°	47.3	43.3	41.1	39.7	38.7	37.1	36.5	35.7	35.9	34.7	34.7
85°	24.2	23.2	22.1	21.1	21.1	19.6	20.1	19.6	19.6	18.6	18.1
87.5°	10.5	10.6	10.2	10.7	11.1	11.1	11.4	11.3	11.5	11.8	11.6
90°	13.3	16.0	18.1	20.3	22.5	24.7	26.1	27.5	28.8	30.2	31.2
92.5°	23.8	24.2	25.3	26.5	27.6	28.7	29.4	30.1	30.8	31.5	32.0
95°	44.0	40.5	42.4	44.3	46.3	48.2	49.6	50.9	52.3	53.6	54.2
97.5°	57.3	46.7	51.1	55.5	60.1	64.5	65.5	66.7	67.8	68.9	69.6
100°	68.3	51.7	56.5	61.1	65.7	70.4	72.6	74.8	77.0	79.2	80.6
102.5°	252.1	228.5	189.5	150.5	111.4	72.4	75.2	78.1	81.0	83.8	85.6
105°	408.5	375.2	300.2	225.2	150.3	75.3	78.4	81.4	84.4	87.5	89.5
107.5°	506.6	465.0	375.2	285.3	195.4	105.5	102.4	99.4	96.2	93.2	92.2
110°	570.3	533.5	454.2	374.9	295.5	216.2	188.7	161.3	133.8	106.3	93.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	631.0	623.7	604.1	584.5	564.9	545.2	445.1	345.0	244.9	144.7	95.0
115°	729.0	734.8	741.6	748.5	755.4	762.2	635.1	508.0	380.9	253.8	180.4
117.5°	820.4	825.4	830.0	834.8	839.5	844.2	813.4	782.7	751.9	721.2	673.4
120°	881.2	885.8	890.7	895.6	900.6	905.4	908.8	912.1	915.3	918.7	901.8
122.5°	937.5	942.3	947.7	953.0	958.5	963.8	965.7	967.8	969.8	971.7	969.1
125°	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8	1047.7	1049.7	1051.6	1052.9
127.5°	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8	1121.6	1124.4	1127.2	1128.7
130°	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5	1168.5	1171.5	1174.5	1175.9
132.5°	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4	1214.1	1216.6	1219.2	1220.3
135°	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4	1279.1	1281.8	1284.6	1285.7
137.5°	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9	1339.5	1342.2	1344.9	1345.7
140°	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1	1378.7	1381.1	1383.6	1384.1
142.5°	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5	1414.7	1417.0	1419.3	1419.7
145°	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3	1465.2	1467.1	1469.1	1469.4
147.5°	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8	1509.2	1510.7	1512.1	1512.2
150°	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7	1536.3	1538.0	1539.6	1539.7
152.5°	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4	1561.0	1562.7	1564.4	1564.3
155°	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8	1594.4	1596.1	1597.7	1597.4
157.5°	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6	1622.6	1624.4	1626.3	1626.1
160°	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2	1638.9	1640.5	1642.1	1642.0
162.5°	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2	1654.2	1656.0	1657.9	1657.6
165°	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6
167.5°	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4	1688.3	1690.2	1692.1	1691.9
170°	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4	1696.3	1698.2	1700.1	1699.8
172.5°	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2	1702.1	1704.0	1706.0	1705.8
175°	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7	1708.6	1710.5	1712.4	1712.0
177.5°	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8	1709.3	1710.8	1712.4	1712.1
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1424.6	1425.4	1424.2	1425.0	1424.2	1425.4	1424.6	1429.2	1430.0	1430.8	1430.0
5°	1327.4	1321.2	1320.2	1318.6	1320.2	1321.2	1327.4	1330.0	1332.0	1336.2	1343.3
7.5°	1211.3	1210.3	1207.8	1204.2	1207.8	1210.3	1211.3	1220.1	1227.2	1235.2	1249.9
10°	1136.6	1134.1	1133.6	1129.9	1133.6	1134.1	1136.6	1148.0	1156.2	1167.6	1187.7
12.5°	1049.2	1032.6	1030.9	1021.9	1030.9	1032.6	1049.2	1063.9	1086.1	1097.0	1118.4
15°	893.3	890.3	879.9	873.2	879.9	890.3	893.3	905.7	913.9	943.8	978.4
17.5°	804.3	794.2	790.9	789.5	790.9	794.2	804.3	810.2	822.0	837.8	858.6
20°	746.9	737.7	736.1	735.1	736.1	737.7	746.9	754.2	763.5	780.4	802.1
22.5°	707.3	697.6	693.7	690.5	693.7	697.6	707.3	713.0	721.3	734.7	749.3
25°	639.7	636.1	634.1	633.0	634.1	636.1	639.7	644.9	653.1	671.2	686.6
27.5°	586.8	578.9	577.3	574.7	577.3	578.9	586.8	596.0	604.6	612.7	626.5
30°	556.7	554.1	550.6	547.4	550.6	554.1	556.7	561.4	567.0	581.0	594.4
32.5°	521.3	519.1	515.9	514.4	515.9	519.1	521.3	527.6	539.4	548.0	557.6
35°	482.0	474.7	471.7	467.1	471.7	474.7	482.0	487.2	491.8	499.0	516.5
37.5°	440.4	436.7	432.3	433.8	432.3	436.7	440.4	442.6	452.4	462.4	470.0
40°	408.3	405.7	404.7	404.1	404.7	405.7	408.3	415.0	426.9	431.4	442.8
42.5°	382.7	375.6	372.9	372.8	372.9	375.6	382.7	390.2	397.6	405.1	416.9
45°	343.9	337.1	332.4	333.1	332.4	337.1	343.9	346.4	352.5	367.6	374.3
47.5°	304.1	303.9	300.9	301.8	300.9	303.9	304.1	308.5	316.4	325.6	336.3
50°	285.1	282.0	279.9	280.4	279.9	282.0	285.1	288.7	293.3	297.9	314.5
52.5°	266.9	264.3	262.6	264.8	262.6	264.3	266.9	268.9	272.3	276.9	288.0
55°	237.1	234.0	233.5	233.0	233.5	234.0	237.1	239.7	243.8	247.4	252.6
57.5°	203.8	201.8	198.6	197.3	198.6	201.8	203.8	207.6	212.6	217.3	222.7
60°	179.9	175.8	170.7	170.1	170.7	175.8	179.9	186.6	188.6	195.9	202.1
62.5°	158.0	157.2	156.2	156.1	156.2	157.2	158.0	160.2	163.1	173.6	181.1
65°	138.7	138.1	138.7	139.2	138.7	138.1	138.7	139.7	140.2	141.3	144.3
67.5°	120.9	119.9	119.0	119.4	119.0	119.9	120.9	121.1	122.5	123.1	125.2
70°	107.2	106.7	106.2	106.2	106.2	106.7	107.2	108.3	109.3	110.3	112.9
72.5°	94.0	93.9	93.4	93.0	93.4	93.9	94.0	95.8	96.5	97.6	99.3
75°	75.2	74.2	74.2	74.2	74.2	74.2	75.2	75.7	76.2	77.9	78.9
77.5°	57.4	56.9	56.2	55.8	56.2	56.9	57.4	57.5	58.3	58.6	59.7
80°	45.3	44.8	44.3	44.3	44.3	44.8	45.3	45.8	45.8	47.5	47.0
82.5°	34.6	34.1	34.0	33.6	34.0	34.1	34.6	34.7	34.7	35.9	35.7
85°	18.6	19.1	18.6	19.6	18.6	19.1	18.6	18.1	18.6	19.6	19.6
87.5°	11.7	11.4	11.9	11.6	11.9	11.4	11.7	11.6	11.8	11.5	11.3
90°	31.7	32.2	32.8	33.3	32.8	32.2	31.7	31.2	30.2	28.8	27.5
92.5°	32.3	32.7	33.0	33.3	33.0	32.7	32.3	32.0	31.5	30.8	30.1
95°	53.9	53.6	53.4	53.1	53.4	53.6	53.9	54.2	53.6	52.3	50.9
97.5°	69.9	70.3	70.6	70.9	70.6	70.3	69.9	69.6	68.9	67.8	66.7
100°	81.1	81.7	82.2	82.8	82.2	81.7	81.1	80.6	79.2	77.0	74.8
102.5°	86.3	87.2	88.0	88.7	88.0	87.2	86.3	85.6	83.8	81.0	78.1
105°	90.6	91.7	92.8	93.9	92.8	91.7	90.6	89.5	87.5	84.4	81.4
107.5°	93.3	94.4	95.5	96.6	95.5	94.4	93.3	92.2	93.2	96.2	99.4
110°	94.3	95.4	96.5	97.6	96.5	95.4	94.3	93.2	106.3	133.8	161.3



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.9	96.8	97.7	98.6	97.7	96.8	95.9	95.0	144.7	244.9	345.0
115°	160.6	140.9	121.1	101.3	121.1	140.9	160.6	180.4	253.8	380.9	508.0
117.5°	608.4	543.5	478.6	413.5	478.6	543.5	608.4	673.4	721.2	751.9	782.7
120°	864.7	827.7	790.6	753.6	790.6	827.7	864.7	901.8	918.7	915.3	912.1
122.5°	961.9	954.7	947.6	940.3	947.6	954.7	961.9	969.1	971.7	969.8	967.8
125°	1053.7	1054.6	1055.4	1056.2	1055.4	1054.6	1053.7	1052.9	1051.6	1049.7	1047.7
127.5°	1128.8	1129.0	1129.1	1129.3	1129.1	1129.0	1128.8	1128.7	1127.2	1124.4	1121.6
130°	1175.6	1175.4	1175.1	1174.8	1175.1	1175.4	1175.6	1175.9	1174.5	1171.5	1168.5
132.5°	1220.1	1219.8	1219.5	1219.3	1219.5	1219.8	1220.1	1220.3	1219.2	1216.6	1214.1
135°	1285.2	1284.6	1284.0	1283.5	1284.0	1284.6	1285.2	1285.7	1284.6	1281.8	1279.1
137.5°	1344.8	1343.9	1343.0	1342.0	1343.0	1343.9	1344.8	1345.7	1344.9	1342.2	1339.5
140°	1382.7	1381.4	1380.0	1378.7	1380.0	1381.4	1382.7	1384.1	1383.6	1381.1	1378.7
142.5°	1418.4	1416.9	1415.5	1414.2	1415.5	1416.9	1418.4	1419.7	1419.3	1417.0	1414.7
145°	1467.9	1466.6	1465.2	1463.9	1465.2	1466.6	1467.9	1469.4	1469.1	1467.1	1465.2
147.5°	1511.1	1509.8	1508.7	1507.6	1508.7	1509.8	1511.1	1512.2	1512.1	1510.7	1509.2
150°	1538.4	1537.0	1535.6	1534.3	1535.6	1537.0	1538.4	1539.7	1539.6	1538.0	1536.3
152.5°	1562.5	1560.6	1558.8	1557.0	1558.8	1560.6	1562.5	1564.3	1564.4	1562.7	1561.0
155°	1595.2	1593.1	1590.8	1588.6	1590.8	1593.1	1595.2	1597.4	1597.7	1596.1	1594.4
157.5°	1624.0	1621.8	1619.7	1617.5	1619.7	1621.8	1624.0	1626.1	1626.3	1624.4	1622.6
160°	1640.1	1638.2	1636.3	1634.4	1636.3	1638.2	1640.1	1642.0	1642.1	1640.5	1638.9
162.5°	1655.3	1652.8	1650.5	1648.2	1650.5	1652.8	1655.3	1657.6	1657.9	1656.0	1654.2
165°	1674.7	1672.7	1670.8	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7
167.5°	1689.4	1687.0	1684.5	1682.0	1684.5	1687.0	1689.4	1691.9	1692.1	1690.2	1688.3
170°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1699.8	1700.1	1698.2	1696.3
172.5°	1703.2	1700.8	1698.3	1695.9	1698.3	1700.8	1703.2	1705.8	1706.0	1704.0	1702.1
175°	1709.3	1706.6	1703.7	1701.0	1703.7	1706.6	1709.3	1712.0	1712.4	1710.5	1708.6
177.5°	1710.2	1708.2	1706.3	1704.2	1706.3	1708.2	1710.2	1712.1	1712.4	1710.8	1709.3
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1426.6	1432.4	1441.1	1446.0	1454.3	1459.7	1462.6	1467.9	1470.8	1481.1	1491.9
5°	1347.0	1355.2	1369.7	1383.0	1397.5	1412.4	1423.3	1435.6	1446.9	1466.5	1487.2
7.5°	1255.7	1267.1	1289.4	1310.8	1336.0	1357.1	1375.7	1396.8	1415.7	1443.8	1473.1
10°	1187.2	1207.3	1236.7	1256.8	1289.8	1310.9	1340.3	1363.4	1389.8	1426.8	1459.9
12.5°	1128.2	1152.5	1176.0	1204.0	1233.7	1268.8	1301.1	1330.9	1362.1	1400.5	1439.3
15°	1021.2	1056.2	1092.9	1121.2	1161.4	1198.5	1236.2	1276.4	1314.5	1360.4	1410.9
17.5°	883.4	924.0	985.6	1034.2	1081.4	1118.6	1165.2	1213.9	1258.8	1314.1	1370.4
20°	821.2	851.1	892.8	958.3	1029.5	1069.1	1116.5	1170.1	1221.7	1282.0	1342.3
22.5°	771.2	797.9	831.4	882.4	961.8	1015.9	1065.4	1119.8	1179.6	1241.2	1308.1
25°	700.0	718.6	753.7	794.9	849.5	938.7	992.8	1047.4	1112.5	1178.4	1254.7
27.5°	646.5	663.2	686.0	725.4	766.0	830.0	916.1	975.7	1040.5	1114.7	1193.9
30°	605.7	625.3	650.6	678.4	722.8	772.7	858.8	927.9	991.8	1068.1	1152.7
32.5°	576.0	591.5	613.0	641.3	678.2	726.1	794.9	878.8	941.1	1021.5	1109.7
35°	527.4	545.4	562.9	589.8	619.7	663.5	715.5	805.2	867.1	946.4	1035.1
37.5°	487.3	498.3	517.7	538.9	570.5	603.1	648.2	728.7	795.6	873.5	964.3
40°	456.8	470.6	485.0	508.8	534.5	566.0	610.4	670.1	746.9	823.2	911.9
42.5°	427.1	444.6	459.9	475.7	504.0	535.5	571.6	622.3	700.7	773.0	859.1
45°	391.2	402.6	418.6	436.1	459.3	486.1	518.1	562.4	637.6	700.0	780.9
47.5°	349.6	366.2	376.6	393.7	415.8	441.3	471.1	509.4	570.4	628.8	703.9
50°	321.1	338.2	353.1	368.6	388.2	412.9	437.7	474.7	523.7	585.1	655.2
52.5°	296.8	311.7	326.3	341.7	360.9	383.6	407.2	439.7	481.7	538.1	606.1
55°	263.4	272.7	287.6	303.1	320.1	341.7	364.5	391.7	427.9	475.2	530.5
57.5°	229.1	239.9	251.8	267.3	284.6	301.1	321.5	346.3	374.8	417.7	464.8
60°	209.8	218.0	227.8	243.8	259.8	274.8	294.4	315.0	341.7	378.9	419.1
62.5°	188.3	196.2	205.2	219.0	234.7	248.3	265.5	287.3	310.0	343.9	379.1
65°	152.6	163.9	172.7	185.1	197.9	212.4	225.8	243.3	263.4	290.2	321.6
67.5°	126.5	132.3	140.4	151.7	164.8	177.2	190.0	203.6	221.1	241.8	266.7
70°	114.9	117.0	118.6	129.4	141.8	154.1	166.0	178.8	193.8	210.9	232.5
72.5°	101.4	103.4	105.3	110.0	119.9	132.3	144.5	154.1	168.2	182.4	200.0
75°	80.4	83.5	85.0	87.7	91.3	99.5	110.8	120.1	128.4	139.2	153.1
77.5°	61.2	63.0	64.6	67.4	69.6	73.4	79.8	88.2	95.8	102.2	111.8
80°	48.5	49.0	51.0	52.1	55.1	57.8	60.8	67.6	75.2	77.9	84.5
82.5°	36.5	37.1	38.7	39.7	41.1	43.3	47.3	49.0	55.0	58.5	62.7
85°	20.1	19.6	21.1	21.1	22.1	23.2	24.2	26.8	28.4	32.5	33.5
87.5°	11.4	11.1	11.1	10.7	10.2	10.6	10.5	10.3	10.5	11.2	12.2
90°	26.1	24.7	22.5	20.3	18.1	16.0	13.3	10.3	7.3	4.2	1.2
92.5°	29.4	28.7	27.6	26.5	25.3	24.2	23.8	24.1	24.4	24.6	24.9
95°	49.6	48.2	46.3	44.3	42.4	40.5	44.0	53.1	62.2	71.2	80.3
97.5°	65.5	64.5	60.1	55.5	51.1	46.7	57.3	82.8	108.3	133.8	159.4
100°	72.6	70.4	65.7	61.1	56.5	51.7	68.3	105.8	143.4	181.1	218.6
102.5°	75.2	72.4	111.4	150.5	189.5	228.5	252.1	260.0	267.9	275.9	283.9
105°	78.4	75.3	150.3	225.2	300.2	375.2	408.5	400.2	392.0	383.7	375.6
107.5°	102.4	105.5	195.4	285.3	375.2	465.0	506.6	500.0	493.3	486.7	480.1
110°	188.7	216.2	295.5	374.9	454.2	533.5	570.3	564.5	558.8	553.0	547.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	445.1	545.2	564.9	584.5	604.1	623.7	631.0	625.8	620.7	615.6	610.5
115°	635.1	762.2	755.4	748.5	741.6	734.8	729.0	724.3	719.6	715.0	710.3
117.5°	813.4	844.2	839.5	834.8	830.0	825.4	820.4	815.2	809.9	804.8	799.5
120°	908.8	905.4	900.6	895.6	890.7	885.8	881.2	877.1	872.9	868.9	864.7
122.5°	965.7	963.8	958.5	953.0	947.7	942.3	937.5	933.1	928.8	924.4	920.1
125°	1045.8	1043.9	1038.6	1033.4	1028.2	1023.0	1018.5	1015.0	1011.5	1007.8	1004.3
127.5°	1118.8	1116.0	1112.1	1108.2	1104.3	1100.4	1096.5	1092.6	1088.5	1084.6	1080.7
130°	1165.5	1162.5	1159.4	1156.4	1153.4	1150.3	1146.7	1142.3	1137.9	1133.5	1129.1
132.5°	1211.4	1208.9	1205.9	1202.9	1199.8	1196.8	1193.5	1189.7	1186.0	1182.2	1178.5
135°	1276.4	1273.6	1271.1	1268.7	1266.2	1263.7	1260.3	1255.9	1251.5	1247.1	1242.7
137.5°	1336.9	1334.1	1331.3	1328.6	1325.8	1322.9	1320.0	1317.0	1313.8	1310.8	1307.7
140°	1376.1	1373.7	1370.7	1367.7	1364.6	1361.6	1359.0	1356.8	1354.6	1352.4	1350.2
142.5°	1412.5	1410.3	1406.7	1403.3	1399.9	1396.4	1393.7	1391.7	1389.8	1387.8	1385.8
145°	1463.3	1461.4	1456.7	1452.1	1447.4	1442.7	1440.6	1440.8	1441.1	1441.4	1441.6
147.5°	1507.8	1506.3	1501.8	1497.1	1492.5	1487.9	1486.1	1487.1	1488.2	1489.2	1490.3
150°	1534.7	1533.1	1528.6	1524.3	1519.8	1515.5	1514.2	1516.1	1518.1	1520.0	1522.0
152.5°	1559.4	1557.7	1553.6	1549.4	1545.2	1541.1	1540.0	1542.2	1544.3	1546.5	1548.6
155°	1592.8	1591.1	1587.8	1584.5	1581.2	1577.9	1577.5	1579.9	1582.5	1584.9	1587.4
157.5°	1620.6	1618.8	1616.5	1614.2	1611.8	1609.5	1609.4	1611.5	1613.6	1615.7	1617.8
160°	1637.2	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6
162.5°	1652.2	1650.4	1649.0	1647.5	1646.1	1644.7	1644.8	1646.5	1648.1	1649.7	1651.4
165°	1670.8	1668.9	1668.1	1667.3	1666.5	1665.7	1666.1	1667.7	1669.3	1671.0	1672.6
167.5°	1686.4	1684.5	1683.7	1682.9	1682.2	1681.4	1681.8	1683.5	1685.2	1686.8	1688.5
170°	1694.4	1692.4	1691.8	1691.3	1690.7	1690.2	1690.7	1692.4	1694.0	1695.7	1697.4
172.5°	1700.2	1698.3	1697.8	1697.2	1696.7	1696.2	1696.7	1698.3	1700.0	1701.6	1703.2
175°	1706.7	1704.8	1704.2	1703.6	1703.1	1702.5	1703.2	1705.2	1707.1	1709.0	1710.9
177.5°	1707.8	1706.3	1706.0	1705.8	1705.6	1705.4	1706.0	1707.6	1709.1	1710.6	1712.1
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1492.3	1493.5	1501.8	1505.4	1512.9	1515.7	1519.0	1518.2	1518.2	1519.8	1531.5
5°	1495.4	1505.7	1521.2	1536.1	1550.5	1563.0	1571.2	1579.4	1582.6	1597.5	1610.9
7.5°	1490.1	1509.0	1534.6	1557.4	1584.7	1606.1	1623.8	1639.8	1650.7	1672.4	1694.8
10°	1483.1	1509.8	1538.7	1568.1	1605.8	1634.1	1662.9	1685.2	1692.3	1724.8	1743.4
12.5°	1469.1	1504.9	1541.7	1579.6	1616.5	1655.6	1687.3	1709.5	1734.8	1764.0	1798.3
15°	1448.0	1489.2	1537.2	1586.2	1638.7	1686.2	1720.2	1758.9	1786.7	1818.7	1848.6
17.5°	1417.7	1470.9	1531.9	1588.5	1649.3	1700.3	1747.1	1784.2	1803.8	1822.0	1826.4
20°	1393.9	1451.1	1522.8	1589.7	1650.6	1709.4	1755.8	1786.7	1791.8	1792.3	1765.0
22.5°	1367.9	1432.5	1507.5	1576.2	1648.9	1714.3	1750.4	1763.6	1743.1	1708.2	1655.4
25°	1320.2	1394.9	1482.1	1560.3	1639.8	1701.6	1714.0	1690.8	1619.1	1543.9	1448.6
27.5°	1268.4	1352.4	1445.8	1533.0	1617.5	1655.9	1629.1	1545.5	1416.4	1304.2	1168.3
30°	1230.5	1324.8	1416.5	1514.0	1592.4	1608.8	1547.5	1424.3	1273.7	1104.7	969.2
32.5°	1187.2	1286.1	1386.8	1487.6	1553.2	1537.1	1435.7	1284.0	1107.6	941.4	813.2
35°	1125.3	1227.4	1336.2	1437.1	1478.9	1409.4	1257.8	1060.4	879.9	724.8	636.6
37.5°	1053.9	1165.0	1278.1	1370.9	1367.9	1251.9	1045.5	841.7	690.0	598.2	535.5
40°	1003.1	1115.5	1237.7	1316.1	1282.5	1131.5	907.8	715.5	604.7	531.5	485.5
42.5°	954.5	1067.2	1188.6	1250.9	1192.7	1006.9	784.1	633.4	542.0	484.8	447.7
45°	871.7	990.8	1103.2	1137.7	1033.6	828.9	634.1	524.7	463.9	421.7	395.9
47.5°	790.7	907.9	1010.5	1011.1	870.2	672.2	534.8	454.1	402.2	369.5	350.7
50°	741.2	852.6	938.7	925.3	765.5	597.9	478.4	408.8	365.5	340.2	320.6
52.5°	685.6	793.7	868.2	830.0	676.8	526.2	427.7	369.2	333.4	311.3	293.9
55°	604.7	700.5	753.2	695.4	552.1	437.7	361.3	315.5	288.7	270.1	255.2
57.5°	525.1	604.3	637.3	570.2	454.7	362.9	305.7	271.2	244.7	231.4	223.6
60°	475.2	542.8	566.0	491.8	395.4	317.5	270.6	238.6	219.0	210.4	202.6
62.5°	426.2	481.4	491.0	422.9	344.7	277.9	237.6	210.7	197.6	189.2	182.0
65°	353.7	393.3	388.7	334.1	272.7	220.7	191.3	174.7	164.9	153.1	140.2
67.5°	291.1	315.4	300.7	259.8	208.1	171.5	152.3	139.8	127.6	116.4	113.4
70°	251.6	265.5	250.0	212.4	170.7	143.8	128.4	113.4	106.2	103.6	99.0
72.5°	213.6	218.4	201.8	169.5	138.9	119.1	104.0	95.6	91.8	89.6	86.6
75°	160.4	156.7	142.3	117.0	96.4	83.0	78.4	75.2	72.7	70.6	69.1
77.5°	112.6	107.3	94.4	78.0	67.2	60.7	58.0	56.2	55.0	54.0	52.5
80°	84.5	80.9	68.1	55.6	51.0	48.0	46.4	44.3	44.3	43.3	41.7
82.5°	61.9	57.9	46.6	40.8	38.3	36.4	35.2	34.0	33.6	33.8	32.7
85°	32.5	26.3	23.2	22.1	20.6	19.6	20.1	19.1	19.1	19.1	18.6
87.5°	10.7	9.3	9.5	9.7	10.6	11.0	11.1	11.5	12.3	12.2	12.9
90°	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1	27.5
92.5°	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4	30.1
95°	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6	50.9
97.5°	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5	66.7
100°	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6	74.8
102.5°	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2	78.1
105°	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4	81.4
107.5°	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4	99.4
110°	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7	161.3



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1	345.0
115°	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1	508.0
117.5°	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4	782.7
120°	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8	912.1
122.5°	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7	967.8
125°	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8	1047.7
127.5°	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8	1121.6
130°	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5	1168.5
132.5°	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4	1214.1
135°	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4	1279.1
137.5°	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9	1339.5
140°	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1	1378.7
142.5°	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5	1414.7
145°	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3	1465.2
147.5°	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8	1509.2
150°	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7	1536.3
152.5°	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4	1561.0
155°	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8	1594.4
157.5°	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6	1622.6
160°	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2	1638.9
162.5°	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2	1654.2
165°	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8	1672.7
167.5°	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4	1688.3
170°	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4	1696.3
172.5°	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2	1702.1
175°	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7	1708.6
177.5°	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8	1709.3
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1535.5	1540.9	1543.4	1543.4	1546.3	1545.0	1543.8
5°	1623.8	1633.6	1635.7	1645.0	1651.6	1649.5	1650.6
7.5°	1711.5	1727.3	1742.8	1750.0	1751.1	1755.2	1756.8
10°	1765.5	1778.5	1802.7	1799.1	1817.1	1827.5	1810.4
12.5°	1817.6	1834.9	1851.7	1856.3	1866.6	1869.9	1863.2
15°	1864.5	1873.8	1874.8	1872.3	1875.3	1872.8	1863.0
17.5°	1820.6	1805.5	1775.0	1760.6	1749.2	1732.2	1725.5
20°	1748.0	1703.6	1652.1	1631.5	1607.3	1559.8	1571.2
22.5°	1591.3	1540.8	1489.2	1429.1	1400.3	1355.3	1352.6
25°	1347.5	1260.4	1164.5	1097.5	1058.3	1013.5	993.9
27.5°	1047.6	938.0	859.4	819.6	783.5	747.9	746.4
30°	850.5	768.1	707.2	673.3	651.1	636.1	639.2
32.5°	716.9	660.5	619.5	591.2	574.8	563.5	563.3
35°	586.1	547.4	521.2	509.3	497.5	489.2	489.7
37.5°	501.6	478.4	463.7	450.6	443.2	439.2	437.0
40°	458.3	439.2	427.9	420.1	413.9	408.3	407.3
42.5°	424.0	408.3	396.9	390.8	385.1	381.0	380.0
45°	376.3	363.5	353.1	346.4	343.9	340.2	340.2
47.5°	334.8	322.0	314.1	309.8	305.4	303.0	302.9
50°	306.7	296.9	289.7	287.1	283.5	282.0	281.4
52.5°	281.6	274.3	269.1	267.3	265.8	263.8	264.2
55°	247.4	243.3	241.3	239.7	237.1	234.0	236.1
57.5°	218.6	215.2	209.6	204.8	202.4	200.3	201.1
60°	198.4	191.3	184.0	178.3	176.8	172.2	172.2
62.5°	172.9	162.8	153.9	150.8	149.2	147.0	146.6
65°	133.0	128.9	126.8	124.7	123.7	123.7	122.7
67.5°	110.2	108.6	106.3	105.7	104.7	104.4	104.1
70°	97.5	95.3	94.3	93.8	92.8	93.3	91.8
72.5°	85.0	83.4	83.2	81.9	81.2	81.3	80.2
75°	67.1	67.1	66.4	65.9	64.9	64.4	64.9
77.5°	51.5	51.6	50.7	50.6	50.5	50.6	50.1
80°	41.2	41.7	41.2	40.7	40.2	40.7	40.2
82.5°	32.6	31.8	31.7	31.6	31.5	31.2	31.1
85°	18.6	19.1	18.6	18.1	18.1	18.1	18.6
87.5°	12.8	13.0	13.2	13.3	13.4	13.5	13.2
90°	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331817-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)