

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332119-830

Luminaire Tested: **S123DIW-S340D1535U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332119-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6347.4 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	83	80	81	77	74	71	59	57	55	42	40	39	26	25	25	18
2	83	76	70	65	73	67	63	58	51	48	45	37	35	33	23	22	21	15
3	76	67	60	54	67	59	53	49	45	41	38	32	30	28	20	19	18	12
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	16	15	11
5	63	52	45	39	56	46	40	35	36	31	28	26	23	20	16	14	13	9
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12	8
7	54	42	34	29	47	37	31	26	29	24	21	21	18	15	13	12	10	7
8	50	38	30	25	44	34	27	23	26	22	18	19	16	14	12	10	9	6
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	0.8
10°-20°	135.9	2.1
20°-30°	200.7	3.2
30°-40°	234.4	3.7
40°-50°	235.7	3.7
50°-60°	207.0	3.3
60°-70°	154.2	2.4
70°-80°	87.9	1.4
80°-90°	30.6	0.5
90°-100°	117.9	1.9
100°-110°	352.8	5.6
110°-120°	600.0	9.5
120°-130°	789.3	12.4
130°-140°	887.1	14.0
140°-150°	872.0	13.7
150°-160°	734.1	11.6
160°-170°	488.7	7.7
170°-180°	171.1	2.7
0°-30°	384.6	6.1
0°-40°	619.1	9.8
0°-60°	1061.7	16.7
0°-90°	1334.4	21.0
90°-120°	1070.7	16.9
90°-150°	3619.1	57.0
90°-180°	5013.0	79.0
0°-180°	6347.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	16	34	40	43	6
95°	84	94	105	110	111	94
105°	320	323	336	336	338	343
115°	604	608	606	607	606	597
125°	884	888	886	880	874	788
135°	1147	1155	1154	1149	1146	884
145°	1392	1394	1398	1397	1392	869
155°	1593	1593	1595	1600	1590	733
165°	1735	1731	1731	1739	1730	489
175°	1805	1800	1799	1807	1798	171
180°	1809	1809	1809	1809	1809	



TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.4	9.8	10.2	10.7	11.0	11.6	12.3	13.1	13.9	14.5	14.7
90°	1.4	4.6	7.7	10.9	14.0	17.7	21.8	25.9	30.0	34.1	35.3
92.5°	34.4	36.6	38.6	40.8	43.0	45.2	47.6	49.9	52.2	54.6	55.6
95°	83.9	86.1	88.3	90.5	92.7	95.1	97.6	100.1	102.6	105.2	106.4
97.5°	148.9	150.6	152.2	153.9	155.5	157.2	159.1	160.9	162.8	164.6	166.1
100°	193.3	195.2	197.1	199.0	200.9	202.6	204.2	205.8	207.4	209.0	209.9
102.5°	244.5	245.6	246.8	247.9	249.0	250.6	252.7	254.8	256.8	258.9	260.0
105°	319.8	320.5	321.0	321.7	322.3	324.0	326.9	329.7	332.6	335.5	335.5
107.5°	407.4	407.7	408.1	408.5	408.9	409.6	410.8	411.9	413.0	414.2	415.2
110°	461.9	462.6	463.2	463.8	464.5	465.1	465.7	466.4	466.9	467.6	468.9



TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.8	519.2	519.5	519.9	520.3	520.6	520.7	520.8	520.9	521.0	522.5
115°	604.1	605.0	606.0	606.9	607.8	608.0	607.4	606.7	606.1	605.5	605.8
117.5°	689.9	690.5	691.2	691.8	692.4	692.3	691.5	690.7	689.8	689.1	689.0
120°	743.4	745.3	747.2	749.0	750.9	751.1	749.5	747.9	746.3	744.8	744.4
122.5°	799.1	800.4	801.8	803.2	804.6	804.9	804.1	803.2	802.5	801.6	800.8
125°	884.0	885.0	886.0	886.9	887.9	888.0	887.4	886.7	886.1	885.5	884.2
127.5°	962.5	964.5	966.6	968.6	970.6	971.3	970.5	969.9	969.2	968.5	966.7
130°	1014.8	1017.4	1019.8	1022.4	1024.9	1025.7	1024.7	1023.8	1022.8	1021.9	1020.7
132.5°	1067.1	1069.6	1072.1	1074.7	1077.2	1078.2	1077.4	1076.8	1076.0	1075.3	1073.8
135°	1147.0	1148.9	1150.8	1152.6	1154.6	1155.4	1155.1	1154.7	1154.4	1154.1	1152.8
137.5°	1220.9	1222.5	1224.1	1225.7	1227.2	1228.4	1229.3	1230.0	1230.9	1231.7	1230.4
140°	1272.1	1273.7	1275.3	1276.8	1278.4	1279.3	1279.7	1280.0	1280.3	1280.6	1280.3
142.5°	1318.7	1320.2	1321.8	1323.4	1325.0	1326.1	1326.6	1327.2	1327.8	1328.3	1328.0
145°	1391.5	1392.1	1392.7	1393.4	1394.0	1394.8	1395.7	1396.7	1397.6	1398.5	1398.3
147.5°	1455.1	1456.2	1457.4	1458.6	1459.7	1460.7	1461.6	1462.4	1463.3	1464.2	1464.2
150°	1499.5	1500.2	1500.7	1501.4	1502.0	1502.6	1503.3	1503.9	1504.5	1505.1	1505.1
152.5°	1535.9	1536.7	1537.7	1538.5	1539.4	1540.0	1540.4	1540.8	1541.2	1541.5	1542.1
155°	1593.3	1593.3	1593.3	1593.3	1593.3	1593.5	1593.7	1594.0	1594.4	1594.7	1596.0
157.5°	1642.2	1641.8	1641.4	1641.1	1640.7	1640.6	1640.9	1641.1	1641.3	1641.6	1642.9
160°	1672.9	1672.3	1671.6	1670.9	1670.4	1670.0	1670.0	1670.0	1670.0	1670.0	1671.6
162.5°	1700.2	1699.3	1698.4	1697.5	1696.7	1696.3	1696.6	1696.9	1697.0	1697.3	1698.9
165°	1735.4	1734.5	1733.5	1732.6	1731.6	1731.2	1731.2	1731.2	1731.2	1731.2	1733.1
167.5°	1763.6	1762.3	1761.0	1759.7	1758.5	1758.0	1758.2	1758.5	1758.8	1759.0	1761.0
170°	1779.4	1778.2	1777.0	1775.7	1774.4	1773.8	1773.8	1773.8	1773.8	1773.8	1776.0
172.5°	1792.0	1790.7	1789.4	1788.2	1787.0	1786.3	1786.3	1786.3	1786.3	1786.3	1788.3
175°	1805.1	1803.8	1802.5	1801.3	1800.0	1799.4	1799.4	1799.4	1799.4	1799.4	1801.3
177.5°	1810.4	1809.5	1808.5	1807.4	1806.4	1805.9	1805.9	1805.9	1805.9	1805.9	1807.4
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3



TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	14.9	15.1	15.3	15.4	15.6	15.6	15.7	15.9
90°	36.7	37.9	39.2	40.2	40.7	41.4	42.0	42.6
92.5°	56.6	57.6	58.6	58.9	58.5	58.2	57.8	57.4
95°	107.7	109.0	110.2	110.8	110.8	110.8	110.8	110.8
97.5°	167.5	168.9	170.4	171.1	171.0	170.8	170.7	170.6
100°	210.8	211.8	212.7	213.5	214.1	214.8	215.4	216.0
102.5°	260.9	261.8	262.8	263.2	263.1	262.9	262.8	262.7
105°	335.5	335.5	335.5	335.7	336.4	337.1	337.6	338.3
107.5°	416.2	417.2	418.2	418.5	418.1	417.7	417.4	417.0
110°	470.1	471.4	472.7	473.0	472.3	471.7	471.1	470.4



TEST NUMBER: P332119-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	524.1	525.6	527.1	527.8	527.7	527.5	527.4	527.3
115°	606.1	606.4	606.7	606.7	606.4	606.1	605.8	605.5
117.5°	688.9	688.9	688.8	688.3	687.4	686.5	685.7	684.8
120°	744.1	743.9	743.5	743.0	742.4	741.8	741.1	740.5
122.5°	799.9	799.2	798.3	797.5	796.6	795.7	794.8	793.9
125°	883.0	881.7	880.4	879.1	877.9	876.7	875.3	874.1
127.5°	965.0	963.2	961.4	959.8	958.4	956.9	955.5	953.9
130°	1019.4	1018.1	1016.9	1015.1	1013.0	1010.7	1008.5	1006.3
132.5°	1072.3	1070.8	1069.3	1067.7	1066.0	1064.3	1062.5	1060.8
135°	1151.6	1150.3	1149.1	1148.1	1147.5	1146.8	1146.2	1145.6
137.5°	1229.1	1227.8	1226.4	1225.1	1223.9	1222.8	1221.5	1220.3
140°	1280.0	1279.7	1279.3	1278.1	1275.8	1273.7	1271.4	1269.2
142.5°	1327.8	1327.4	1327.1	1326.1	1324.4	1322.7	1321.0	1319.3
145°	1397.9	1397.6	1397.3	1396.5	1395.2	1394.0	1392.7	1391.5
147.5°	1464.2	1464.2	1464.2	1463.3	1461.4	1459.5	1457.5	1455.7
150°	1505.1	1505.1	1505.1	1504.2	1502.3	1500.4	1498.5	1496.7
152.5°	1542.6	1543.0	1543.6	1543.0	1541.3	1539.7	1538.0	1536.4
155°	1597.2	1598.5	1599.8	1599.3	1597.0	1594.9	1592.6	1590.4
157.5°	1644.3	1645.6	1646.9	1646.7	1644.9	1643.1	1641.3	1639.6
160°	1673.2	1674.8	1676.3	1676.5	1675.3	1674.0	1672.7	1671.4
162.5°	1700.4	1702.0	1703.6	1703.5	1701.4	1699.4	1697.3	1695.4
165°	1734.9	1736.8	1738.7	1738.6	1736.4	1734.2	1731.9	1729.8
167.5°	1762.9	1764.9	1766.8	1766.8	1764.9	1762.9	1761.0	1759.0
170°	1778.2	1780.5	1782.6	1782.6	1780.5	1778.2	1776.0	1773.8
172.5°	1790.2	1792.2	1794.1	1794.0	1791.8	1789.6	1787.3	1785.2
175°	1803.2	1805.1	1806.9	1806.8	1804.6	1802.3	1800.2	1798.0
177.5°	1808.9	1810.4	1811.9	1811.8	1810.1	1808.3	1806.6	1804.8
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3

(END OF REPORT)