

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332095-830

Luminaire Tested: **S123DIW-S340D460U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332095-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D460U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2837.2 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45	39
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38	33
3	81	71	64	58	74	66	59	54	55	50	46	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	33	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	14
9	50	37	30	25	46	35	28	24	30	24	21	25	21	18	21	17	15	13
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.7
10°-20°	135.9	4.8
20°-30°	200.7	7.1
30°-40°	234.4	8.3
40°-50°	235.7	8.3
50°-60°	207.0	7.3
60°-70°	154.2	5.4
70°-80°	87.9	3.1
80°-90°	26.8	0.9
90°-100°	35.4	1.2
100°-110°	106.0	3.7
110°-120°	180.3	6.4
120°-130°	237.2	8.4
130°-140°	266.6	9.4
140°-150°	262.1	9.2
150°-160°	220.6	7.8
160°-170°	146.9	5.2
170°-180°	51.4	1.8
0°-30°	384.6	13.6
0°-40°	619.1	21.8
0°-60°	1061.7	37.4
0°-90°	1330.7	46.9
90°-120°	321.8	11.3
90°-150°	1087.6	38.3
90°-180°	1507.0	53.1
0°-180°	2837.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	0	5	10	12	13	3
95°	25	28	32	33	33	28
105°	96	97	101	101	102	103
115°	182	183	182	182	182	180
125°	266	267	266	264	263	237
135°	345	347	347	345	344	266
145°	418	419	420	420	418	261
155°	479	479	479	481	478	220
165°	522	520	520	522	520	147
175°	542	541	541	543	540	52
180°	544	544	544	544	544	



TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.2	9.1	9.1	9.0	9.0	9.1	9.2	9.4	9.6	9.8	9.8
90°	0.5	1.4	2.4	3.3	4.2	5.3	6.5	7.8	9.0	10.3	10.7
92.5°	10.4	11.0	11.6	12.3	12.9	13.6	14.3	15.0	15.7	16.4	16.7
95°	25.2	25.8	26.5	27.2	27.9	28.6	29.3	30.1	30.8	31.6	32.0
97.5°	44.8	45.2	45.7	46.3	46.8	47.2	47.8	48.4	48.9	49.5	49.9
100°	58.1	58.6	59.2	59.8	60.3	60.9	61.4	61.8	62.3	62.8	63.1
102.5°	73.4	73.8	74.2	74.5	74.8	75.3	76.0	76.5	77.2	77.9	78.1
105°	96.1	96.3	96.5	96.7	96.9	97.4	98.2	99.1	99.9	100.8	100.8
107.5°	122.4	122.5	122.6	122.7	122.9	123.1	123.5	123.8	124.1	124.5	124.8
110°	138.8	139.0	139.2	139.4	139.6	139.8	140.0	140.2	140.3	140.5	140.9



TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.9	156.0	156.2	156.3	156.4	156.5	156.5	156.6	156.6	156.6	157.0
115°	181.5	181.8	182.1	182.4	182.7	182.8	182.6	182.4	182.2	182.0	182.1
117.5°	207.4	207.5	207.7	207.9	208.1	208.0	207.8	207.5	207.4	207.1	207.1
120°	223.4	223.9	224.5	225.1	225.6	225.7	225.3	224.8	224.3	223.9	223.8
122.5°	240.2	240.5	241.0	241.4	241.8	241.9	241.7	241.4	241.2	240.9	240.6
125°	265.7	266.0	266.3	266.6	266.8	266.8	266.6	266.5	266.3	266.1	265.7
127.5°	289.3	289.8	290.5	291.1	291.7	291.9	291.7	291.4	291.2	291.1	290.5
130°	305.0	305.8	306.5	307.3	308.0	308.2	307.9	307.6	307.4	307.1	306.7
132.5°	320.7	321.4	322.3	323.0	323.8	324.0	323.8	323.6	323.4	323.2	322.7
135°	344.7	345.3	345.8	346.4	346.9	347.2	347.1	347.0	346.9	346.9	346.5
137.5°	366.9	367.4	367.9	368.3	368.8	369.2	369.4	369.7	369.9	370.1	369.8
140°	382.3	382.8	383.2	383.7	384.2	384.5	384.6	384.7	384.7	384.8	384.7
142.5°	396.3	396.8	397.3	397.8	398.2	398.5	398.7	398.9	399.1	399.2	399.1
145°	418.2	418.4	418.6	418.8	419.0	419.1	419.4	419.7	420.0	420.3	420.2
147.5°	437.3	437.6	438.0	438.3	438.7	438.9	439.2	439.5	439.8	440.1	440.1
150°	450.6	450.8	451.0	451.2	451.4	451.6	451.8	451.9	452.1	452.3	452.3
152.5°	461.6	461.8	462.1	462.3	462.6	462.8	462.9	463.1	463.2	463.3	463.4
155°	478.8	478.8	478.8	478.8	478.8	478.9	479.0	479.1	479.2	479.3	479.7
157.5°	493.5	493.4	493.3	493.1	493.0	493.0	493.1	493.2	493.2	493.3	493.7
160°	502.8	502.6	502.4	502.2	502.0	501.9	501.9	501.9	501.9	501.9	502.4
162.5°	511.0	510.7	510.4	510.1	509.9	509.8	509.8	509.9	510.0	510.1	510.6
165°	521.5	521.2	520.9	520.7	520.4	520.3	520.3	520.3	520.3	520.3	520.8
167.5°	530.0	529.6	529.2	528.9	528.5	528.3	528.4	528.5	528.6	528.6	529.2
170°	534.8	534.4	534.0	533.7	533.3	533.1	533.1	533.1	533.1	533.1	533.8
172.5°	538.6	538.2	537.8	537.4	537.0	536.8	536.8	536.8	536.8	536.8	537.4
175°	542.4	542.1	541.7	541.3	540.9	540.7	540.7	540.7	540.7	540.7	541.3
177.5°	544.1	543.8	543.5	543.2	542.9	542.7	542.7	542.7	542.7	542.7	543.2
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8



TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	9.8	9.8	9.8	9.8	9.8	9.9	9.9	9.9
90°	11.0	11.4	11.8	12.1	12.3	12.4	12.6	12.8
92.5°	17.0	17.3	17.6	17.7	17.6	17.4	17.3	17.2
95°	32.3	32.7	33.1	33.3	33.3	33.3	33.3	33.3
97.5°	50.3	50.8	51.2	51.4	51.4	51.4	51.3	51.3
100°	63.3	63.6	63.9	64.2	64.4	64.6	64.8	64.9
102.5°	78.4	78.7	79.0	79.1	79.1	79.0	79.0	78.9
105°	100.8	100.8	100.8	100.9	101.1	101.3	101.5	101.7
107.5°	125.1	125.4	125.6	125.7	125.6	125.5	125.5	125.4
110°	141.3	141.7	142.0	142.1	141.9	141.8	141.6	141.4





TEST NUMBER: P332095-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	158.0	158.4	158.6	158.5	158.5	158.5	158.4
115°	182.2	182.3	182.4	182.4	182.3	182.2	182.1	182.0
117.5°	207.1	207.0	207.0	206.9	206.6	206.3	206.0	205.8
120°	223.7	223.6	223.5	223.3	223.1	222.9	222.7	222.5
122.5°	240.4	240.2	239.9	239.7	239.4	239.1	238.8	238.6
125°	265.3	264.9	264.6	264.2	263.8	263.4	263.1	262.7
127.5°	290.0	289.5	288.9	288.4	288.0	287.6	287.1	286.7
130°	306.3	305.9	305.6	305.1	304.4	303.8	303.1	302.4
132.5°	322.3	321.8	321.3	320.8	320.4	319.8	319.3	318.8
135°	346.1	345.7	345.3	345.1	344.9	344.7	344.5	344.3
137.5°	369.4	369.0	368.5	368.2	367.8	367.5	367.1	366.7
140°	384.7	384.6	384.5	384.1	383.4	382.8	382.1	381.4
142.5°	399.0	398.9	398.8	398.5	398.0	397.5	397.0	396.4
145°	420.1	420.0	419.9	419.7	419.3	419.0	418.6	418.2
147.5°	440.1	440.1	440.1	439.8	439.2	438.6	438.0	437.4
150°	452.3	452.3	452.3	452.0	451.5	450.9	450.3	449.8
152.5°	463.5	463.7	463.9	463.7	463.3	462.7	462.2	461.8
155°	480.0	480.4	480.8	480.6	479.9	479.3	478.6	478.0
157.5°	494.2	494.6	494.9	494.8	494.4	493.8	493.2	492.8
160°	502.8	503.3	503.8	503.8	503.4	503.0	502.7	502.3
162.5°	511.0	511.5	512.0	511.9	511.3	510.7	510.1	509.4
165°	521.4	522.0	522.5	522.5	521.8	521.1	520.5	519.8
167.5°	529.8	530.4	530.9	530.9	530.4	529.8	529.2	528.6
170°	534.4	535.1	535.7	535.7	535.1	534.4	533.8	533.1
172.5°	538.0	538.6	539.1	539.1	538.5	537.8	537.2	536.5
175°	541.9	542.4	543.0	543.0	542.3	541.7	541.0	540.4
177.5°	543.7	544.1	544.5	544.5	543.9	543.5	542.9	542.3
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8

(END OF REPORT)