

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332101-830

Luminaire Tested: **S123DIW-S340D755U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332101-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3799.2 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.3
10°-20°	135.9	3.6
20°-30°	200.7	5.3
30°-40°	234.4	6.2
40°-50°	235.7	6.2
50°-60°	207.0	5.4
60°-70°	154.2	4.1
70°-80°	87.9	2.3
80°-90°	27.9	0.7
90°-100°	58.0	1.5
100°-110°	173.6	4.6
110°-120°	295.3	7.8
120°-130°	388.5	10.2
130°-140°	436.7	11.5
140°-150°	429.2	11.3
150°-160°	361.3	9.5
160°-170°	240.5	6.3
170°-180°	84.2	2.2
0°-30°	384.6	10.1
0°-40°	619.1	16.3
0°-60°	1061.7	27.9
0°-90°	1331.7	35.1
90°-120°	527.0	13.9
90°-150°	1781.4	46.9
90°-180°	2468.0	65.0
0°-180°	3799.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	8	17	20	21	4
95°	41	46	52	54	55	46
105°	157	159	165	165	166	169
115°	297	299	298	299	298	294
125°	435	437	436	433	430	388
135°	565	568	568	565	564	435
145°	685	686	688	688	685	428
155°	784	784	785	787	783	361
165°	854	852	852	856	851	241
175°	888	886	886	889	885	84
180°	891	891	891	891	891	



TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.2	9.3	9.4	9.5	9.6	9.8	10.1	10.5	10.7	11.1	11.1
90°	0.7	2.3	3.8	5.4	6.9	8.7	10.7	12.7	14.8	16.8	17.4
92.5°	17.0	18.0	19.0	20.1	21.1	22.2	23.4	24.6	25.7	26.9	27.3
95°	41.3	42.3	43.5	44.6	45.6	46.8	48.1	49.3	50.5	51.7	52.4
97.5°	73.3	74.1	74.9	75.8	76.5	77.4	78.3	79.2	80.1	81.1	81.7
100°	95.1	96.0	97.0	97.9	98.9	99.7	100.5	101.3	102.1	102.8	103.3
102.5°	120.4	120.9	121.5	122.0	122.5	123.4	124.4	125.5	126.4	127.4	127.9
105°	157.4	157.7	158.1	158.3	158.6	159.5	160.9	162.3	163.7	165.1	165.1
107.5°	200.5	200.7	200.9	201.0	201.2	201.6	202.2	202.7	203.3	203.9	204.3
110°	227.3	227.7	228.0	228.3	228.6	228.9	229.2	229.5	229.9	230.2	230.8



TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	255.3	255.5	255.7	255.9	256.1	256.2	256.3	256.4	256.4	256.5	257.2
115°	297.4	297.7	298.2	298.7	299.2	299.3	299.0	298.7	298.3	298.0	298.2
117.5°	339.6	339.9	340.2	340.5	340.8	340.8	340.4	340.0	339.6	339.1	339.1
120°	365.9	366.8	367.8	368.7	369.7	369.7	368.9	368.2	367.4	366.6	366.5
122.5°	393.3	394.0	394.6	395.4	396.1	396.2	395.8	395.4	395.0	394.5	394.2
125°	435.2	435.6	436.1	436.6	437.1	437.1	436.8	436.5	436.1	435.8	435.3
127.5°	473.7	474.8	475.8	476.7	477.8	478.1	477.8	477.4	477.0	476.7	475.8
130°	499.5	500.8	502.0	503.2	504.4	504.9	504.4	504.0	503.5	503.0	502.4
132.5°	525.3	526.5	527.7	529.0	530.3	530.7	530.4	530.0	529.6	529.3	528.6
135°	564.6	565.5	566.5	567.4	568.3	568.7	568.5	568.4	568.3	568.1	567.4
137.5°	601.0	601.7	602.5	603.3	604.1	604.6	605.0	605.5	605.9	606.2	605.6
140°	626.1	626.9	627.7	628.5	629.2	629.7	629.9	630.0	630.2	630.4	630.2
142.5°	649.1	649.9	650.6	651.4	652.1	652.7	653.0	653.3	653.6	653.8	653.7
145°	684.9	685.2	685.5	685.8	686.2	686.5	687.0	687.5	688.0	688.4	688.2
147.5°	716.2	716.8	717.4	717.9	718.5	719.0	719.4	719.8	720.3	720.8	720.8
150°	738.1	738.4	738.7	739.0	739.3	739.6	739.9	740.3	740.6	740.8	740.8
152.5°	756.0	756.4	756.9	757.3	757.7	758.0	758.2	758.4	758.6	758.7	759.0
155°	784.3	784.3	784.3	784.3	784.3	784.3	784.5	784.7	784.8	784.9	785.6
157.5°	808.3	808.1	807.9	807.8	807.6	807.6	807.7	807.8	807.9	808.0	808.7
160°	823.4	823.1	822.8	822.5	822.2	822.0	822.0	822.0	822.0	822.0	822.8
162.5°	836.9	836.4	835.9	835.6	835.1	835.0	835.1	835.2	835.4	835.5	836.2
165°	854.2	853.8	853.3	852.8	852.3	852.1	852.1	852.1	852.1	852.1	853.0
167.5°	868.1	867.4	866.9	866.2	865.5	865.3	865.4	865.5	865.7	865.8	866.8
170°	875.9	875.2	874.7	874.0	873.4	873.1	873.1	873.1	873.1	873.1	874.2
172.5°	882.0	881.5	880.8	880.1	879.6	879.2	879.2	879.2	879.2	879.2	880.2
175°	888.4	887.9	887.2	886.6	886.0	885.7	885.7	885.7	885.7	885.7	886.6
177.5°	891.2	890.6	890.1	889.7	889.2	888.9	888.9	888.9	888.9	888.9	889.7
180°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6



TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	11.2	11.2	11.3	11.3	11.4	11.4	11.5	11.6
90°	18.0	18.7	19.3	19.7	20.1	20.4	20.6	21.0
92.5°	27.9	28.4	28.8	29.0	28.8	28.7	28.5	28.3
95°	53.0	53.6	54.3	54.6	54.6	54.6	54.6	54.6
97.5°	82.5	83.1	83.9	84.2	84.2	84.1	84.0	84.0
100°	103.8	104.2	104.7	105.1	105.4	105.8	106.0	106.3
102.5°	128.4	128.8	129.3	129.5	129.5	129.4	129.3	129.3
105°	165.1	165.1	165.1	165.2	165.6	165.9	166.2	166.5
107.5°	204.8	205.4	205.9	206.0	205.9	205.7	205.5	205.3
110°	231.4	232.1	232.6	232.8	232.5	232.1	231.9	231.6



TEST NUMBER: P332101-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	258.0	258.7	259.5	259.8	259.8	259.7	259.6	259.6
115°	298.3	298.5	298.7	298.7	298.5	298.3	298.2	298.0
117.5°	339.1	339.0	339.0	338.8	338.4	337.9	337.5	337.1
120°	366.3	366.1	366.0	365.7	365.4	365.1	364.8	364.5
122.5°	393.8	393.3	392.9	392.6	392.1	391.6	391.2	390.8
125°	434.6	433.9	433.4	432.7	432.2	431.5	430.8	430.3
127.5°	474.9	474.1	473.3	472.4	471.7	471.0	470.3	469.6
130°	501.8	501.1	500.5	499.6	498.6	497.5	496.4	495.3
132.5°	527.8	527.1	526.3	525.6	524.7	523.9	523.0	522.2
135°	566.8	566.2	565.6	565.1	564.8	564.5	564.2	563.8
137.5°	604.9	604.3	603.7	603.0	602.5	601.8	601.2	600.7
140°	630.0	629.9	629.7	629.1	628.0	626.9	625.8	624.7
142.5°	653.6	653.4	653.2	652.7	651.9	651.0	650.2	649.3
145°	688.1	688.0	687.8	687.4	686.7	686.2	685.5	684.9
147.5°	720.8	720.8	720.8	720.3	719.3	718.4	717.5	716.5
150°	740.8	740.8	740.8	740.4	739.4	738.6	737.6	736.7
152.5°	759.3	759.5	759.8	759.5	758.7	757.9	757.1	756.3
155°	786.2	786.8	787.4	787.2	786.1	785.0	783.9	782.9
157.5°	809.4	810.0	810.7	810.5	809.6	808.8	807.9	807.0
160°	823.6	824.3	825.1	825.2	824.6	824.0	823.3	822.7
162.5°	837.0	837.8	838.6	838.5	837.4	836.5	835.5	834.4
165°	853.9	854.9	855.8	855.7	854.7	853.6	852.5	851.4
167.5°	867.7	868.7	869.7	869.7	868.7	867.7	866.8	865.8
170°	875.2	876.4	877.4	877.4	876.4	875.2	874.2	873.1
172.5°	881.2	882.1	883.1	883.1	881.9	880.9	879.8	878.7
175°	887.6	888.4	889.4	889.4	888.3	887.1	886.1	885.0
177.5°	890.4	891.2	891.9	891.8	891.0	890.0	889.2	888.3
180°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6

(END OF REPORT)