

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331813-840

Luminaire Tested: **S122RDIW-S675D970U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331813-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6475.3 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23954	23954	23954	23954
5°	26752	24104	21371	24104
10°	29681	23935	18525	23935
15°	31141	23584	14596	23584
20°	26996	23063	12631	23063
25°	17706	22352	11277	22352
30°	11917	21490	10206	21490
35°	9652	20402	9207	20402
40°	8585	19220	8517	19220
45°	7768	17831	7606	17831
50°	7068	16458	7043	16458
55°	6646	14933	6559	14933
60°	5561	13533	5493	13533
65°	4688	12287	5318	12287
70°	4334	10976	5013	10976
75°	4049	9551	4629	9551
80°	3738	7857	4119	7857
85°	3446	6206	3631	6206



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	2.2
10°-20°	391.9	6.1
20°-30°	505.0	7.8
30°-40°	479.9	7.4
40°-50°	411.1	6.3
50°-60°	313.0	4.8
60°-70°	197.9	3.1
70°-80°	98.8	1.5
80°-90°	29.0	0.4
90°-100°	44.5	0.7
100°-110°	163.1	2.5
110°-120°	436.1	6.7
120°-130°	719.8	11.1
130°-140°	765.5	11.8
140°-150°	711.5	11.0
150°-160°	572.1	8.8
160°-170°	368.6	5.7
170°-180°	126.9	2.0
0°-30°	1037.5	16.0
0°-40°	1517.4	23.4
0°-60°	2241.5	34.6
0°-90°	2567.2	39.6
90°-120°	643.7	9.9
90°-150°	2840.5	43.9
90°-180°	3908.0	60.4
0°-180°	6475.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1484	1484	1484	1484	1484	
5°	1651	1487	1319	1487	1651	163
15°	1863	1411	873	1411	1863	503
25°	994	1255	633	1255	994	472
35°	490	1035	467	1035	490	313
45°	340	781	333	781	340	263
55°	236	530	233	530	236	207
65°	123	322	139	322	123	125
75°	65	153	74	153	65	69
85°	19	34	20	34	19	21
90°	26	1	26	1	26	12
95°	42	63	42	63	42	39
105°	73	293	73	293	73	76
115°	79	555	79	555	79	198
125°	825	784	825	784	825	714
135°	1003	971	1003	971	1003	773
145°	1144	1126	1144	1126	1144	715
155°	1241	1240	1241	1240	1241	573
165°	1304	1307	1304	1307	1304	368
175°	1329	1336	1329	1336	1329	127
180°	1334	1334	1334	1334	1334	



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1543.8	1545.0	1546.3	1543.4	1543.4	1540.9	1535.5	1531.5	1519.8	1518.2	1518.2
5°	1650.6	1649.5	1651.6	1645.0	1635.7	1633.6	1623.8	1610.9	1597.5	1582.6	1579.4
7.5°	1756.8	1755.2	1751.1	1750.0	1742.8	1727.3	1711.5	1694.8	1672.4	1650.7	1639.8
10°	1810.4	1827.5	1817.1	1799.1	1802.7	1778.5	1765.5	1743.4	1724.8	1692.3	1685.2
12.5°	1863.2	1869.9	1866.6	1856.3	1851.7	1834.9	1817.6	1798.3	1764.0	1734.8	1709.5
15°	1863.0	1872.8	1875.3	1872.3	1874.8	1873.8	1864.5	1848.6	1818.7	1786.7	1758.9
17.5°	1725.5	1732.2	1749.2	1760.6	1775.0	1805.5	1820.6	1826.4	1822.0	1803.8	1784.2
20°	1571.2	1559.8	1607.3	1631.5	1652.1	1703.6	1748.0	1765.0	1792.3	1791.8	1786.7
22.5°	1352.6	1355.3	1400.3	1429.1	1489.2	1540.8	1591.3	1655.4	1708.2	1743.1	1763.6
25°	993.9	1013.5	1058.3	1097.5	1164.5	1260.4	1347.5	1448.6	1543.9	1619.1	1690.8
27.5°	746.4	747.9	783.5	819.6	859.4	938.0	1047.6	1168.3	1304.2	1416.4	1545.5
30°	639.2	636.1	651.1	673.3	707.2	768.1	850.5	969.2	1104.7	1273.7	1424.3
32.5°	563.3	563.5	574.8	591.2	619.5	660.5	716.9	813.2	941.4	1107.6	1284.0
35°	489.7	489.2	497.5	509.3	521.2	547.4	586.1	636.6	724.8	879.9	1060.4
37.5°	437.0	439.2	443.2	450.6	463.7	478.4	501.6	535.5	598.2	690.0	841.7
40°	407.3	408.3	413.9	420.1	427.9	439.2	458.3	485.5	531.5	604.7	715.5
42.5°	380.0	381.0	385.1	390.8	396.9	408.3	424.0	447.7	484.8	542.0	633.4
45°	340.2	340.2	343.9	346.4	353.1	363.5	376.3	395.9	421.7	463.9	524.7
47.5°	302.9	303.0	305.4	309.8	314.1	322.0	334.8	350.7	369.5	402.2	454.1
50°	281.4	282.0	283.5	287.1	289.7	296.9	306.7	320.6	340.2	365.5	408.8
52.5°	264.2	263.8	265.8	267.3	269.1	274.3	281.6	293.9	311.3	333.4	369.2
55°	236.1	234.0	237.1	239.7	241.3	243.3	247.4	255.2	270.1	288.7	315.5
57.5°	201.1	200.3	202.4	204.8	209.6	215.2	218.6	223.6	231.4	244.7	271.2
60°	172.2	172.2	176.8	178.3	184.0	191.3	198.4	202.6	210.4	219.0	238.6
62.5°	146.6	147.0	149.2	150.8	153.9	162.8	172.9	182.0	189.2	197.6	210.7
65°	122.7	123.7	123.7	124.7	126.8	128.9	133.0	140.2	153.1	164.9	174.7
67.5°	104.1	104.4	104.7	105.7	106.3	108.6	110.2	113.4	116.4	127.6	139.8
70°	91.8	93.3	92.8	93.8	94.3	95.3	97.5	99.0	103.6	106.2	113.4
72.5°	80.2	81.3	81.2	81.9	83.2	83.4	85.0	86.6	89.6	91.8	95.6
75°	64.9	64.4	64.9	65.9	66.4	67.1	67.1	69.1	70.6	72.7	75.2
77.5°	50.1	50.6	50.5	50.6	50.7	51.6	51.5	52.5	54.0	55.0	56.2
80°	40.2	40.7	40.2	40.7	41.2	41.7	41.2	41.7	43.3	44.3	44.3
82.5°	31.1	31.2	31.5	31.6	31.7	31.8	32.6	32.7	33.8	33.6	34.0
85°	18.6	18.1	18.1	18.1	18.6	19.1	18.6	18.6	19.1	19.1	19.1
87.5°	11.8	12.1	12.0	11.9	11.9	11.7	11.5	11.7	11.1	11.3	10.5
90°	26.1	25.7	25.1	24.7	24.3	23.6	22.5	21.4	20.4	19.3	17.6
92.5°	26.1	25.8	25.5	25.2	25.0	24.6	24.0	23.5	22.9	22.4	21.5
95°	41.5	41.7	41.9	42.1	42.3	41.9	40.9	39.8	38.7	37.7	36.2
97.5°	55.3	55.1	54.8	54.6	54.3	53.8	52.9	52.1	51.2	50.4	46.9
100°	64.6	64.2	63.8	63.3	62.9	61.9	60.2	58.5	56.8	55.0	51.4
102.5°	69.3	68.7	68.1	67.5	66.9	65.4	63.2	61.0	58.8	56.6	87.1
105°	73.3	72.5	71.6	70.8	69.9	68.3	65.9	63.6	61.2	58.9	117.4
107.5°	75.4	74.6	73.7	72.9	72.0	72.8	75.2	77.6	80.0	82.4	152.6
110°	76.2	75.3	74.5	73.6	72.8	83.1	104.5	125.9	147.4	168.8	230.9



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.1	76.3	75.6	74.9	74.2	113.0	191.3	269.4	347.7	426.0	441.2
115°	79.2	94.5	110.0	125.4	140.9	198.2	297.5	396.8	496.0	595.4	590.1
117.5°	323.1	373.9	424.5	475.2	526.0	563.4	587.4	611.4	635.4	659.4	655.8
120°	588.7	617.5	646.5	675.5	704.4	717.6	715.0	712.5	709.9	707.3	703.5
122.5°	734.6	740.1	745.8	751.3	757.0	759.0	757.5	756.0	754.4	752.9	748.6
125°	825.1	824.4	823.7	823.1	822.4	821.4	819.9	818.4	816.9	815.4	811.3
127.5°	882.1	882.0	881.9	881.8	881.6	880.5	878.3	876.2	873.9	871.7	868.7
130°	917.7	917.9	918.1	918.3	918.6	917.5	915.1	912.7	910.4	908.1	905.6
132.5°	952.4	952.6	952.8	953.0	953.3	952.4	950.4	948.4	946.3	944.3	941.9
135°	1002.6	1003.0	1003.4	1003.9	1004.3	1003.4	1001.3	999.2	997.0	994.9	992.9
137.5°	1048.3	1049.0	1049.8	1050.6	1051.3	1050.6	1048.4	1046.3	1044.3	1042.2	1040.0
140°	1076.9	1077.9	1079.0	1080.2	1081.2	1080.8	1078.8	1076.9	1075.0	1073.1	1070.7
142.5°	1104.7	1105.8	1106.8	1107.9	1108.9	1108.6	1106.9	1105.1	1103.4	1101.6	1098.9
145°	1143.5	1144.6	1145.6	1146.7	1147.8	1147.5	1146.1	1144.6	1143.1	1141.6	1137.9
147.5°	1177.6	1178.5	1179.4	1180.3	1181.2	1181.1	1180.0	1178.9	1177.8	1176.7	1173.1
150°	1198.5	1199.5	1200.6	1201.7	1202.7	1202.6	1201.3	1200.1	1198.8	1197.5	1194.1
152.5°	1216.3	1217.7	1219.1	1220.5	1221.9	1221.9	1220.6	1219.4	1218.1	1216.8	1213.6
155°	1240.9	1242.6	1244.4	1246.1	1247.8	1248.0	1246.7	1245.5	1244.2	1242.8	1240.3
157.5°	1263.5	1265.2	1266.9	1268.5	1270.2	1270.3	1268.9	1267.4	1266.0	1264.5	1262.6
160°	1276.7	1278.2	1279.6	1281.1	1282.6	1282.7	1281.4	1280.2	1278.9	1277.6	1276.4
162.5°	1287.5	1289.3	1291.1	1292.9	1294.8	1295.1	1293.5	1292.1	1290.6	1289.2	1288.1
165°	1303.6	1305.1	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6	1303.0
167.5°	1313.9	1315.9	1317.8	1319.7	1321.6	1321.8	1320.3	1318.8	1317.3	1315.9	1315.2
170°	1320.1	1322.0	1323.9	1325.9	1327.8	1328.0	1326.5	1325.0	1323.5	1322.0	1321.6
172.5°	1324.7	1326.7	1328.6	1330.5	1332.4	1332.6	1331.1	1329.6	1328.2	1326.7	1326.2
175°	1328.8	1330.9	1333.0	1335.1	1337.4	1337.7	1336.2	1334.6	1333.1	1331.6	1331.2
177.5°	1331.3	1332.8	1334.3	1335.8	1337.5	1337.6	1336.4	1335.2	1334.0	1332.8	1332.6
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1519.0	1515.7	1512.9	1505.4	1501.8	1493.5	1492.3	1491.9	1481.1	1470.8	1467.9
5°	1571.2	1563.0	1550.5	1536.1	1521.2	1505.7	1495.4	1487.2	1466.5	1446.9	1435.6
7.5°	1623.8	1606.1	1584.7	1557.4	1534.6	1509.0	1490.1	1473.1	1443.8	1415.7	1396.8
10°	1662.9	1634.1	1605.8	1568.1	1538.7	1509.8	1483.1	1459.9	1426.8	1389.8	1363.4
12.5°	1687.3	1655.6	1616.5	1579.6	1541.7	1504.9	1469.1	1439.3	1400.5	1362.1	1330.9
15°	1720.2	1686.2	1638.7	1586.2	1537.2	1489.2	1448.0	1410.9	1360.4	1314.5	1276.4
17.5°	1747.1	1700.3	1649.3	1588.5	1531.9	1470.9	1417.7	1370.4	1314.1	1258.8	1213.9
20°	1755.8	1709.4	1650.6	1589.7	1522.8	1451.1	1393.9	1342.3	1282.0	1221.7	1170.1
22.5°	1750.4	1714.3	1648.9	1576.2	1507.5	1432.5	1367.9	1308.1	1241.2	1179.6	1119.8
25°	1714.0	1701.6	1639.8	1560.3	1482.1	1394.9	1320.2	1254.7	1178.4	1112.5	1047.4
27.5°	1629.1	1655.9	1617.5	1533.0	1445.8	1352.4	1268.4	1193.9	1114.7	1040.5	975.7
30°	1547.5	1608.8	1592.4	1514.0	1416.5	1324.8	1230.5	1152.7	1068.1	991.8	927.9
32.5°	1435.7	1537.1	1553.2	1487.6	1386.8	1286.1	1187.2	1109.7	1021.5	941.1	878.8
35°	1257.8	1409.4	1478.9	1437.1	1336.2	1227.4	1125.3	1035.1	946.4	867.1	805.2
37.5°	1045.5	1251.9	1367.9	1370.9	1278.1	1165.0	1053.9	964.3	873.5	795.6	728.7
40°	907.8	1131.5	1282.5	1316.1	1237.7	1115.5	1003.1	911.9	823.2	746.9	670.1
42.5°	784.1	1006.9	1192.7	1250.9	1188.6	1067.2	954.5	859.1	773.0	700.7	622.3
45°	634.1	828.9	1033.6	1137.7	1103.2	990.8	871.7	780.9	700.0	637.6	562.4
47.5°	534.8	672.2	870.2	1011.1	1010.5	907.9	790.7	703.9	628.8	570.4	509.4
50°	478.4	597.9	765.5	925.3	938.7	852.6	741.2	655.2	585.1	523.7	474.7
52.5°	427.7	526.2	676.8	830.0	868.2	793.7	685.6	606.1	538.1	481.7	439.7
55°	361.3	437.7	552.1	695.4	753.2	700.5	604.7	530.5	475.2	427.9	391.7
57.5°	305.7	362.9	454.7	570.2	637.3	604.3	525.1	464.8	417.7	374.8	346.3
60°	270.6	317.5	395.4	491.8	566.0	542.8	475.2	419.1	378.9	341.7	315.0
62.5°	237.6	277.9	344.7	422.9	491.0	481.4	426.2	379.1	343.9	310.0	287.3
65°	191.3	220.7	272.7	334.1	388.7	393.3	353.7	321.6	290.2	263.4	243.3
67.5°	152.3	171.5	208.1	259.8	300.7	315.4	291.1	266.7	241.8	221.1	203.6
70°	128.4	143.8	170.7	212.4	250.0	265.5	251.6	232.5	210.9	193.8	178.8
72.5°	104.0	119.1	138.9	169.5	201.8	218.4	213.6	200.0	182.4	168.2	154.1
75°	78.4	83.0	96.4	117.0	142.3	156.7	160.4	153.1	139.2	128.4	120.1
77.5°	58.0	60.7	67.2	78.0	94.4	107.3	112.6	111.8	102.2	95.8	88.2
80°	46.4	48.0	51.0	55.6	68.1	80.9	84.5	84.5	77.9	75.2	67.6
82.5°	35.2	36.4	38.3	40.8	46.6	57.9	61.9	62.7	58.5	55.0	49.0
85°	20.1	19.6	20.6	22.1	23.2	26.3	32.5	33.5	32.5	28.4	26.8
87.5°	10.2	10.3	9.9	9.1	9.0	9.0	10.6	12.1	11.0	10.2	9.9
90°	15.9	14.1	12.4	10.4	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.7	19.8	19.0	18.7	18.9	19.1	19.3	19.5	19.3	19.1	18.9
95°	34.6	33.1	31.6	34.4	41.5	48.6	55.6	62.7	55.6	48.6	41.5
97.5°	43.4	40.0	36.5	44.7	64.6	84.6	104.5	124.5	104.5	84.6	64.6
100°	47.7	44.0	40.4	53.3	82.7	112.0	141.4	170.8	141.4	112.0	82.7
102.5°	117.5	148.0	178.5	196.8	203.1	209.3	215.5	221.8	215.5	209.3	203.1
105°	175.9	234.5	293.1	319.1	312.7	306.2	299.8	293.4	299.8	306.2	312.7
107.5°	222.8	293.1	363.2	395.8	390.5	385.4	380.2	375.0	380.2	385.4	390.5
110°	292.9	354.8	416.8	445.5	441.0	436.5	432.0	427.5	432.0	436.5	441.0



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	456.6	471.9	487.2	492.8	488.9	484.8	480.9	476.9	480.9	484.8	488.9
115°	584.6	579.3	573.9	569.5	565.8	562.2	558.5	554.8	558.5	562.2	565.8
117.5°	652.1	648.4	644.7	640.9	636.7	632.7	628.6	624.5	628.6	632.7	636.7
120°	699.6	695.7	691.9	688.3	685.1	681.9	678.7	675.5	678.7	681.9	685.1
122.5°	744.5	740.2	736.1	732.3	728.8	725.5	722.1	718.7	722.1	725.5	728.8
125°	807.3	803.1	799.1	795.7	792.8	790.1	787.3	784.5	787.3	790.1	792.8
127.5°	865.7	862.6	859.6	856.5	853.4	850.3	847.3	844.1	847.3	850.3	853.4
130°	903.3	900.9	898.6	895.6	892.2	888.9	885.4	882.0	885.4	888.9	892.2
132.5°	939.6	937.3	934.8	932.2	929.3	926.5	923.5	920.6	923.5	926.5	929.3
135°	991.0	989.1	987.1	984.5	981.1	977.7	974.2	970.8	974.2	977.7	981.1
137.5°	1037.7	1035.6	1033.4	1031.1	1028.7	1026.3	1023.9	1021.5	1023.9	1026.3	1028.7
140°	1068.3	1065.9	1063.6	1061.6	1059.9	1058.1	1056.4	1054.7	1056.4	1058.1	1059.9
142.5°	1096.2	1093.5	1090.8	1088.6	1087.1	1085.6	1084.0	1082.5	1084.0	1085.6	1087.1
145°	1134.3	1130.6	1127.0	1125.3	1125.5	1125.7	1125.9	1126.1	1125.9	1125.7	1125.5
147.5°	1169.4	1165.9	1162.3	1160.8	1161.6	1162.5	1163.3	1164.2	1163.3	1162.5	1161.6
150°	1190.6	1187.2	1183.8	1182.9	1184.4	1185.8	1187.3	1188.8	1187.3	1185.8	1184.4
152.5°	1210.3	1207.0	1203.8	1203.0	1204.7	1206.3	1208.0	1209.7	1208.0	1206.3	1204.7
155°	1237.7	1235.2	1232.5	1232.2	1234.2	1236.1	1238.0	1240.0	1238.0	1236.1	1234.2
157.5°	1260.9	1259.1	1257.3	1257.2	1258.8	1260.4	1262.1	1263.7	1262.1	1260.4	1258.8
160°	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1276.4	1275.1	1273.7
162.5°	1287.0	1285.9	1284.8	1284.9	1286.1	1287.4	1288.7	1290.0	1288.7	1287.4	1286.1
165°	1302.3	1301.7	1301.1	1301.4	1302.7	1303.9	1305.3	1306.6	1305.3	1303.9	1302.7
167.5°	1314.6	1314.0	1313.4	1313.7	1315.0	1316.4	1317.6	1318.9	1317.6	1316.4	1315.0
170°	1321.1	1320.7	1320.3	1320.7	1322.0	1323.3	1324.5	1325.9	1324.5	1323.3	1322.0
172.5°	1325.8	1325.3	1324.9	1325.3	1326.7	1327.9	1329.2	1330.5	1329.2	1327.9	1326.7
175°	1330.8	1330.4	1329.9	1330.5	1332.0	1333.4	1334.9	1336.5	1334.9	1333.4	1332.0
177.5°	1332.4	1332.3	1332.1	1332.6	1333.8	1335.0	1336.3	1337.5	1336.3	1335.0	1333.8
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1462.6	1459.7	1454.3	1446.0	1441.1	1432.4	1426.6	1430.0	1430.8	1430.0	1429.2
5°	1423.3	1412.4	1397.5	1383.0	1369.7	1355.2	1347.0	1343.3	1336.2	1332.0	1330.0
7.5°	1375.7	1357.1	1336.0	1310.8	1289.4	1267.1	1255.7	1249.9	1235.2	1227.2	1220.1
10°	1340.3	1310.9	1289.8	1256.8	1236.7	1207.3	1187.2	1187.7	1167.6	1156.2	1148.0
12.5°	1301.1	1268.8	1233.7	1204.0	1176.0	1152.5	1128.2	1118.4	1097.0	1086.1	1063.9
15°	1236.2	1198.5	1161.4	1121.2	1092.9	1056.2	1021.2	978.4	943.8	913.9	905.7
17.5°	1165.2	1118.6	1081.4	1034.2	985.6	924.0	883.4	858.6	837.8	822.0	810.2
20°	1116.5	1069.1	1029.5	958.3	892.8	851.1	821.2	802.1	780.4	763.5	754.2
22.5°	1065.4	1015.9	961.8	882.4	831.4	797.9	771.2	749.3	734.7	721.3	713.0
25°	992.8	938.7	849.5	794.9	753.7	718.6	700.0	686.6	671.2	653.1	644.9
27.5°	916.1	830.0	766.0	725.4	686.0	663.2	646.5	626.5	612.7	604.6	596.0
30°	858.8	772.7	722.8	678.4	650.6	625.3	605.7	594.4	581.0	567.0	561.4
32.5°	794.9	726.1	678.2	641.3	613.0	591.5	576.0	557.6	548.0	539.4	527.6
35°	715.5	663.5	619.7	589.8	562.9	545.4	527.4	516.5	499.0	491.8	487.2
37.5°	648.2	603.1	570.5	538.9	517.7	498.3	487.3	470.0	462.4	452.4	442.6
40°	610.4	566.0	534.5	508.8	485.0	470.6	456.8	442.8	431.4	426.9	415.0
42.5°	571.6	535.5	504.0	475.7	459.9	444.6	427.1	416.9	405.1	397.6	390.2
45°	518.1	486.1	459.3	436.1	418.6	402.6	391.2	374.3	367.6	352.5	346.4
47.5°	471.1	441.3	415.8	393.7	376.6	366.2	349.6	336.3	325.6	316.4	308.5
50°	437.7	412.9	388.2	368.6	353.1	338.2	321.1	314.5	297.9	293.3	288.7
52.5°	407.2	383.6	360.9	341.7	326.3	311.7	296.8	288.0	276.9	272.3	268.9
55°	364.5	341.7	320.1	303.1	287.6	272.7	263.4	252.6	247.4	243.8	239.7
57.5°	321.5	301.1	284.6	267.3	251.8	239.9	229.1	222.7	217.3	212.6	207.6
60°	294.4	274.8	259.8	243.8	227.8	218.0	209.8	202.1	195.9	188.6	186.6
62.5°	265.5	248.3	234.7	219.0	205.2	196.2	188.3	181.1	173.6	163.1	160.2
65°	225.8	212.4	197.9	185.1	172.7	163.9	152.6	144.3	141.3	140.2	139.7
67.5°	190.0	177.2	164.8	151.7	140.4	132.3	126.5	125.2	123.1	122.5	121.1
70°	166.0	154.1	141.8	129.4	118.6	117.0	114.9	112.9	110.3	109.3	108.3
72.5°	144.5	132.3	119.9	110.0	105.3	103.4	101.4	99.3	97.6	96.5	95.8
75°	110.8	99.5	91.3	87.7	85.0	83.5	80.4	78.9	77.9	76.2	75.7
77.5°	79.8	73.4	69.6	67.4	64.6	63.0	61.2	59.7	58.6	58.3	57.5
80°	60.8	57.8	55.1	52.1	51.0	49.0	48.5	47.0	47.5	45.8	45.8
82.5°	47.3	43.3	41.1	39.7	38.7	37.1	36.5	35.7	35.9	34.7	34.7
85°	24.2	23.2	22.1	21.1	21.1	19.6	20.1	19.6	19.6	18.6	18.1
87.5°	9.9	9.9	9.4	9.8	10.1	10.0	10.3	10.1	10.3	10.5	10.2
90°	10.4	12.4	14.1	15.9	17.6	19.3	20.4	21.4	22.5	23.6	24.3
92.5°	18.7	19.0	19.8	20.7	21.5	22.4	22.9	23.5	24.0	24.6	25.0
95°	34.4	31.6	33.1	34.6	36.2	37.7	38.7	39.8	40.9	41.9	42.3
97.5°	44.7	36.5	40.0	43.4	46.9	50.4	51.2	52.1	52.9	53.8	54.3
100°	53.3	40.4	44.0	47.7	51.4	55.0	56.8	58.5	60.2	61.9	62.9
102.5°	196.8	178.5	148.0	117.5	87.1	56.6	58.8	61.0	63.2	65.4	66.9
105°	319.1	293.1	234.5	175.9	117.4	58.9	61.2	63.6	65.9	68.3	69.9
107.5°	395.8	363.2	293.1	222.8	152.6	82.4	80.0	77.6	75.2	72.8	72.0
110°	445.5	416.8	354.8	292.9	230.9	168.8	147.4	125.9	104.5	83.1	72.8



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.8	487.2	471.9	456.6	441.2	426.0	347.7	269.4	191.3	113.0	74.2
115°	569.5	573.9	579.3	584.6	590.1	595.4	496.0	396.8	297.5	198.2	140.9
117.5°	640.9	644.7	648.4	652.1	655.8	659.4	635.4	611.4	587.4	563.4	526.0
120°	688.3	691.9	695.7	699.6	703.5	707.3	709.9	712.5	715.0	717.6	704.4
122.5°	732.3	736.1	740.2	744.5	748.6	752.9	754.4	756.0	757.5	759.0	757.0
125°	795.7	799.1	803.1	807.3	811.3	815.4	816.9	818.4	819.9	821.4	822.4
127.5°	856.5	859.6	862.6	865.7	868.7	871.7	873.9	876.2	878.3	880.5	881.6
130°	895.6	898.6	900.9	903.3	905.6	908.1	910.4	912.7	915.1	917.5	918.6
132.5°	932.2	934.8	937.3	939.6	941.9	944.3	946.3	948.4	950.4	952.4	953.3
135°	984.5	987.1	989.1	991.0	992.9	994.9	997.0	999.2	1001.3	1003.4	1004.3
137.5°	1031.1	1033.4	1035.6	1037.7	1040.0	1042.2	1044.3	1046.3	1048.4	1050.6	1051.3
140°	1061.6	1063.6	1065.9	1068.3	1070.7	1073.1	1075.0	1076.9	1078.8	1080.8	1081.2
142.5°	1088.6	1090.8	1093.5	1096.2	1098.9	1101.6	1103.4	1105.1	1106.9	1108.6	1108.9
145°	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1143.1	1144.6	1146.1	1147.5	1147.8
147.5°	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1177.8	1178.9	1180.0	1181.1	1181.2
150°	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8	1200.1	1201.3	1202.6	1202.7
152.5°	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1	1219.4	1220.6	1221.9	1221.9
155°	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2	1245.5	1246.7	1248.0	1247.8
157.5°	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0	1267.4	1268.9	1270.3	1270.2
160°	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9	1280.2	1281.4	1282.7	1282.6
162.5°	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6	1292.1	1293.5	1295.1	1294.8
165°	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1	1306.7	1308.2	1309.7	1309.7
167.5°	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3	1318.8	1320.3	1321.8	1321.6
170°	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5	1325.0	1326.5	1328.0	1327.8
172.5°	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2	1329.6	1331.1	1332.6	1332.4
175°	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1	1334.6	1336.2	1337.7	1337.4
177.5°	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0	1335.2	1336.4	1337.6	1337.5
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1424.6	1425.4	1424.2	1425.0	1424.2	1425.4	1424.6	1429.2	1430.0	1430.8	1430.0
5°	1327.4	1321.2	1320.2	1318.6	1320.2	1321.2	1327.4	1330.0	1332.0	1336.2	1343.3
7.5°	1211.3	1210.3	1207.8	1204.2	1207.8	1210.3	1211.3	1220.1	1227.2	1235.2	1249.9
10°	1136.6	1134.1	1133.6	1129.9	1133.6	1134.1	1136.6	1148.0	1156.2	1167.6	1187.7
12.5°	1049.2	1032.6	1030.9	1021.9	1030.9	1032.6	1049.2	1063.9	1086.1	1097.0	1118.4
15°	893.3	890.3	879.9	873.2	879.9	890.3	893.3	905.7	913.9	943.8	978.4
17.5°	804.3	794.2	790.9	789.5	790.9	794.2	804.3	810.2	822.0	837.8	858.6
20°	746.9	737.7	736.1	735.1	736.1	737.7	746.9	754.2	763.5	780.4	802.1
22.5°	707.3	697.6	693.7	690.5	693.7	697.6	707.3	713.0	721.3	734.7	749.3
25°	639.7	636.1	634.1	633.0	634.1	636.1	639.7	644.9	653.1	671.2	686.6
27.5°	586.8	578.9	577.3	574.7	577.3	578.9	586.8	596.0	604.6	612.7	626.5
30°	556.7	554.1	550.6	547.4	550.6	554.1	556.7	561.4	567.0	581.0	594.4
32.5°	521.3	519.1	515.9	514.4	515.9	519.1	521.3	527.6	539.4	548.0	557.6
35°	482.0	474.7	471.7	467.1	471.7	474.7	482.0	487.2	491.8	499.0	516.5
37.5°	440.4	436.7	432.3	433.8	432.3	436.7	440.4	442.6	452.4	462.4	470.0
40°	408.3	405.7	404.7	404.1	404.7	405.7	408.3	415.0	426.9	431.4	442.8
42.5°	382.7	375.6	372.9	372.8	372.9	375.6	382.7	390.2	397.6	405.1	416.9
45°	343.9	337.1	332.4	333.1	332.4	337.1	343.9	346.4	352.5	367.6	374.3
47.5°	304.1	303.9	300.9	301.8	300.9	303.9	304.1	308.5	316.4	325.6	336.3
50°	285.1	282.0	279.9	280.4	279.9	282.0	285.1	288.7	293.3	297.9	314.5
52.5°	266.9	264.3	262.6	264.8	262.6	264.3	266.9	268.9	272.3	276.9	288.0
55°	237.1	234.0	233.5	233.0	233.5	234.0	237.1	239.7	243.8	247.4	252.6
57.5°	203.8	201.8	198.6	197.3	198.6	201.8	203.8	207.6	212.6	217.3	222.7
60°	179.9	175.8	170.7	170.1	170.7	175.8	179.9	186.6	188.6	195.9	202.1
62.5°	158.0	157.2	156.2	156.1	156.2	157.2	158.0	160.2	163.1	173.6	181.1
65°	138.7	138.1	138.7	139.2	138.7	138.1	138.7	139.7	140.2	141.3	144.3
67.5°	120.9	119.9	119.0	119.4	119.0	119.9	120.9	121.1	122.5	123.1	125.2
70°	107.2	106.7	106.2	106.2	106.2	106.7	107.2	108.3	109.3	110.3	112.9
72.5°	94.0	93.9	93.4	93.0	93.4	93.9	94.0	95.8	96.5	97.6	99.3
75°	75.2	74.2	74.2	74.2	74.2	74.2	75.2	75.7	76.2	77.9	78.9
77.5°	57.4	56.9	56.2	55.8	56.2	56.9	57.4	57.5	58.3	58.6	59.7
80°	45.3	44.8	44.3	44.3	44.3	44.8	45.3	45.8	45.8	47.5	47.0
82.5°	34.6	34.1	34.0	33.6	34.0	34.1	34.6	34.7	34.7	35.9	35.7
85°	18.6	19.1	18.6	19.6	18.6	19.1	18.6	18.1	18.6	19.6	19.6
87.5°	10.3	10.0	10.5	10.2	10.5	10.0	10.3	10.2	10.5	10.3	10.1
90°	24.7	25.1	25.7	26.1	25.7	25.1	24.7	24.3	23.6	22.5	21.4
92.5°	25.2	25.5	25.8	26.1	25.8	25.5	25.2	25.0	24.6	24.0	23.5
95°	42.1	41.9	41.7	41.5	41.7	41.9	42.1	42.3	41.9	40.9	39.8
97.5°	54.6	54.8	55.1	55.3	55.1	54.8	54.6	54.3	53.8	52.9	52.1
100°	63.3	63.8	64.2	64.6	64.2	63.8	63.3	62.9	61.9	60.2	58.5
102.5°	67.5	68.1	68.7	69.3	68.7	68.1	67.5	66.9	65.4	63.2	61.0
105°	70.8	71.6	72.5	73.3	72.5	71.6	70.8	69.9	68.3	65.9	63.6
107.5°	72.9	73.7	74.6	75.4	74.6	73.7	72.9	72.0	72.8	75.2	77.6
110°	73.6	74.5	75.3	76.2	75.3	74.5	73.6	72.8	83.1	104.5	125.9



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	74.9	75.6	76.3	77.1	76.3	75.6	74.9	74.2	113.0	191.3	269.4
115°	125.4	110.0	94.5	79.2	94.5	110.0	125.4	140.9	198.2	297.5	396.8
117.5°	475.2	424.5	373.9	323.1	373.9	424.5	475.2	526.0	563.4	587.4	611.4
120°	675.5	646.5	617.5	588.7	617.5	646.5	675.5	704.4	717.6	715.0	712.5
122.5°	751.3	745.8	740.1	734.6	740.1	745.8	751.3	757.0	759.0	757.5	756.0
125°	823.1	823.7	824.4	825.1	824.4	823.7	823.1	822.4	821.4	819.9	818.4
127.5°	881.8	881.9	882.0	882.1	882.0	881.9	881.8	881.6	880.5	878.3	876.2
130°	918.3	918.1	917.9	917.7	917.9	918.1	918.3	918.6	917.5	915.1	912.7
132.5°	953.0	952.8	952.6	952.4	952.6	952.8	953.0	953.3	952.4	950.4	948.4
135°	1003.9	1003.4	1003.0	1002.6	1003.0	1003.4	1003.9	1004.3	1003.4	1001.3	999.2
137.5°	1050.6	1049.8	1049.0	1048.3	1049.0	1049.8	1050.6	1051.3	1050.6	1048.4	1046.3
140°	1080.2	1079.0	1077.9	1076.9	1077.9	1079.0	1080.2	1081.2	1080.8	1078.8	1076.9
142.5°	1107.9	1106.8	1105.8	1104.7	1105.8	1106.8	1107.9	1108.9	1108.6	1106.9	1105.1
145°	1146.7	1145.6	1144.6	1143.5	1144.6	1145.6	1146.7	1147.8	1147.5	1146.1	1144.6
147.5°	1180.3	1179.4	1178.5	1177.6	1178.5	1179.4	1180.3	1181.2	1181.1	1180.0	1178.9
150°	1201.7	1200.6	1199.5	1198.5	1199.5	1200.6	1201.7	1202.7	1202.6	1201.3	1200.1
152.5°	1220.5	1219.1	1217.7	1216.3	1217.7	1219.1	1220.5	1221.9	1221.9	1220.6	1219.4
155°	1246.1	1244.4	1242.6	1240.9	1242.6	1244.4	1246.1	1247.8	1248.0	1246.7	1245.5
157.5°	1268.5	1266.9	1265.2	1263.5	1265.2	1266.9	1268.5	1270.2	1270.3	1268.9	1267.4
160°	1281.1	1279.6	1278.2	1276.7	1278.2	1279.6	1281.1	1282.6	1282.7	1281.4	1280.2
162.5°	1292.9	1291.1	1289.3	1287.5	1289.3	1291.1	1292.9	1294.8	1295.1	1293.5	1292.1
165°	1308.2	1306.7	1305.1	1303.6	1305.1	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7
167.5°	1319.7	1317.8	1315.9	1313.9	1315.9	1317.8	1319.7	1321.6	1321.8	1320.3	1318.8
170°	1325.9	1323.9	1322.0	1320.1	1322.0	1323.9	1325.9	1327.8	1328.0	1326.5	1325.0
172.5°	1330.5	1328.6	1326.7	1324.7	1326.7	1328.6	1330.5	1332.4	1332.6	1331.1	1329.6
175°	1335.1	1333.0	1330.9	1328.8	1330.9	1333.0	1335.1	1337.4	1337.7	1336.2	1334.6
177.5°	1335.8	1334.3	1332.8	1331.3	1332.8	1334.3	1335.8	1337.5	1337.6	1336.4	1335.2
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1426.6	1432.4	1441.1	1446.0	1454.3	1459.7	1462.6	1467.9	1470.8	1481.1	1491.9
5°	1347.0	1355.2	1369.7	1383.0	1397.5	1412.4	1423.3	1435.6	1446.9	1466.5	1487.2
7.5°	1255.7	1267.1	1289.4	1310.8	1336.0	1357.1	1375.7	1396.8	1415.7	1443.8	1473.1
10°	1187.2	1207.3	1236.7	1256.8	1289.8	1310.9	1340.3	1363.4	1389.8	1426.8	1459.9
12.5°	1128.2	1152.5	1176.0	1204.0	1233.7	1268.8	1301.1	1330.9	1362.1	1400.5	1439.3
15°	1021.2	1056.2	1092.9	1121.2	1161.4	1198.5	1236.2	1276.4	1314.5	1360.4	1410.9
17.5°	883.4	924.0	985.6	1034.2	1081.4	1118.6	1165.2	1213.9	1258.8	1314.1	1370.4
20°	821.2	851.1	892.8	958.3	1029.5	1069.1	1116.5	1170.1	1221.7	1282.0	1342.3
22.5°	771.2	797.9	831.4	882.4	961.8	1015.9	1065.4	1119.8	1179.6	1241.2	1308.1
25°	700.0	718.6	753.7	794.9	849.5	938.7	992.8	1047.4	1112.5	1178.4	1254.7
27.5°	646.5	663.2	686.0	725.4	766.0	830.0	916.1	975.7	1040.5	1114.7	1193.9
30°	605.7	625.3	650.6	678.4	722.8	772.7	858.8	927.9	991.8	1068.1	1152.7
32.5°	576.0	591.5	613.0	641.3	678.2	726.1	794.9	878.8	941.1	1021.5	1109.7
35°	527.4	545.4	562.9	589.8	619.7	663.5	715.5	805.2	867.1	946.4	1035.1
37.5°	487.3	498.3	517.7	538.9	570.5	603.1	648.2	728.7	795.6	873.5	964.3
40°	456.8	470.6	485.0	508.8	534.5	566.0	610.4	670.1	746.9	823.2	911.9
42.5°	427.1	444.6	459.9	475.7	504.0	535.5	571.6	622.3	700.7	773.0	859.1
45°	391.2	402.6	418.6	436.1	459.3	486.1	518.1	562.4	637.6	700.0	780.9
47.5°	349.6	366.2	376.6	393.7	415.8	441.3	471.1	509.4	570.4	628.8	703.9
50°	321.1	338.2	353.1	368.6	388.2	412.9	437.7	474.7	523.7	585.1	655.2
52.5°	296.8	311.7	326.3	341.7	360.9	383.6	407.2	439.7	481.7	538.1	606.1
55°	263.4	272.7	287.6	303.1	320.1	341.7	364.5	391.7	427.9	475.2	530.5
57.5°	229.1	239.9	251.8	267.3	284.6	301.1	321.5	346.3	374.8	417.7	464.8
60°	209.8	218.0	227.8	243.8	259.8	274.8	294.4	315.0	341.7	378.9	419.1
62.5°	188.3	196.2	205.2	219.0	234.7	248.3	265.5	287.3	310.0	343.9	379.1
65°	152.6	163.9	172.7	185.1	197.9	212.4	225.8	243.3	263.4	290.2	321.6
67.5°	126.5	132.3	140.4	151.7	164.8	177.2	190.0	203.6	221.1	241.8	266.7
70°	114.9	117.0	118.6	129.4	141.8	154.1	166.0	178.8	193.8	210.9	232.5
72.5°	101.4	103.4	105.3	110.0	119.9	132.3	144.5	154.1	168.2	182.4	200.0
75°	80.4	83.5	85.0	87.7	91.3	99.5	110.8	120.1	128.4	139.2	153.1
77.5°	61.2	63.0	64.6	67.4	69.6	73.4	79.8	88.2	95.8	102.2	111.8
80°	48.5	49.0	51.0	52.1	55.1	57.8	60.8	67.6	75.2	77.9	84.5
82.5°	36.5	37.1	38.7	39.7	41.1	43.3	47.3	49.0	55.0	58.5	62.7
85°	20.1	19.6	21.1	21.1	22.1	23.2	24.2	26.8	28.4	32.5	33.5
87.5°	10.3	10.0	10.1	9.8	9.4	9.9	9.9	9.9	10.2	11.0	12.1
90°	20.4	19.3	17.6	15.9	14.1	12.4	10.4	8.1	5.7	3.3	1.0
92.5°	22.9	22.4	21.5	20.7	19.8	19.0	18.7	18.9	19.1	19.3	19.5
95°	38.7	37.7	36.2	34.6	33.1	31.6	34.4	41.5	48.6	55.6	62.7
97.5°	51.2	50.4	46.9	43.4	40.0	36.5	44.7	64.6	84.6	104.5	124.5
100°	56.8	55.0	51.4	47.7	44.0	40.4	53.3	82.7	112.0	141.4	170.8
102.5°	58.8	56.6	87.1	117.5	148.0	178.5	196.8	203.1	209.3	215.5	221.8
105°	61.2	58.9	117.4	175.9	234.5	293.1	319.1	312.7	306.2	299.8	293.4
107.5°	80.0	82.4	152.6	222.8	293.1	363.2	395.8	390.5	385.4	380.2	375.0
110°	147.4	168.8	230.9	292.9	354.8	416.8	445.5	441.0	436.5	432.0	427.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.7	426.0	441.2	456.6	471.9	487.2	492.8	488.9	484.8	480.9	476.9
115°	496.0	595.4	590.1	584.6	579.3	573.9	569.5	565.8	562.2	558.5	554.8
117.5°	635.4	659.4	655.8	652.1	648.4	644.7	640.9	636.7	632.7	628.6	624.5
120°	709.9	707.3	703.5	699.6	695.7	691.9	688.3	685.1	681.9	678.7	675.5
122.5°	754.4	752.9	748.6	744.5	740.2	736.1	732.3	728.8	725.5	722.1	718.7
125°	816.9	815.4	811.3	807.3	803.1	799.1	795.7	792.8	790.1	787.3	784.5
127.5°	873.9	871.7	868.7	865.7	862.6	859.6	856.5	853.4	850.3	847.3	844.1
130°	910.4	908.1	905.6	903.3	900.9	898.6	895.6	892.2	888.9	885.4	882.0
132.5°	946.3	944.3	941.9	939.6	937.3	934.8	932.2	929.3	926.5	923.5	920.6
135°	997.0	994.9	992.9	991.0	989.1	987.1	984.5	981.1	977.7	974.2	970.8
137.5°	1044.3	1042.2	1040.0	1037.7	1035.6	1033.4	1031.1	1028.7	1026.3	1023.9	1021.5
140°	1075.0	1073.1	1070.7	1068.3	1065.9	1063.6	1061.6	1059.9	1058.1	1056.4	1054.7
142.5°	1103.4	1101.6	1098.9	1096.2	1093.5	1090.8	1088.6	1087.1	1085.6	1084.0	1082.5
145°	1143.1	1141.6	1137.9	1134.3	1130.6	1127.0	1125.3	1125.5	1125.7	1125.9	1126.1
147.5°	1177.8	1176.7	1173.1	1169.4	1165.9	1162.3	1160.8	1161.6	1162.5	1163.3	1164.2
150°	1198.8	1197.5	1194.1	1190.6	1187.2	1183.8	1182.9	1184.4	1185.8	1187.3	1188.8
152.5°	1218.1	1216.8	1213.6	1210.3	1207.0	1203.8	1203.0	1204.7	1206.3	1208.0	1209.7
155°	1244.2	1242.8	1240.3	1237.7	1235.2	1232.5	1232.2	1234.2	1236.1	1238.0	1240.0
157.5°	1266.0	1264.5	1262.6	1260.9	1259.1	1257.3	1257.2	1258.8	1260.4	1262.1	1263.7
160°	1278.9	1277.6	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6
162.5°	1290.6	1289.2	1288.1	1287.0	1285.9	1284.8	1284.9	1286.1	1287.4	1288.7	1290.0
165°	1305.1	1303.6	1303.0	1302.3	1301.7	1301.1	1301.4	1302.7	1303.9	1305.3	1306.6
167.5°	1317.3	1315.9	1315.2	1314.6	1314.0	1313.4	1313.7	1315.0	1316.4	1317.6	1318.9
170°	1323.5	1322.0	1321.6	1321.1	1320.7	1320.3	1320.7	1322.0	1323.3	1324.5	1325.9
172.5°	1328.2	1326.7	1326.2	1325.8	1325.3	1324.9	1325.3	1326.7	1327.9	1329.2	1330.5
175°	1333.1	1331.6	1331.2	1330.8	1330.4	1329.9	1330.5	1332.0	1333.4	1334.9	1336.5
177.5°	1334.0	1332.8	1332.6	1332.4	1332.3	1332.1	1332.6	1333.8	1335.0	1336.3	1337.5
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1492.3	1493.5	1501.8	1505.4	1512.9	1515.7	1519.0	1518.2	1518.2	1519.8	1531.5
5°	1495.4	1505.7	1521.2	1536.1	1550.5	1563.0	1571.2	1579.4	1582.6	1597.5	1610.9
7.5°	1490.1	1509.0	1534.6	1557.4	1584.7	1606.1	1623.8	1639.8	1650.7	1672.4	1694.8
10°	1483.1	1509.8	1538.7	1568.1	1605.8	1634.1	1662.9	1685.2	1692.3	1724.8	1743.4
12.5°	1469.1	1504.9	1541.7	1579.6	1616.5	1655.6	1687.3	1709.5	1734.8	1764.0	1798.3
15°	1448.0	1489.2	1537.2	1586.2	1638.7	1686.2	1720.2	1758.9	1786.7	1818.7	1848.6
17.5°	1417.7	1470.9	1531.9	1588.5	1649.3	1700.3	1747.1	1784.2	1803.8	1822.0	1826.4
20°	1393.9	1451.1	1522.8	1589.7	1650.6	1709.4	1755.8	1786.7	1791.8	1792.3	1765.0
22.5°	1367.9	1432.5	1507.5	1576.2	1648.9	1714.3	1750.4	1763.6	1743.1	1708.2	1655.4
25°	1320.2	1394.9	1482.1	1560.3	1639.8	1701.6	1714.0	1690.8	1619.1	1543.9	1448.6
27.5°	1268.4	1352.4	1445.8	1533.0	1617.5	1655.9	1629.1	1545.5	1416.4	1304.2	1168.3
30°	1230.5	1324.8	1416.5	1514.0	1592.4	1608.8	1547.5	1424.3	1273.7	1104.7	969.2
32.5°	1187.2	1286.1	1386.8	1487.6	1553.2	1537.1	1435.7	1284.0	1107.6	941.4	813.2
35°	1125.3	1227.4	1336.2	1437.1	1478.9	1409.4	1257.8	1060.4	879.9	724.8	636.6
37.5°	1053.9	1165.0	1278.1	1370.9	1367.9	1251.9	1045.5	841.7	690.0	598.2	535.5
40°	1003.1	1115.5	1237.7	1316.1	1282.5	1131.5	907.8	715.5	604.7	531.5	485.5
42.5°	954.5	1067.2	1188.6	1250.9	1192.7	1006.9	784.1	633.4	542.0	484.8	447.7
45°	871.7	990.8	1103.2	1137.7	1033.6	828.9	634.1	524.7	463.9	421.7	395.9
47.5°	790.7	907.9	1010.5	1011.1	870.2	672.2	534.8	454.1	402.2	369.5	350.7
50°	741.2	852.6	938.7	925.3	765.5	597.9	478.4	408.8	365.5	340.2	320.6
52.5°	685.6	793.7	868.2	830.0	676.8	526.2	427.7	369.2	333.4	311.3	293.9
55°	604.7	700.5	753.2	695.4	552.1	437.7	361.3	315.5	288.7	270.1	255.2
57.5°	525.1	604.3	637.3	570.2	454.7	362.9	305.7	271.2	244.7	231.4	223.6
60°	475.2	542.8	566.0	491.8	395.4	317.5	270.6	238.6	219.0	210.4	202.6
62.5°	426.2	481.4	491.0	422.9	344.7	277.9	237.6	210.7	197.6	189.2	182.0
65°	353.7	393.3	388.7	334.1	272.7	220.7	191.3	174.7	164.9	153.1	140.2
67.5°	291.1	315.4	300.7	259.8	208.1	171.5	152.3	139.8	127.6	116.4	113.4
70°	251.6	265.5	250.0	212.4	170.7	143.8	128.4	113.4	106.2	103.6	99.0
72.5°	213.6	218.4	201.8	169.5	138.9	119.1	104.0	95.6	91.8	89.6	86.6
75°	160.4	156.7	142.3	117.0	96.4	83.0	78.4	75.2	72.7	70.6	69.1
77.5°	112.6	107.3	94.4	78.0	67.2	60.7	58.0	56.2	55.0	54.0	52.5
80°	84.5	80.9	68.1	55.6	51.0	48.0	46.4	44.3	44.3	43.3	41.7
82.5°	61.9	57.9	46.6	40.8	38.3	36.4	35.2	34.0	33.6	33.8	32.7
85°	32.5	26.3	23.2	22.1	20.6	19.6	20.1	19.1	19.1	19.1	18.6
87.5°	10.6	9.0	9.0	9.1	9.9	10.3	10.2	10.5	11.3	11.1	11.7
90°	3.3	5.7	8.1	10.4	12.4	14.1	15.9	17.6	19.3	20.4	21.4
92.5°	19.3	19.1	18.9	18.7	19.0	19.8	20.7	21.5	22.4	22.9	23.5
95°	55.6	48.6	41.5	34.4	31.6	33.1	34.6	36.2	37.7	38.7	39.8
97.5°	104.5	84.6	64.6	44.7	36.5	40.0	43.4	46.9	50.4	51.2	52.1
100°	141.4	112.0	82.7	53.3	40.4	44.0	47.7	51.4	55.0	56.8	58.5
102.5°	215.5	209.3	203.1	196.8	178.5	148.0	117.5	87.1	56.6	58.8	61.0
105°	299.8	306.2	312.7	319.1	293.1	234.5	175.9	117.4	58.9	61.2	63.6
107.5°	380.2	385.4	390.5	395.8	363.2	293.1	222.8	152.6	82.4	80.0	77.6
110°	432.0	436.5	441.0	445.5	416.8	354.8	292.9	230.9	168.8	147.4	125.9



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.9	484.8	488.9	492.8	487.2	471.9	456.6	441.2	426.0	347.7	269.4
115°	558.5	562.2	565.8	569.5	573.9	579.3	584.6	590.1	595.4	496.0	396.8
117.5°	628.6	632.7	636.7	640.9	644.7	648.4	652.1	655.8	659.4	635.4	611.4
120°	678.7	681.9	685.1	688.3	691.9	695.7	699.6	703.5	707.3	709.9	712.5
122.5°	722.1	725.5	728.8	732.3	736.1	740.2	744.5	748.6	752.9	754.4	756.0
125°	787.3	790.1	792.8	795.7	799.1	803.1	807.3	811.3	815.4	816.9	818.4
127.5°	847.3	850.3	853.4	856.5	859.6	862.6	865.7	868.7	871.7	873.9	876.2
130°	885.4	888.9	892.2	895.6	898.6	900.9	903.3	905.6	908.1	910.4	912.7
132.5°	923.5	926.5	929.3	932.2	934.8	937.3	939.6	941.9	944.3	946.3	948.4
135°	974.2	977.7	981.1	984.5	987.1	989.1	991.0	992.9	994.9	997.0	999.2
137.5°	1023.9	1026.3	1028.7	1031.1	1033.4	1035.6	1037.7	1040.0	1042.2	1044.3	1046.3
140°	1056.4	1058.1	1059.9	1061.6	1063.6	1065.9	1068.3	1070.7	1073.1	1075.0	1076.9
142.5°	1084.0	1085.6	1087.1	1088.6	1090.8	1093.5	1096.2	1098.9	1101.6	1103.4	1105.1
145°	1125.9	1125.7	1125.5	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1143.1	1144.6
147.5°	1163.3	1162.5	1161.6	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1177.8	1178.9
150°	1187.3	1185.8	1184.4	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8	1200.1
152.5°	1208.0	1206.3	1204.7	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1	1219.4
155°	1238.0	1236.1	1234.2	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2	1245.5
157.5°	1262.1	1260.4	1258.8	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0	1267.4
160°	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9	1280.2
162.5°	1288.7	1287.4	1286.1	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6	1292.1
165°	1305.3	1303.9	1302.7	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1	1306.7
167.5°	1317.6	1316.4	1315.0	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3	1318.8
170°	1324.5	1323.3	1322.0	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5	1325.0
172.5°	1329.2	1327.9	1326.7	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2	1329.6
175°	1334.9	1333.4	1332.0	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1	1334.6
177.5°	1336.3	1335.0	1333.8	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0	1335.2
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1535.5	1540.9	1543.4	1543.4	1546.3	1545.0	1543.8
5°	1623.8	1633.6	1635.7	1645.0	1651.6	1649.5	1650.6
7.5°	1711.5	1727.3	1742.8	1750.0	1751.1	1755.2	1756.8
10°	1765.5	1778.5	1802.7	1799.1	1817.1	1827.5	1810.4
12.5°	1817.6	1834.9	1851.7	1856.3	1866.6	1869.9	1863.2
15°	1864.5	1873.8	1874.8	1872.3	1875.3	1872.8	1863.0
17.5°	1820.6	1805.5	1775.0	1760.6	1749.2	1732.2	1725.5
20°	1748.0	1703.6	1652.1	1631.5	1607.3	1559.8	1571.2
22.5°	1591.3	1540.8	1489.2	1429.1	1400.3	1355.3	1352.6
25°	1347.5	1260.4	1164.5	1097.5	1058.3	1013.5	993.9
27.5°	1047.6	938.0	859.4	819.6	783.5	747.9	746.4
30°	850.5	768.1	707.2	673.3	651.1	636.1	639.2
32.5°	716.9	660.5	619.5	591.2	574.8	563.5	563.3
35°	586.1	547.4	521.2	509.3	497.5	489.2	489.7
37.5°	501.6	478.4	463.7	450.6	443.2	439.2	437.0
40°	458.3	439.2	427.9	420.1	413.9	408.3	407.3
42.5°	424.0	408.3	396.9	390.8	385.1	381.0	380.0
45°	376.3	363.5	353.1	346.4	343.9	340.2	340.2
47.5°	334.8	322.0	314.1	309.8	305.4	303.0	302.9
50°	306.7	296.9	289.7	287.1	283.5	282.0	281.4
52.5°	281.6	274.3	269.1	267.3	265.8	263.8	264.2
55°	247.4	243.3	241.3	239.7	237.1	234.0	236.1
57.5°	218.6	215.2	209.6	204.8	202.4	200.3	201.1
60°	198.4	191.3	184.0	178.3	176.8	172.2	172.2
62.5°	172.9	162.8	153.9	150.8	149.2	147.0	146.6
65°	133.0	128.9	126.8	124.7	123.7	123.7	122.7
67.5°	110.2	108.6	106.3	105.7	104.7	104.4	104.1
70°	97.5	95.3	94.3	93.8	92.8	93.3	91.8
72.5°	85.0	83.4	83.2	81.9	81.2	81.3	80.2
75°	67.1	67.1	66.4	65.9	64.9	64.4	64.9
77.5°	51.5	51.6	50.7	50.6	50.5	50.6	50.1
80°	41.2	41.7	41.2	40.7	40.2	40.7	40.2
82.5°	32.6	31.8	31.7	31.6	31.5	31.2	31.1
85°	18.6	19.1	18.6	18.1	18.1	18.1	18.6
87.5°	11.5	11.7	11.9	11.9	12.0	12.1	11.8
90°	22.5	23.6	24.3	24.7	25.1	25.7	26.1
92.5°	24.0	24.6	25.0	25.2	25.5	25.8	26.1
95°	40.9	41.9	42.3	42.1	41.9	41.7	41.5
97.5°	52.9	53.8	54.3	54.6	54.8	55.1	55.3
100°	60.2	61.9	62.9	63.3	63.8	64.2	64.6
102.5°	63.2	65.4	66.9	67.5	68.1	68.7	69.3
105°	65.9	68.3	69.9	70.8	71.6	72.5	73.3
107.5°	75.2	72.8	72.0	72.9	73.7	74.6	75.4
110°	104.5	83.1	72.8	73.6	74.5	75.3	76.2



TEST NUMBER: P331813-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	191.3	113.0	74.2	74.9	75.6	76.3	77.1
115°	297.5	198.2	140.9	125.4	110.0	94.5	79.2
117.5°	587.4	563.4	526.0	475.2	424.5	373.9	323.1
120°	715.0	717.6	704.4	675.5	646.5	617.5	588.7
122.5°	757.5	759.0	757.0	751.3	745.8	740.1	734.6
125°	819.9	821.4	822.4	823.1	823.7	824.4	825.1
127.5°	878.3	880.5	881.6	881.8	881.9	882.0	882.1
130°	915.1	917.5	918.6	918.3	918.1	917.9	917.7
132.5°	950.4	952.4	953.3	953.0	952.8	952.6	952.4
135°	1001.3	1003.4	1004.3	1003.9	1003.4	1003.0	1002.6
137.5°	1048.4	1050.6	1051.3	1050.6	1049.8	1049.0	1048.3
140°	1078.8	1080.8	1081.2	1080.2	1079.0	1077.9	1076.9
142.5°	1106.9	1108.6	1108.9	1107.9	1106.8	1105.8	1104.7
145°	1146.1	1147.5	1147.8	1146.7	1145.6	1144.6	1143.5
147.5°	1180.0	1181.1	1181.2	1180.3	1179.4	1178.5	1177.6
150°	1201.3	1202.6	1202.7	1201.7	1200.6	1199.5	1198.5
152.5°	1220.6	1221.9	1221.9	1220.5	1219.1	1217.7	1216.3
155°	1246.7	1248.0	1247.8	1246.1	1244.4	1242.6	1240.9
157.5°	1268.9	1270.3	1270.2	1268.5	1266.9	1265.2	1263.5
160°	1281.4	1282.7	1282.6	1281.1	1279.6	1278.2	1276.7
162.5°	1293.5	1295.1	1294.8	1292.9	1291.1	1289.3	1287.5
165°	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6
167.5°	1320.3	1321.8	1321.6	1319.7	1317.8	1315.9	1313.9
170°	1326.5	1328.0	1327.8	1325.9	1323.9	1322.0	1320.1
172.5°	1331.1	1332.6	1332.4	1330.5	1328.6	1326.7	1324.7
175°	1336.2	1337.7	1337.4	1335.1	1333.0	1330.9	1328.8
177.5°	1336.4	1337.6	1337.5	1335.8	1334.3	1332.8	1331.3
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5

(END OF REPORT)