

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332143-830

Luminaire Tested: **S123DIW-S560D1320U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332143-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6501.2 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	32	30	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20
4	71	61	53	47	64	55	48	43	44	40	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15
6	60	48	40	35	54	44	37	32	36	31	27	28	24	21	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	15	12	11	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.2
10°-20°	223.3	3.4
20°-30°	329.9	5.1
30°-40°	385.4	5.9
40°-50°	387.4	6.0
50°-60°	340.3	5.2
60°-70°	253.5	3.9
70°-80°	144.5	2.2
80°-90°	46.1	0.7
90°-100°	101.4	1.6
100°-110°	303.4	4.7
110°-120°	516.1	7.9
120°-130°	678.8	10.4
130°-140°	763.0	11.7
140°-150°	750.0	11.5
150°-160°	631.4	9.7
160°-170°	420.3	6.5
170°-180°	147.2	2.3
0°-30°	632.3	9.7
0°-40°	1017.7	15.7
0°-60°	1745.5	26.8
0°-90°	2189.6	33.7
90°-120°	920.9	14.2
90°-150°	3112.8	47.9
90°-180°	4312.0	66.3
0°-180°	6501.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	14	29	34	37	6
95°	72	81	90	95	95	81
105°	275	278	288	289	291	295
115°	520	523	521	522	521	514
125°	760	764	762	757	752	678
135°	987	993	993	988	985	760
145°	1197	1199	1203	1202	1197	747
155°	1370	1370	1372	1376	1368	631
165°	1493	1489	1489	1495	1488	421
175°	1553	1548	1548	1554	1546	147
180°	1556	1556	1556	1556	1556	



TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.3	15.5	15.6	15.7	15.9	16.3	16.9	17.4	18.0	18.6	18.7
90°	1.2	4.0	6.7	9.3	12.1	15.2	18.8	22.2	25.8	29.3	30.4
92.5°	29.6	31.4	33.3	35.2	36.9	38.9	40.9	42.9	45.0	46.9	47.8
95°	72.1	74.0	76.0	77.9	79.7	81.8	84.0	86.1	88.3	90.5	91.5
97.5°	128.1	129.5	130.9	132.3	133.7	135.3	136.9	138.4	140.0	141.6	142.8
100°	166.3	167.9	169.5	171.2	172.8	174.3	175.6	177.0	178.3	179.7	180.5
102.5°	210.3	211.2	212.3	213.2	214.1	215.6	217.4	219.1	220.9	222.7	223.6
105°	275.0	275.6	276.2	276.6	277.2	278.7	281.2	283.6	286.1	288.5	288.5
107.5°	350.3	350.7	351.0	351.4	351.7	352.3	353.3	354.3	355.2	356.2	357.1
110°	397.3	397.8	398.4	398.9	399.4	400.0	400.6	401.1	401.6	402.2	403.3



TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.5	446.9	447.1	447.5	447.7	447.8	447.9	448.1	448.2	449.5
115°	519.5	520.4	521.1	522.0	522.8	522.9	522.4	521.9	521.3	520.8	521.0
117.5°	593.4	593.9	594.5	595.0	595.6	595.5	594.7	594.1	593.3	592.7	592.6
120°	639.3	640.9	642.6	644.2	645.8	646.0	644.6	643.3	642.0	640.6	640.3
122.5°	687.3	688.4	689.7	690.9	692.0	692.3	691.5	690.9	690.1	689.5	688.7
125°	760.3	761.2	762.0	762.8	763.6	763.7	763.2	762.7	762.1	761.6	760.5
127.5°	827.8	829.6	831.3	833.0	834.8	835.4	834.8	834.2	833.6	833.0	831.4
130°	872.8	875.0	877.2	879.4	881.6	882.2	881.4	880.6	879.8	878.9	877.9
132.5°	917.8	920.0	922.2	924.4	926.5	927.3	926.7	926.1	925.5	924.9	923.6
135°	986.6	988.2	989.8	991.4	993.1	993.7	993.4	993.2	992.9	992.6	991.6
137.5°	1050.1	1051.4	1052.8	1054.1	1055.6	1056.6	1057.2	1058.0	1058.7	1059.4	1058.2
140°	1094.1	1095.4	1096.8	1098.2	1099.6	1100.3	1100.6	1100.9	1101.2	1101.5	1101.2
142.5°	1134.2	1135.6	1136.9	1138.3	1139.6	1140.6	1141.0	1141.5	1142.0	1142.6	1142.3
145°	1196.7	1197.3	1197.9	1198.4	1198.9	1199.7	1200.4	1201.3	1202.1	1202.9	1202.6
147.5°	1251.5	1252.5	1253.5	1254.5	1255.5	1256.3	1257.1	1257.8	1258.6	1259.3	1259.3
150°	1289.7	1290.2	1290.8	1291.3	1291.8	1292.4	1293.0	1293.5	1294.0	1294.6	1294.6
152.5°	1321.0	1321.7	1322.5	1323.2	1324.0	1324.6	1324.9	1325.2	1325.6	1325.9	1326.3
155°	1370.4	1370.4	1370.4	1370.4	1370.4	1370.6	1370.7	1371.0	1371.3	1371.6	1372.7
157.5°	1412.4	1412.1	1411.7	1411.5	1411.1	1411.1	1411.3	1411.5	1411.7	1411.9	1413.1
160°	1438.8	1438.3	1437.8	1437.2	1436.6	1436.3	1436.3	1436.3	1436.3	1436.3	1437.8
162.5°	1462.3	1461.5	1460.8	1460.0	1459.2	1459.0	1459.2	1459.4	1459.6	1459.8	1461.2
165°	1492.6	1491.8	1491.0	1490.2	1489.4	1488.9	1488.9	1488.9	1488.9	1488.9	1490.5
167.5°	1516.8	1515.7	1514.7	1513.5	1512.5	1512.0	1512.2	1512.5	1512.7	1512.9	1514.6
170°	1530.5	1529.5	1528.3	1527.3	1526.2	1525.6	1525.6	1525.6	1525.6	1525.6	1527.5
172.5°	1541.2	1540.2	1539.1	1538.0	1536.9	1536.3	1536.3	1536.3	1536.3	1536.3	1538.0
175°	1552.6	1551.4	1550.4	1549.3	1548.1	1547.7	1547.7	1547.7	1547.7	1547.7	1549.3
177.5°	1557.2	1556.3	1555.4	1554.5	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1554.5
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2



TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	18.8	18.9	18.9	19.0	19.1	19.2	19.3	19.5
90°	31.5	32.6	33.6	34.5	35.1	35.6	36.1	36.7
92.5°	48.6	49.6	50.4	50.7	50.3	50.0	49.7	49.4
95°	92.7	93.7	94.8	95.4	95.4	95.4	95.4	95.4
97.5°	144.0	145.3	146.6	147.1	147.0	146.9	146.8	146.7
100°	181.3	182.1	182.9	183.6	184.2	184.7	185.3	185.8
102.5°	224.3	225.2	226.0	226.3	226.2	226.1	226.0	225.9
105°	288.5	288.5	288.5	288.8	289.4	289.8	290.4	291.0
107.5°	358.0	358.8	359.7	360.0	359.7	359.3	359.0	358.6
110°	404.4	405.5	406.5	406.8	406.2	405.8	405.2	404.6



TEST NUMBER: P332143-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.7	452.0	453.4	453.9	453.8	453.7	453.6	453.6
115°	521.3	521.6	521.9	521.9	521.6	521.3	521.0	520.8
117.5°	592.6	592.5	592.4	592.0	591.3	590.5	589.7	589.0
120°	640.0	639.8	639.5	639.0	638.6	638.0	637.4	636.9
122.5°	688.1	687.3	686.6	685.9	685.1	684.4	683.6	682.9
125°	759.4	758.4	757.2	756.2	755.1	753.9	752.9	751.8
127.5°	829.9	828.4	826.9	825.5	824.3	823.0	821.8	820.5
130°	876.8	875.7	874.6	873.1	871.2	869.3	867.4	865.5
132.5°	922.3	921.0	919.7	918.3	916.8	915.4	913.9	912.5
135°	990.4	989.4	988.3	987.5	986.9	986.4	985.8	985.3
137.5°	1057.1	1055.9	1054.8	1053.8	1052.7	1051.7	1050.7	1049.6
140°	1100.9	1100.6	1100.3	1099.3	1097.4	1095.4	1093.5	1091.7
142.5°	1142.0	1141.7	1141.4	1140.6	1139.1	1137.6	1136.1	1134.7
145°	1202.3	1202.1	1201.8	1201.2	1200.0	1198.9	1197.9	1196.7
147.5°	1259.3	1259.3	1259.3	1258.6	1257.0	1255.3	1253.7	1252.1
150°	1294.6	1294.6	1294.6	1293.7	1292.1	1290.5	1288.8	1287.2
152.5°	1326.7	1327.2	1327.6	1327.1	1325.7	1324.3	1322.9	1321.4
155°	1373.8	1374.9	1375.9	1375.5	1373.7	1371.8	1369.8	1367.9
157.5°	1414.2	1415.3	1416.5	1416.3	1414.8	1413.2	1411.7	1410.2
160°	1439.1	1440.5	1441.8	1442.0	1440.9	1439.8	1438.7	1437.6
162.5°	1462.5	1464.0	1465.3	1465.1	1463.4	1461.6	1459.9	1458.1
165°	1492.2	1493.8	1495.4	1495.3	1493.5	1491.6	1489.6	1487.7
167.5°	1516.3	1518.0	1519.7	1519.7	1518.0	1516.3	1514.6	1512.9
170°	1529.5	1531.3	1533.2	1533.2	1531.3	1529.5	1527.5	1525.6
172.5°	1539.7	1541.4	1543.1	1543.0	1541.2	1539.2	1537.3	1535.4
175°	1550.9	1552.6	1554.2	1554.0	1552.1	1550.2	1548.3	1546.4
177.5°	1555.9	1557.2	1558.5	1558.4	1556.8	1555.3	1553.8	1552.3
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2

(END OF REPORT)