

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332124-830

Luminaire Tested: **S123DIW-S560D460U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332124-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D460U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3924.7 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52	47
2	90	83	76	71	83	77	71	67	66	62	59	57	54	51	48	45	43	39
3	82	73	65	59	76	68	61	56	59	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.0
10°-20°	223.3	5.7
20°-30°	329.9	8.4
30°-40°	385.4	9.8
40°-50°	387.4	9.9
50°-60°	340.3	8.7
60°-70°	253.5	6.5
70°-80°	144.5	3.7
80°-90°	43.1	1.1
90°-100°	20.7	0.5
100°-110°	98.8	2.5
110°-120°	237.2	6.0
120°-130°	302.1	7.7
130°-140°	322.8	8.2
140°-150°	301.8	7.7
150°-160°	243.5	6.2
160°-170°	157.1	4.0
170°-180°	54.2	1.4
0°-30°	632.3	16.1
0°-40°	1017.7	25.9
0°-60°	1745.5	44.5
0°-90°	2186.5	55.7
90°-120°	356.7	9.1
90°-150°	1283.4	32.7
90°-180°	1738.0	44.3
0°-180°	3924.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	0	5	10	12	13	3
95°	26	10	13	16	16	32
105°	126	128	93	22	19	134
115°	237	239	243	247	249	234
125°	334	337	339	340	340	298
135°	415	418	420	421	420	320
145°	479	482	483	484	484	300
155°	528	527	528	529	527	243
165°	557	556	555	558	556	157
175°	570	568	568	571	568	54
180°	570	570	570	570	570	



TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.1	14.9	14.7	14.5	14.3	14.2	14.4	14.5	14.6	14.7	14.7
90°	0.4	1.3	2.3	3.2	4.1	5.3	6.5	7.7	9.0	10.2	10.6
92.5°	7.9	7.6	7.4	7.1	6.8	7.2	8.1	9.0	9.9	10.8	11.4
95°	25.8	22.0	18.1	14.2	10.4	9.0	10.0	11.0	12.1	13.1	13.8
97.5°	51.9	50.1	48.4	46.8	45.0	40.7	33.9	27.1	20.5	13.7	14.4
100°	71.5	73.4	75.3	77.2	79.1	72.7	58.1	43.4	28.7	13.9	14.7
102.5°	93.9	95.3	96.6	98.0	99.3	92.0	76.0	59.9	43.9	27.9	25.5
105°	126.2	127.2	128.3	129.3	130.4	126.6	118.1	109.7	101.2	92.7	76.1
107.5°	160.2	161.1	161.9	162.7	163.5	164.7	166.0	167.3	168.6	169.9	157.8
110°	182.9	183.7	184.5	185.2	186.0	186.8	187.8	188.9	189.9	191.0	187.8



TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.6	205.3	205.9	206.6	207.4	208.2	209.2	210.3	211.3	212.4	212.4
115°	236.7	237.2	237.8	238.4	238.9	239.7	240.5	241.4	242.2	243.1	244.0
117.5°	267.8	268.5	269.2	269.8	270.6	271.2	271.5	272.0	272.5	272.9	273.6
120°	287.1	287.9	288.8	289.6	290.5	291.1	291.3	291.6	291.9	292.2	292.9
122.5°	306.8	307.5	308.1	308.9	309.5	310.1	310.5	310.8	311.1	311.5	312.0
125°	333.7	334.4	335.2	335.9	336.7	337.2	337.6	338.0	338.4	338.7	338.9
127.5°	359.8	360.5	361.3	362.0	362.8	363.4	363.8	364.3	364.8	365.2	365.5
130°	376.1	376.8	377.6	378.3	379.1	379.7	380.0	380.4	380.8	381.1	381.4
132.5°	391.6	392.4	393.1	393.9	394.6	395.1	395.5	395.8	396.1	396.3	396.7
135°	415.4	415.9	416.5	417.1	417.6	418.1	418.5	418.9	419.2	419.6	419.9
137.5°	435.7	436.5	437.2	437.9	438.6	439.0	439.3	439.5	439.7	439.9	440.4
140°	449.3	449.9	450.4	451.0	451.6	451.9	452.2	452.5	452.8	453.1	453.5
142.5°	461.8	462.4	463.0	463.5	464.1	464.5	464.8	465.1	465.3	465.6	465.9
145°	479.4	480.0	480.7	481.4	482.0	482.4	482.6	482.8	483.0	483.1	483.3
147.5°	495.9	496.3	496.7	497.2	497.6	497.9	498.1	498.3	498.5	498.7	498.9
150°	506.1	506.3	506.6	506.9	507.2	507.4	507.6	507.7	507.9	508.1	508.3
152.5°	515.2	515.3	515.5	515.6	515.8	515.9	515.9	516.0	516.1	516.3	516.6
155°	528.0	527.8	527.6	527.5	527.4	527.3	527.4	527.4	527.5	527.6	528.1
157.5°	538.1	538.0	538.0	538.0	538.0	537.9	537.8	537.7	537.6	537.5	538.1
160°	544.1	544.0	543.9	543.8	543.8	543.7	543.6	543.5	543.4	543.3	543.8
162.5°	549.9	549.7	549.4	549.2	548.9	548.7	548.7	548.6	548.5	548.4	549.0
165°	556.9	556.6	556.3	556.0	555.7	555.5	555.4	555.3	555.3	555.2	555.9
167.5°	562.3	561.9	561.6	561.2	560.8	560.6	560.6	560.6	560.6	560.6	561.4
170°	565.3	565.0	564.6	564.2	563.8	563.6	563.6	563.6	563.6	563.6	564.4
172.5°	567.3	566.9	566.5	566.0	565.5	565.3	565.4	565.5	565.6	565.6	566.4
175°	570.0	569.5	569.0	568.5	568.1	567.9	568.0	568.1	568.2	568.3	568.9
177.5°	570.6	570.2	569.9	569.5	569.1	569.0	569.1	569.1	569.2	569.3	569.9
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	14.6	14.6	14.5	14.5	14.5	14.6	14.6	14.7
90°	10.9	11.3	11.7	12.0	12.2	12.3	12.5	12.7
92.5°	12.1	12.6	13.3	13.6	13.8	13.9	13.9	14.0
95°	14.4	15.1	15.7	16.1	16.1	16.1	16.1	16.1
97.5°	15.2	15.9	16.7	17.1	17.2	17.2	17.3	17.4
100°	15.5	16.2	17.0	17.4	17.5	17.6	17.7	17.8
102.5°	23.2	20.8	18.6	17.4	17.6	17.8	17.9	18.1
105°	59.4	42.8	26.1	17.9	18.1	18.3	18.5	18.7
107.5°	145.5	133.4	121.1	108.8	96.1	83.6	71.1	58.5
110°	184.7	181.6	178.5	170.3	156.8	143.4	129.9	116.5



TEST NUMBER: P332124-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.4	212.4	212.5	211.1	208.3	205.5	202.6	199.8
115°	245.0	245.9	246.9	247.5	247.9	248.3	248.6	249.0
117.5°	274.4	275.1	275.9	276.3	276.4	276.4	276.5	276.6
120°	293.7	294.5	295.2	295.6	295.6	295.6	295.6	295.6
122.5°	312.5	313.1	313.6	313.9	314.0	314.1	314.1	314.2
125°	339.1	339.3	339.5	339.7	339.9	340.1	340.3	340.4
127.5°	365.8	366.1	366.4	366.5	366.3	366.1	365.9	365.7
130°	381.8	382.2	382.6	382.7	382.5	382.3	382.1	381.9
132.5°	397.1	397.5	397.8	397.9	397.7	397.4	397.1	396.9
135°	420.2	420.5	420.8	420.8	420.5	420.2	419.9	419.6
137.5°	440.8	441.2	441.7	441.9	441.7	441.5	441.3	441.1
140°	453.8	454.2	454.6	454.7	454.5	454.3	454.1	453.9
142.5°	466.3	466.6	466.8	466.8	466.6	466.4	466.1	465.8
145°	483.5	483.7	483.9	484.0	484.0	484.0	484.0	484.0
147.5°	499.1	499.3	499.5	499.3	498.9	498.4	498.0	497.6
150°	508.5	508.7	508.9	508.9	508.6	508.3	508.0	507.7
152.5°	517.0	517.3	517.6	517.6	517.2	516.7	516.3	515.9
155°	528.6	529.0	529.5	529.4	528.9	528.3	527.7	527.3
157.5°	538.7	539.2	539.8	539.7	538.9	538.3	537.5	536.8
160°	544.4	545.0	545.5	545.5	544.9	544.2	543.6	542.9
162.5°	549.7	550.4	550.9	551.0	550.4	549.8	549.2	548.7
165°	556.7	557.4	558.2	558.2	557.5	556.9	556.3	555.6
167.5°	562.1	562.8	563.5	563.5	562.8	562.1	561.4	560.6
170°	565.1	565.9	566.7	566.7	565.9	565.1	564.4	563.6
172.5°	567.1	567.9	568.6	568.6	567.8	566.9	566.2	565.3
175°	569.6	570.2	570.9	570.9	570.1	569.4	568.6	567.9
177.5°	570.5	571.1	571.7	571.7	570.9	570.1	569.4	568.6
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0

(END OF REPORT)