

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332162-830

Luminaire Tested: **S123DIW-S775D1030U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332162-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1030U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6963.3 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44								
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38								
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32								
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27								
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24								
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21								
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18								
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16								
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14								
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13								
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	1.4
10°-20°	321.7	4.6
20°-30°	539.9	7.8
30°-40°	611.3	8.8
40°-50°	548.2	7.9
50°-60°	442.4	6.4
60°-70°	308.3	4.4
70°-80°	162.0	2.3
80°-90°	43.2	0.6
90°-100°	46.3	0.7
100°-110°	220.8	3.2
110°-120°	530.4	7.6
120°-130°	675.4	9.7
130°-140°	721.6	10.4
140°-150°	674.8	9.7
150°-160°	544.3	7.8
160°-170°	351.3	5.0
170°-180°	121.1	1.7
0°-30°	961.9	13.8
0°-40°	1573.3	22.6
0°-60°	2563.9	36.8
0°-90°	3077.5	44.2
90°-120°	797.5	11.5
90°-150°	2869.2	41.2
90°-180°	3886.0	55.8
0°-180°	6963.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	28	1	28	1	28	14
95°	36	58	36	58	36	30
105°	42	282	42	282	42	95
115°	557	529	557	529	557	514
125°	761	746	761	746	761	680
135°	938	929	938	929	938	723
145°	1082	1072	1082	1072	1082	675
155°	1179	1180	1179	1180	1179	543
165°	1242	1245	1242	1245	1242	351
175°	1270	1274	1270	1274	1270	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	17.5	16.7	17.0	17.2	16.8	17.1	17.2	17.5	17.7	18.0	17.8
90°	28.4	28.0	27.5	27.1	26.7	26.1	25.3	24.4	23.6	22.7	20.0
92.5°	31.4	31.2	30.9	30.6	30.4	29.6	28.3	27.0	25.5	24.2	22.1
95°	36.0	36.0	36.0	36.0	36.0	35.3	33.7	32.3	30.8	29.3	27.1
97.5°	39.0	38.8	38.5	38.4	38.2	37.2	35.5	33.8	32.1	30.4	45.6
100°	39.8	39.6	39.3	39.1	38.9	38.0	36.3	34.6	32.9	31.2	64.1
102.5°	40.5	40.2	39.8	39.4	39.0	41.4	46.7	51.8	57.1	62.3	98.1
105°	41.7	41.2	40.8	40.4	40.0	58.3	95.6	132.9	170.1	207.4	226.3
107.5°	130.8	158.9	187.0	215.0	243.1	270.8	298.1	325.4	352.7	380.0	377.0
110°	260.3	290.4	320.5	350.6	380.7	399.2	406.1	413.1	420.0	427.0	424.6



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.7	453.0	459.4	465.7	472.0	475.1	475.0	474.9	474.8	474.7	472.4
115°	556.7	555.8	555.0	554.1	553.3	551.9	549.7	547.6	545.5	543.4	541.5
117.5°	618.4	618.2	618.0	617.8	617.7	616.8	615.1	613.4	611.7	610.0	609.1
120°	660.8	660.8	660.8	660.8	660.8	660.0	658.3	656.6	654.9	653.2	652.6
122.5°	702.5	702.3	702.1	701.9	701.8	701.1	699.9	698.7	697.6	696.4	695.6
125°	761.1	760.7	760.3	759.9	759.5	759.0	758.7	758.2	757.8	757.3	756.5
127.5°	817.6	818.0	818.4	818.8	819.3	819.2	818.4	817.7	817.1	816.4	815.4
130°	853.9	854.3	854.8	855.2	855.6	855.4	854.5	853.8	852.9	852.1	851.2
132.5°	887.2	887.9	888.4	889.0	889.6	889.5	888.6	887.8	886.9	886.1	885.4
135°	938.2	938.8	939.4	940.1	940.7	940.7	940.1	939.4	938.8	938.2	937.4
137.5°	986.1	986.5	986.9	987.3	987.8	987.5	986.5	985.4	984.4	983.4	983.0
140°	1014.8	1015.3	1015.7	1016.2	1016.5	1016.3	1015.5	1014.6	1013.8	1013.0	1012.3
142.5°	1041.3	1042.0	1042.5	1043.1	1043.7	1043.7	1043.0	1042.4	1041.7	1040.9	1040.4
145°	1082.0	1082.0	1082.0	1082.0	1082.0	1081.9	1081.5	1081.0	1080.6	1080.2	1079.8
147.5°	1112.4	1113.3	1114.3	1115.3	1116.3	1116.5	1116.1	1115.7	1115.2	1114.8	1114.4
150°	1135.1	1135.8	1136.3	1137.0	1137.6	1137.7	1137.3	1136.9	1136.4	1136.0	1135.6
152.5°	1153.3	1154.2	1155.2	1156.1	1157.2	1157.3	1156.5	1155.7	1155.0	1154.2	1154.0
155°	1178.6	1179.9	1181.2	1182.4	1183.6	1183.8	1182.7	1181.7	1180.6	1179.6	1179.4
157.5°	1200.0	1201.6	1203.3	1204.9	1206.5	1206.7	1205.5	1204.3	1203.0	1201.7	1201.9
160°	1213.6	1215.1	1216.6	1218.0	1219.6	1219.7	1218.4	1217.1	1215.9	1214.7	1214.8
162.5°	1226.5	1227.9	1229.2	1230.5	1231.7	1231.7	1230.3	1228.8	1227.4	1226.0	1226.2
165°	1242.1	1243.5	1245.0	1246.5	1247.9	1247.8	1246.1	1244.4	1242.8	1241.1	1241.3
167.5°	1253.2	1254.9	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2	1253.2
170°	1260.1	1261.7	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1	1260.1
172.5°	1263.9	1265.6	1267.5	1269.4	1271.2	1271.3	1269.6	1268.0	1266.3	1264.6	1264.4
175°	1269.5	1271.2	1272.9	1274.6	1276.3	1276.4	1274.9	1273.4	1272.0	1270.5	1270.3
177.5°	1271.2	1272.9	1274.6	1276.3	1278.0	1278.1	1276.8	1275.4	1274.1	1272.7	1272.5
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	18.1	17.9	16.2	14.1	12.9	11.3	10.8	9.7	9.3	9.7	9.7
90°	17.2	14.5	11.8	9.3	7.3	5.2	3.0	0.9	3.0	5.2	7.3
92.5°	20.1	18.1	16.0	15.3	15.8	16.4	17.1	17.6	17.1	16.4	15.8
95°	24.7	22.4	20.1	23.3	31.9	40.5	49.1	57.8	49.1	40.5	31.9
97.5°	60.8	76.0	91.0	100.6	104.4	108.3	112.2	116.0	112.2	108.3	104.4
100°	96.9	129.7	162.5	176.8	172.6	168.4	164.2	159.9	164.2	168.4	172.6
102.5°	134.0	169.8	205.7	222.1	219.0	216.0	213.0	210.0	213.0	216.0	219.0
105°	245.2	264.1	283.0	291.3	289.1	286.7	284.5	282.1	284.5	286.7	289.1
107.5°	374.0	371.1	368.1	365.6	363.8	361.9	360.1	358.3	360.1	361.9	363.8
110°	422.4	420.0	417.7	415.7	414.1	412.4	410.7	409.0	410.7	412.4	414.1



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	470.0	467.7	465.4	463.5	462.0	460.4	458.9	457.4	458.9	460.4	462.0
115°	539.6	537.7	535.8	534.2	533.0	531.7	530.5	529.2	530.5	531.7	533.0
117.5°	608.1	607.2	606.1	604.9	603.3	601.8	600.2	598.7	600.2	601.8	603.3
120°	652.0	651.3	650.7	649.4	647.5	645.6	643.8	641.9	643.8	645.6	647.5
122.5°	694.7	694.0	693.1	692.0	690.4	688.9	687.3	685.8	687.3	688.9	690.4
125°	755.6	754.8	754.0	752.7	751.0	749.3	747.7	746.0	747.7	749.3	751.0
127.5°	814.5	813.4	812.4	811.1	809.4	807.7	806.0	804.3	806.0	807.7	809.4
130°	850.4	849.5	848.7	847.4	845.7	844.0	842.4	840.7	842.4	844.0	845.7
132.5°	884.8	884.1	883.4	882.2	880.5	878.8	877.2	875.5	877.2	878.8	880.5
135°	936.5	935.7	934.8	933.8	932.5	931.2	930.0	928.7	930.0	931.2	932.5
137.5°	982.5	982.0	981.6	980.5	978.9	977.3	975.7	974.1	975.7	977.3	978.9
140°	1011.7	1011.1	1010.4	1009.5	1008.2	1007.0	1005.7	1004.5	1005.7	1007.0	1008.2
142.5°	1039.7	1039.1	1038.5	1037.6	1036.2	1035.0	1033.7	1032.5	1033.7	1035.0	1036.2
145°	1079.3	1078.9	1078.5	1077.5	1076.1	1074.6	1073.1	1071.7	1073.1	1074.6	1076.1
147.5°	1114.0	1113.5	1113.1	1112.5	1111.4	1110.5	1109.6	1108.6	1109.6	1110.5	1111.4
150°	1135.2	1134.7	1134.3	1133.8	1133.2	1132.6	1131.9	1131.3	1131.9	1132.6	1133.2
152.5°	1153.7	1153.5	1153.2	1152.9	1152.6	1152.4	1152.1	1151.8	1152.1	1152.4	1152.6
155°	1179.1	1178.9	1178.7	1178.8	1179.3	1179.7	1180.1	1180.5	1180.1	1179.7	1179.3
157.5°	1202.1	1202.4	1202.6	1202.7	1202.8	1202.8	1202.9	1202.9	1202.9	1202.8	1202.8
160°	1215.0	1215.2	1215.4	1215.7	1215.9	1216.1	1216.3	1216.5	1216.3	1216.1	1215.9
162.5°	1226.4	1226.6	1226.8	1227.2	1227.8	1228.3	1228.8	1229.4	1228.8	1228.3	1227.8
165°	1241.5	1241.7	1242.0	1242.4	1243.0	1243.7	1244.3	1244.9	1244.3	1243.7	1243.0
167.5°	1253.2	1253.2	1253.2	1253.7	1254.5	1255.4	1256.2	1257.0	1256.2	1255.4	1254.5
170°	1260.1	1260.1	1260.1	1260.5	1261.3	1262.2	1263.0	1263.9	1263.0	1262.2	1261.3
172.5°	1264.2	1264.0	1263.9	1264.3	1265.4	1266.4	1267.3	1268.4	1267.3	1266.4	1265.4
175°	1270.1	1269.8	1269.6	1270.1	1271.1	1272.1	1273.2	1274.2	1273.2	1272.1	1271.1
177.5°	1272.4	1272.2	1272.1	1272.4	1273.3	1274.1	1274.9	1275.7	1274.9	1274.1	1273.3
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	9.8	10.7	10.8	11.8	11.9	12.8	13.0	12.3	12.5	13.9	12.4
90°	9.3	11.8	14.5	17.2	20.0	22.7	23.6	24.4	25.3	26.1	26.7
92.5°	15.3	16.0	18.1	20.1	22.1	24.2	25.5	27.0	28.3	29.6	30.4
95°	23.3	20.1	22.4	24.7	27.1	29.3	30.8	32.3	33.7	35.3	36.0
97.5°	100.6	91.0	76.0	60.8	45.6	30.4	32.1	33.8	35.5	37.2	38.2
100°	176.8	162.5	129.7	96.9	64.1	31.2	32.9	34.6	36.3	38.0	38.9
102.5°	222.1	205.7	169.8	134.0	98.1	62.3	57.1	51.8	46.7	41.4	39.0
105°	291.3	283.0	264.1	245.2	226.3	207.4	170.1	132.9	95.6	58.3	40.0
107.5°	365.6	368.1	371.1	374.0	377.0	380.0	352.7	325.4	298.1	270.8	243.1
110°	415.7	417.7	420.0	422.4	424.6	427.0	420.0	413.1	406.1	399.2	380.7



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	463.5	465.4	467.7	470.0	472.4	474.7	474.8	474.9	475.0	475.1	472.0
115°	534.2	535.8	537.7	539.6	541.5	543.4	545.5	547.6	549.7	551.9	553.3
117.5°	604.9	606.1	607.2	608.1	609.1	610.0	611.7	613.4	615.1	616.8	617.7
120°	649.4	650.7	651.3	652.0	652.6	653.2	654.9	656.6	658.3	660.0	660.8
122.5°	692.0	693.1	694.0	694.7	695.6	696.4	697.6	698.7	699.9	701.1	701.8
125°	752.7	754.0	754.8	755.6	756.5	757.3	757.8	758.2	758.7	759.0	759.5
127.5°	811.1	812.4	813.4	814.5	815.4	816.4	817.1	817.7	818.4	819.2	819.3
130°	847.4	848.7	849.5	850.4	851.2	852.1	852.9	853.8	854.5	855.4	855.6
132.5°	882.2	883.4	884.1	884.8	885.4	886.1	886.9	887.8	888.6	889.5	889.6
135°	933.8	934.8	935.7	936.5	937.4	938.2	938.8	939.4	940.1	940.7	940.7
137.5°	980.5	981.6	982.0	982.5	983.0	983.4	984.4	985.4	986.5	987.5	987.8
140°	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8	1014.6	1015.5	1016.3	1016.5
142.5°	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7	1042.4	1043.0	1043.7	1043.7
145°	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6	1081.0	1081.5	1081.9	1082.0
147.5°	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2	1115.7	1116.1	1116.5	1116.3
150°	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4	1136.9	1137.3	1137.7	1137.6
152.5°	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0	1155.7	1156.5	1157.3	1157.2
155°	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6	1181.7	1182.7	1183.8	1183.6
157.5°	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0	1204.3	1205.5	1206.7	1206.5
160°	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9	1217.1	1218.4	1219.7	1219.6
162.5°	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4	1228.8	1230.3	1231.7	1231.7
165°	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8	1244.4	1246.1	1247.8	1247.9
167.5°	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9	1256.6	1258.3	1260.0	1260.0
170°	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7	1263.4	1265.1	1266.8	1266.8
172.5°	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3	1268.0	1269.6	1271.3	1271.2
175°	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0	1273.4	1274.9	1276.4	1276.3
177.5°	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1	1275.4	1276.8	1278.1	1278.0
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	12.5	12.6	12.3	12.0	12.3	12.6	12.5	12.4	13.9	12.5	12.3
90°	27.1	27.5	28.0	28.4	28.0	27.5	27.1	26.7	26.1	25.3	24.4
92.5°	30.6	30.9	31.2	31.4	31.2	30.9	30.6	30.4	29.6	28.3	27.0
95°	36.0	36.0	36.0	36.0	36.0	36.0	36.0	36.0	35.3	33.7	32.3
97.5°	38.4	38.5	38.8	39.0	38.8	38.5	38.4	38.2	37.2	35.5	33.8
100°	39.1	39.3	39.6	39.8	39.6	39.3	39.1	38.9	38.0	36.3	34.6
102.5°	39.4	39.8	40.2	40.5	40.2	39.8	39.4	39.0	41.4	46.7	51.8
105°	40.4	40.8	41.2	41.7	41.2	40.8	40.4	40.0	58.3	95.6	132.9
107.5°	215.0	187.0	158.9	130.8	158.9	187.0	215.0	243.1	270.8	298.1	325.4
110°	350.6	320.5	290.4	260.3	290.4	320.5	350.6	380.7	399.2	406.1	413.1



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	465.7	459.4	453.0	446.7	453.0	459.4	465.7	472.0	475.1	475.0	474.9
115°	554.1	555.0	555.8	556.7	555.8	555.0	554.1	553.3	551.9	549.7	547.6
117.5°	617.8	618.0	618.2	618.4	618.2	618.0	617.8	617.7	616.8	615.1	613.4
120°	660.8	660.8	660.8	660.8	660.8	660.8	660.8	660.8	660.0	658.3	656.6
122.5°	701.9	702.1	702.3	702.5	702.3	702.1	701.9	701.8	701.1	699.9	698.7
125°	759.9	760.3	760.7	761.1	760.7	760.3	759.9	759.5	759.0	758.7	758.2
127.5°	818.8	818.4	818.0	817.6	818.0	818.4	818.8	819.3	819.2	818.4	817.7
130°	855.2	854.8	854.3	853.9	854.3	854.8	855.2	855.6	855.4	854.5	853.8
132.5°	889.0	888.4	887.9	887.2	887.9	888.4	889.0	889.6	889.5	888.6	887.8
135°	940.1	939.4	938.8	938.2	938.8	939.4	940.1	940.7	940.7	940.1	939.4
137.5°	987.3	986.9	986.5	986.1	986.5	986.9	987.3	987.8	987.5	986.5	985.4
140°	1016.2	1015.7	1015.3	1014.8	1015.3	1015.7	1016.2	1016.5	1016.3	1015.5	1014.6
142.5°	1043.1	1042.5	1042.0	1041.3	1042.0	1042.5	1043.1	1043.7	1043.7	1043.0	1042.4
145°	1082.0	1082.0	1082.0	1082.0	1082.0	1082.0	1082.0	1082.0	1081.9	1081.5	1081.0
147.5°	1115.3	1114.3	1113.3	1112.4	1113.3	1114.3	1115.3	1116.3	1116.5	1116.1	1115.7
150°	1137.0	1136.3	1135.8	1135.1	1135.8	1136.3	1137.0	1137.6	1137.7	1137.3	1136.9
152.5°	1156.1	1155.2	1154.2	1153.3	1154.2	1155.2	1156.1	1157.2	1157.3	1156.5	1155.7
155°	1182.4	1181.2	1179.9	1178.6	1179.9	1181.2	1182.4	1183.6	1183.8	1182.7	1181.7
157.5°	1204.9	1203.3	1201.6	1200.0	1201.6	1203.3	1204.9	1206.5	1206.7	1205.5	1204.3
160°	1218.0	1216.6	1215.1	1213.6	1215.1	1216.6	1218.0	1219.6	1219.7	1218.4	1217.1
162.5°	1230.5	1229.2	1227.9	1226.5	1227.9	1229.2	1230.5	1231.7	1231.7	1230.3	1228.8
165°	1246.5	1245.0	1243.5	1242.1	1243.5	1245.0	1246.5	1247.9	1247.8	1246.1	1244.4
167.5°	1258.3	1256.6	1254.9	1253.2	1254.9	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6
170°	1265.1	1263.4	1261.7	1260.1	1261.7	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4
172.5°	1269.4	1267.5	1265.6	1263.9	1265.6	1267.5	1269.4	1271.2	1271.3	1269.6	1268.0
175°	1274.6	1272.9	1271.2	1269.5	1271.2	1272.9	1274.6	1276.3	1276.4	1274.9	1273.4
177.5°	1276.3	1274.6	1272.9	1271.2	1272.9	1274.6	1276.3	1278.0	1278.1	1276.8	1275.4
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	13.0	12.8	11.9	11.8	10.8	10.7	9.8	9.7	9.7	9.3	9.7
90°	23.6	22.7	20.0	17.2	14.5	11.8	9.3	7.3	5.2	3.0	0.9
92.5°	25.5	24.2	22.1	20.1	18.1	16.0	15.3	15.8	16.4	17.1	17.6
95°	30.8	29.3	27.1	24.7	22.4	20.1	23.3	31.9	40.5	49.1	57.8
97.5°	32.1	30.4	45.6	60.8	76.0	91.0	100.6	104.4	108.3	112.2	116.0
100°	32.9	31.2	64.1	96.9	129.7	162.5	176.8	172.6	168.4	164.2	159.9
102.5°	57.1	62.3	98.1	134.0	169.8	205.7	222.1	219.0	216.0	213.0	210.0
105°	170.1	207.4	226.3	245.2	264.1	283.0	291.3	289.1	286.7	284.5	282.1
107.5°	352.7	380.0	377.0	374.0	371.1	368.1	365.6	363.8	361.9	360.1	358.3
110°	420.0	427.0	424.6	422.4	420.0	417.7	415.7	414.1	412.4	410.7	409.0



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	474.8	474.7	472.4	470.0	467.7	465.4	463.5	462.0	460.4	458.9	457.4
115°	545.5	543.4	541.5	539.6	537.7	535.8	534.2	533.0	531.7	530.5	529.2
117.5°	611.7	610.0	609.1	608.1	607.2	606.1	604.9	603.3	601.8	600.2	598.7
120°	654.9	653.2	652.6	652.0	651.3	650.7	649.4	647.5	645.6	643.8	641.9
122.5°	697.6	696.4	695.6	694.7	694.0	693.1	692.0	690.4	688.9	687.3	685.8
125°	757.8	757.3	756.5	755.6	754.8	754.0	752.7	751.0	749.3	747.7	746.0
127.5°	817.1	816.4	815.4	814.5	813.4	812.4	811.1	809.4	807.7	806.0	804.3
130°	852.9	852.1	851.2	850.4	849.5	848.7	847.4	845.7	844.0	842.4	840.7
132.5°	886.9	886.1	885.4	884.8	884.1	883.4	882.2	880.5	878.8	877.2	875.5
135°	938.8	938.2	937.4	936.5	935.7	934.8	933.8	932.5	931.2	930.0	928.7
137.5°	984.4	983.4	983.0	982.5	982.0	981.6	980.5	978.9	977.3	975.7	974.1
140°	1013.8	1013.0	1012.3	1011.7	1011.1	1010.4	1009.5	1008.2	1007.0	1005.7	1004.5
142.5°	1041.7	1040.9	1040.4	1039.7	1039.1	1038.5	1037.6	1036.2	1035.0	1033.7	1032.5
145°	1080.6	1080.2	1079.8	1079.3	1078.9	1078.5	1077.5	1076.1	1074.6	1073.1	1071.7
147.5°	1115.2	1114.8	1114.4	1114.0	1113.5	1113.1	1112.5	1111.4	1110.5	1109.6	1108.6
150°	1136.4	1136.0	1135.6	1135.2	1134.7	1134.3	1133.8	1133.2	1132.6	1131.9	1131.3
152.5°	1155.0	1154.2	1154.0	1153.7	1153.5	1153.2	1152.9	1152.6	1152.4	1152.1	1151.8
155°	1180.6	1179.6	1179.4	1179.1	1178.9	1178.7	1178.8	1179.3	1179.7	1180.1	1180.5
157.5°	1203.0	1201.7	1201.9	1202.1	1202.4	1202.6	1202.7	1202.8	1202.8	1202.9	1202.9
160°	1215.9	1214.7	1214.8	1215.0	1215.2	1215.4	1215.7	1215.9	1216.1	1216.3	1216.5
162.5°	1227.4	1226.0	1226.2	1226.4	1226.6	1226.8	1227.2	1227.8	1228.3	1228.8	1229.4
165°	1242.8	1241.1	1241.3	1241.5	1241.7	1242.0	1242.4	1243.0	1243.7	1244.3	1244.9
167.5°	1254.9	1253.2	1253.2	1253.2	1253.2	1253.2	1253.7	1254.5	1255.4	1256.2	1257.0
170°	1261.7	1260.1	1260.1	1260.1	1260.1	1260.1	1260.5	1261.3	1262.2	1263.0	1263.9
172.5°	1266.3	1264.6	1264.4	1264.2	1264.0	1263.9	1264.3	1265.4	1266.4	1267.3	1268.4
175°	1272.0	1270.5	1270.3	1270.1	1269.8	1269.6	1270.1	1271.1	1272.1	1273.2	1274.2
177.5°	1274.1	1272.7	1272.5	1272.4	1272.2	1272.1	1272.4	1273.3	1274.1	1274.9	1275.7
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.8	11.3	12.9	14.1	16.2	17.9	18.1	17.8	18.0	17.7	17.5
90°	3.0	5.2	7.3	9.3	11.8	14.5	17.2	20.0	22.7	23.6	24.4
92.5°	17.1	16.4	15.8	15.3	16.0	18.1	20.1	22.1	24.2	25.5	27.0
95°	49.1	40.5	31.9	23.3	20.1	22.4	24.7	27.1	29.3	30.8	32.3
97.5°	112.2	108.3	104.4	100.6	91.0	76.0	60.8	45.6	30.4	32.1	33.8
100°	164.2	168.4	172.6	176.8	162.5	129.7	96.9	64.1	31.2	32.9	34.6
102.5°	213.0	216.0	219.0	222.1	205.7	169.8	134.0	98.1	62.3	57.1	51.8
105°	284.5	286.7	289.1	291.3	283.0	264.1	245.2	226.3	207.4	170.1	132.9
107.5°	360.1	361.9	363.8	365.6	368.1	371.1	374.0	377.0	380.0	352.7	325.4
110°	410.7	412.4	414.1	415.7	417.7	420.0	422.4	424.6	427.0	420.0	413.1



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	458.9	460.4	462.0	463.5	465.4	467.7	470.0	472.4	474.7	474.8	474.9
115°	530.5	531.7	533.0	534.2	535.8	537.7	539.6	541.5	543.4	545.5	547.6
117.5°	600.2	601.8	603.3	604.9	606.1	607.2	608.1	609.1	610.0	611.7	613.4
120°	643.8	645.6	647.5	649.4	650.7	651.3	652.0	652.6	653.2	654.9	656.6
122.5°	687.3	688.9	690.4	692.0	693.1	694.0	694.7	695.6	696.4	697.6	698.7
125°	747.7	749.3	751.0	752.7	754.0	754.8	755.6	756.5	757.3	757.8	758.2
127.5°	806.0	807.7	809.4	811.1	812.4	813.4	814.5	815.4	816.4	817.1	817.7
130°	842.4	844.0	845.7	847.4	848.7	849.5	850.4	851.2	852.1	852.9	853.8
132.5°	877.2	878.8	880.5	882.2	883.4	884.1	884.8	885.4	886.1	886.9	887.8
135°	930.0	931.2	932.5	933.8	934.8	935.7	936.5	937.4	938.2	938.8	939.4
137.5°	975.7	977.3	978.9	980.5	981.6	982.0	982.5	983.0	983.4	984.4	985.4
140°	1005.7	1007.0	1008.2	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8	1014.6
142.5°	1033.7	1035.0	1036.2	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7	1042.4
145°	1073.1	1074.6	1076.1	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6	1081.0
147.5°	1109.6	1110.5	1111.4	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2	1115.7
150°	1131.9	1132.6	1133.2	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4	1136.9
152.5°	1152.1	1152.4	1152.6	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0	1155.7
155°	1180.1	1179.7	1179.3	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6	1181.7
157.5°	1202.9	1202.8	1202.8	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0	1204.3
160°	1216.3	1216.1	1215.9	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9	1217.1
162.5°	1228.8	1228.3	1227.8	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4	1228.8
165°	1244.3	1243.7	1243.0	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8	1244.4
167.5°	1256.2	1255.4	1254.5	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9	1256.6
170°	1263.0	1262.2	1261.3	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7	1263.4
172.5°	1267.3	1266.4	1265.4	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3	1268.0
175°	1273.2	1272.1	1271.1	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0	1273.4
177.5°	1274.9	1274.1	1273.3	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1	1275.4
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	17.2	17.1	16.8	17.2	17.0	16.7	17.5
90°	25.3	26.1	26.7	27.1	27.5	28.0	28.4
92.5°	28.3	29.6	30.4	30.6	30.9	31.2	31.4
95°	33.7	35.3	36.0	36.0	36.0	36.0	36.0
97.5°	35.5	37.2	38.2	38.4	38.5	38.8	39.0
100°	36.3	38.0	38.9	39.1	39.3	39.6	39.8
102.5°	46.7	41.4	39.0	39.4	39.8	40.2	40.5
105°	95.6	58.3	40.0	40.4	40.8	41.2	41.7
107.5°	298.1	270.8	243.1	215.0	187.0	158.9	130.8
110°	406.1	399.2	380.7	350.6	320.5	290.4	260.3



TEST NUMBER: P332162-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	475.0	475.1	472.0	465.7	459.4	453.0	446.7
115°	549.7	551.9	553.3	554.1	555.0	555.8	556.7
117.5°	615.1	616.8	617.7	617.8	618.0	618.2	618.4
120°	658.3	660.0	660.8	660.8	660.8	660.8	660.8
122.5°	699.9	701.1	701.8	701.9	702.1	702.3	702.5
125°	758.7	759.0	759.5	759.9	760.3	760.7	761.1
127.5°	818.4	819.2	819.3	818.8	818.4	818.0	817.6
130°	854.5	855.4	855.6	855.2	854.8	854.3	853.9
132.5°	888.6	889.5	889.6	889.0	888.4	887.9	887.2
135°	940.1	940.7	940.7	940.1	939.4	938.8	938.2
137.5°	986.5	987.5	987.8	987.3	986.9	986.5	986.1
140°	1015.5	1016.3	1016.5	1016.2	1015.7	1015.3	1014.8
142.5°	1043.0	1043.7	1043.7	1043.1	1042.5	1042.0	1041.3
145°	1081.5	1081.9	1082.0	1082.0	1082.0	1082.0	1082.0
147.5°	1116.1	1116.5	1116.3	1115.3	1114.3	1113.3	1112.4
150°	1137.3	1137.7	1137.6	1137.0	1136.3	1135.8	1135.1
152.5°	1156.5	1157.3	1157.2	1156.1	1155.2	1154.2	1153.3
155°	1182.7	1183.8	1183.6	1182.4	1181.2	1179.9	1178.6
157.5°	1205.5	1206.7	1206.5	1204.9	1203.3	1201.6	1200.0
160°	1218.4	1219.7	1219.6	1218.0	1216.6	1215.1	1213.6
162.5°	1230.3	1231.7	1231.7	1230.5	1229.2	1227.9	1226.5
165°	1246.1	1247.8	1247.9	1246.5	1245.0	1243.5	1242.1
167.5°	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2
170°	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1
172.5°	1269.6	1271.3	1271.2	1269.4	1267.5	1265.6	1263.9
175°	1274.9	1276.4	1276.3	1274.6	1272.9	1271.2	1269.5
177.5°	1276.8	1278.1	1278.0	1276.3	1274.6	1272.9	1271.2
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2

(END OF REPORT)