

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331816-840

Luminaire Tested: **S122RDIW-S675D970U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331816-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D970U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5737.0 lumens  
Efficiency: N/A  
Efficacy: 109.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	1.9
10°-20°	292.8	5.1
20°-30°	411.1	7.2
30°-40°	448.3	7.8
40°-50°	412.2	7.2
50°-60°	323.8	5.6
60°-70°	211.1	3.7
70°-80°	108.8	1.9
80°-90°	33.1	0.6
90°-100°	76.8	1.3
100°-110°	238.5	4.2
110°-120°	407.7	7.1
120°-130°	536.2	9.3
130°-140°	601.8	10.5
140°-150°	590.1	10.3
150°-160°	494.9	8.6
160°-170°	328.3	5.7
170°-180°	114.7	2.0
0°-30°	810.5	14.1
0°-40°	1258.9	21.9
0°-60°	1994.8	34.8
0°-90°	2347.8	40.9
90°-120°	723.1	12.6
90°-150°	2451.2	42.7
90°-180°	3389.0	59.1
0°-180°	5737.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	14	36	34	35	5
95°	53	63	65	65	63	61
105°	220	223	225	227	227	232
115°	409	415	413	412	409	405
125°	595	604	602	598	597	532
135°	770	781	784	782	779	595
145°	935	942	948	949	945	584
155°	1069	1072	1075	1080	1077	492
165°	1163	1162	1162	1168	1164	328
175°	1210	1207	1205	1211	1206	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.4	12.5	11.5	10.6	9.7	9.8	10.8	11.7	12.7	13.7	13.5
90°	1.0	3.7	6.5	9.2	11.9	15.8	20.8	25.8	30.8	35.7	35.3
92.5°	18.2	20.2	22.2	24.2	26.3	27.8	29.0	30.2	31.3	32.5	32.6
95°	53.2	55.4	57.8	60.0	62.3	63.6	64.1	64.5	65.0	65.4	65.4
97.5°	97.1	99.2	101.2	103.2	105.1	106.6	107.4	108.4	109.2	110.1	110.1
100°	129.9	131.7	133.5	135.3	137.1	138.5	139.1	139.8	140.5	141.2	141.2
102.5°	164.3	165.7	167.1	168.6	170.1	171.3	172.1	173.0	173.8	174.7	174.9
105°	219.9	220.6	221.3	222.0	222.7	223.2	223.7	224.1	224.6	225.0	225.5
107.5°	276.0	277.0	277.9	278.9	279.9	280.4	280.4	280.4	280.4	280.4	280.6
110°	311.9	313.4	314.7	316.1	317.4	318.1	318.1	318.1	318.1	318.1	318.1



TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.2	352.6	354.0	355.4	356.7	357.3	357.1	356.9	356.8	356.6	356.0
115°	409.1	410.5	411.8	413.2	414.5	415.1	414.5	414.1	413.6	413.2	413.0
117.5°	466.9	468.7	470.5	472.3	474.1	474.3	473.1	471.8	470.6	469.3	468.8
120°	505.3	507.2	509.0	510.8	512.6	512.6	510.8	509.0	507.2	505.3	505.3
122.5°	540.5	542.7	544.8	547.0	549.2	549.7	548.4	547.1	545.8	544.5	544.0
125°	595.3	597.3	599.4	601.5	603.5	604.2	603.5	602.8	602.1	601.5	600.8
127.5°	648.7	651.3	653.9	656.5	659.0	659.9	659.1	658.3	657.5	656.7	655.8
130°	682.3	685.2	688.1	691.2	694.1	695.3	694.9	694.4	694.0	693.5	693.1
132.5°	719.8	722.3	724.7	727.1	729.5	730.7	730.8	730.9	731.0	731.1	730.1
135°	770.2	772.7	775.2	777.7	780.2	781.6	782.1	782.5	783.0	783.5	783.3
137.5°	823.1	825.3	827.3	829.3	831.3	832.7	833.2	833.8	834.5	835.1	834.9
140°	855.1	857.2	859.2	861.2	863.2	864.8	866.1	867.2	868.3	869.4	869.4
142.5°	887.9	889.9	891.9	893.9	896.1	897.5	898.2	899.0	899.8	900.5	900.7
145°	934.8	936.4	938.1	939.7	941.3	942.7	944.1	945.4	946.8	948.2	948.4
147.5°	976.8	978.8	980.7	982.5	984.4	985.8	986.7	987.6	988.6	989.5	990.0
150°	1005.4	1006.8	1008.1	1009.6	1010.9	1012.1	1013.0	1013.9	1014.8	1015.7	1016.3
152.5°	1030.9	1032.2	1033.6	1034.9	1036.3	1037.5	1038.6	1039.7	1040.8	1041.9	1042.7
155°	1068.8	1069.5	1070.3	1071.0	1071.6	1072.3	1073.0	1073.7	1074.3	1075.0	1076.1
157.5°	1101.4	1101.9	1102.3	1102.8	1103.2	1103.7	1104.1	1104.5	1104.9	1105.3	1106.8
160°	1121.1	1121.5	1122.0	1122.4	1122.9	1123.2	1123.5	1123.7	1123.9	1124.1	1125.5
162.5°	1139.0	1139.1	1139.2	1139.3	1139.4	1139.5	1139.8	1140.0	1140.2	1140.4	1142.1
165°	1163.0	1162.8	1162.6	1162.3	1162.1	1162.0	1162.0	1162.0	1162.0	1162.0	1163.6
167.5°	1183.1	1182.3	1181.6	1180.9	1180.3	1179.9	1179.9	1179.8	1179.8	1179.7	1181.3
170°	1193.7	1193.0	1192.3	1191.6	1190.9	1190.5	1190.2	1190.0	1189.8	1189.6	1191.1
172.5°	1201.0	1200.3	1199.6	1199.0	1198.3	1197.8	1197.6	1197.4	1197.2	1196.9	1198.5
175°	1210.0	1209.3	1208.7	1208.0	1207.3	1206.7	1206.3	1205.8	1205.4	1204.9	1206.5
177.5°	1213.8	1213.2	1212.6	1212.0	1211.5	1211.0	1210.7	1210.3	1210.0	1209.6	1210.7
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0



TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	13.2	12.9	12.6	12.5	12.6	12.6	12.7	12.7
90°	34.8	34.4	33.9	33.8	34.1	34.3	34.5	34.7
92.5°	32.7	32.8	32.9	32.9	33.0	33.0	33.1	33.1
95°	65.4	65.4	65.4	65.2	64.7	64.3	63.8	63.4
97.5°	110.1	110.1	110.1	110.1	110.0	110.0	109.9	109.9
100°	141.2	141.2	141.2	141.1	140.8	140.6	140.4	140.2
102.5°	175.1	175.2	175.4	175.4	175.2	174.9	174.7	174.5
105°	225.9	226.4	226.8	227.1	227.1	227.1	227.1	227.1
107.5°	280.8	281.0	281.1	280.7	279.7	278.6	277.6	276.6
110°	318.1	318.1	318.1	317.8	317.1	316.4	315.7	315.1





TEST NUMBER: P331816-840

CATALOG NUMBER: S122RDIW-S675D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.5	355.0	354.4	353.9	353.4	352.8	352.3	351.8
115°	412.7	412.5	412.3	411.8	411.2	410.5	409.8	409.1
117.5°	468.2	467.7	467.1	466.5	465.9	465.1	464.4	463.7
120°	505.3	505.3	505.3	504.9	504.2	503.6	502.9	502.2
122.5°	543.5	542.9	542.4	541.9	541.4	540.9	540.4	539.9
125°	600.1	599.4	598.7	598.2	598.0	597.8	597.5	597.3
127.5°	655.0	654.2	653.4	652.6	651.9	651.2	650.5	649.7
130°	692.6	692.2	691.7	690.9	690.0	689.1	688.2	687.3
132.5°	729.1	728.1	727.1	726.3	725.6	724.8	724.1	723.4
135°	783.0	782.8	782.5	782.1	781.4	780.7	780.1	779.4
137.5°	834.7	834.6	834.4	833.7	832.8	831.9	831.0	830.1
140°	869.4	869.4	869.4	869.0	868.1	867.2	866.3	865.4
142.5°	900.9	901.1	901.2	900.9	900.0	899.1	898.2	897.3
145°	948.7	948.9	949.1	948.8	947.9	947.0	946.0	945.1
147.5°	990.5	991.0	991.5	991.3	990.5	989.6	988.8	987.8
150°	1017.0	1017.7	1018.4	1018.4	1017.7	1017.0	1016.3	1015.7
152.5°	1043.6	1044.5	1045.3	1045.3	1044.5	1043.6	1042.7	1041.9
155°	1077.3	1078.4	1079.5	1079.7	1079.1	1078.4	1077.7	1077.0
157.5°	1108.4	1109.9	1111.5	1111.7	1110.6	1109.5	1108.4	1107.3
160°	1126.8	1128.2	1129.5	1129.8	1128.9	1128.0	1127.1	1126.2
162.5°	1143.6	1145.1	1146.7	1146.9	1145.8	1144.7	1143.6	1142.6
165°	1165.2	1166.7	1168.3	1168.5	1167.4	1166.3	1165.2	1164.0
167.5°	1183.0	1184.6	1186.1	1186.3	1185.2	1184.0	1182.8	1181.6
170°	1192.8	1194.4	1196.0	1196.1	1194.7	1193.4	1191.9	1190.6
172.5°	1200.1	1201.7	1203.3	1203.5	1202.0	1200.7	1199.3	1198.0
175°	1208.1	1209.7	1211.2	1211.4	1210.0	1208.7	1207.3	1206.0
177.5°	1211.8	1212.8	1214.0	1214.0	1212.8	1211.8	1210.7	1209.6
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0

(END OF REPORT)