

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331840-840

Luminaire Tested: **S122RDIW-S865D1240U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331840-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1240U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7390.5 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20
6	63	51	43	37	57	47	40	35	39	34	30	32	28	26	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23909	23909	23909
5°	24000	23608	23738
10°	23815	23222	23023
15°	23542	22534	21884
20°	23163	21551	20469
25°	22775	20436	19099
30°	22236	19287	17339
35°	21711	18039	15794
40°	21182	16750	14010
45°	20562	15299	12392
50°	19926	13835	10803
55°	19277	12262	9278
60°	18519	10601	7702
65°	17662	8909	7014
70°	16636	7336	6449
75°	15384	6687	6014
80°	13575	5979	5486
85°	10689	4705	4705



TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	1.9
10°-20°	380.6	5.1
20°-30°	534.4	7.2
30°-40°	582.7	7.9
40°-50°	535.8	7.3
50°-60°	420.8	5.7
60°-70°	274.4	3.7
70°-80°	141.5	1.9
80°-90°	42.9	0.6
90°-100°	98.3	1.3
100°-110°	305.4	4.1
110°-120°	522.0	7.1
120°-130°	686.4	9.3
130°-140°	770.4	10.4
140°-150°	755.4	10.2
150°-160°	633.6	8.6
160°-170°	420.3	5.7
170°-180°	146.9	2.0
0°-30°	1053.6	14.3
0°-40°	1636.3	22.1
0°-60°	2593.0	35.1
0°-90°	3051.7	41.3
90°-120°	925.7	12.5
90°-150°	3138.0	42.5
90°-180°	4339.0	58.7
0°-180°	7390.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1481	1481	1481	1481	1481	
5°	1481	1473	1457	1468	1465	140
15°	1408	1392	1348	1323	1309	397
25°	1278	1233	1147	1094	1072	588
35°	1102	1030	915	834	801	689
45°	900	808	670	578	543	695
55°	685	578	436	358	330	612
65°	462	353	233	190	184	458
75°	247	155	107	98	96	261
85°	58	31	25	25	25	68
90°	1	18	46	43	44	6
95°	68	81	84	84	81	78
105°	282	285	288	291	291	297
115°	524	531	529	528	524	518
125°	762	773	770	766	765	681
135°	986	1000	1003	1002	998	761
145°	1197	1206	1214	1215	1210	747
155°	1368	1372	1376	1382	1379	630
165°	1489	1488	1488	1496	1490	420
175°	1549	1545	1542	1551	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1486.1	1484.9	1483.7	1482.5	1481.4	1479.5	1476.8	1474.2	1471.6	1468.9	1471.4
5°	1480.8	1479.3	1477.7	1476.2	1474.8	1472.1	1468.2	1464.4	1460.5	1456.6	1459.3
7.5°	1465.4	1463.6	1461.8	1460.0	1458.0	1454.9	1450.4	1445.8	1441.3	1436.7	1437.5
10°	1452.6	1450.5	1448.4	1446.3	1444.2	1440.3	1434.3	1428.4	1422.4	1416.4	1415.5
12.5°	1436.5	1433.9	1431.4	1428.9	1426.2	1421.2	1413.5	1405.9	1398.3	1390.7	1389.1
15°	1408.4	1405.1	1401.8	1398.6	1395.2	1388.6	1378.5	1368.4	1358.2	1348.1	1342.4
17.5°	1373.8	1368.8	1363.8	1358.8	1353.8	1344.8	1331.8	1318.8	1305.9	1292.8	1286.2
20°	1348.1	1342.1	1336.2	1330.2	1324.2	1313.8	1298.9	1284.0	1269.2	1254.3	1246.8
22.5°	1320.2	1313.5	1306.9	1300.2	1293.5	1281.8	1265.0	1248.2	1231.4	1214.6	1205.0
25°	1278.4	1268.9	1259.3	1249.8	1240.3	1225.7	1206.0	1186.4	1166.7	1147.1	1134.9
27.5°	1228.0	1217.6	1207.3	1196.9	1186.6	1170.3	1148.1	1126.0	1103.8	1081.7	1067.4
30°	1192.7	1181.3	1170.0	1158.7	1147.4	1129.8	1106.0	1082.2	1058.3	1034.5	1019.4
32.5°	1158.3	1145.1	1131.9	1118.6	1105.4	1086.7	1062.4	1038.0	1013.8	989.5	972.2
35°	1101.5	1086.3	1071.2	1055.9	1040.8	1020.1	993.8	967.7	941.5	915.2	896.5
37.5°	1044.7	1028.0	1011.4	994.6	978.0	955.6	927.8	899.8	871.9	843.9	823.2
40°	1005.0	987.1	969.3	951.4	933.5	910.2	881.3	852.4	823.5	794.7	773.5
42.5°	964.3	945.4	926.7	907.9	889.0	864.6	834.9	805.0	775.2	745.3	723.5
45°	900.5	880.5	860.6	840.6	820.7	795.1	763.9	732.6	701.3	670.0	648.8
47.5°	838.3	817.2	796.1	774.9	753.8	727.0	694.8	662.5	630.2	597.9	576.9
50°	793.3	772.1	751.0	729.8	708.7	681.8	649.0	616.2	583.5	550.8	530.2
52.5°	749.3	727.2	705.2	683.1	661.0	633.9	601.9	569.8	537.8	505.7	485.8
55°	684.8	661.6	638.3	615.1	591.9	564.1	532.0	499.8	467.7	435.6	417.7
57.5°	618.5	594.7	570.9	547.0	523.3	495.9	464.9	434.0	403.1	372.2	355.9
60°	573.5	549.7	525.9	502.1	478.3	451.0	420.3	389.6	359.0	328.3	313.2
62.5°	529.6	505.7	481.9	458.1	434.2	407.8	378.5	349.3	320.0	290.7	276.3
65°	462.3	438.2	414.0	389.9	365.9	340.3	313.6	286.8	259.9	233.2	223.1
67.5°	397.5	373.5	349.6	325.6	301.6	277.6	253.6	229.4	205.3	181.2	176.5
70°	352.4	329.2	306.0	282.8	259.5	237.6	217.1	196.5	176.0	155.4	152.5
72.5°	309.5	287.3	265.0	242.8	220.5	201.1	184.6	168.0	151.6	135.1	132.6
75°	246.6	225.7	204.9	184.0	163.2	147.7	137.5	127.4	117.3	107.2	105.1
77.5°	184.7	166.3	148.0	129.8	111.5	100.0	95.0	90.2	85.3	80.4	79.2
80°	146.0	130.9	115.7	100.5	85.3	76.2	73.2	70.3	67.3	64.3	63.1
82.5°	110.7	98.9	86.9	75.1	63.3	56.4	54.3	52.3	50.3	48.3	47.6
85°	57.7	51.4	45.1	38.9	32.6	29.1	28.2	27.3	26.4	25.4	25.4
87.5°	17.4	16.2	15.0	13.8	12.6	12.6	13.9	15.1	16.5	17.8	17.4
90°	1.3	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2
92.5°	23.3	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7
95°	68.1	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8
97.5°	124.4	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9
100°	166.3	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7
102.5°	210.3	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9
105°	281.6	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6
107.5°	353.3	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3
110°	399.4	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	449.7	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8
115°	523.8	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8
117.5°	597.6	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1
120°	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8
122.5°	691.9	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4
125°	762.0	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1
127.5°	830.4	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6
130°	873.4	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2
132.5°	921.6	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7
135°	986.0	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7
137.5°	1053.8	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8
140°	1094.7	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0
142.5°	1136.6	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1
145°	1196.8	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2
147.5°	1250.5	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4
150°	1287.2	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1
152.5°	1319.7	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9
155°	1368.4	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7
157.5°	1410.0	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9
160°	1435.1	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8
162.5°	1458.1	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0
165°	1488.8	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6
167.5°	1514.5	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4
170°	1528.1	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9
172.5°	1537.5	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4
175°	1549.0	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6
177.5°	1553.8	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1473.7	1476.1	1478.4	1479.5	1478.9	1478.4	1478.0	1477.5
5°	1462.0	1464.6	1467.3	1468.2	1467.3	1466.4	1465.5	1464.6
7.5°	1438.4	1439.1	1439.9	1439.5	1437.9	1436.4	1434.8	1433.3
10°	1414.6	1413.7	1412.8	1411.5	1409.7	1408.0	1406.1	1404.3
12.5°	1387.5	1385.8	1384.2	1382.0	1379.0	1376.0	1373.0	1370.1
15°	1336.8	1331.1	1325.4	1321.1	1318.2	1315.1	1312.2	1309.2
17.5°	1279.4	1272.6	1266.0	1260.0	1254.9	1249.8	1244.7	1239.5
20°	1239.4	1231.9	1224.5	1217.5	1210.9	1204.4	1197.8	1191.3
22.5°	1195.5	1185.9	1176.3	1169.0	1164.2	1159.2	1154.4	1149.5
25°	1122.7	1110.4	1098.2	1089.8	1085.4	1081.0	1076.5	1072.1
27.5°	1053.2	1038.9	1024.7	1014.1	1007.0	999.9	992.8	985.7
30°	1004.1	989.0	973.7	962.1	954.1	946.0	938.1	930.0
32.5°	954.8	937.5	920.2	907.7	900.2	892.6	885.0	877.5
35°	877.7	859.0	840.2	827.6	821.0	814.5	807.9	801.3
37.5°	802.6	781.9	761.3	747.2	739.7	732.2	724.7	717.2
40°	752.3	731.2	710.0	695.6	687.9	680.1	672.4	664.7
42.5°	701.7	679.7	657.9	643.2	635.7	628.2	620.7	613.2
45°	627.7	606.6	585.4	571.3	564.1	557.0	549.9	542.7
47.5°	555.8	534.8	513.8	500.1	493.6	487.1	480.6	474.1
50°	509.7	489.1	468.6	455.1	448.9	442.6	436.4	430.1
52.5°	466.1	446.3	426.4	413.6	407.8	402.0	396.3	390.5
55°	399.8	381.9	364.1	352.2	346.6	340.9	335.3	329.6
57.5°	339.5	323.2	306.8	296.2	291.4	286.6	281.9	277.1
60°	297.9	282.8	267.5	257.6	252.8	248.0	243.3	238.5
62.5°	261.9	247.4	232.9	224.2	221.4	218.5	215.6	212.8
65°	212.9	202.8	192.7	187.1	186.2	185.4	184.5	183.6
67.5°	171.9	167.2	162.6	159.8	158.9	157.8	156.9	156.0
70°	149.5	146.5	143.5	141.5	140.3	139.1	137.8	136.6
72.5°	130.1	127.5	125.0	123.5	122.7	122.0	121.3	120.6
75°	103.0	101.0	98.9	97.7	97.4	97.0	96.7	96.4
77.5°	78.1	76.9	75.6	74.8	74.3	73.8	73.4	72.9
80°	61.9	60.8	59.6	59.0	59.0	59.0	59.0	59.0
82.5°	46.9	46.0	45.3	45.0	45.0	45.0	45.0	45.0
85°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
87.5°	17.1	16.7	16.4	16.2	16.3	16.3	16.4	16.4
90°	44.6	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	41.9	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.1	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.2	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.5	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331840-840

CATALOG NUMBER: S122RDIW-S865D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	455.0	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.5	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	599.4	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.8	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	768.2	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	838.6	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.7	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	933.4	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.5	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.5	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.3	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.5	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.0	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1379.2	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1419.0	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1442.6	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1464.0	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1491.6	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1514.4	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1526.9	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1536.4	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1546.6	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)