

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332160-830

Luminaire Tested: **S123DIW-S775D755U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332160-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D755U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5836.2 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	50	49	48	43				
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	36				
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30				
4	74	64	56	49	68	59	52	47	50	45	41	43	38	35	35	32	30	26				
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20				
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	30	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	1.9
10°-20°	305.3	5.2
20°-30°	451.0	7.7
30°-40°	526.8	9.0
40°-50°	529.6	9.1
50°-60°	465.2	8.0
60°-70°	346.6	5.9
70°-80°	197.5	3.4
80°-90°	59.3	1.0
90°-100°	33.9	0.6
100°-110°	161.8	2.8
110°-120°	388.6	6.7
120°-130°	494.8	8.5
130°-140°	528.7	9.1
140°-150°	494.4	8.5
150°-160°	398.8	6.8
160°-170°	257.4	4.4
170°-180°	88.7	1.5
0°-30°	864.4	14.8
0°-40°	1391.1	23.8
0°-60°	2385.9	40.9
0°-90°	2989.3	51.2
90°-120°	584.3	10.0
90°-150°	2102.1	36.0
90°-180°	2847.0	48.8
0°-180°	5836.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	8	17	19	21	5
95°	42	16	22	26	26	52
105°	207	210	152	36	30	219
115°	388	392	398	405	408	383
125°	547	552	555	556	558	488
135°	680	684	687	689	687	524
145°	785	790	791	793	793	491
155°	865	864	864	867	864	398
165°	912	910	909	914	910	258
175°	934	930	931	935	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.6	20.5	20.3	20.0	19.8	19.8	20.0	20.3	20.5	20.7	20.6
90°	0.7	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2
92.5°	12.9	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8
95°	42.3	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6
97.5°	85.0	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6
100°	117.3	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1
102.5°	153.8	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8
105°	206.7	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6
107.5°	262.4	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4
110°	299.6	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7



TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	335.2	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9
115°	387.7	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6
117.5°	438.7	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2
120°	470.2	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8
122.5°	502.5	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0
125°	546.6	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2
127.5°	589.3	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6
130°	615.9	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8
132.5°	641.4	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8
135°	680.4	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8
137.5°	713.7	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2
140°	735.8	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7
142.5°	756.4	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2
145°	785.1	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6
147.5°	812.2	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1
150°	828.9	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6
152.5°	843.8	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1
155°	864.9	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0
157.5°	881.3	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4
160°	891.3	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8
162.5°	900.7	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3
165°	912.1	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5
167.5°	921.0	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4
170°	926.0	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4
172.5°	929.3	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7
175°	933.6	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9
177.5°	934.6	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	20.6	20.5	20.5	20.5	20.5	20.6	20.6	20.7
90°	17.9	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	19.7	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	23.7	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	24.8	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	25.4	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	38.0	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	97.4	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	238.4	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	302.7	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332160-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	348.0	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	401.2	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	449.4	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	481.1	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	511.9	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.4	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.2	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	625.5	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	650.4	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.0	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.4	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	763.6	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.0	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.4	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	832.9	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	846.7	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	865.7	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	882.3	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	891.7	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	900.3	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	911.7	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	929.0	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	932.9	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	934.4	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)