

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331830-840

Luminaire Tested: **S122RDIW-S865D710U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331830-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D710U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5819.3 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43
3	85	76	69	63	79	71	65	60	62	58	54	54	50	48	46	44	42	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	33
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31136	31136	31136	31136
5°	34775	31331	27780	31331
10°	38581	31111	24079	31111
15°	40478	30654	18974	30654
20°	35093	29979	16417	29979
25°	23013	29054	14658	29054
30°	15491	27932	13267	27932
35°	12546	26518	11964	26518
40°	11158	24982	11072	24982
45°	10097	23178	9882	23178
50°	9191	21391	9156	21391
55°	8639	19409	8526	19409
60°	7227	17589	7143	17589
65°	6094	15973	6911	15973
70°	5632	14266	6515	14266
75°	5265	12414	6014	12414
80°	4863	10219	5365	10219
85°	4465	8058	4705	8058



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.8	3.1
10°-20°	509.4	8.8
20°-30°	656.4	11.3
30°-40°	623.8	10.7
40°-50°	534.4	9.2
50°-60°	406.9	7.0
60°-70°	257.2	4.4
70°-80°	128.5	2.2
80°-90°	37.0	0.6
90°-100°	56.3	1.0
100°-110°	174.8	3.0
110°-120°	298.7	5.1
120°-130°	392.8	6.8
130°-140°	440.9	7.6
140°-150°	432.3	7.4
150°-160°	362.6	6.2
160°-170°	240.5	4.1
170°-180°	84.1	1.4
0°-30°	1348.5	23.2
0°-40°	1972.3	33.9
0°-60°	2913.6	50.1
0°-90°	3336.3	57.3
90°-120°	529.8	9.1
90°-150°	1795.8	30.9
90°-180°	2483.0	42.7
0°-180°	5819.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1928	1928	1928	1928	1928	
5°	2146	1933	1714	1933	2146	212
15°	2422	1834	1135	1834	2422	653
25°	1292	1631	823	1631	1292	613
35°	636	1345	607	1345	636	407
45°	442	1015	433	1015	442	342
55°	307	690	303	690	307	269
65°	160	418	181	418	160	162
75°	84	199	96	199	84	90
85°	24	44	25	44	24	27
90°	25	1	25	1	25	12
95°	46	39	46	39	46	52
105°	166	161	166	161	166	175
115°	300	300	300	300	300	296
125°	438	436	438	436	438	390
135°	571	564	571	564	571	440
145°	692	685	692	685	692	432
155°	789	783	789	783	789	363
165°	853	852	853	852	853	241
175°	884	886	884	886	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	2006.7	2008.3	2009.9	2006.1	2006.1	2003.0	1996.0	1990.6	1975.6	1973.5	1973.5
5°	2145.6	2144.1	2146.9	2138.2	2126.1	2123.4	2110.7	2094.0	2076.5	2057.1	2053.1
7.5°	2283.5	2281.5	2276.1	2274.7	2265.4	2245.2	2224.7	2202.9	2173.9	2145.7	2131.4
10°	2353.2	2375.3	2362.0	2338.4	2343.2	2311.7	2294.9	2266.1	2242.0	2199.8	2190.4
12.5°	2421.9	2430.5	2426.3	2413.0	2407.0	2385.1	2362.5	2337.4	2292.9	2255.0	2222.0
15°	2421.6	2434.3	2437.6	2433.7	2437.0	2435.7	2423.6	2402.8	2364.0	2322.4	2286.2
17.5°	2242.8	2251.7	2273.6	2288.5	2307.2	2346.9	2366.5	2374.1	2368.3	2344.6	2319.2
20°	2042.4	2027.6	2089.2	2120.7	2147.5	2214.5	2272.2	2294.3	2329.8	2329.2	2322.4
22.5°	1758.2	1761.7	1820.2	1857.5	1935.8	2002.8	2068.5	2151.7	2220.4	2265.8	2292.4
25°	1291.8	1317.4	1375.6	1426.5	1513.7	1638.3	1751.5	1882.9	2006.8	2104.7	2197.8
27.5°	970.3	972.1	1018.3	1065.4	1117.1	1219.2	1361.8	1518.6	1695.4	1841.2	2008.9
30°	830.9	826.9	846.3	875.0	919.3	998.4	1105.6	1259.7	1435.9	1655.7	1851.4
32.5°	732.3	732.5	747.1	768.4	805.2	858.5	931.9	1057.1	1223.7	1439.7	1669.1
35°	636.5	635.9	646.6	662.0	677.4	711.6	761.8	827.5	942.1	1143.8	1378.3
37.5°	567.9	570.9	576.1	585.7	602.8	621.8	652.0	696.1	777.7	897.0	1094.1
40°	529.4	530.7	538.1	546.1	556.1	570.9	595.7	631.2	690.8	786.0	930.0
42.5°	493.9	495.3	500.5	508.1	515.9	530.7	551.2	581.9	630.3	704.5	823.3
45°	442.2	442.2	447.0	450.3	459.0	472.4	489.2	514.6	548.1	603.1	682.2
47.5°	393.7	393.8	397.0	402.7	408.2	418.7	435.2	456.0	480.3	522.8	590.4
50°	365.9	366.5	368.5	373.2	376.6	386.0	398.7	416.8	442.2	475.0	531.4
52.5°	343.4	343.0	345.5	347.5	349.8	356.5	366.0	381.9	404.8	433.2	479.9
55°	306.9	304.2	308.2	311.5	313.6	316.3	321.6	331.6	351.1	375.3	410.1
57.5°	261.4	260.2	263.1	266.1	272.5	279.6	284.3	290.6	300.7	318.0	352.5
60°	223.8	223.8	229.8	231.9	239.2	248.6	258.0	263.4	273.4	284.8	310.2
62.5°	190.6	191.1	193.9	195.9	200.1	211.6	224.7	236.5	246.0	256.9	273.8
65°	159.5	160.8	160.8	162.2	164.8	167.5	172.9	182.3	199.0	214.4	227.1
67.5°	135.3	135.7	136.1	137.5	138.1	141.1	143.3	147.4	151.3	165.9	181.7
70°	119.3	121.3	120.6	122.0	122.6	123.9	126.6	128.7	134.7	138.0	147.4
72.5°	104.2	105.7	105.6	106.4	108.2	108.5	110.6	112.6	116.4	119.3	124.3
75°	84.4	83.7	84.4	85.7	86.4	87.2	87.2	89.8	91.8	94.5	97.9
77.5°	65.1	65.8	65.6	65.8	65.9	67.2	67.1	68.2	70.2	71.6	73.2
80°	52.3	52.9	52.3	52.9	53.6	54.2	53.6	54.2	56.2	57.7	57.7
82.5°	40.5	40.6	41.0	41.1	41.3	41.4	42.3	42.5	43.9	43.7	44.2
85°	24.1	23.4	23.4	23.4	24.1	24.7	24.1	24.1	24.7	24.7	24.7
87.5°	13.6	14.1	14.1	14.1	14.0	14.1	14.1	14.7	14.3	14.8	13.6
90°	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5	25.9	26.3	22.5
92.5°	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9	23.9	23.8	22.9
95°	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0	48.0	48.0	47.7
97.5°	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.0
100°	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4	103.4	103.4	102.9
102.5°	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3	128.2	127.9	127.3
105°	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5	165.2	164.9	164.5
107.5°	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7	205.6	205.5	205.5
110°	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4	260.8	261.3	261.4
115°	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5	302.6	302.8	303.1
117.5°	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1	343.5	343.9	344.8
120°	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2	370.2	370.2	371.5
122.5°	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2	398.6	399.0	399.9
125°	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6	440.1	440.6	441.1
127.5°	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9	480.5	481.1	481.7
130°	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5	507.8	508.1	508.4
132.5°	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2	534.9	535.6	535.6
135°	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7	573.8	574.0	573.7
137.5°	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5	611.7	611.8	611.4
140°	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9	636.9	636.9	636.1
142.5°	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0	659.8	659.7	659.1
145°	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0	694.8	694.7	693.7
147.5°	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7	725.3	725.0	724.3
150°	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2	743.5
152.5°	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4	762.5
155°	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2	788.4	787.6	787.1
157.5°	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0	810.9	809.8	809.5
160°	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6	824.6	823.5	823.3
162.5°	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8	836.7	835.6	835.4
165°	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6	852.4	851.3	851.3
167.5°	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7	865.5	864.3	864.3
170°	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8	872.7	871.5	871.7
172.5°	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3	878.1	876.9	877.1
175°	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0	883.9	882.7	883.1
177.5°	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2	886.5
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1974.5	1970.2	1966.5	1956.8	1952.0	1941.3	1939.6	1939.1	1925.2	1911.8	1908.0
5°	2042.4	2031.6	2015.5	1996.8	1977.3	1957.2	1943.8	1933.1	1906.3	1880.9	1866.1
7.5°	2110.7	2087.6	2059.9	2024.4	1994.8	1961.6	1936.8	1914.7	1876.7	1840.3	1815.7
10°	2161.6	2124.0	2087.2	2038.3	2000.1	1962.6	1927.7	1897.6	1854.7	1806.4	1772.3
12.5°	2193.2	2151.9	2101.1	2053.4	2003.9	1956.1	1909.6	1870.8	1820.4	1770.6	1729.9
15°	2235.9	2191.7	2130.1	2061.7	1998.1	1935.8	1882.2	1833.9	1768.3	1708.6	1659.0
17.5°	2271.0	2210.1	2143.9	2064.9	1991.2	1912.0	1842.9	1781.3	1708.2	1636.3	1577.8
20°	2282.2	2221.9	2145.6	2066.5	1979.3	1886.2	1811.8	1744.8	1666.4	1588.0	1521.1
22.5°	2275.2	2228.4	2143.3	2048.7	1959.5	1862.1	1778.1	1700.3	1613.4	1533.4	1455.6
25°	2228.0	2211.8	2131.4	2028.2	1926.4	1813.2	1716.0	1630.9	1531.8	1446.0	1361.5
27.5°	2117.7	2152.3	2102.5	1992.6	1879.4	1758.0	1648.7	1551.9	1449.0	1352.4	1268.3
30°	2011.6	2091.2	2069.8	1967.9	1841.3	1722.0	1599.4	1498.2	1388.4	1289.2	1206.1
32.5°	1866.2	1997.9	2018.9	1933.7	1802.7	1671.6	1543.2	1442.5	1327.8	1223.2	1142.3
35°	1635.0	1831.9	1922.4	1868.1	1736.8	1595.4	1462.7	1345.4	1230.2	1127.0	1046.6
37.5°	1359.0	1627.3	1778.1	1781.9	1661.3	1514.3	1369.9	1253.4	1135.5	1034.2	947.2
40°	1179.9	1470.8	1667.1	1710.6	1608.8	1450.0	1303.9	1185.3	1070.1	970.9	871.1
42.5°	1019.2	1308.9	1550.2	1626.0	1545.0	1387.3	1240.7	1116.7	1004.7	910.9	808.9
45°	824.2	1077.4	1343.4	1478.8	1433.9	1287.9	1133.1	1015.1	909.9	828.9	731.0
47.5°	695.3	873.7	1131.1	1314.2	1313.4	1180.1	1027.8	914.9	817.3	741.3	662.2
50°	621.8	777.3	995.0	1202.7	1220.1	1108.2	963.5	851.6	760.5	680.8	617.1
52.5°	555.8	684.0	879.8	1078.9	1128.5	1031.6	891.2	787.9	699.4	626.1	571.6
55°	469.7	568.9	717.6	903.9	979.0	910.6	786.0	689.5	617.8	556.1	509.3
57.5°	397.4	471.7	591.1	741.0	828.5	785.5	682.7	604.3	542.9	487.2	450.1
60°	351.7	412.7	513.9	639.2	735.7	705.6	617.8	544.7	492.5	444.2	409.4
62.5°	308.9	361.3	448.0	549.7	638.1	625.7	554.0	492.7	447.0	402.9	373.4
65°	248.6	286.8	354.5	434.2	505.2	511.3	459.7	418.1	377.3	342.4	316.3
67.5°	197.9	222.9	270.5	337.7	390.9	409.9	378.4	346.7	314.3	287.3	264.7
70°	166.8	186.9	221.8	276.1	325.0	345.1	327.0	302.2	274.1	252.0	232.5
72.5°	135.2	154.8	180.5	220.4	262.3	284.0	277.7	259.8	237.0	218.7	200.4
75°	101.9	107.9	125.3	152.1	184.9	203.7	208.4	199.0	180.9	166.8	156.1
77.5°	75.3	79.0	87.3	101.3	122.8	139.5	146.3	145.2	132.8	124.6	114.6
80°	60.3	62.3	66.3	72.4	88.5	105.2	109.9	109.9	101.2	97.9	87.8
82.5°	45.8	47.3	49.7	53.0	60.6	75.1	80.4	81.5	75.9	71.6	63.6
85°	26.2	25.4	26.8	28.8	30.2	34.1	42.2	43.5	42.2	36.9	34.8
87.5°	12.9	12.7	11.9	10.9	11.0	11.1	13.4	15.7	13.9	12.7	12.1
90°	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7	2.7	4.7	6.8
92.5°	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3	14.8	16.3	17.8
95°	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0	40.6	42.3	43.9
97.5°	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2	72.6	74.1	75.5
100°	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1	96.5	97.9	99.2
102.5°	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4	121.4	122.5	123.5
105°	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1	161.6	162.1	162.6
107.5°	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2	202.9	203.7	204.4
110°	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5	229.5	230.6	231.6



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3	258.3	259.3	260.3
115°	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7	300.7	301.7	302.8
117.5°	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0	343.4	344.7	346.0
120°	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	371.5	372.8	374.2
122.5°	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0	397.6	399.2	400.7
125°	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2	437.7	439.1	440.6
127.5°	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2	477.2	479.1	480.9
130°	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8	502.0	504.1	506.3
132.5°	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5	529.2	531.0	532.7
135°	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3	566.1	567.9	569.8
137.5°	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1	604.6	606.1	607.6
140°	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5	627.9	629.4	631.0
142.5°	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5	652.0	653.5	655.0
145°	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9	686.1	687.2	688.4
147.5°	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7	717.0	718.4	719.8
150°	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6	737.6	738.6	739.6
152.5°	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2	756.2	757.2	758.2
155°	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0	783.6	784.1	784.6
157.5°	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9	807.3	807.6	807.9
160°	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3	821.6	821.9	822.3
162.5°	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5	834.6	834.7	834.7
165°	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0	851.8	851.7	851.5
167.5°	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8	866.3	865.8	865.3
170°	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5	874.0	873.5	873.0
172.5°	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9	879.4	878.9	878.4
175°	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5	886.1	885.6	885.0
177.5°	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2	888.8	888.4	888.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1901.1	1897.3	1890.4	1879.7	1873.2	1862.0	1854.4	1858.8	1859.8	1858.8	1857.6
5°	1850.0	1835.9	1816.5	1797.8	1780.3	1761.6	1750.8	1746.2	1736.8	1731.4	1728.8
7.5°	1788.3	1764.0	1736.5	1703.8	1676.1	1647.0	1632.1	1624.8	1605.6	1595.1	1586.0
10°	1742.1	1703.9	1676.5	1633.6	1607.5	1569.2	1543.2	1543.8	1517.6	1502.9	1492.2
12.5°	1691.2	1649.3	1603.6	1565.0	1528.6	1497.9	1466.5	1453.7	1426.0	1411.8	1382.8
15°	1606.8	1557.9	1509.6	1457.3	1420.5	1372.9	1327.4	1271.7	1226.9	1188.0	1177.3
17.5°	1514.6	1454.0	1405.6	1344.2	1281.1	1201.1	1148.3	1116.0	1088.9	1068.4	1053.2
20°	1451.4	1389.7	1338.1	1245.7	1160.5	1106.3	1067.4	1042.6	1014.5	992.4	980.3
22.5°	1384.8	1320.5	1250.2	1147.0	1080.7	1037.1	1002.5	974.0	954.9	937.7	926.7
25°	1290.5	1220.1	1104.3	1033.2	979.6	934.0	909.9	892.5	872.4	849.0	838.2
27.5°	1190.8	1078.9	995.7	942.9	891.7	862.1	840.4	814.4	796.4	785.9	774.7
30°	1116.3	1004.4	939.4	881.8	845.6	812.7	787.3	772.5	755.2	737.1	729.7
32.5°	1033.2	943.8	881.5	833.5	796.8	768.8	748.7	724.9	712.3	701.1	685.7
35°	930.0	862.3	805.4	766.6	731.7	708.9	685.5	671.4	648.6	639.2	633.2
37.5°	842.6	784.0	741.4	700.4	672.9	647.6	633.3	611.0	601.1	588.0	575.3
40°	793.3	735.7	694.9	661.4	630.6	611.8	593.7	575.6	560.9	554.8	539.4
42.5°	743.0	696.1	655.2	618.4	597.8	577.9	555.1	541.8	526.5	516.7	507.3
45°	673.4	631.9	597.0	566.8	544.1	523.3	508.6	486.5	477.8	458.3	450.3
47.5°	612.3	573.7	540.5	511.8	489.6	476.1	454.4	437.2	423.2	411.3	400.9
50°	568.9	536.7	504.5	479.1	459.0	439.6	417.5	408.7	387.3	381.2	375.3
52.5°	529.2	498.7	469.2	444.2	424.1	405.3	385.8	374.5	359.9	354.0	349.5
55°	473.7	444.2	416.1	393.9	373.9	354.5	342.4	328.3	321.6	316.9	311.5
57.5°	418.0	391.4	369.9	347.5	327.3	311.8	297.9	289.4	282.5	276.3	269.9
60°	382.6	357.1	337.7	316.9	296.2	283.5	272.7	262.7	254.6	245.2	242.6
62.5°	345.1	322.9	305.0	284.8	266.7	255.0	244.8	235.3	225.7	212.0	208.2
65°	293.5	276.1	257.3	240.5	224.5	213.1	198.3	187.6	183.6	182.3	181.6
67.5°	246.8	230.4	214.3	197.1	182.5	172.0	164.4	162.8	160.0	159.2	157.3
70°	215.7	200.4	184.3	168.1	154.1	152.1	149.5	146.7	143.4	142.1	140.7
72.5°	187.8	172.0	155.8	143.0	136.9	134.4	131.7	129.1	126.7	125.4	124.6
75°	144.1	129.4	118.6	113.9	110.6	108.6	104.5	102.5	101.2	99.2	98.5
77.5°	103.7	95.4	90.5	87.6	84.0	81.9	79.6	77.6	76.1	75.7	74.6
80°	79.1	75.0	71.7	67.7	66.3	63.6	63.0	61.0	61.6	59.7	59.7
82.5°	61.4	56.2	53.4	51.6	50.3	48.1	47.5	46.5	46.7	45.1	45.1
85°	31.5	30.2	28.8	27.5	27.5	25.4	26.2	25.4	25.4	24.1	23.4
87.5°	11.9	11.9	11.6	12.3	13.1	13.3	13.2	12.6	12.5	12.5	11.9
90°	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5	25.2	24.9	24.8
92.5°	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9	24.0	24.1	24.1
95°	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0	48.0	48.0	47.8
97.5°	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6	80.6	80.6	80.6
100°	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4	103.4	103.4	103.3
102.5°	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3	128.4	128.6	128.6
105°	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5	165.8	166.2	166.3
107.5°	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7	205.9	206.0	205.7
110°	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	232.8



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4	260.0	259.6	259.2
115°	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5	302.3	302.1	301.7
117.5°	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1	342.6	342.2	341.7
120°	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2	370.2	370.2	369.9
122.5°	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2	397.8	397.4	397.0
125°	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6	439.1	438.6	438.3
127.5°	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9	479.3	478.7	478.2
130°	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5	507.1	506.8	506.2
132.5°	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2	533.4	532.7	532.1
135°	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7	573.5	573.4	573.0
137.5°	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5	611.4	611.3	610.9
140°	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9	636.9	636.9	636.6
142.5°	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0	660.1	660.2	660.0
145°	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0	695.2	695.3	695.1
147.5°	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7	726.0	726.4	726.3
150°	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1	745.6	746.1	746.1
152.5°	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6	765.2	765.9	765.9
155°	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2	790.1	790.9	791.1
157.5°	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0	813.1	814.3	814.5
160°	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6	826.6	827.6	827.7
162.5°	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8	839.0	840.1	840.2
165°	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6	854.7	856.0	856.2
167.5°	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7	867.8	869.0	869.1
170°	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8	875.0	876.2	876.3
172.5°	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3	880.4	881.6	881.6
175°	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0	886.3	887.5	887.5
177.5°	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8	888.6	889.4	889.4
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1851.8	1852.8	1851.2	1852.3	1851.2	1852.8	1851.8	1857.6	1858.8	1859.8	1858.8
5°	1725.4	1717.4	1716.0	1714.0	1716.0	1717.4	1725.4	1728.8	1731.4	1736.8	1746.2
7.5°	1574.5	1573.3	1569.9	1565.3	1569.9	1573.3	1574.5	1586.0	1595.1	1605.6	1624.8
10°	1477.4	1474.1	1473.5	1468.7	1473.5	1474.1	1477.4	1492.2	1502.9	1517.6	1543.8
12.5°	1363.8	1342.2	1340.0	1328.3	1340.0	1342.2	1363.8	1382.8	1411.8	1426.0	1453.7
15°	1161.2	1157.2	1143.8	1135.1	1143.8	1157.2	1161.2	1177.3	1188.0	1226.9	1271.7
17.5°	1045.4	1032.3	1028.1	1026.2	1028.1	1032.3	1045.4	1053.2	1068.4	1088.9	1116.0
20°	970.9	958.9	956.8	955.5	956.8	958.9	970.9	980.3	992.4	1014.5	1042.6
22.5°	919.5	906.9	901.6	897.6	901.6	906.9	919.5	926.7	937.7	954.9	974.0
25°	831.5	826.9	824.2	822.8	824.2	826.9	831.5	838.2	849.0	872.4	892.5
27.5°	762.8	752.5	750.4	747.0	750.4	752.5	762.8	774.7	785.9	796.4	814.4
30°	723.7	720.3	715.6	711.6	715.6	720.3	723.7	729.7	737.1	755.2	772.5
32.5°	677.5	674.8	670.6	668.7	670.6	674.8	677.5	685.7	701.1	712.3	724.9
35°	626.5	617.1	613.1	607.0	613.1	617.1	626.5	633.2	639.2	648.6	671.4
37.5°	572.5	567.5	561.9	563.9	561.9	567.5	572.5	575.3	588.0	601.1	611.0
40°	530.7	527.4	526.0	525.3	526.0	527.4	530.7	539.4	554.8	560.9	575.6
42.5°	497.5	488.2	484.7	484.5	484.7	488.2	497.5	507.3	516.7	526.5	541.8
45°	447.0	438.2	432.2	432.8	432.2	438.2	447.0	450.3	458.3	477.8	486.5
47.5°	395.2	395.0	391.2	392.4	391.2	395.0	395.2	400.9	411.3	423.2	437.2
50°	370.5	366.5	363.9	364.5	363.9	366.5	370.5	375.3	381.2	387.3	408.7
52.5°	347.0	343.5	341.3	344.2	341.3	343.5	347.0	349.5	354.0	359.9	374.5
55°	308.2	304.2	303.6	302.9	303.6	304.2	308.2	311.5	316.9	321.6	328.3
57.5°	265.0	262.3	258.2	256.5	258.2	262.3	265.0	269.9	276.3	282.5	289.4
60°	233.9	228.5	221.8	221.2	221.8	228.5	233.9	242.6	245.2	254.6	262.7
62.5°	205.4	204.4	203.0	202.9	203.0	204.4	205.4	208.2	212.0	225.7	235.3
65°	180.3	179.6	180.3	180.9	180.3	179.6	180.3	181.6	182.3	183.6	187.6
67.5°	157.0	155.8	154.6	155.2	154.6	155.8	157.0	157.3	159.2	160.0	162.8
70°	139.4	138.7	138.0	138.0	138.0	138.7	139.4	140.7	142.1	143.4	146.7
72.5°	122.2	122.1	121.4	120.9	121.4	122.1	122.2	124.6	125.4	126.7	129.1
75°	97.9	96.4	96.4	96.4	96.4	96.4	97.9	98.5	99.2	101.2	102.5
77.5°	74.5	73.8	73.2	72.6	73.2	73.8	74.5	74.6	75.7	76.1	77.6
80°	59.0	58.3	57.7	57.7	57.7	58.3	59.0	59.7	59.7	61.6	61.0
82.5°	45.0	44.3	44.2	43.7	44.2	44.3	45.0	45.1	45.1	46.7	46.5
85°	24.1	24.7	24.1	25.4	24.1	24.7	24.1	23.4	24.1	25.4	25.4
87.5°	11.9	11.4	12.0	11.5	12.0	11.4	11.9	11.9	12.5	12.5	12.6
90°	24.9	25.1	25.3	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5
92.5°	24.1	24.2	24.2	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9
95°	47.5	47.2	46.8	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0
97.5°	80.6	80.6	80.5	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6
100°	103.2	103.0	102.8	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4
102.5°	128.4	128.2	128.1	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3
105°	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5
107.5°	204.9	204.2	203.4	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7
110°	232.3	231.8	231.3	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.5	258.1	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4
115°	301.2	300.7	300.2	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5
117.5°	341.2	340.7	340.2	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1
120°	369.4	368.9	368.4	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2
122.5°	396.6	396.3	395.9	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2
125°	438.2	438.0	437.8	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6
127.5°	477.6	477.1	476.6	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9
130°	505.5	504.9	504.2	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5
132.5°	531.6	531.0	530.5	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2
135°	572.5	572.0	571.5	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7
137.5°	610.2	609.6	608.8	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5
140°	636.0	635.3	634.6	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9
142.5°	659.3	658.6	658.0	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0
145°	694.4	693.8	693.1	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0
147.5°	725.7	725.0	724.4	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7
150°	745.6	745.1	744.7	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1
152.5°	765.2	764.6	764.0	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6
155°	790.6	790.1	789.6	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2
157.5°	813.6	812.8	812.0	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0
160°	827.1	826.4	825.8	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6
162.5°	839.4	838.7	837.9	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8
165°	855.3	854.4	853.6	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6
167.5°	868.3	867.4	866.6	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7
170°	875.3	874.2	873.2	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8
172.5°	880.7	879.7	878.7	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3
175°	886.5	885.6	884.5	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0
177.5°	888.6	887.8	887.0	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1854.4	1862.0	1873.2	1879.7	1890.4	1897.3	1901.1	1908.0	1911.8	1925.2	1939.1
5°	1750.8	1761.6	1780.3	1797.8	1816.5	1835.9	1850.0	1866.1	1880.9	1906.3	1933.1
7.5°	1632.1	1647.0	1676.1	1703.8	1736.5	1764.0	1788.3	1815.7	1840.3	1876.7	1914.7
10°	1543.2	1569.2	1607.5	1633.6	1676.5	1703.9	1742.1	1772.3	1806.4	1854.7	1897.6
12.5°	1466.5	1497.9	1528.6	1565.0	1603.6	1649.3	1691.2	1729.9	1770.6	1820.4	1870.8
15°	1327.4	1372.9	1420.5	1457.3	1509.6	1557.9	1606.8	1659.0	1708.6	1768.3	1833.9
17.5°	1148.3	1201.1	1281.1	1344.2	1405.6	1454.0	1514.6	1577.8	1636.3	1708.2	1781.3
20°	1067.4	1106.3	1160.5	1245.7	1338.1	1389.7	1451.4	1521.1	1588.0	1666.4	1744.8
22.5°	1002.5	1037.1	1080.7	1147.0	1250.2	1320.5	1384.8	1455.6	1533.4	1613.4	1700.3
25°	909.9	934.0	979.6	1033.2	1104.3	1220.1	1290.5	1361.5	1446.0	1531.8	1630.9
27.5°	840.4	862.1	891.7	942.9	995.7	1078.9	1190.8	1268.3	1352.4	1449.0	1551.9
30°	787.3	812.7	845.6	881.8	939.4	1004.4	1116.3	1206.1	1289.2	1388.4	1498.2
32.5°	748.7	768.8	796.8	833.5	881.5	943.8	1033.2	1142.3	1223.2	1327.8	1442.5
35°	685.5	708.9	731.7	766.6	805.4	862.3	930.0	1046.6	1127.0	1230.2	1345.4
37.5°	633.3	647.6	672.9	700.4	741.4	784.0	842.6	947.2	1034.2	1135.5	1253.4
40°	593.7	611.8	630.6	661.4	694.9	735.7	793.3	871.1	970.9	1070.1	1185.3
42.5°	555.1	577.9	597.8	618.4	655.2	696.1	743.0	808.9	910.9	1004.7	1116.7
45°	508.6	523.3	544.1	566.8	597.0	631.9	673.4	731.0	828.9	909.9	1015.1
47.5°	454.4	476.1	489.6	511.8	540.5	573.7	612.3	662.2	741.3	817.3	914.9
50°	417.5	439.6	459.0	479.1	504.5	536.7	568.9	617.1	680.8	760.5	851.6
52.5°	385.8	405.3	424.1	444.2	469.2	498.7	529.2	571.6	626.1	699.4	787.9
55°	342.4	354.5	373.9	393.9	416.1	444.2	473.7	509.3	556.1	617.8	689.5
57.5°	297.9	311.8	327.3	347.5	369.9	391.4	418.0	450.1	487.2	542.9	604.3
60°	272.7	283.5	296.2	316.9	337.7	357.1	382.6	409.4	444.2	492.5	544.7
62.5°	244.8	255.0	266.7	284.8	305.0	322.9	345.1	373.4	402.9	447.0	492.7
65°	198.3	213.1	224.5	240.5	257.3	276.1	293.5	316.3	342.4	377.3	418.1
67.5°	164.4	172.0	182.5	197.1	214.3	230.4	246.8	264.7	287.3	314.3	346.7
70°	149.5	152.1	154.1	168.1	184.3	200.4	215.7	232.5	252.0	274.1	302.2
72.5°	131.7	134.4	136.9	143.0	155.8	172.0	187.8	200.4	218.7	237.0	259.8
75°	104.5	108.6	110.6	113.9	118.6	129.4	144.1	156.1	166.8	180.9	199.0
77.5°	79.6	81.9	84.0	87.6	90.5	95.4	103.7	114.6	124.6	132.8	145.2
80°	63.0	63.6	66.3	67.7	71.7	75.0	79.1	87.8	97.9	101.2	109.9
82.5°	47.5	48.1	50.3	51.6	53.4	56.2	61.4	63.6	71.6	75.9	81.5
85°	26.2	25.4	27.5	27.5	28.8	30.2	31.5	34.8	36.9	42.2	43.5
87.5°	13.2	13.3	13.1	12.3	11.6	11.9	11.9	12.1	12.7	13.9	15.7
90°	25.9	26.3	22.5	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7
92.5°	23.9	23.8	22.9	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3
95°	48.0	48.0	47.7	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0
97.5°	80.6	80.6	80.0	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2
100°	103.4	103.4	102.9	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1
102.5°	128.2	127.9	127.3	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4
105°	165.2	164.9	164.5	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1
107.5°	205.6	205.5	205.5	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2
110°	233.1	233.1	233.1	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.8	261.3	261.4	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3
115°	302.6	302.8	303.1	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7
117.5°	343.5	343.9	344.8	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0
120°	370.2	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2
122.5°	398.6	399.0	399.9	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0
125°	440.1	440.6	441.1	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2
127.5°	480.5	481.1	481.7	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2
130°	507.8	508.1	508.4	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8
132.5°	534.9	535.6	535.6	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5
135°	573.8	574.0	573.7	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3
137.5°	611.7	611.8	611.4	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1
140°	636.9	636.9	636.1	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5
142.5°	659.8	659.7	659.1	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5
145°	694.8	694.7	693.7	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9
147.5°	725.3	725.0	724.3	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7
150°	744.7	744.2	743.5	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6
152.5°	764.0	763.4	762.5	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2
155°	788.4	787.6	787.1	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0
157.5°	810.9	809.8	809.5	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9
160°	824.6	823.5	823.3	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3
162.5°	836.7	835.6	835.4	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5
165°	852.4	851.3	851.3	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0
167.5°	865.5	864.3	864.3	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8
170°	872.7	871.5	871.7	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5
172.5°	878.1	876.9	877.1	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9
175°	883.9	882.7	883.1	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5
177.5°	887.0	886.2	886.5	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1939.6	1941.3	1952.0	1956.8	1966.5	1970.2	1974.5	1973.5	1973.5	1975.6	1990.6
5°	1943.8	1957.2	1977.3	1996.8	2015.5	2031.6	2042.4	2053.1	2057.1	2076.5	2094.0
7.5°	1936.8	1961.6	1994.8	2024.4	2059.9	2087.6	2110.7	2131.4	2145.7	2173.9	2202.9
10°	1927.7	1962.6	2000.1	2038.3	2087.2	2124.0	2161.6	2190.4	2199.8	2242.0	2266.1
12.5°	1909.6	1956.1	2003.9	2053.4	2101.1	2151.9	2193.2	2222.0	2255.0	2292.9	2337.4
15°	1882.2	1935.8	1998.1	2061.7	2130.1	2191.7	2235.9	2286.2	2322.4	2364.0	2402.8
17.5°	1842.9	1912.0	1991.2	2064.9	2143.9	2210.1	2271.0	2319.2	2344.6	2368.3	2374.1
20°	1811.8	1886.2	1979.3	2066.5	2145.6	2221.9	2282.2	2322.4	2329.2	2329.8	2294.3
22.5°	1778.1	1862.1	1959.5	2048.7	2143.3	2228.4	2275.2	2292.4	2265.8	2220.4	2151.7
25°	1716.0	1813.2	1926.4	2028.2	2131.4	2211.8	2228.0	2197.8	2104.7	2006.8	1882.9
27.5°	1648.7	1758.0	1879.4	1992.6	2102.5	2152.3	2117.7	2008.9	1841.2	1695.4	1518.6
30°	1599.4	1722.0	1841.3	1967.9	2069.8	2091.2	2011.6	1851.4	1655.7	1435.9	1259.7
32.5°	1543.2	1671.6	1802.7	1933.7	2018.9	1997.9	1866.2	1669.1	1439.7	1223.7	1057.1
35°	1462.7	1595.4	1736.8	1868.1	1922.4	1831.9	1635.0	1378.3	1143.8	942.1	827.5
37.5°	1369.9	1514.3	1661.3	1781.9	1778.1	1627.3	1359.0	1094.1	897.0	777.7	696.1
40°	1303.9	1450.0	1608.8	1710.6	1667.1	1470.8	1179.9	930.0	786.0	690.8	631.2
42.5°	1240.7	1387.3	1545.0	1626.0	1550.2	1308.9	1019.2	823.3	704.5	630.3	581.9
45°	1133.1	1287.9	1433.9	1478.8	1343.4	1077.4	824.2	682.2	603.1	548.1	514.6
47.5°	1027.8	1180.1	1313.4	1314.2	1131.1	873.7	695.3	590.4	522.8	480.3	456.0
50°	963.5	1108.2	1220.1	1202.7	995.0	777.3	621.8	531.4	475.0	442.2	416.8
52.5°	891.2	1031.6	1128.5	1078.9	879.8	684.0	555.8	479.9	433.2	404.8	381.9
55°	786.0	910.6	979.0	903.9	717.6	568.9	469.7	410.1	375.3	351.1	331.6
57.5°	682.7	785.5	828.5	741.0	591.1	471.7	397.4	352.5	318.0	300.7	290.6
60°	617.8	705.6	735.7	639.2	513.9	412.7	351.7	310.2	284.8	273.4	263.4
62.5°	554.0	625.7	638.1	549.7	448.0	361.3	308.9	273.8	256.9	246.0	236.5
65°	459.7	511.3	505.2	434.2	354.5	286.8	248.6	227.1	214.4	199.0	182.3
67.5°	378.4	409.9	390.9	337.7	270.5	222.9	197.9	181.7	165.9	151.3	147.4
70°	327.0	345.1	325.0	276.1	221.8	186.9	166.8	147.4	138.0	134.7	128.7
72.5°	277.7	284.0	262.3	220.4	180.5	154.8	135.2	124.3	119.3	116.4	112.6
75°	208.4	203.7	184.9	152.1	125.3	107.9	101.9	97.9	94.5	91.8	89.8
77.5°	146.3	139.5	122.8	101.3	87.3	79.0	75.3	73.2	71.6	70.2	68.2
80°	109.9	105.2	88.5	72.4	66.3	62.3	60.3	57.7	57.7	56.2	54.2
82.5°	80.4	75.1	60.6	53.0	49.7	47.3	45.8	44.2	43.7	43.9	42.5
85°	42.2	34.1	30.2	28.8	26.8	25.4	26.2	24.7	24.7	24.7	24.1
87.5°	13.4	11.1	11.0	10.9	11.9	12.7	12.9	13.6	14.8	14.3	14.7
90°	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5
92.5°	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9
95°	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0
97.5°	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6
100°	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4
102.5°	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3
105°	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5
107.5°	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7
110°	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4
115°	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5
117.5°	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1
120°	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2
122.5°	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2
125°	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6
127.5°	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9
130°	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5
132.5°	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2
135°	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7
137.5°	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5
140°	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9
142.5°	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0
145°	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0
147.5°	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7
150°	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1
152.5°	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6
155°	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2
157.5°	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0
160°	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6
162.5°	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8
165°	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6
167.5°	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7
170°	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8
172.5°	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3
175°	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0
177.5°	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1996.0	2003.0	2006.1	2006.1	2009.9	2008.3	2006.7
5°	2110.7	2123.4	2126.1	2138.2	2146.9	2144.1	2145.6
7.5°	2224.7	2245.2	2265.4	2274.7	2276.1	2281.5	2283.5
10°	2294.9	2311.7	2343.2	2338.4	2362.0	2375.3	2353.2
12.5°	2362.5	2385.1	2407.0	2413.0	2426.3	2430.5	2421.9
15°	2423.6	2435.7	2437.0	2433.7	2437.6	2434.3	2421.6
17.5°	2366.5	2346.9	2307.2	2288.5	2273.6	2251.7	2242.8
20°	2272.2	2214.5	2147.5	2120.7	2089.2	2027.6	2042.4
22.5°	2068.5	2002.8	1935.8	1857.5	1820.2	1761.7	1758.2
25°	1751.5	1638.3	1513.7	1426.5	1375.6	1317.4	1291.8
27.5°	1361.8	1219.2	1117.1	1065.4	1018.3	972.1	970.3
30°	1105.6	998.4	919.3	875.0	846.3	826.9	830.9
32.5°	931.9	858.5	805.2	768.4	747.1	732.5	732.3
35°	761.8	711.6	677.4	662.0	646.6	635.9	636.5
37.5°	652.0	621.8	602.8	585.7	576.1	570.9	567.9
40°	595.7	570.9	556.1	546.1	538.1	530.7	529.4
42.5°	551.2	530.7	515.9	508.1	500.5	495.3	493.9
45°	489.2	472.4	459.0	450.3	447.0	442.2	442.2
47.5°	435.2	418.7	408.2	402.7	397.0	393.8	393.7
50°	398.7	386.0	376.6	373.2	368.5	366.5	365.9
52.5°	366.0	356.5	349.8	347.5	345.5	343.0	343.4
55°	321.6	316.3	313.6	311.5	308.2	304.2	306.9
57.5°	284.3	279.6	272.5	266.1	263.1	260.2	261.4
60°	258.0	248.6	239.2	231.9	229.8	223.8	223.8
62.5°	224.7	211.6	200.1	195.9	193.9	191.1	190.6
65°	172.9	167.5	164.8	162.2	160.8	160.8	159.5
67.5°	143.3	141.1	138.1	137.5	136.1	135.7	135.3
70°	126.6	123.9	122.6	122.0	120.6	121.3	119.3
72.5°	110.6	108.5	108.2	106.4	105.6	105.7	104.2
75°	87.2	87.2	86.4	85.7	84.4	83.7	84.4
77.5°	67.1	67.2	65.9	65.8	65.6	65.8	65.1
80°	53.6	54.2	53.6	52.9	52.3	52.9	52.3
82.5°	42.3	41.4	41.3	41.1	41.0	40.6	40.5
85°	24.1	24.7	24.1	23.4	23.4	23.4	24.1
87.5°	14.1	14.1	14.0	14.1	14.1	14.1	13.6
90°	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331830-840

CATALOG NUMBER: S122RDIW-S865D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)