

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332161-830

Luminaire Tested: **S123DIW-S775D755U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332161-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D755U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5456.8 lumens  
Efficiency: N/A  
Efficacy: 121.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51	46																				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43	38																				
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	36	33																				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31	28																				
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27	24																				
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21																				
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19																				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17																				
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	24	20	17	15																				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	2.0
10°-20°	305.3	5.6
20°-30°	451.0	8.3
30°-40°	526.8	9.7
40°-50°	529.6	9.7
50°-60°	465.2	8.5
60°-70°	346.6	6.4
70°-80°	197.5	3.6
80°-90°	59.3	1.1
90°-100°	58.0	1.1
100°-110°	173.6	3.2
110°-120°	295.3	5.4
120°-130°	388.5	7.1
130°-140°	436.7	8.0
140°-150°	429.2	7.9
150°-160°	361.3	6.6
160°-170°	240.5	4.4
170°-180°	84.2	1.5
0°-30°	864.4	15.8
0°-40°	1391.1	25.5
0°-60°	2385.9	43.7
0°-90°	2989.3	54.8
90°-120°	527.0	9.7
90°-150°	1781.4	32.6
90°-180°	2468.0	45.2
0°-180°	5456.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	8	17	20	21	5
95°	41	46	52	54	55	46
105°	157	159	165	165	166	169
115°	297	299	298	299	298	294
125°	435	437	436	433	430	388
135°	565	568	568	565	564	435
145°	685	686	688	688	685	428
155°	784	784	785	787	783	361
165°	854	852	852	856	851	241
175°	888	886	886	889	885	84
180°	891	891	891	891	891	



TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.6	20.5	20.3	20.0	19.8	19.8	20.1	20.3	20.5	20.7	20.6
90°	0.7	2.3	3.8	5.4	6.9	8.7	10.7	12.7	14.8	16.8	17.4
92.5°	17.0	18.0	19.0	20.1	21.1	22.2	23.4	24.6	25.7	26.9	27.3
95°	41.3	42.3	43.5	44.6	45.6	46.8	48.1	49.3	50.5	51.7	52.4
97.5°	73.3	74.1	74.9	75.8	76.5	77.4	78.3	79.2	80.1	81.1	81.7
100°	95.1	96.0	97.0	97.9	98.9	99.7	100.5	101.3	102.1	102.8	103.3
102.5°	120.4	120.9	121.5	122.0	122.5	123.4	124.4	125.5	126.4	127.4	127.9
105°	157.4	157.7	158.1	158.3	158.6	159.5	160.9	162.3	163.7	165.1	165.1
107.5°	200.5	200.7	200.9	201.0	201.2	201.6	202.2	202.7	203.3	203.9	204.3
110°	227.3	227.7	228.0	228.3	228.6	228.9	229.2	229.5	229.9	230.2	230.8



TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	255.3	255.5	255.7	255.9	256.1	256.2	256.3	256.4	256.4	256.5	257.2
115°	297.4	297.7	298.2	298.7	299.2	299.3	299.0	298.7	298.3	298.0	298.2
117.5°	339.6	339.9	340.2	340.5	340.8	340.8	340.4	340.0	339.6	339.1	339.1
120°	365.9	366.8	367.8	368.7	369.7	369.7	368.9	368.2	367.4	366.6	366.5
122.5°	393.3	394.0	394.6	395.4	396.1	396.2	395.8	395.4	395.0	394.5	394.2
125°	435.2	435.6	436.1	436.6	437.1	437.1	436.8	436.5	436.1	435.8	435.3
127.5°	473.7	474.8	475.8	476.7	477.8	478.1	477.8	477.4	477.0	476.7	475.8
130°	499.5	500.8	502.0	503.2	504.4	504.9	504.4	504.0	503.5	503.0	502.4
132.5°	525.3	526.5	527.7	529.0	530.3	530.7	530.4	530.0	529.6	529.3	528.6
135°	564.6	565.5	566.5	567.4	568.3	568.7	568.5	568.4	568.3	568.1	567.4
137.5°	601.0	601.7	602.5	603.3	604.1	604.6	605.0	605.5	605.9	606.2	605.6
140°	626.1	626.9	627.7	628.5	629.2	629.7	629.9	630.0	630.2	630.4	630.2
142.5°	649.1	649.9	650.6	651.4	652.1	652.7	653.0	653.3	653.6	653.8	653.7
145°	684.9	685.2	685.5	685.8	686.2	686.5	687.0	687.5	688.0	688.4	688.2
147.5°	716.2	716.8	717.4	717.9	718.5	719.0	719.4	719.8	720.3	720.8	720.8
150°	738.1	738.4	738.7	739.0	739.3	739.6	739.9	740.3	740.6	740.8	740.8
152.5°	756.0	756.4	756.9	757.3	757.7	758.0	758.2	758.4	758.6	758.7	759.0
155°	784.3	784.3	784.3	784.3	784.3	784.3	784.5	784.7	784.8	784.9	785.6
157.5°	808.3	808.1	807.9	807.8	807.6	807.6	807.7	807.8	807.9	808.0	808.7
160°	823.4	823.1	822.8	822.5	822.2	822.0	822.0	822.0	822.0	822.0	822.8
162.5°	836.9	836.4	835.9	835.6	835.1	835.0	835.1	835.2	835.4	835.5	836.2
165°	854.2	853.8	853.3	852.8	852.3	852.1	852.1	852.1	852.1	852.1	853.0
167.5°	868.1	867.4	866.9	866.2	865.5	865.3	865.4	865.5	865.7	865.8	866.8
170°	875.9	875.2	874.7	874.0	873.4	873.1	873.1	873.1	873.1	873.1	874.2
172.5°	882.0	881.5	880.8	880.1	879.6	879.2	879.2	879.2	879.2	879.2	880.2
175°	888.4	887.9	887.2	886.6	886.0	885.7	885.7	885.7	885.7	885.7	886.6
177.5°	891.2	890.6	890.1	889.7	889.2	888.9	888.9	888.9	888.9	888.9	889.7
180°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6



TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	20.6	20.5	20.5	20.5	20.5	20.6	20.7	20.7
90°	18.0	18.7	19.3	19.7	20.1	20.4	20.6	21.0
92.5°	27.9	28.4	28.8	29.0	28.8	28.7	28.5	28.3
95°	53.0	53.6	54.3	54.6	54.6	54.6	54.6	54.6
97.5°	82.5	83.1	83.9	84.2	84.2	84.1	84.0	84.0
100°	103.8	104.2	104.7	105.1	105.4	105.8	106.0	106.3
102.5°	128.4	128.8	129.3	129.5	129.5	129.4	129.3	129.3
105°	165.1	165.1	165.1	165.2	165.6	165.9	166.2	166.5
107.5°	204.8	205.4	205.9	206.0	205.9	205.7	205.5	205.3
110°	231.4	232.1	232.6	232.8	232.5	232.1	231.9	231.6





TEST NUMBER: P332161-830

CATALOG NUMBER: S123DIW-S775D755U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	258.0	258.7	259.5	259.8	259.8	259.7	259.6	259.6
115°	298.3	298.5	298.7	298.7	298.5	298.3	298.2	298.0
117.5°	339.1	339.0	339.0	338.8	338.4	337.9	337.5	337.1
120°	366.3	366.1	366.0	365.7	365.4	365.1	364.8	364.5
122.5°	393.8	393.3	392.9	392.6	392.1	391.6	391.2	390.8
125°	434.6	433.9	433.4	432.7	432.2	431.5	430.8	430.3
127.5°	474.9	474.1	473.3	472.4	471.7	471.0	470.3	469.6
130°	501.8	501.1	500.5	499.6	498.6	497.5	496.4	495.3
132.5°	527.8	527.1	526.3	525.6	524.7	523.9	523.0	522.2
135°	566.8	566.2	565.6	565.1	564.8	564.5	564.2	563.8
137.5°	604.9	604.3	603.7	603.0	602.5	601.8	601.2	600.7
140°	630.0	629.9	629.7	629.1	628.0	626.9	625.8	624.7
142.5°	653.6	653.4	653.2	652.7	651.9	651.0	650.2	649.3
145°	688.1	688.0	687.8	687.4	686.7	686.2	685.5	684.9
147.5°	720.8	720.8	720.8	720.3	719.3	718.4	717.5	716.5
150°	740.8	740.8	740.8	740.4	739.4	738.6	737.6	736.7
152.5°	759.3	759.5	759.8	759.5	758.7	757.9	757.1	756.3
155°	786.2	786.8	787.4	787.2	786.1	785.0	783.9	782.9
157.5°	809.4	810.0	810.7	810.5	809.6	808.8	807.9	807.0
160°	823.6	824.3	825.1	825.2	824.6	824.0	823.3	822.7
162.5°	837.0	837.8	838.6	838.5	837.4	836.5	835.5	834.4
165°	853.9	854.9	855.8	855.7	854.7	853.6	852.5	851.4
167.5°	867.7	868.7	869.7	869.7	868.7	867.7	866.8	865.8
170°	875.2	876.4	877.4	877.4	876.4	875.2	874.2	873.1
172.5°	881.2	882.1	883.1	883.1	881.9	880.9	879.8	878.7
175°	887.6	888.4	889.4	889.4	888.3	887.1	886.1	885.0
177.5°	890.4	891.2	891.9	891.8	891.0	890.0	889.2	888.3
180°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6

(END OF REPORT)