

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331604-940

Luminaire Tested: **S122DIW-S1005D1240U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331604-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7759.5 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.3	2.2
10°-20°	492.3	6.3
20°-30°	714.5	9.2
30°-40°	754.0	9.7
40°-50°	667.6	8.6
50°-60°	532.7	6.9
60°-70°	362.1	4.7
70°-80°	185.6	2.4
80°-90°	50.2	0.6
90°-100°	86.8	1.1
100°-110°	269.6	3.5
110°-120°	460.9	5.9
120°-130°	606.1	7.8
130°-140°	680.3	8.8
140°-150°	667.1	8.6
150°-160°	559.5	7.2
160°-170°	371.1	4.8
170°-180°	129.7	1.7
0°-30°	1376.1	17.7
0°-40°	2130.1	27.5
0°-60°	3330.4	42.9
0°-90°	3928.3	50.6
90°-120°	817.4	10.5
90°-150°	2770.9	35.7
90°-180°	3831.0	49.4
0°-180°	7759.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	39	1	39	1	39	19
95°	72	60	72	60	72	80
105°	257	249	257	249	257	270
115°	462	462	462	462	462	457
125°	675	673	675	673	675	602
135°	881	871	881	871	881	678
145°	1068	1057	1068	1057	1068	667
155°	1218	1208	1218	1208	1218	560
165°	1316	1315	1316	1315	1316	371
175°	1363	1368	1363	1368	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	22.1	22.0	22.6	21.9	21.8	22.5	22.6	22.1	22.7	23.4	22.8
90°	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4	39.9	40.5	34.8
92.5°	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0	36.8	36.7	35.4
95°	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0	74.0	74.0	73.5
97.5°	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4	124.4	124.4	123.4
100°	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5	159.5	159.5	158.8
102.5°	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9	197.7	197.5	196.5
105°	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4	254.9	254.4	253.9
107.5°	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4	317.3	317.0	317.0
110°	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8	402.4	403.1	403.2
115°	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6	466.9	467.1	467.6
117.5°	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2	529.9	530.5	531.9
120°	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1	571.1	571.1	573.2
122.5°	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4	614.9	615.5	617.0
125°	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3	679.1	679.8	680.6
127.5°	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5	741.4	742.3	743.2
130°	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9	783.4	783.9	784.4
132.5°	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2	825.4	826.4	826.3
135°	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2	885.4	885.6	885.2
137.5°	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5	943.8	944.0	943.3
140°	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8	982.8	982.8	981.5
142.5°	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3	1018.2	1018.0	1017.1
145°	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4	1072.1	1071.8	1070.3
147.5°	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6	1119.1	1118.6	1117.5
150°	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2	1147.1
152.5°	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8	1176.5
155°	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8	1216.5	1215.2	1214.4
157.5°	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9	1251.2	1249.5	1248.9
160°	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8	1272.2	1270.7	1270.4
162.5°	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7	1290.9	1289.2	1289.0
165°	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1	1315.3	1313.5	1313.5
167.5°	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2	1335.4	1333.6	1333.6
170°	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3	1346.5	1344.7	1345.0
172.5°	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6	1354.9	1353.0	1353.3
175°	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7	1363.9	1362.0	1362.5
177.5°	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3	1367.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	22.2	21.1	20.0	20.2	17.9	17.3	14.5	12.2	12.3	12.4	11.9
90°	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6	22.8	25.1	27.4
95°	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1	62.7	65.3	67.9
97.5°	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9	112.1	114.4	116.6
100°	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9	148.9	151.0	153.0
102.5°	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7	187.3	189.0	190.6
105°	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6	249.3	250.1	250.9
107.5°	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9	313.1	314.2	315.3
110°	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7	354.2	355.7	357.3



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1	398.6	400.1	401.7
115°	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5	464.0	465.6	467.1
117.5°	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7	529.8	531.8	533.9
120°	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	573.2	575.3	577.4
122.5°	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9	613.4	615.9	618.3
125°	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9	675.2	677.5	679.8
127.5°	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3	736.2	739.1	742.1
130°	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2	774.5	777.9	781.2
132.5°	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8	816.5	819.2	821.9
135°	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7	873.4	876.3	879.1
137.5°	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5	932.8	935.1	937.5
140°	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6	968.9	971.3	973.6
142.5°	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6	1005.9	1008.3	1010.6
145°	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8	1058.6	1060.4	1062.2
147.5°	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2	1106.3	1108.5	1110.7
150°	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1	1139.7	1141.2
152.5°	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3	1166.8	1168.3	1169.8
155°	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3	1209.1	1209.8	1210.6
157.5°	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0	1245.5	1246.1	1246.6
160°	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2	1267.7	1268.3	1268.8
162.5°	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5	1287.7	1287.8	1287.9
165°	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6	1314.4	1314.1	1313.8
167.5°	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3	1336.5	1335.8	1335.0
170°	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3	1348.5	1347.8	1347.0
172.5°	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6	1356.9	1356.1	1355.3
175°	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8	1367.1	1366.3	1365.5
177.5°	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0	1371.4	1370.7	1370.1
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	11.9	12.3	12.9	14.0	14.6	15.2	14.5	14.4	14.4	13.1	13.1
90°	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4	39.0	38.4	38.3
92.5°	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0	37.1	37.2	37.3
95°	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0	74.0	74.0	73.7
97.5°	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4	124.4	124.4	124.4
100°	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5	159.5	159.5	159.4
102.5°	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9	198.1	198.3	198.3
105°	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4	255.9	256.5	256.7
107.5°	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4	317.6	317.9	317.4
110°	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.2



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8	401.2	400.6	400.0
115°	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6	466.4	466.1	465.6
117.5°	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2	528.6	528.0	527.4
120°	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1	571.1	571.1	570.8
122.5°	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4	613.8	613.1	612.5
125°	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3	677.5	676.8	676.3
127.5°	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5	739.5	738.6	737.7
130°	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9	782.4	781.9	781.1
132.5°	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2	823.0	822.0	821.0
135°	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2	884.9	884.7	884.1
137.5°	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5	943.3	943.2	942.5
140°	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8	982.8	982.8	982.3
142.5°	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3	1018.6	1018.8	1018.3
145°	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4	1072.6	1072.8	1072.5
147.5°	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6	1120.3	1120.8	1120.6
150°	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2
152.5°	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6
155°	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8	1219.1	1220.3	1220.6
157.5°	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9	1254.6	1256.4	1256.7
160°	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8	1275.3	1276.8	1277.1
162.5°	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7	1294.4	1296.2	1296.5
165°	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1	1318.8	1320.7	1320.9
167.5°	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2	1339.0	1340.8	1341.0
170°	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3	1350.1	1351.9	1352.0
172.5°	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6	1358.4	1360.2	1360.3
175°	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7	1367.4	1369.2	1369.4
177.5°	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	13.2	12.7	12.8	12.2	12.8	12.7	13.2	13.1	13.1	14.4	14.4
90°	38.5	38.8	39.1	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4
92.5°	37.3	37.4	37.5	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0
95°	73.2	72.7	72.2	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0
97.5°	124.3	124.3	124.2	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4
100°	159.2	158.9	158.6	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5
102.5°	198.0	197.8	197.5	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9
105°	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4
107.5°	316.2	315.0	313.8	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4
110°	358.5	357.7	356.9	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	399.4	398.9	398.3	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8
115°	464.8	464.0	463.2	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6
117.5°	526.6	525.8	525.0	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2
120°	570.0	569.3	568.5	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1
122.5°	612.0	611.4	610.8	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4
125°	676.0	675.7	675.5	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3
127.5°	736.9	736.1	735.3	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5
130°	780.1	779.1	778.0	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9
132.5°	820.2	819.3	818.5	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2
135°	883.3	882.6	881.8	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2
137.5°	941.5	940.5	939.4	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5
140°	981.2	980.3	979.2	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8
142.5°	1017.4	1016.3	1015.3	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3
145°	1071.5	1070.4	1069.4	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4
147.5°	1119.6	1118.7	1117.7	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6
150°	1150.5	1149.7	1148.9	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7
152.5°	1180.6	1179.7	1178.8	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7
155°	1219.9	1219.1	1218.3	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8
157.5°	1255.4	1254.2	1252.9	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9
160°	1276.1	1275.1	1274.1	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8
162.5°	1295.2	1294.0	1292.7	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7
165°	1319.6	1318.4	1317.1	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1
167.5°	1339.7	1338.4	1337.0	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2
170°	1350.5	1349.0	1347.4	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3
172.5°	1358.8	1357.3	1355.8	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6
175°	1367.8	1366.3	1364.8	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7
177.5°	1371.1	1369.8	1368.6	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	14.5	15.2	14.6	14.0	12.9	12.3	11.9	11.9	12.4	12.3	12.2
90°	39.9	40.5	34.8	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2
92.5°	36.8	36.7	35.4	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6
95°	74.0	74.0	73.5	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1
97.5°	124.4	124.4	123.4	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9
100°	159.5	159.5	158.8	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9
102.5°	197.7	197.5	196.5	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7
105°	254.9	254.4	253.9	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6
107.5°	317.3	317.0	317.0	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9
110°	359.6	359.6	359.6	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	402.4	403.1	403.2	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1
115°	466.9	467.1	467.6	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5
117.5°	529.9	530.5	531.9	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7
120°	571.1	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1
122.5°	614.9	615.5	617.0	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9
125°	679.1	679.8	680.6	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9
127.5°	741.4	742.3	743.2	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3
130°	783.4	783.9	784.4	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2
132.5°	825.4	826.4	826.3	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8
135°	885.4	885.6	885.2	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7
137.5°	943.8	944.0	943.3	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5
140°	982.8	982.8	981.5	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6
142.5°	1018.2	1018.0	1017.1	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6
145°	1072.1	1071.8	1070.3	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8
147.5°	1119.1	1118.6	1117.5	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2
150°	1148.9	1148.2	1147.1	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6
152.5°	1178.8	1177.8	1176.5	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3
155°	1216.5	1215.2	1214.4	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3
157.5°	1251.2	1249.5	1248.9	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0
160°	1272.2	1270.7	1270.4	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2
162.5°	1290.9	1289.2	1289.0	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5
165°	1315.3	1313.5	1313.5	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6
167.5°	1335.4	1333.6	1333.6	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3
170°	1346.5	1344.7	1345.0	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3
172.5°	1354.9	1353.0	1353.3	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6
175°	1363.9	1362.0	1362.5	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8
177.5°	1368.6	1367.3	1367.8	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	14.5	17.3	17.9	20.2	20.0	21.1	22.2	22.8	23.4	22.7	22.1
90°	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4
92.5°	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0
95°	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0
97.5°	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4
100°	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5
102.5°	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9
105°	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4
107.5°	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4
110°	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8
115°	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6
117.5°	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2
120°	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1
122.5°	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4
125°	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3
127.5°	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5
130°	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9
132.5°	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2
135°	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2
137.5°	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5
140°	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8
142.5°	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3
145°	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4
147.5°	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6
150°	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7
152.5°	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7
155°	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8
157.5°	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9
160°	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8
162.5°	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7
165°	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1
167.5°	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2
170°	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3
172.5°	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6
175°	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7
177.5°	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	22.6	22.5	21.8	21.9	22.6	22.0	22.1
90°	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331604-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)