

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331607-940

Luminaire Tested: **S122DIW-S1005D1240U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331607-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8037.3 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	79	71	68	66	58	56	54	46	44	44	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	52	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	1.7
10°-20°	376.0	4.7
20°-30°	552.7	6.9
30°-40°	642.0	8.0
40°-50°	641.3	8.0
50°-60°	559.3	7.0
60°-70°	413.6	5.1
70°-80°	234.2	2.9
80°-90°	66.7	0.8
90°-100°	50.3	0.6
100°-110°	184.4	2.3
110°-120°	492.9	6.1
120°-130°	813.7	10.1
130°-140°	865.3	10.8
140°-150°	804.3	10.0
150°-160°	646.7	8.0
160°-170°	416.7	5.2
170°-180°	143.4	1.8
0°-30°	1062.4	13.2
0°-40°	1704.4	21.2
0°-60°	2905.1	36.1
0°-90°	3619.6	45.0
90°-120°	727.6	9.1
90°-150°	3210.9	40.0
90°-180°	4418.0	55.0
0°-180°	8037.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	1	13	22	27	29	6
95°	71	37	42	48	47	87
105°	332	346	66	78	83	354
115°	627	646	673	192	89	617
125°	887	901	922	929	933	790
135°	1097	1114	1125	1135	1133	847
145°	1273	1273	1290	1297	1293	796
155°	1402	1393	1405	1411	1403	646
165°	1477	1471	1474	1480	1474	417
175°	1511	1504	1505	1512	1502	144
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.9	20.0	20.0	20.1	20.1	20.1	20.0	19.9	19.8	19.7	19.2
90°	1.1	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0
92.5°	22.0	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9
95°	70.9	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8
97.5°	140.7	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9
100°	193.1	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1
102.5°	250.7	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4
105°	331.6	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2
107.5°	423.9	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4
110°	483.2	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7



TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.0	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1
115°	627.2	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8
117.5°	706.0	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3
120°	763.6	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5
122.5°	812.4	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7
125°	886.8	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5
127.5°	954.2	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9
130°	997.0	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1
132.5°	1040.6	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7
135°	1097.3	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0
137.5°	1154.7	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4
140°	1192.2	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1
142.5°	1223.7	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2
145°	1272.9	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1
147.5°	1315.9	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4
150°	1343.9	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1
152.5°	1367.4	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0
155°	1401.7	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4
157.5°	1428.5	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0
160°	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6
162.5°	1458.2	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9
165°	1476.9	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3
167.5°	1490.9	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1
170°	1498.8	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1
172.5°	1504.0	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3
175°	1510.7	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0
177.5°	1511.8	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	18.7	18.2	17.7	17.4	17.3	17.1	16.9	16.9
90°	24.3	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	26.6	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	44.9	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	58.9	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	66.1	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	68.9	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	71.9	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	87.7	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	142.4	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331607-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	448.5	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	691.2	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	805.4	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	854.5	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	925.1	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	990.3	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1031.8	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1072.0	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1129.4	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1182.8	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1217.4	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1249.2	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1293.8	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1332.7	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1356.6	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1378.4	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1407.8	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1432.7	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1447.2	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1460.6	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1490.8	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1497.8	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1503.0	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1508.7	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1509.3	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)