

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332465-830

Luminaire Tested: **S123RDIW-S1000D1320U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332465-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7889.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	1.9
10°-20°	413.3	5.2
20°-30°	595.1	7.5
30°-40°	670.3	8.5
40°-50°	641.3	8.1
50°-60°	525.1	6.7
60°-70°	354.3	4.5
70°-80°	178.2	2.3
80°-90°	51.8	0.7
90°-100°	101.4	1.3
100°-110°	303.4	3.8
110°-120°	516.1	6.5
120°-130°	678.8	8.6
130°-140°	763.0	9.7
140°-150°	750.0	9.5
150°-160°	631.4	8.0
160°-170°	420.3	5.3
170°-180°	147.2	1.9
0°-30°	1156.9	14.7
0°-40°	1827.2	23.2
0°-60°	2993.6	37.9
0°-90°	3577.9	45.3
90°-120°	920.9	11.7
90°-150°	3112.8	39.5
90°-180°	4312.0	54.7
0°-180°	7889.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	14	29	34	37	8
95°	72	81	90	95	95	81
105°	275	278	288	289	291	295
115°	520	523	521	522	521	514
125°	760	764	762	757	752	678
135°	987	993	993	988	985	760
145°	1197	1199	1203	1202	1197	747
155°	1370	1370	1372	1376	1368	631
165°	1493	1489	1489	1495	1488	421
175°	1553	1548	1548	1554	1546	147
180°	1556	1556	1556	1556	1556	



TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.9	22.9	20.9	18.9	17.1	16.4	17.1	17.8	18.5	19.2	19.2
90°	1.2	4.0	6.7	9.3	12.1	15.2	18.8	22.2	25.8	29.3	30.4
92.5°	29.6	31.4	33.3	35.2	36.9	38.9	40.9	42.9	45.0	46.9	47.8
95°	72.1	74.0	76.0	77.9	79.7	81.8	84.0	86.1	88.3	90.5	91.5
97.5°	128.1	129.5	130.9	132.3	133.7	135.3	136.9	138.4	140.0	141.6	142.8
100°	166.3	167.9	169.5	171.2	172.8	174.3	175.6	177.0	178.3	179.7	180.5
102.5°	210.3	211.2	212.3	213.2	214.1	215.6	217.4	219.1	220.9	222.7	223.6
105°	275.0	275.6	276.2	276.6	277.2	278.7	281.2	283.6	286.1	288.5	288.5
107.5°	350.3	350.7	351.0	351.4	351.7	352.3	353.3	354.3	355.2	356.2	357.1
110°	397.3	397.8	398.4	398.9	399.4	400.0	400.6	401.1	401.6	402.2	403.3



TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.5	446.9	447.1	447.5	447.7	447.8	447.9	448.1	448.2	449.5
115°	519.5	520.4	521.1	522.0	522.8	522.9	522.4	521.9	521.3	520.8	521.0
117.5°	593.4	593.9	594.5	595.0	595.6	595.5	594.7	594.1	593.3	592.7	592.6
120°	639.3	640.9	642.6	644.2	645.8	646.0	644.6	643.3	642.0	640.6	640.3
122.5°	687.3	688.4	689.7	690.9	692.0	692.3	691.5	690.9	690.1	689.5	688.7
125°	760.3	761.2	762.0	762.8	763.6	763.7	763.2	762.7	762.1	761.6	760.5
127.5°	827.8	829.6	831.3	833.0	834.8	835.4	834.8	834.2	833.6	833.0	831.4
130°	872.8	875.0	877.2	879.4	881.6	882.2	881.4	880.6	879.8	878.9	877.9
132.5°	917.8	920.0	922.2	924.4	926.5	927.3	926.7	926.1	925.5	924.9	923.6
135°	986.6	988.2	989.8	991.4	993.1	993.7	993.4	993.2	992.9	992.6	991.6
137.5°	1050.1	1051.4	1052.8	1054.1	1055.6	1056.6	1057.2	1058.0	1058.7	1059.4	1058.2
140°	1094.1	1095.4	1096.8	1098.2	1099.6	1100.3	1100.6	1100.9	1101.2	1101.5	1101.2
142.5°	1134.2	1135.6	1136.9	1138.3	1139.6	1140.6	1141.0	1141.5	1142.0	1142.6	1142.3
145°	1196.7	1197.3	1197.9	1198.4	1198.9	1199.7	1200.4	1201.3	1202.1	1202.9	1202.6
147.5°	1251.5	1252.5	1253.5	1254.5	1255.5	1256.3	1257.1	1257.8	1258.6	1259.3	1259.3
150°	1289.7	1290.2	1290.8	1291.3	1291.8	1292.4	1293.0	1293.5	1294.0	1294.6	1294.6
152.5°	1321.0	1321.7	1322.5	1323.2	1324.0	1324.6	1324.9	1325.2	1325.6	1325.9	1326.3
155°	1370.4	1370.4	1370.4	1370.4	1370.4	1370.6	1370.7	1371.0	1371.3	1371.6	1372.7
157.5°	1412.4	1412.1	1411.7	1411.5	1411.1	1411.1	1411.3	1411.5	1411.7	1411.9	1413.1
160°	1438.8	1438.3	1437.8	1437.2	1436.6	1436.3	1436.3	1436.3	1436.3	1436.3	1437.8
162.5°	1462.3	1461.5	1460.8	1460.0	1459.2	1459.0	1459.2	1459.4	1459.6	1459.8	1461.2
165°	1492.6	1491.8	1491.0	1490.2	1489.4	1488.9	1488.9	1488.9	1488.9	1488.9	1490.5
167.5°	1516.8	1515.7	1514.7	1513.5	1512.5	1512.0	1512.2	1512.5	1512.7	1512.9	1514.6
170°	1530.5	1529.5	1528.3	1527.3	1526.2	1525.6	1525.6	1525.6	1525.6	1525.6	1527.5
172.5°	1541.2	1540.2	1539.1	1538.0	1536.9	1536.3	1536.3	1536.3	1536.3	1536.3	1538.0
175°	1552.6	1551.4	1550.4	1549.3	1548.1	1547.7	1547.7	1547.7	1547.7	1547.7	1549.3
177.5°	1557.2	1556.3	1555.4	1554.5	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1554.5
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2



TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	19.2	19.1	19.1	19.1	18.9	18.9	18.8	18.7
90°	31.5	32.6	33.6	34.5	35.1	35.6	36.1	36.7
92.5°	48.6	49.6	50.4	50.7	50.3	50.0	49.7	49.4
95°	92.7	93.7	94.8	95.4	95.4	95.4	95.4	95.4
97.5°	144.0	145.3	146.6	147.1	147.0	146.9	146.8	146.7
100°	181.3	182.1	182.9	183.6	184.2	184.7	185.3	185.8
102.5°	224.3	225.2	226.0	226.3	226.2	226.1	226.0	225.9
105°	288.5	288.5	288.5	288.8	289.4	289.8	290.4	291.0
107.5°	358.0	358.8	359.7	360.0	359.7	359.3	359.0	358.6
110°	404.4	405.5	406.5	406.8	406.2	405.8	405.2	404.6



TEST NUMBER: P332465-830

CATALOG NUMBER: S123RDIW-S1000D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.7	452.0	453.4	453.9	453.8	453.7	453.6	453.6
115°	521.3	521.6	521.9	521.9	521.6	521.3	521.0	520.8
117.5°	592.6	592.5	592.4	592.0	591.3	590.5	589.7	589.0
120°	640.0	639.8	639.5	639.0	638.6	638.0	637.4	636.9
122.5°	688.1	687.3	686.6	685.9	685.1	684.4	683.6	682.9
125°	759.4	758.4	757.2	756.2	755.1	753.9	752.9	751.8
127.5°	829.9	828.4	826.9	825.5	824.3	823.0	821.8	820.5
130°	876.8	875.7	874.6	873.1	871.2	869.3	867.4	865.5
132.5°	922.3	921.0	919.7	918.3	916.8	915.4	913.9	912.5
135°	990.4	989.4	988.3	987.5	986.9	986.4	985.8	985.3
137.5°	1057.1	1055.9	1054.8	1053.8	1052.7	1051.7	1050.7	1049.6
140°	1100.9	1100.6	1100.3	1099.3	1097.4	1095.4	1093.5	1091.7
142.5°	1142.0	1141.7	1141.4	1140.6	1139.1	1137.6	1136.1	1134.7
145°	1202.3	1202.1	1201.8	1201.2	1200.0	1198.9	1197.9	1196.7
147.5°	1259.3	1259.3	1259.3	1258.6	1257.0	1255.3	1253.7	1252.1
150°	1294.6	1294.6	1294.6	1293.7	1292.1	1290.5	1288.8	1287.2
152.5°	1326.7	1327.2	1327.6	1327.1	1325.7	1324.3	1322.9	1321.4
155°	1373.8	1374.9	1375.9	1375.5	1373.7	1371.8	1369.8	1367.9
157.5°	1414.2	1415.3	1416.5	1416.3	1414.8	1413.2	1411.7	1410.2
160°	1439.1	1440.5	1441.8	1442.0	1440.9	1439.8	1438.7	1437.6
162.5°	1462.5	1464.0	1465.3	1465.1	1463.4	1461.6	1459.9	1458.1
165°	1492.2	1493.8	1495.4	1495.3	1493.5	1491.6	1489.6	1487.7
167.5°	1516.3	1518.0	1519.7	1519.7	1518.0	1516.3	1514.6	1512.9
170°	1529.5	1531.3	1533.2	1533.2	1531.3	1529.5	1527.5	1525.6
172.5°	1539.7	1541.4	1543.1	1543.0	1541.2	1539.2	1537.3	1535.4
175°	1550.9	1552.6	1554.2	1554.0	1552.1	1550.2	1548.3	1546.4
177.5°	1555.9	1557.2	1558.5	1558.4	1556.8	1555.3	1553.8	1552.3
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2

(END OF REPORT)