

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331595-940

Luminaire Tested: **S122DIW-S1005D710U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331595-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6146.1 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	2.2
10°-20°	376.0	6.1
20°-30°	552.7	9.0
30°-40°	642.0	10.4
40°-50°	641.3	10.4
50°-60°	559.3	9.1
60°-70°	413.6	6.7
70°-80°	234.2	3.8
80°-90°	65.1	1.1
90°-100°	28.8	0.5
100°-110°	105.5	1.7
110°-120°	282.1	4.6
120°-130°	465.6	7.6
130°-140°	495.2	8.1
140°-150°	460.3	7.5
150°-160°	370.1	6.0
160°-170°	238.5	3.9
170°-180°	82.1	1.3
0°-30°	1062.4	17.3
0°-40°	1704.4	27.7
0°-60°	2905.1	47.3
0°-90°	3618.0	58.9
90°-120°	416.4	6.8
90°-150°	1837.6	29.9
90°-180°	2528.0	41.1
0°-180°	6146.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	1	7	12	16	17	5
95°	41	21	24	27	27	50
105°	190	198	38	45	47	203
115°	359	370	385	110	51	353
125°	508	516	527	532	534	452
135°	628	638	644	649	649	485
145°	728	728	738	742	740	455
155°	802	797	804	807	803	369
165°	845	842	843	847	843	239
175°	865	860	862	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.8	19.6	19.4	19.3	19.1	18.8	18.6	18.4	18.1	17.8	17.2
90°	0.6	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2
92.5°	12.6	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8
95°	40.6	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1
97.5°	80.5	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2
100°	110.5	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6
102.5°	143.5	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0
105°	189.8	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6
107.5°	242.5	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7
110°	276.5	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4



TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.5	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0
115°	358.9	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9
117.5°	404.0	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1
120°	436.9	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2
122.5°	464.9	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0
125°	507.5	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4
127.5°	546.1	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3
130°	570.5	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0
132.5°	595.6	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2
135°	628.0	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0
137.5°	660.8	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6
140°	682.3	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4
142.5°	700.3	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8
145°	728.5	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5
147.5°	753.0	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0
150°	769.1	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5
152.5°	782.6	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0
155°	802.2	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9
157.5°	817.5	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9
160°	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3
162.5°	834.5	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9
165°	845.3	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4
167.5°	853.2	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2
170°	857.7	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2
172.5°	860.7	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2
175°	864.6	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5
177.5°	865.2	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	16.6	16.1	15.4	15.1	14.9	14.7	14.5	14.3
90°	13.9	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.2	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	25.8	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	33.7	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	37.8	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	39.5	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	41.1	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	50.2	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	81.5	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331595-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	174.3	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	256.7	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	395.6	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	460.9	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	489.0	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	529.4	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	566.8	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	590.5	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	613.5	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	646.4	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	676.9	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	696.7	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	714.9	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	740.4	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	762.7	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	776.3	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	788.8	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	805.7	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	819.9	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	828.1	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	835.9	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	853.2	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	857.2	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	860.1	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	863.4	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	863.8	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)