

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331597-940

Luminaire Tested: **S122DIW-S1005D970U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331597-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7376.6 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.3	2.3
10°-20°	492.3	6.7
20°-30°	714.5	9.7
30°-40°	754.0	10.2
40°-50°	667.6	9.0
50°-60°	532.7	7.2
60°-70°	362.1	4.9
70°-80°	185.6	2.5
80°-90°	47.7	0.6
90°-100°	39.3	0.5
100°-110°	144.0	2.0
110°-120°	385.0	5.2
120°-130°	635.6	8.6
130°-140°	675.9	9.2
140°-150°	628.3	8.5
150°-160°	505.1	6.8
160°-170°	325.5	4.4
170°-180°	112.0	1.5
0°-30°	1376.1	18.7
0°-40°	2130.1	28.9
0°-60°	3330.4	45.1
0°-90°	3925.8	53.2
90°-120°	568.4	7.7
90°-150°	2508.2	34.0
90°-180°	3451.0	46.8
0°-180°	7376.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	23	1	23	1	23	12
95°	37	55	37	55	37	34
105°	65	259	65	259	65	67
115°	70	490	70	490	70	175
125°	728	693	728	693	728	630
135°	885	857	885	857	885	682
145°	1010	994	1010	994	1010	631
155°	1096	1095	1096	1095	1096	506
165°	1151	1154	1151	1154	1151	325
175°	1173	1180	1173	1180	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	18.8	18.7	19.2	18.5	18.5	18.9	18.7	18.0	18.4	18.7	19.0
90°	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9	18.0	17.0	15.5
92.5°	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8	20.2	19.8	19.0
95°	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1	34.2	33.3	31.9
97.5°	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0	45.2	44.5	41.4
100°	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6	50.1	48.6	45.4
102.5°	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9	51.9	49.9	46.9
105°	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2	54.0	52.0	49.7
107.5°	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5	70.6	72.8	70.7
110°	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2	130.2	149.1	203.8



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9	307.0	376.1	389.6
115°	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4	438.0	525.8	521.0
117.5°	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8	561.1	582.3	579.1
120°	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1	626.9	624.6	621.2
122.5°	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5	666.1	664.8	661.0
125°	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6	721.3	720.0	716.4
127.5°	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6	771.7	769.7	767.0
130°	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9	803.9	801.8	799.7
132.5°	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4	835.6	833.8	831.7
135°	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3	880.4	878.5	876.7
137.5°	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9	922.1	920.2	918.3
140°	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9	949.2	947.5	945.4
142.5°	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8	974.3	972.7	970.4
145°	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7	1009.3	1008.0	1004.8
147.5°	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0	1040.0	1039.0	1035.8
150°	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7	1058.5	1057.4	1054.4
152.5°	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7	1075.6	1074.4	1071.6
155°	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7	1098.6	1097.4	1095.2
157.5°	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1	1117.8	1116.5	1114.9
160°	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4	1129.3	1128.1	1127.0
162.5°	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9	1139.6	1138.4	1137.4
165°	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1	1150.6
167.5°	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5	1163.1	1161.9	1161.4
170°	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0	1168.7	1167.3	1167.0
172.5°	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0	1172.8	1171.4	1171.0
175°	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5	1177.1	1175.8	1175.5
177.5°	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0	1177.9	1176.9	1176.7
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	19.2	18.9	18.6	19.4	17.3	16.9	14.3	12.2	12.0	11.9	11.2
90°	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9	2.9	5.0	7.1
92.5°	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2	17.0	16.9	16.7
95°	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4	49.1	42.9	36.6
97.5°	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9	92.3	74.7	57.1
100°	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8	124.8	98.9	73.0
102.5°	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8	190.3	184.9	179.3
105°	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0	264.7	270.4	276.1
107.5°	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1	335.7	340.3	344.8
110°	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5	381.5	385.4	389.4



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1	424.6	428.1	431.7
115°	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9	493.1	496.4	499.6
117.5°	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4	555.1	558.7	562.2
120°	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5	599.3	602.1	604.9
122.5°	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6	637.6	640.6	643.5
125°	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7	695.2	697.7	700.1
127.5°	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4	748.1	750.8	753.6
130°	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8	781.9	784.9	787.8
132.5°	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9	815.5	818.1	820.6
135°	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2	860.2	863.3	866.3
137.5°	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0	904.1	906.2	908.4
140°	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3	932.8	934.3	935.9
142.5°	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8	957.2	958.6	959.9
145°	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3	994.2	994.0	993.8
147.5°	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0	1027.2	1026.4	1025.7
150°	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7	1048.4	1047.0	1045.8
152.5°	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2	1066.7	1065.1	1063.7
155°	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9	1093.1	1091.5	1089.8
157.5°	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9	1114.5	1112.9	1111.5
160°	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1127.0	1125.9	1124.7
162.5°	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1	1137.9	1136.8	1135.6
165°	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7	1152.5	1151.4	1150.3
167.5°	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6	1163.4	1162.3	1161.2
170°	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7	1169.6	1168.5	1167.3
172.5°	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8	1173.7	1172.5	1171.4
175°	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1	1178.8	1177.4	1176.2
177.5°	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0	1179.9	1178.8	1177.8
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	11.1	11.0	10.7	11.0	10.8	10.5	10.2	10.3	10.5	9.6	9.8
90°	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9	19.9	20.9	21.5
92.5°	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8	21.2	21.8	22.1
95°	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1	36.1	37.0	37.4
97.5°	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0	46.7	47.5	48.0
100°	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6	53.1	54.7	55.6
102.5°	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9	55.8	57.8	59.0
105°	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2	58.2	60.3	61.7
107.5°	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5	66.4	64.3	63.6
110°	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2	92.3	73.4	64.3



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9	168.9	99.8	65.5
115°	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4	262.7	175.0	124.4
117.5°	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8	518.7	497.5	464.5
120°	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1	631.3	633.6	622.0
122.5°	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5	668.9	670.2	668.4
125°	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6	724.0	725.3	726.2
127.5°	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6	775.5	777.5	778.5
130°	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9	808.1	810.1	811.1
132.5°	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4	839.2	841.0	841.8
135°	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3	884.1	886.0	886.8
137.5°	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9	925.8	927.6	928.3
140°	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9	952.6	954.3	954.7
142.5°	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8	977.4	978.9	979.2
145°	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7	1012.0	1013.3	1013.5
147.5°	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0	1042.0	1042.9	1043.0
150°	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7	1060.8	1061.9	1062.0
152.5°	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7	1077.8	1079.0	1079.0
155°	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7	1100.8	1102.0	1101.8
157.5°	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1	1120.4	1121.7	1121.6
160°	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4	1131.5	1132.7	1132.6
162.5°	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9	1142.2	1143.5	1143.4
165°	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5
167.5°	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5	1165.8	1167.2	1167.0
170°	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0	1171.3	1172.6	1172.4
172.5°	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0	1175.4	1176.7	1176.5
175°	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5	1179.8	1181.2	1180.9
177.5°	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0	1180.0	1181.1	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	9.8	9.4	9.5	9.0	9.5	9.4	9.8	9.8	9.6	10.5	10.3
90°	21.8	22.2	22.6	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9
92.5°	22.3	22.6	22.7	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8
95°	37.2	37.0	36.8	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1
97.5°	48.2	48.4	48.7	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0
100°	55.9	56.4	56.7	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6
102.5°	59.6	60.1	60.6	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9
105°	62.5	63.2	64.0	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2
107.5°	64.4	65.1	65.9	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5
110°	65.0	65.8	66.5	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	66.2	66.8	67.4	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9
115°	110.8	97.1	83.5	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4
117.5°	419.6	374.9	330.1	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8
120°	596.5	570.9	545.3	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1
122.5°	663.4	658.5	653.5	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5
125°	726.8	727.4	727.9	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6
127.5°	778.6	778.7	778.8	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6
130°	810.8	810.7	810.5	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9
132.5°	841.5	841.3	841.2	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4
135°	886.4	886.0	885.6	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3
137.5°	927.6	926.9	926.3	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9
140°	953.8	952.8	951.8	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9
142.5°	978.3	977.3	976.4	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8
145°	1012.5	1011.6	1010.7	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7
147.5°	1042.2	1041.4	1040.6	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0
150°	1061.1	1060.2	1059.2	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7
152.5°	1077.7	1076.5	1075.2	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7
155°	1100.3	1098.8	1097.3	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7
157.5°	1120.1	1118.7	1117.1	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1
160°	1131.2	1129.9	1128.6	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4
162.5°	1141.7	1140.1	1138.4	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9
165°	1155.1	1153.8	1152.4	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8
167.5°	1165.3	1163.6	1161.9	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5
170°	1170.7	1169.0	1167.3	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0
172.5°	1174.8	1173.1	1171.4	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0
175°	1178.9	1177.1	1175.2	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5
177.5°	1179.6	1178.2	1176.9	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	10.2	10.5	10.8	11.0	10.7	11.0	11.1	11.2	11.9	12.0	12.2
90°	18.0	17.0	15.5	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9
92.5°	20.2	19.8	19.0	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2
95°	34.2	33.3	31.9	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4
97.5°	45.2	44.5	41.4	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9
100°	50.1	48.6	45.4	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8
102.5°	51.9	49.9	76.9	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8
105°	54.0	52.0	103.7	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0
107.5°	70.6	72.8	134.7	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1
110°	130.2	149.1	203.8	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	307.0	376.1	389.6	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1
115°	438.0	525.8	521.0	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9
117.5°	561.1	582.3	579.1	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4
120°	626.9	624.6	621.2	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5
122.5°	666.1	664.8	661.0	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6
125°	721.3	720.0	716.4	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7
127.5°	771.7	769.7	767.0	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4
130°	803.9	801.8	799.7	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8
132.5°	835.6	833.8	831.7	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9
135°	880.4	878.5	876.7	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2
137.5°	922.1	920.2	918.3	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0
140°	949.2	947.5	945.4	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3
142.5°	974.3	972.7	970.4	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8
145°	1009.3	1008.0	1004.8	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3
147.5°	1040.0	1039.0	1035.8	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0
150°	1058.5	1057.4	1054.4	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7
152.5°	1075.6	1074.4	1071.6	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2
155°	1098.6	1097.4	1095.2	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9
157.5°	1117.8	1116.5	1114.9	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9
160°	1129.3	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1
162.5°	1139.6	1138.4	1137.4	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1
165°	1152.4	1151.1	1150.6	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7
167.5°	1163.1	1161.9	1161.4	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6
170°	1168.7	1167.3	1167.0	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7
172.5°	1172.8	1171.4	1171.0	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8
175°	1177.1	1175.8	1175.5	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1
177.5°	1177.9	1176.9	1176.7	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	14.3	16.9	17.3	19.4	18.6	18.9	19.2	19.0	18.7	18.4	18.0
90°	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9
92.5°	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8
95°	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1
97.5°	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0
100°	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6
102.5°	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9
105°	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2
107.5°	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5
110°	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9
115°	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4
117.5°	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8
120°	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1
122.5°	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5
125°	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6
127.5°	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6
130°	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9
132.5°	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4
135°	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3
137.5°	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9
140°	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9
142.5°	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8
145°	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7
147.5°	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0
150°	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7
152.5°	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7
155°	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7
157.5°	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1
160°	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4
162.5°	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9
165°	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8
167.5°	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5
170°	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0
172.5°	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0
175°	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5
177.5°	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	18.7	18.9	18.5	18.5	19.2	18.7	18.8
90°	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	92.3	73.4	64.3	65.0	65.8	66.5	67.3



TEST NUMBER: P331597-940

CATALOG NUMBER: S122DIW-S1005D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)