

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332485-830

Luminaire Tested: **S123RDIW-S1165D1320U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332485-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8443.1 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	30
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21	18
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.5	2.0
10°-20°	477.3	5.7
20°-30°	687.3	8.1
30°-40°	774.2	9.2
40°-50°	740.6	8.8
50°-60°	606.5	7.2
60°-70°	409.2	4.8
70°-80°	205.9	2.4
80°-90°	59.1	0.7
90°-100°	101.4	1.2
100°-110°	303.4	3.6
110°-120°	516.1	6.1
120°-130°	678.8	8.0
130°-140°	763.0	9.0
140°-150°	750.0	8.9
150°-160°	631.4	7.5
160°-170°	420.3	5.0
170°-180°	147.2	1.7
0°-30°	1336.1	15.8
0°-40°	2110.3	25.0
0°-60°	3457.4	40.9
0°-90°	4131.5	48.9
90°-120°	920.9	10.9
90°-150°	3112.8	36.9
90°-180°	4312.0	51.1
0°-180°	8443.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	14	29	34	37	8
95°	72	81	90	95	95	81
105°	275	278	288	289	291	295
115°	520	523	521	522	521	514
125°	760	764	762	757	752	678
135°	987	993	993	988	985	760
145°	1197	1199	1203	1202	1197	747
155°	1370	1370	1372	1376	1368	631
165°	1493	1489	1489	1495	1488	421
175°	1553	1548	1548	1554	1546	147
180°	1556	1556	1556	1556	1556	



TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.7	26.3	23.9	21.6	19.2	18.5	19.1	19.9	20.5	21.3	21.2
90°	1.2	4.0	6.7	9.3	12.1	15.2	18.8	22.2	25.8	29.3	30.4
92.5°	29.6	31.4	33.3	35.2	36.9	38.9	40.9	42.9	45.0	46.9	47.8
95°	72.1	74.0	76.0	77.9	79.7	81.8	84.0	86.1	88.3	90.5	91.5
97.5°	128.1	129.5	130.9	132.3	133.7	135.3	136.9	138.4	140.0	141.6	142.8
100°	166.3	167.9	169.5	171.2	172.8	174.3	175.6	177.0	178.3	179.7	180.5
102.5°	210.3	211.2	212.3	213.2	214.1	215.6	217.4	219.1	220.9	222.7	223.6
105°	275.0	275.6	276.2	276.6	277.2	278.7	281.2	283.6	286.1	288.5	288.5
107.5°	350.3	350.7	351.0	351.4	351.7	352.3	353.3	354.3	355.2	356.2	357.1
110°	397.3	397.8	398.4	398.9	399.4	400.0	400.6	401.1	401.6	402.2	403.3



TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.5	446.9	447.1	447.5	447.7	447.8	447.9	448.1	448.2	449.5
115°	519.5	520.4	521.1	522.0	522.8	522.9	522.4	521.9	521.3	520.8	521.0
117.5°	593.4	593.9	594.5	595.0	595.6	595.5	594.7	594.1	593.3	592.7	592.6
120°	639.3	640.9	642.6	644.2	645.8	646.0	644.6	643.3	642.0	640.6	640.3
122.5°	687.3	688.4	689.7	690.9	692.0	692.3	691.5	690.9	690.1	689.5	688.7
125°	760.3	761.2	762.0	762.8	763.6	763.7	763.2	762.7	762.1	761.6	760.5
127.5°	827.8	829.6	831.3	833.0	834.8	835.4	834.8	834.2	833.6	833.0	831.4
130°	872.8	875.0	877.2	879.4	881.6	882.2	881.4	880.6	879.8	878.9	877.9
132.5°	917.8	920.0	922.2	924.4	926.5	927.3	926.7	926.1	925.5	924.9	923.6
135°	986.6	988.2	989.8	991.4	993.1	993.7	993.4	993.2	992.9	992.6	991.6
137.5°	1050.1	1051.4	1052.8	1054.1	1055.6	1056.6	1057.2	1058.0	1058.7	1059.4	1058.2
140°	1094.1	1095.4	1096.8	1098.2	1099.6	1100.3	1100.6	1100.9	1101.2	1101.5	1101.2
142.5°	1134.2	1135.6	1136.9	1138.3	1139.6	1140.6	1141.0	1141.5	1142.0	1142.6	1142.3
145°	1196.7	1197.3	1197.9	1198.4	1198.9	1199.7	1200.4	1201.3	1202.1	1202.9	1202.6
147.5°	1251.5	1252.5	1253.5	1254.5	1255.5	1256.3	1257.1	1257.8	1258.6	1259.3	1259.3
150°	1289.7	1290.2	1290.8	1291.3	1291.8	1292.4	1293.0	1293.5	1294.0	1294.6	1294.6
152.5°	1321.0	1321.7	1322.5	1323.2	1324.0	1324.6	1324.9	1325.2	1325.6	1325.9	1326.3
155°	1370.4	1370.4	1370.4	1370.4	1370.4	1370.6	1370.7	1371.0	1371.3	1371.6	1372.7
157.5°	1412.4	1412.1	1411.7	1411.5	1411.1	1411.1	1411.3	1411.5	1411.7	1411.9	1413.1
160°	1438.8	1438.3	1437.8	1437.2	1436.6	1436.3	1436.3	1436.3	1436.3	1436.3	1437.8
162.5°	1462.3	1461.5	1460.8	1460.0	1459.2	1459.0	1459.2	1459.4	1459.6	1459.8	1461.2
165°	1492.6	1491.8	1491.0	1490.2	1489.4	1488.9	1488.9	1488.9	1488.9	1488.9	1490.5
167.5°	1516.8	1515.7	1514.7	1513.5	1512.5	1512.0	1512.2	1512.5	1512.7	1512.9	1514.6
170°	1530.5	1529.5	1528.3	1527.3	1526.2	1525.6	1525.6	1525.6	1525.6	1525.6	1527.5
172.5°	1541.2	1540.2	1539.1	1538.0	1536.9	1536.3	1536.3	1536.3	1536.3	1536.3	1538.0
175°	1552.6	1551.4	1550.4	1549.3	1548.1	1547.7	1547.7	1547.7	1547.7	1547.7	1549.3
177.5°	1557.2	1556.3	1555.4	1554.5	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1554.5
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2



TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	21.2	21.1	21.1	21.0	20.8	20.6	20.5	20.4
90°	31.5	32.6	33.6	34.5	35.1	35.6	36.1	36.7
92.5°	48.6	49.6	50.4	50.7	50.3	50.0	49.7	49.4
95°	92.7	93.7	94.8	95.4	95.4	95.4	95.4	95.4
97.5°	144.0	145.3	146.6	147.1	147.0	146.9	146.8	146.7
100°	181.3	182.1	182.9	183.6	184.2	184.7	185.3	185.8
102.5°	224.3	225.2	226.0	226.3	226.2	226.1	226.0	225.9
105°	288.5	288.5	288.5	288.8	289.4	289.8	290.4	291.0
107.5°	358.0	358.8	359.7	360.0	359.7	359.3	359.0	358.6
110°	404.4	405.5	406.5	406.8	406.2	405.8	405.2	404.6





TEST NUMBER: P332485-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.7	452.0	453.4	453.9	453.8	453.7	453.6	453.6
115°	521.3	521.6	521.9	521.9	521.6	521.3	521.0	520.8
117.5°	592.6	592.5	592.4	592.0	591.3	590.5	589.7	589.0
120°	640.0	639.8	639.5	639.0	638.6	638.0	637.4	636.9
122.5°	688.1	687.3	686.6	685.9	685.1	684.4	683.6	682.9
125°	759.4	758.4	757.2	756.2	755.1	753.9	752.9	751.8
127.5°	829.9	828.4	826.9	825.5	824.3	823.0	821.8	820.5
130°	876.8	875.7	874.6	873.1	871.2	869.3	867.4	865.5
132.5°	922.3	921.0	919.7	918.3	916.8	915.4	913.9	912.5
135°	990.4	989.4	988.3	987.5	986.9	986.4	985.8	985.3
137.5°	1057.1	1055.9	1054.8	1053.8	1052.7	1051.7	1050.7	1049.6
140°	1100.9	1100.6	1100.3	1099.3	1097.4	1095.4	1093.5	1091.7
142.5°	1142.0	1141.7	1141.4	1140.6	1139.1	1137.6	1136.1	1134.7
145°	1202.3	1202.1	1201.8	1201.2	1200.0	1198.9	1197.9	1196.7
147.5°	1259.3	1259.3	1259.3	1258.6	1257.0	1255.3	1253.7	1252.1
150°	1294.6	1294.6	1294.6	1293.7	1292.1	1290.5	1288.8	1287.2
152.5°	1326.7	1327.2	1327.6	1327.1	1325.7	1324.3	1322.9	1321.4
155°	1373.8	1374.9	1375.9	1375.5	1373.7	1371.8	1369.8	1367.9
157.5°	1414.2	1415.3	1416.5	1416.3	1414.8	1413.2	1411.7	1410.2
160°	1439.1	1440.5	1441.8	1442.0	1440.9	1439.8	1438.7	1437.6
162.5°	1462.5	1464.0	1465.3	1465.1	1463.4	1461.6	1459.9	1458.1
165°	1492.2	1493.8	1495.4	1495.3	1493.5	1491.6	1489.6	1487.7
167.5°	1516.3	1518.0	1519.7	1519.7	1518.0	1516.3	1514.6	1512.9
170°	1529.5	1531.3	1533.2	1533.2	1531.3	1529.5	1527.5	1525.6
172.5°	1539.7	1541.4	1543.1	1543.0	1541.2	1539.2	1537.3	1535.4
175°	1550.9	1552.6	1554.2	1554.0	1552.1	1550.2	1548.3	1546.4
177.5°	1555.9	1557.2	1558.5	1558.4	1556.8	1555.3	1553.8	1552.3
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2

(END OF REPORT)