

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331488-940

Luminaire Tested: **S122DIW-S290D1240U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331488-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D1240U940-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4908.4 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	91	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	25	18
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	54	67	59	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	47	38	31	26	29	24	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.6	0.8
10°-20°	111.5	2.3
20°-30°	163.8	3.3
30°-40°	190.3	3.9
40°-50°	190.1	3.9
50°-60°	165.8	3.4
60°-70°	122.6	2.5
70°-80°	69.4	1.4
80°-90°	24.1	0.5
90°-100°	86.8	1.8
100°-110°	269.6	5.5
110°-120°	460.9	9.4
120°-130°	606.1	12.3
130°-140°	680.3	13.9
140°-150°	667.1	13.6
150°-160°	559.5	11.4
160°-170°	371.1	7.6
170°-180°	129.7	2.6
0°-30°	314.9	6.4
0°-40°	505.2	10.3
0°-60°	861.1	17.5
0°-90°	1077.2	21.9
90°-120°	817.4	16.7
90°-150°	2770.9	56.5
90°-180°	3831.0	78.1
0°-180°	4908.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	1	16	40	38	39	4
95°	60	71	74	74	72	69
105°	249	252	254	257	257	263
115°	462	469	467	466	462	457
125°	673	683	680	677	675	601
135°	871	883	886	884	881	672
145°	1057	1065	1072	1073	1068	660
155°	1208	1212	1215	1220	1218	556
165°	1315	1314	1314	1321	1316	371
175°	1368	1364	1362	1369	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	6.1	6.5	7.0	7.5	7.9	8.6	9.6	10.7	11.7	12.7	12.3
90°	1.2	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9
92.5°	20.6	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8
95°	60.1	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0
97.5°	109.9	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4
100°	146.9	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5
102.5°	185.7	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7
105°	248.6	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9
107.5°	311.9	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3
110°	352.7	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.1	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4
115°	462.5	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9
117.5°	527.7	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9
120°	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1
122.5°	610.9	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9
125°	672.9	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1
127.5°	733.3	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4
130°	771.2	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4
132.5°	813.8	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4
135°	870.7	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4
137.5°	930.5	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8
140°	966.6	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8
142.5°	1003.6	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2
145°	1056.8	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1
147.5°	1104.2	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1
150°	1136.6	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9
152.5°	1165.3	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8
155°	1208.3	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5
157.5°	1245.0	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2
160°	1267.2	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2
162.5°	1287.5	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9
165°	1314.6	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3
167.5°	1337.3	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4
170°	1349.3	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5
172.5°	1357.6	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9
175°	1367.8	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9
177.5°	1372.0	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	11.9	11.7	11.3	11.1	11.1	11.1	11.1	11.1
90°	39.4	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.0	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	197.9	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.4	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.4	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.6	359.2	358.5	357.7	356.9	356.1





TEST NUMBER: P331488-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.8	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.6	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	529.2	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	614.4	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	678.3	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	740.5	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.9	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	824.2	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	885.2	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.5	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.3	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.4	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1119.6	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1217.8	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1252.9	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1273.8	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1292.7	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1317.1	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1337.2	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1348.3	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1356.6	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1365.7	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)