

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331493-940

Luminaire Tested: **S122DIW-S290D1440U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331493-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6212.4 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17				
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	23	22	22	15				
2	82	75	70	65	72	66	62	58	50	47	44	34	33	31	20	19	18	12				
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	18	17	16	10				
4	68	58	51	45	60	52	45	40	39	35	31	27	24	22	16	15	13	9				
5	63	52	44	38	55	46	39	34	35	30	27	24	21	19	14	13	12	8				
6	58	46	39	33	50	41	34	30	31	26	23	22	19	17	13	11	10	7				
7	53	41	34	29	47	37	30	26	28	23	20	20	17	15	12	10	9	6				
8	49	37	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5				
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5				
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	0.6
10°-20°	111.5	1.8
20°-30°	163.8	2.6
30°-40°	190.3	3.1
40°-50°	190.1	3.1
50°-60°	165.8	2.7
60°-70°	122.6	2.0
70°-80°	69.4	1.1
80°-90°	23.0	0.4
90°-100°	58.5	0.9
100°-110°	214.4	3.5
110°-120°	573.1	9.2
120°-130°	946.0	15.2
130°-140°	1006.1	16.2
140°-150°	935.1	15.1
150°-160°	751.8	12.1
160°-170°	484.5	7.8
170°-180°	166.8	2.7
0°-30°	314.9	5.1
0°-40°	505.2	8.1
0°-60°	861.1	13.9
0°-90°	1076.1	17.3
90°-120°	846.0	13.6
90°-150°	3733.2	60.1
90°-180°	5136.0	82.7
0°-180°	6212.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	1	15	25	32	34	5
95°	82	43	50	55	55	101
105°	386	402	77	91	96	412
115°	729	751	782	223	104	718
125°	1031	1048	1072	1080	1084	919
135°	1276	1296	1308	1319	1318	985
145°	1480	1480	1500	1508	1503	925
155°	1630	1620	1633	1640	1631	751
165°	1717	1710	1713	1721	1713	485
175°	1756	1748	1750	1758	1746	167
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	6.1	6.6	7.0	7.5	8.0	8.4	8.6	9.0	9.3	9.6	9.7
90°	1.2	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8
92.5°	25.6	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1
95°	82.4	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8
97.5°	163.6	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3
100°	224.4	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5
102.5°	291.4	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2
105°	385.6	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4
107.5°	492.8	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1
110°	561.9	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8



TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.8	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0
115°	729.2	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0
117.5°	820.8	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2
120°	887.8	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0
122.5°	944.6	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5
125°	1031.1	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6
127.5°	1109.5	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6
130°	1159.1	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5
132.5°	1209.9	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8
135°	1275.9	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4
137.5°	1342.6	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4
140°	1386.2	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8
142.5°	1422.7	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1
145°	1480.1	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3
147.5°	1530.0	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9
150°	1562.5	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6
152.5°	1589.8	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9
155°	1629.7	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1
157.5°	1660.9	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8
160°	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8
162.5°	1695.3	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3
165°	1717.2	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4
167.5°	1733.4	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3
170°	1742.6	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5
172.5°	1748.6	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5
175°	1756.5	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1
177.5°	1757.7	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	9.7	9.8	9.9	9.9	10.0	10.0	10.1	10.1
90°	28.2	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	30.9	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	52.3	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	68.5	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	76.8	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	80.2	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	83.6	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	102.0	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	165.6	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331493-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	354.2	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	521.6	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	803.6	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	936.4	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	993.5	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1075.6	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1151.5	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1199.6	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1246.3	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1313.1	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1375.2	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1415.3	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1452.4	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1504.2	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1549.4	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1577.3	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1602.6	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1636.8	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1665.7	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1682.5	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1698.2	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1733.3	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1741.4	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1747.5	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1754.1	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1754.8	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)