

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331465-940

Luminaire Tested: **S122DIW-S290D435U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331465-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D435U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2707.7 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.9
10°-20°	145.9	5.4
20°-30°	211.8	7.8
30°-40°	223.5	8.3
40°-50°	197.9	7.3
50°-60°	157.9	5.8
60°-70°	107.3	4.0
70°-80°	55.0	2.0
80°-90°	14.6	0.5
90°-100°	17.6	0.6
100°-110°	64.4	2.4
110°-120°	172.2	6.4
120°-130°	284.3	10.5
130°-140°	302.4	11.2
140°-150°	281.0	10.4
150°-160°	225.9	8.3
160°-170°	145.6	5.4
170°-180°	50.1	1.9
0°-30°	407.9	15.1
0°-40°	631.4	23.3
0°-60°	987.2	36.5
0°-90°	1164.1	43.0
90°-120°	254.2	9.4
90°-150°	1121.9	41.4
90°-180°	1544.0	57.0
0°-180°	2707.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	12
90°	10	0	10	0	10	5
95°	16	25	16	25	16	15
105°	29	116	29	116	29	30
115°	31	219	31	219	31	78
125°	326	310	326	310	326	282
135°	396	383	396	383	396	305
145°	452	445	452	445	452	282
155°	490	490	490	490	490	226
165°	515	516	515	516	515	145
175°	525	528	525	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	6.2	6.2	6.3	6.2	6.2	6.2	6.2	5.9	6.0	6.1	6.1
90°	10.3	10.2	10.0	9.8	9.6	9.3	8.9	8.5	8.0	7.6	7.0
92.5°	10.3	10.2	10.1	10.0	9.9	9.7	9.5	9.3	9.1	8.8	8.5
95°	16.4	16.5	16.6	16.7	16.8	16.6	16.1	15.7	15.2	14.9	14.3
97.5°	21.8	21.8	21.7	21.6	21.5	21.2	21.0	20.6	20.2	19.9	18.5
100°	25.5	25.3	25.2	25.1	24.9	24.4	23.7	23.1	22.4	21.8	20.2
102.5°	27.4	27.1	26.9	26.7	26.4	25.9	25.0	24.1	23.2	22.3	34.4
105°	29.0	28.6	28.3	27.9	27.6	27.0	26.0	25.1	24.2	23.3	46.4
107.5°	29.8	29.4	29.2	28.8	28.4	28.7	29.7	30.7	31.6	32.5	60.3
110°	30.1	29.8	29.4	29.1	28.7	32.8	41.3	49.8	58.2	66.7	91.1



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	30.4	30.1	29.9	29.6	29.3	44.7	75.5	106.5	137.3	168.3	174.2
115°	31.2	37.4	43.4	49.6	55.6	78.3	117.5	156.8	195.9	235.1	233.0
117.5°	127.6	147.7	167.6	187.7	207.8	222.5	232.0	241.5	251.0	260.5	259.0
120°	232.5	243.9	255.4	266.8	278.2	283.5	282.4	281.4	280.4	279.4	277.9
122.5°	290.1	292.3	294.5	296.8	299.0	299.8	299.2	298.5	298.0	297.4	295.7
125°	325.8	325.7	325.4	325.1	324.9	324.4	323.9	323.2	322.6	322.1	320.5
127.5°	348.4	348.4	348.3	348.3	348.2	347.8	346.9	346.1	345.2	344.3	343.1
130°	362.5	362.6	362.7	362.7	362.8	362.4	361.4	360.5	359.5	358.6	357.8
132.5°	376.2	376.3	376.3	376.4	376.5	376.1	375.3	374.6	373.8	373.0	372.0
135°	396.0	396.2	396.4	396.5	396.6	396.4	395.5	394.7	393.8	393.0	392.2
137.5°	414.0	414.4	414.6	414.9	415.2	414.9	414.1	413.3	412.4	411.6	410.7
140°	425.3	425.8	426.1	426.6	427.0	426.9	426.1	425.3	424.5	423.8	422.8
142.5°	436.3	436.8	437.2	437.6	438.0	437.9	437.2	436.5	435.8	435.1	434.0
145°	451.7	452.1	452.5	452.9	453.3	453.3	452.6	452.1	451.5	450.8	449.4
147.5°	465.1	465.5	465.8	466.2	466.5	466.5	466.1	465.7	465.2	464.8	463.3
150°	473.4	473.8	474.2	474.7	475.1	475.0	474.5	474.0	473.5	473.0	471.6
152.5°	480.4	480.9	481.5	482.1	482.6	482.7	482.1	481.6	481.1	480.6	479.3
155°	490.2	490.8	491.5	492.1	492.8	492.9	492.4	492.0	491.4	490.9	489.9
157.5°	499.1	499.7	500.3	501.1	501.7	501.8	501.1	500.6	500.0	499.4	498.7
160°	504.3	504.8	505.4	506.0	506.6	506.7	506.1	505.6	505.2	504.6	504.1
162.5°	508.5	509.3	510.0	510.7	511.4	511.5	511.0	510.3	509.8	509.2	508.7
165°	514.9	515.5	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9	514.7
167.5°	519.0	519.7	520.5	521.2	522.0	522.1	521.5	520.9	520.3	519.7	519.5
170°	521.4	522.2	522.9	523.7	524.4	524.5	524.0	523.3	522.7	522.2	522.0
172.5°	523.3	524.0	524.8	525.5	526.3	526.4	525.8	525.1	524.6	524.0	523.8
175°	524.9	525.7	526.6	527.4	528.2	528.3	527.7	527.2	526.6	525.9	525.8
177.5°	525.8	526.4	527.0	527.6	528.2	528.3	527.8	527.4	526.9	526.4	526.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	6.2	6.0	5.9	6.0	5.4	5.2	4.3	3.7	3.7	3.7	3.6
90°	6.2	5.6	4.9	4.1	3.2	2.2	1.3	0.4	1.3	2.2	3.2
92.5°	8.2	7.8	7.5	7.4	7.4	7.5	7.6	7.7	7.6	7.5	7.4
95°	13.6	13.1	12.5	13.6	16.4	19.2	21.9	24.8	21.9	19.2	16.4
97.5°	17.1	15.8	14.4	17.7	25.5	33.4	41.3	49.1	41.3	33.4	25.5
100°	18.8	17.4	16.0	21.0	32.6	44.2	55.8	67.5	55.8	44.2	32.6
102.5°	46.5	58.5	70.5	77.8	80.3	82.7	85.2	87.6	85.2	82.7	80.3
105°	69.5	92.6	115.7	126.0	123.5	120.9	118.4	115.8	118.4	120.9	123.5
107.5°	88.0	115.7	143.5	156.3	154.3	152.2	150.2	148.1	150.2	152.2	154.3
110°	115.7	140.1	164.6	175.9	174.2	172.4	170.6	168.8	170.6	172.4	174.2



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	180.3	186.4	192.4	194.7	193.1	191.5	189.9	188.3	189.9	191.5	193.1
115°	231.0	228.8	226.7	224.9	223.5	222.0	220.6	219.2	220.6	222.0	223.5
117.5°	257.5	256.1	254.7	253.1	251.5	249.9	248.3	246.6	248.3	249.9	251.5
120°	276.3	274.8	273.3	271.9	270.6	269.3	268.0	266.8	268.0	269.3	270.6
122.5°	294.0	292.4	290.7	289.2	287.8	286.5	285.2	283.8	285.2	286.5	287.8
125°	318.9	317.3	315.6	314.2	313.2	312.1	310.9	309.9	310.9	312.1	313.2
127.5°	341.9	340.7	339.5	338.3	337.1	335.8	334.7	333.4	334.7	335.8	337.1
130°	356.8	355.9	354.9	353.7	352.4	351.1	349.7	348.4	349.7	351.1	352.4
132.5°	371.1	370.1	369.3	368.2	367.0	365.9	364.7	363.6	364.7	365.9	367.0
135°	391.5	390.7	389.9	388.9	387.4	386.1	384.8	383.4	384.8	386.1	387.4
137.5°	409.9	409.0	408.1	407.2	406.4	405.4	404.4	403.5	404.4	405.4	406.4
140°	422.0	421.1	420.1	419.3	418.6	417.9	417.2	416.6	417.2	417.9	418.6
142.5°	432.9	431.9	430.9	430.0	429.4	428.7	428.2	427.6	428.2	428.7	429.4
145°	448.0	446.6	445.1	444.4	444.5	444.6	444.7	444.8	444.7	444.6	444.5
147.5°	461.9	460.5	459.1	458.5	458.9	459.1	459.5	459.8	459.5	459.1	458.9
150°	470.3	469.0	467.5	467.2	467.8	468.3	469.0	469.6	469.0	468.3	467.8
152.5°	478.0	476.7	475.5	475.1	475.8	476.4	477.2	477.8	477.2	476.4	475.8
155°	488.8	487.9	486.9	486.7	487.5	488.2	489.0	489.7	489.0	488.2	487.5
157.5°	498.0	497.3	496.6	496.6	497.2	497.8	498.5	499.1	498.5	497.8	497.2
160°	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	504.1	503.6	503.1
162.5°	508.3	507.8	507.5	507.5	508.0	508.5	509.0	509.5	509.0	508.5	508.0
165°	514.4	514.2	513.9	514.0	514.5	515.1	515.6	516.0	515.6	515.1	514.5
167.5°	519.2	519.0	518.8	518.9	519.4	520.0	520.4	520.9	520.4	520.0	519.4
170°	521.8	521.7	521.5	521.7	522.2	522.6	523.2	523.7	523.2	522.6	522.2
172.5°	523.6	523.4	523.3	523.4	524.0	524.5	525.0	525.5	525.0	524.5	524.0
175°	525.7	525.5	525.3	525.5	526.1	526.6	527.3	527.9	527.3	526.6	526.1
177.5°	526.3	526.2	526.1	526.4	526.8	527.3	527.8	528.2	527.8	527.3	526.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	3.6	3.6	3.6	3.7	3.7	3.7	3.6	3.7	3.7	3.5	3.6
90°	4.1	4.9	5.6	6.2	7.0	7.6	8.0	8.5	8.9	9.3	9.6
92.5°	7.4	7.5	7.8	8.2	8.5	8.8	9.1	9.3	9.5	9.7	9.9
95°	13.6	12.5	13.1	13.6	14.3	14.9	15.2	15.7	16.1	16.6	16.8
97.5°	17.7	14.4	15.8	17.1	18.5	19.9	20.2	20.6	21.0	21.2	21.5
100°	21.0	16.0	17.4	18.8	20.2	21.8	22.4	23.1	23.7	24.4	24.9
102.5°	77.8	70.5	58.5	46.5	34.4	22.3	23.2	24.1	25.0	25.9	26.4
105°	126.0	115.7	92.6	69.5	46.4	23.3	24.2	25.1	26.0	27.0	27.6
107.5°	156.3	143.5	115.7	88.0	60.3	32.5	31.6	30.7	29.7	28.7	28.4
110°	175.9	164.6	140.1	115.7	91.1	66.7	58.2	49.8	41.3	32.8	28.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	194.7	192.4	186.4	180.3	174.2	168.3	137.3	106.5	75.5	44.7	29.3
115°	224.9	226.7	228.8	231.0	233.0	235.1	195.9	156.8	117.5	78.3	55.6
117.5°	253.1	254.7	256.1	257.5	259.0	260.5	251.0	241.5	232.0	222.5	207.8
120°	271.9	273.3	274.8	276.3	277.9	279.4	280.4	281.4	282.4	283.5	278.2
122.5°	289.2	290.7	292.4	294.0	295.7	297.4	298.0	298.5	299.2	299.8	299.0
125°	314.2	315.6	317.3	318.9	320.5	322.1	322.6	323.2	323.9	324.4	324.9
127.5°	338.3	339.5	340.7	341.9	343.1	344.3	345.2	346.1	346.9	347.8	348.2
130°	353.7	354.9	355.9	356.8	357.8	358.6	359.5	360.5	361.4	362.4	362.8
132.5°	368.2	369.3	370.1	371.1	372.0	373.0	373.8	374.6	375.3	376.1	376.5
135°	388.9	389.9	390.7	391.5	392.2	393.0	393.8	394.7	395.5	396.4	396.6
137.5°	407.2	408.1	409.0	409.9	410.7	411.6	412.4	413.3	414.1	414.9	415.2
140°	419.3	420.1	421.1	422.0	422.8	423.8	424.5	425.3	426.1	426.9	427.0
142.5°	430.0	430.9	431.9	432.9	434.0	435.1	435.8	436.5	437.2	437.9	438.0
145°	444.4	445.1	446.6	448.0	449.4	450.8	451.5	452.1	452.6	453.3	453.3
147.5°	458.5	459.1	460.5	461.9	463.3	464.8	465.2	465.7	466.1	466.5	466.5
150°	467.2	467.5	469.0	470.3	471.6	473.0	473.5	474.0	474.5	475.0	475.1
152.5°	475.1	475.5	476.7	478.0	479.3	480.6	481.1	481.6	482.1	482.7	482.6
155°	486.7	486.9	487.9	488.8	489.9	490.9	491.4	492.0	492.4	492.9	492.8
157.5°	496.6	496.6	497.3	498.0	498.7	499.4	500.0	500.6	501.1	501.8	501.7
160°	502.6	502.6	503.1	503.6	504.1	504.6	505.2	505.6	506.1	506.7	506.6
162.5°	507.5	507.5	507.8	508.3	508.7	509.2	509.8	510.3	511.0	511.5	511.4
165°	514.0	513.9	514.2	514.4	514.7	514.9	515.5	516.1	516.7	517.3	517.3
167.5°	518.9	518.8	519.0	519.2	519.5	519.7	520.3	520.9	521.5	522.1	522.0
170°	521.7	521.5	521.7	521.8	522.0	522.2	522.7	523.3	524.0	524.5	524.4
172.5°	523.4	523.3	523.4	523.6	523.8	524.0	524.6	525.1	525.8	526.4	526.3
175°	525.5	525.3	525.5	525.7	525.8	525.9	526.6	527.2	527.7	528.3	528.2
177.5°	526.4	526.1	526.2	526.3	526.4	526.4	526.9	527.4	527.8	528.3	528.2
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	3.6	3.5	3.5	3.4	3.5	3.5	3.6	3.6	3.5	3.7	3.7
90°	9.8	10.0	10.2	10.3	10.2	10.0	9.8	9.6	9.3	8.9	8.5
92.5°	10.0	10.1	10.2	10.3	10.2	10.1	10.0	9.9	9.7	9.5	9.3
95°	16.7	16.6	16.5	16.4	16.5	16.6	16.7	16.8	16.6	16.1	15.7
97.5°	21.6	21.7	21.8	21.8	21.8	21.7	21.6	21.5	21.2	21.0	20.6
100°	25.1	25.2	25.3	25.5	25.3	25.2	25.1	24.9	24.4	23.7	23.1
102.5°	26.7	26.9	27.1	27.4	27.1	26.9	26.7	26.4	25.9	25.0	24.1
105°	27.9	28.3	28.6	29.0	28.6	28.3	27.9	27.6	27.0	26.0	25.1
107.5°	28.8	29.2	29.4	29.8	29.4	29.2	28.8	28.4	28.7	29.7	30.7
110°	29.1	29.4	29.8	30.1	29.8	29.4	29.1	28.7	32.8	41.3	49.8



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	29.6	29.9	30.1	30.4	30.1	29.9	29.6	29.3	44.7	75.5	106.5
115°	49.6	43.4	37.4	31.2	37.4	43.4	49.6	55.6	78.3	117.5	156.8
117.5°	187.7	167.6	147.7	127.6	147.7	167.6	187.7	207.8	222.5	232.0	241.5
120°	266.8	255.4	243.9	232.5	243.9	255.4	266.8	278.2	283.5	282.4	281.4
122.5°	296.8	294.5	292.3	290.1	292.3	294.5	296.8	299.0	299.8	299.2	298.5
125°	325.1	325.4	325.7	325.8	325.7	325.4	325.1	324.9	324.4	323.9	323.2
127.5°	348.3	348.3	348.4	348.4	348.4	348.3	348.3	348.2	347.8	346.9	346.1
130°	362.7	362.7	362.6	362.5	362.6	362.7	362.7	362.8	362.4	361.4	360.5
132.5°	376.4	376.3	376.3	376.2	376.3	376.3	376.4	376.5	376.1	375.3	374.6
135°	396.5	396.4	396.2	396.0	396.2	396.4	396.5	396.6	396.4	395.5	394.7
137.5°	414.9	414.6	414.4	414.0	414.4	414.6	414.9	415.2	414.9	414.1	413.3
140°	426.6	426.1	425.8	425.3	425.8	426.1	426.6	427.0	426.9	426.1	425.3
142.5°	437.6	437.2	436.8	436.3	436.8	437.2	437.6	438.0	437.9	437.2	436.5
145°	452.9	452.5	452.1	451.7	452.1	452.5	452.9	453.3	453.3	452.6	452.1
147.5°	466.2	465.8	465.5	465.1	465.5	465.8	466.2	466.5	466.5	466.1	465.7
150°	474.7	474.2	473.8	473.4	473.8	474.2	474.7	475.1	475.0	474.5	474.0
152.5°	482.1	481.5	480.9	480.4	480.9	481.5	482.1	482.6	482.7	482.1	481.6
155°	492.1	491.5	490.8	490.2	490.8	491.5	492.1	492.8	492.9	492.4	492.0
157.5°	501.1	500.3	499.7	499.1	499.7	500.3	501.1	501.7	501.8	501.1	500.6
160°	506.0	505.4	504.8	504.3	504.8	505.4	506.0	506.6	506.7	506.1	505.6
162.5°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.4	511.5	511.0	510.3
165°	516.7	516.1	515.5	514.9	515.5	516.1	516.7	517.3	517.3	516.7	516.1
167.5°	521.2	520.5	519.7	519.0	519.7	520.5	521.2	522.0	522.1	521.5	520.9
170°	523.7	522.9	522.2	521.4	522.2	522.9	523.7	524.4	524.5	524.0	523.3
172.5°	525.5	524.8	524.0	523.3	524.0	524.8	525.5	526.3	526.4	525.8	525.1
175°	527.4	526.6	525.7	524.9	525.7	526.6	527.4	528.2	528.3	527.7	527.2
177.5°	527.6	527.0	526.4	525.8	526.4	527.0	527.6	528.2	528.3	527.8	527.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	3.6	3.7	3.7	3.7	3.6	3.6	3.6	3.6	3.7	3.7	3.7
90°	8.0	7.6	7.0	6.2	5.6	4.9	4.1	3.2	2.2	1.3	0.4
92.5°	9.1	8.8	8.5	8.2	7.8	7.5	7.4	7.4	7.5	7.6	7.7
95°	15.2	14.9	14.3	13.6	13.1	12.5	13.6	16.4	19.2	21.9	24.8
97.5°	20.2	19.9	18.5	17.1	15.8	14.4	17.7	25.5	33.4	41.3	49.1
100°	22.4	21.8	20.2	18.8	17.4	16.0	21.0	32.6	44.2	55.8	67.5
102.5°	23.2	22.3	34.4	46.5	58.5	70.5	77.8	80.3	82.7	85.2	87.6
105°	24.2	23.3	46.4	69.5	92.6	115.7	126.0	123.5	120.9	118.4	115.8
107.5°	31.6	32.5	60.3	88.0	115.7	143.5	156.3	154.3	152.2	150.2	148.1
110°	58.2	66.7	91.1	115.7	140.1	164.6	175.9	174.2	172.4	170.6	168.8



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	137.3	168.3	174.2	180.3	186.4	192.4	194.7	193.1	191.5	189.9	188.3
115°	195.9	235.1	233.0	231.0	228.8	226.7	224.9	223.5	222.0	220.6	219.2
117.5°	251.0	260.5	259.0	257.5	256.1	254.7	253.1	251.5	249.9	248.3	246.6
120°	280.4	279.4	277.9	276.3	274.8	273.3	271.9	270.6	269.3	268.0	266.8
122.5°	298.0	297.4	295.7	294.0	292.4	290.7	289.2	287.8	286.5	285.2	283.8
125°	322.6	322.1	320.5	318.9	317.3	315.6	314.2	313.2	312.1	310.9	309.9
127.5°	345.2	344.3	343.1	341.9	340.7	339.5	338.3	337.1	335.8	334.7	333.4
130°	359.5	358.6	357.8	356.8	355.9	354.9	353.7	352.4	351.1	349.7	348.4
132.5°	373.8	373.0	372.0	371.1	370.1	369.3	368.2	367.0	365.9	364.7	363.6
135°	393.8	393.0	392.2	391.5	390.7	389.9	388.9	387.4	386.1	384.8	383.4
137.5°	412.4	411.6	410.7	409.9	409.0	408.1	407.2	406.4	405.4	404.4	403.5
140°	424.5	423.8	422.8	422.0	421.1	420.1	419.3	418.6	417.9	417.2	416.6
142.5°	435.8	435.1	434.0	432.9	431.9	430.9	430.0	429.4	428.7	428.2	427.6
145°	451.5	450.8	449.4	448.0	446.6	445.1	444.4	444.5	444.6	444.7	444.8
147.5°	465.2	464.8	463.3	461.9	460.5	459.1	458.5	458.9	459.1	459.5	459.8
150°	473.5	473.0	471.6	470.3	469.0	467.5	467.2	467.8	468.3	469.0	469.6
152.5°	481.1	480.6	479.3	478.0	476.7	475.5	475.1	475.8	476.4	477.2	477.8
155°	491.4	490.9	489.9	488.8	487.9	486.9	486.7	487.5	488.2	489.0	489.7
157.5°	500.0	499.4	498.7	498.0	497.3	496.6	496.6	497.2	497.8	498.5	499.1
160°	505.2	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6
162.5°	509.8	509.2	508.7	508.3	507.8	507.5	507.5	508.0	508.5	509.0	509.5
165°	515.5	514.9	514.7	514.4	514.2	513.9	514.0	514.5	515.1	515.6	516.0
167.5°	520.3	519.7	519.5	519.2	519.0	518.8	518.9	519.4	520.0	520.4	520.9
170°	522.7	522.2	522.0	521.8	521.7	521.5	521.7	522.2	522.6	523.2	523.7
172.5°	524.6	524.0	523.8	523.6	523.4	523.3	523.4	524.0	524.5	525.0	525.5
175°	526.6	525.9	525.8	525.7	525.5	525.3	525.5	526.1	526.6	527.3	527.9
177.5°	526.9	526.4	526.4	526.3	526.2	526.1	526.4	526.8	527.3	527.8	528.2
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.3	5.2	5.4	6.0	5.9	6.0	6.2	6.1	6.1	6.0	5.9
90°	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0	8.5
92.5°	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1	9.3
95°	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2	15.7
97.5°	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2	20.6
100°	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4	23.1
102.5°	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2	24.1
105°	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2	25.1
107.5°	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6	30.7
110°	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2	49.8



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3	106.5
115°	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9	156.8
117.5°	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0	241.5
120°	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4	281.4
122.5°	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0	298.5
125°	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6	323.2
127.5°	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2	346.1
130°	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5	360.5
132.5°	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8	374.6
135°	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8	394.7
137.5°	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4	413.3
140°	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5	425.3
142.5°	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8	436.5
145°	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5	452.1
147.5°	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2	465.7
150°	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5	474.0
152.5°	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1	481.6
155°	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4	492.0
157.5°	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0	500.6
160°	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2	505.6
162.5°	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8	510.3
165°	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5	516.1
167.5°	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3	520.9
170°	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7	523.3
172.5°	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6	525.1
175°	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6	527.2
177.5°	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9	527.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	6.2	6.2	6.2	6.2	6.3	6.2	6.2
90°	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	41.3	32.8	28.7	29.1	29.4	29.8	30.1



TEST NUMBER: P331465-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)