

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331469-940

Luminaire Tested: **S122DIW-S290D435U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331469-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D435U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2616.7 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	42	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	1.5
10°-20°	111.5	4.3
20°-30°	163.8	6.3
30°-40°	190.3	7.3
40°-50°	190.1	7.3
50°-60°	165.8	6.3
60°-70°	122.6	4.7
70°-80°	69.4	2.7
80°-90°	20.0	0.8
90°-100°	17.6	0.7
100°-110°	64.4	2.5
110°-120°	172.2	6.6
120°-130°	284.3	10.9
130°-140°	302.4	11.6
140°-150°	281.0	10.7
150°-160°	225.9	8.6
160°-170°	145.6	5.6
170°-180°	50.1	1.9
0°-30°	314.9	12.0
0°-40°	505.2	19.3
0°-60°	861.1	32.9
0°-90°	1073.1	41.0
90°-120°	254.2	9.7
90°-150°	1121.9	42.9
90°-180°	1544.0	59.0
0°-180°	2616.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	0	4	8	9	10	2
95°	25	13	15	17	16	30
105°	116	121	23	27	29	124
115°	219	226	235	67	31	216
125°	310	315	322	325	326	276
135°	383	389	393	396	396	296
145°	445	445	451	453	452	278
155°	490	487	491	493	490	226
165°	516	514	515	517	515	146
175°	528	525	526	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	5.9	6.0	6.0	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.0
90°	0.4	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0
92.5°	7.7	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1
95°	24.8	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2
97.5°	49.1	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2
100°	67.5	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4
102.5°	87.6	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2
105°	115.8	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2
107.5°	148.1	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6
110°	168.8	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2



TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.3	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3
115°	219.2	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9
117.5°	246.6	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0
120°	266.8	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4
122.5°	283.8	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0
125°	309.9	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6
127.5°	333.4	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2
130°	348.4	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5
132.5°	363.6	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8
135°	383.4	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8
137.5°	403.5	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4
140°	416.6	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5
142.5°	427.6	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8
145°	444.8	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5
147.5°	459.8	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2
150°	469.6	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5
152.5°	477.8	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1
155°	489.7	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4
157.5°	499.1	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0
160°	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2
162.5°	509.5	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8
165°	516.0	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5
167.5°	520.9	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3
170°	523.7	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7
172.5°	525.5	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6
175°	527.9	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6
177.5°	528.2	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	5.8	5.7	5.5	5.4	5.4	5.4	5.4	5.3
90°	8.5	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.3	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	15.7	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	20.6	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.1	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	24.1	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	25.1	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	30.7	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	49.8	41.3	32.8	28.7	29.1	29.4	29.8	30.1



TEST NUMBER: P331469-940

CATALOG NUMBER: S122DIW-S290D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.5	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	156.8	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	241.5	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	281.4	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	298.5	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.2	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.1	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	360.5	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	374.6	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	394.7	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	413.3	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	425.3	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	436.5	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.1	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	465.7	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.0	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	481.6	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.0	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	500.6	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	505.6	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	510.3	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	520.9	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	523.3	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.1	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.2	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.4	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)