

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332400-830

Luminaire Tested: **S123RDIW-S340D1030U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332400-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1030U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5112.7 lumens
Efficiency: N/A
Efficacy: 134.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	20				
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17				
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15				
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13				
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11				
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10				
7	54	43	35	30	48	38	32	27	30	26	22	22	19	17	15	13	12	9				
8	50	39	31	26	45	35	29	24	27	23	20	20	17	15	14	12	11	8				
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7				
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.0
10°-20°	141.5	2.8
20°-30°	203.7	4.0
30°-40°	229.5	4.5
40°-50°	219.5	4.3
50°-60°	179.8	3.5
60°-70°	121.3	2.4
70°-80°	61.0	1.2
80°-90°	19.7	0.4
90°-100°	46.3	0.9
100°-110°	220.8	4.3
110°-120°	530.4	10.4
120°-130°	675.4	13.2
130°-140°	721.6	14.1
140°-150°	674.8	13.2
150°-160°	544.3	10.6
160°-170°	351.3	6.9
170°-180°	121.1	2.4
0°-30°	396.1	7.7
0°-40°	625.5	12.2
0°-60°	1024.8	20.0
0°-90°	1226.9	24.0
90°-120°	797.5	15.6
90°-150°	2869.2	56.1
90°-180°	3886.0	76.0
0°-180°	5112.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	11	23	26	28	4
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	529	535	543	553	557	522
125°	746	753	757	759	761	666
135°	929	934	938	941	938	715
145°	1072	1078	1080	1082	1082	671
155°	1180	1179	1180	1184	1179	544
165°	1245	1242	1241	1248	1242	352
175°	1274	1270	1270	1276	1270	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	8.2	7.7	7.4	6.9	6.9	7.4	8.0	8.6	9.1	9.2
90°	0.9	3.0	5.2	7.3	9.3	11.8	14.5	17.2	20.0	22.7	23.6
92.5°	17.6	17.1	16.4	15.8	15.3	16.0	18.1	20.1	22.1	24.2	25.5
95°	57.8	49.1	40.5	31.9	23.3	20.1	22.4	24.7	27.1	29.3	30.8
97.5°	116.0	112.2	108.3	104.4	100.6	91.0	76.0	60.8	45.6	30.4	32.1
100°	159.9	164.2	168.4	172.6	176.8	162.5	129.7	96.9	64.1	31.2	32.9
102.5°	210.0	213.0	216.0	219.0	222.1	205.7	169.8	134.0	98.1	62.3	57.1
105°	282.1	284.5	286.7	289.1	291.3	283.0	264.1	245.2	226.3	207.4	170.1
107.5°	358.3	360.1	361.9	363.8	365.6	368.1	371.1	374.0	377.0	380.0	352.7
110°	409.0	410.7	412.4	414.1	415.7	417.7	420.0	422.4	424.6	427.0	420.0



TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.4	458.9	460.4	462.0	463.5	465.4	467.7	470.0	472.4	474.7	474.8
115°	529.2	530.5	531.7	533.0	534.2	535.8	537.7	539.6	541.5	543.4	545.5
117.5°	598.7	600.2	601.8	603.3	604.9	606.1	607.2	608.1	609.1	610.0	611.7
120°	641.9	643.8	645.6	647.5	649.4	650.7	651.3	652.0	652.6	653.2	654.9
122.5°	685.8	687.3	688.9	690.4	692.0	693.1	694.0	694.7	695.6	696.4	697.6
125°	746.0	747.7	749.3	751.0	752.7	754.0	754.8	755.6	756.5	757.3	757.8
127.5°	804.3	806.0	807.7	809.4	811.1	812.4	813.4	814.5	815.4	816.4	817.1
130°	840.7	842.4	844.0	845.7	847.4	848.7	849.5	850.4	851.2	852.1	852.9
132.5°	875.5	877.2	878.8	880.5	882.2	883.4	884.1	884.8	885.4	886.1	886.9
135°	928.7	930.0	931.2	932.5	933.8	934.8	935.7	936.5	937.4	938.2	938.8
137.5°	974.1	975.7	977.3	978.9	980.5	981.6	982.0	982.5	983.0	983.4	984.4
140°	1004.5	1005.7	1007.0	1008.2	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8
142.5°	1032.5	1033.7	1035.0	1036.2	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7
145°	1071.7	1073.1	1074.6	1076.1	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6
147.5°	1108.6	1109.6	1110.5	1111.4	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2
150°	1131.3	1131.9	1132.6	1133.2	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4
152.5°	1151.8	1152.1	1152.4	1152.6	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0
155°	1180.5	1180.1	1179.7	1179.3	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6
157.5°	1202.9	1202.9	1202.8	1202.8	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0
160°	1216.5	1216.3	1216.1	1215.9	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9
162.5°	1229.4	1228.8	1228.3	1227.8	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4
165°	1244.9	1244.3	1243.7	1243.0	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8
167.5°	1257.0	1256.2	1255.4	1254.5	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9
170°	1263.9	1263.0	1262.2	1261.3	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7
172.5°	1268.4	1267.3	1266.4	1265.4	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3
175°	1274.2	1273.2	1272.1	1271.1	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0
177.5°	1275.7	1274.9	1274.1	1273.3	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	9.3	9.4	9.4	9.5	9.5	9.5	9.5	9.5
90°	24.4	25.3	26.1	26.7	27.1	27.5	28.0	28.4
92.5°	27.0	28.3	29.6	30.4	30.6	30.9	31.2	31.4
95°	32.3	33.7	35.3	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.2	38.2	38.4	38.5	38.8	39.0
100°	34.6	36.3	38.0	38.9	39.1	39.3	39.6	39.8
102.5°	51.8	46.7	41.4	39.0	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.3	40.0	40.4	40.8	41.2	41.7
107.5°	325.4	298.1	270.8	243.1	215.0	187.0	158.9	130.8
110°	413.1	406.1	399.2	380.7	350.6	320.5	290.4	260.3



TEST NUMBER: P332400-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	474.9	475.0	475.1	472.0	465.7	459.4	453.0	446.7
115°	547.6	549.7	551.9	553.3	554.1	555.0	555.8	556.7
117.5°	613.4	615.1	616.8	617.7	617.8	618.0	618.2	618.4
120°	656.6	658.3	660.0	660.8	660.8	660.8	660.8	660.8
122.5°	698.7	699.9	701.1	701.8	701.9	702.1	702.3	702.5
125°	758.2	758.7	759.0	759.5	759.9	760.3	760.7	761.1
127.5°	817.7	818.4	819.2	819.3	818.8	818.4	818.0	817.6
130°	853.8	854.5	855.4	855.6	855.2	854.8	854.3	853.9
132.5°	887.8	888.6	889.5	889.6	889.0	888.4	887.9	887.2
135°	939.4	940.1	940.7	940.7	940.1	939.4	938.8	938.2
137.5°	985.4	986.5	987.5	987.8	987.3	986.9	986.5	986.1
140°	1014.6	1015.5	1016.3	1016.5	1016.2	1015.7	1015.3	1014.8
142.5°	1042.4	1043.0	1043.7	1043.7	1043.1	1042.5	1042.0	1041.3
145°	1081.0	1081.5	1081.9	1082.0	1082.0	1082.0	1082.0	1082.0
147.5°	1115.7	1116.1	1116.5	1116.3	1115.3	1114.3	1113.3	1112.4
150°	1136.9	1137.3	1137.7	1137.6	1137.0	1136.3	1135.8	1135.1
152.5°	1155.7	1156.5	1157.3	1157.2	1156.1	1155.2	1154.2	1153.3
155°	1181.7	1182.7	1183.8	1183.6	1182.4	1181.2	1179.9	1178.6
157.5°	1204.3	1205.5	1206.7	1206.5	1204.9	1203.3	1201.6	1200.0
160°	1217.1	1218.4	1219.7	1219.6	1218.0	1216.6	1215.1	1213.6
162.5°	1228.8	1230.3	1231.7	1231.7	1230.5	1229.2	1227.9	1226.5
165°	1244.4	1246.1	1247.8	1247.9	1246.5	1245.0	1243.5	1242.1
167.5°	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2
170°	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1
172.5°	1268.0	1269.6	1271.3	1271.2	1269.4	1267.5	1265.6	1263.9
175°	1273.4	1274.9	1276.4	1276.3	1274.6	1272.9	1271.2	1269.5
177.5°	1275.4	1276.8	1278.1	1278.0	1276.3	1274.6	1272.9	1271.2
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2

(END OF REPORT)