

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331479-940

Luminaire Tested: **S122DIW-S290D970U940-4F0-1E-UDD-D**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331479-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D970U940-4F0-1E-UDD-D  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4520.1 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

### Luminous Intensity Polar Plot





TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	86	82	79	80	76	73	70	58	56	54	41	39	38	25	24	24	16
2	82	75	69	64	72	66	61	57	50	47	44	35	33	31	22	20	19	13
3	75	66	58	53	66	58	52	47	44	40	36	31	28	26	19	17	16	11
4	68	58	50	44	60	51	45	40	39	34	31	27	24	22	17	15	14	9
5	62	51	43	37	55	45	39	34	35	30	26	24	21	19	15	13	12	8
6	57	46	38	32	50	41	34	29	31	26	23	22	19	16	14	12	10	7
7	53	41	33	28	46	36	30	25	28	23	20	20	17	14	12	10	9	6
8	49	37	29	24	43	33	26	22	25	21	17	18	15	13	11	9	8	5
9	45	34	26	21	40	30	24	19	23	18	15	16	13	11	10	8	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	4

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4514	4514	4514
5°	4536	4345	4328
10°	4507	4215	4169
15°	4443	4079	4001
20°	4366	3935	3839
25°	4289	3793	3693
30°	4180	3650	3544
35°	4070	3510	3442
40°	3952	3391	3338
45°	3841	3286	3250
50°	3723	3189	3162
55°	3597	3086	3074
60°	3447	2979	2980
65°	3288	2854	2867
70°	3108	2717	2746
75°	2883	2585	2636
80°	2528	2450	2524
85°	2185	2333	2436



TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.5	0.6
10°-20°	75.9	1.7
20°-30°	115.1	2.5
30°-40°	140.2	3.1
40°-50°	150.8	3.3
50°-60°	146.5	3.2
60°-70°	127.9	2.8
70°-80°	98.4	2.2
80°-90°	69.0	1.5
90°-100°	84.8	1.9
100°-110°	177.3	3.9
110°-120°	407.0	9.0
120°-130°	647.8	14.3
130°-140°	681.1	15.1
140°-150°	629.2	13.9
150°-160°	505.1	11.2
160°-170°	325.5	7.2
170°-180°	112.0	2.5
0°-30°	217.5	4.8
0°-40°	357.7	7.9
0°-60°	654.9	14.5
0°-90°	950.2	21.0
90°-120°	669.1	14.8
90°-150°	2627.2	58.1
90°-180°	3570.0	79.0
0°-180°	4520.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	280	280	280	280	280	
5°	280	279	277	279	279	27
15°	267	268	268	272	271	75
25°	243	246	250	254	256	112
35°	210	216	224	233	236	131
45°	172	183	197	209	214	133
55°	132	147	167	181	187	118
65°	90	110	134	150	156	89
75°	50	73	98	115	121	53
85°	15	40	66	82	88	16
90°	5	38	70	90	98	5
95°	59	52	80	99	103	70
105°	261	284	87	109	118	279
115°	492	512	550	186	111	484
125°	694	706	734	750	757	618
135°	858	871	883	899	902	662
145°	994	994	1008	1016	1014	622
155°	1095	1088	1097	1102	1096	504
165°	1154	1149	1151	1156	1151	326
175°	1180	1175	1176	1181	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.6
2.5°	281.2	280.9	280.7	280.4	280.3	279.9	279.4	278.9	278.4	277.9	278.2
5°	280.4	280.1	279.8	279.6	279.2	278.8	278.3	277.8	277.2	276.7	277.2
7.5°	277.8	277.6	277.4	277.2	277.1	276.8	276.3	276.0	275.5	275.1	275.8
10°	275.9	275.7	275.5	275.4	275.2	274.9	274.6	274.4	274.1	273.8	274.6
12.5°	272.6	272.7	272.7	272.8	272.8	272.7	272.5	272.3	272.1	271.9	272.6
15°	267.3	267.5	267.7	267.9	268.0	268.1	268.1	268.1	268.1	268.1	268.9
17.5°	260.6	260.9	261.3	261.7	262.1	262.4	262.7	263.0	263.2	263.6	264.4
20°	256.0	256.5	256.9	257.3	257.8	258.2	258.6	259.0	259.3	259.7	260.6
22.5°	251.2	251.6	252.2	252.7	253.2	253.8	254.2	254.8	255.3	255.7	256.7
25°	243.1	243.7	244.3	245.0	245.6	246.3	247.1	247.9	248.7	249.5	250.6
27.5°	233.4	234.3	235.4	236.4	237.5	238.4	239.3	240.3	241.3	242.3	243.6
30°	226.9	228.0	229.2	230.3	231.5	232.7	233.9	235.1	236.2	237.4	238.8
32.5°	219.7	221.1	222.3	223.6	225.0	226.3	227.7	229.1	230.5	231.8	233.5
35°	209.5	211.0	212.5	214.0	215.5	217.1	218.9	220.6	222.3	224.0	226.0
37.5°	198.2	200.0	201.8	203.6	205.3	207.3	209.6	211.7	213.9	216.2	218.4
40°	190.8	192.8	194.7	196.7	198.7	200.9	203.3	205.8	208.2	210.6	212.9
42.5°	183.7	185.7	187.6	189.6	191.6	193.9	196.8	199.6	202.3	205.1	207.7
45°	171.7	174.2	176.6	179.1	181.5	184.2	187.4	190.6	193.7	196.9	199.7
47.5°	160.0	162.6	165.3	167.9	170.6	173.8	177.5	181.1	184.9	188.5	191.5
50°	151.9	154.7	157.5	160.2	163.1	166.5	170.6	174.6	178.6	182.7	185.7
52.5°	144.1	147.0	150.0	152.9	155.9	159.4	163.7	168.0	172.3	176.6	179.7
55°	131.6	134.9	138.1	141.3	144.6	148.6	153.3	157.9	162.6	167.3	170.6
57.5°	119.3	123.0	126.6	130.3	133.9	138.1	142.9	147.7	152.5	157.3	160.8
60°	110.6	114.5	118.3	122.2	126.1	130.5	135.7	140.8	146.0	151.1	154.5
62.5°	102.8	106.8	110.8	114.9	118.9	123.4	128.6	133.7	138.8	144.0	147.6
65°	89.9	94.3	98.7	103.2	107.5	112.4	117.7	123.1	128.4	133.7	137.4
67.5°	78.1	82.8	87.3	91.9	96.6	101.6	107.0	112.4	117.9	123.3	127.1
70°	69.6	74.4	79.0	83.7	88.4	93.5	99.1	104.7	110.3	115.8	119.8
72.5°	61.9	66.7	71.5	76.3	81.2	86.4	92.1	97.7	103.4	109.1	112.9
75°	49.8	54.8	59.9	64.9	70.0	75.3	81.1	86.9	92.6	98.4	102.3
77.5°	38.2	43.4	48.7	53.9	59.3	64.8	70.7	76.5	82.4	88.2	92.1
80°	30.4	35.8	41.4	46.8	52.3	58.1	63.8	69.7	75.5	81.4	85.2
82.5°	23.9	29.3	34.8	40.1	45.6	51.3	57.2	63.1	69.0	74.9	78.7
85°	14.6	20.2	25.8	31.3	36.9	42.5	48.3	54.1	59.8	65.6	69.4
87.5°	8.1	13.9	19.7	25.4	31.2	37.2	43.2	49.3	55.4	61.4	65.3
90°	4.9	12.2	19.5	26.8	34.2	41.4	48.7	56.0	63.2	70.5	75.1
92.5°	21.0	25.6	30.3	35.0	39.6	45.1	51.5	57.7	64.0	70.4	74.4
95°	58.6	56.6	54.6	52.6	50.6	52.9	59.7	66.3	73.1	79.8	84.2
97.5°	112.7	98.9	85.1	71.2	57.3	54.6	62.8	71.1	79.4	87.6	91.7
100°	153.6	131.1	108.4	85.8	63.2	56.0	64.3	72.6	80.8	89.1	93.9
102.5°	198.3	195.9	193.4	191.0	188.5	176.3	154.3	132.2	110.2	88.2	93.4
105°	261.1	269.4	277.6	285.9	294.2	274.8	227.8	180.8	133.8	86.9	92.0
107.5°	333.1	339.7	346.4	353.0	359.7	334.3	276.8	219.3	161.8	104.2	105.2
110°	379.1	384.9	390.7	396.5	402.2	380.0	329.6	279.3	229.0	178.7	162.6



TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.7	427.8	432.7	437.8	442.8	440.7	431.4	422.0	412.7	403.4	337.2
115°	491.5	495.8	500.0	504.2	508.4	514.9	523.7	532.4	541.3	550.0	465.0
117.5°	552.7	556.9	561.2	565.4	569.6	575.2	582.3	589.2	596.3	603.2	584.7
120°	597.6	600.8	604.0	607.3	610.5	615.5	622.6	629.5	636.6	643.6	648.4
122.5°	635.8	639.0	642.1	645.2	648.4	653.4	660.6	667.7	674.8	681.9	685.7
125°	693.6	696.0	698.5	700.9	703.4	707.8	714.3	720.8	727.3	733.8	737.5
127.5°	746.2	748.9	751.4	754.1	756.7	760.5	765.5	770.6	775.6	780.6	784.8
130°	779.6	782.6	785.5	788.5	791.4	794.8	798.8	802.7	806.7	810.7	814.9
132.5°	813.7	816.2	818.7	821.1	823.6	826.6	830.2	833.7	837.2	840.8	844.6
135°	857.6	860.6	863.6	866.7	869.7	872.5	875.1	877.7	880.3	883.0	886.7
137.5°	902.4	904.5	906.6	908.7	910.8	913.0	915.3	917.7	920.0	922.3	925.9
140°	931.7	933.1	934.5	935.9	937.4	939.2	941.5	943.8	946.0	948.3	951.5
142.5°	956.3	957.5	958.8	960.1	961.4	963.2	965.6	968.0	970.4	972.9	975.6
145°	994.3	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.9
147.5°	1028.0	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.1
150°	1049.7	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5
152.5°	1068.2	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6
155°	1094.9	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6
157.5°	1115.9	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8
160°	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3
162.5°	1139.1	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6
165°	1153.7	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4
167.5°	1164.6	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1
170°	1170.7	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7
172.5°	1174.8	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8
175°	1180.1	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1
177.5°	1181.0	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.6
2.5°	278.6	278.9	279.3	279.5	279.3	279.1	279.0	278.8
5°	277.8	278.3	278.8	279.0	278.9	278.8	278.7	278.7
7.5°	276.4	277.1	277.8	278.0	277.9	277.9	277.8	277.7
10°	275.3	276.0	276.7	277.1	277.0	276.9	276.8	276.7
12.5°	273.3	274.0	274.7	275.1	275.0	274.9	274.8	274.7
15°	269.7	270.6	271.4	271.8	271.7	271.6	271.5	271.4
17.5°	265.3	266.1	266.9	267.3	267.3	267.3	267.3	267.3
20°	261.6	262.6	263.6	264.1	264.1	264.1	264.1	264.1
22.5°	257.8	258.8	259.8	260.3	260.5	260.6	260.7	260.9
25°	251.7	252.8	253.9	254.5	254.8	255.0	255.3	255.6
27.5°	245.0	246.4	247.7	248.5	248.7	248.9	249.1	249.3
30°	240.2	241.7	243.2	244.0	244.2	244.5	244.8	245.0
32.5°	235.1	236.8	238.5	239.6	240.0	240.6	241.0	241.5
35°	228.0	230.0	231.9	233.3	233.9	234.5	235.1	235.8
37.5°	220.5	222.7	225.0	226.4	227.0	227.7	228.4	229.0
40°	215.3	217.7	220.0	221.6	222.4	223.2	224.0	224.8
42.5°	210.3	212.8	215.3	217.0	217.8	218.6	219.5	220.3
45°	202.4	205.3	208.0	209.9	210.8	211.7	212.6	213.5
47.5°	194.4	197.2	200.2	202.2	203.1	204.1	205.1	206.1
50°	188.8	191.9	194.9	197.0	198.0	198.9	199.9	200.9
52.5°	182.8	185.9	189.0	191.2	192.3	193.3	194.4	195.4
55°	173.8	177.0	180.3	182.4	183.6	184.9	186.0	187.2
57.5°	164.3	167.7	171.2	173.5	174.8	175.9	177.1	178.3
60°	157.9	161.4	164.8	167.1	168.4	169.6	170.9	172.2
62.5°	151.2	154.9	158.5	161.0	162.1	163.3	164.5	165.7
65°	141.1	144.7	148.5	150.9	152.0	153.2	154.4	155.5
67.5°	130.7	134.5	138.2	140.7	141.9	143.1	144.4	145.6
70°	123.6	127.4	131.3	133.8	134.9	136.0	137.1	138.1
72.5°	116.6	120.5	124.2	126.8	128.0	129.4	130.7	132.0
75°	106.2	110.0	114.0	116.5	117.6	118.8	119.9	121.1
77.5°	95.9	99.8	103.6	106.2	107.5	108.7	109.9	111.2
80°	89.0	92.7	96.6	99.1	100.3	101.6	102.8	104.1
82.5°	82.5	86.3	90.1	92.6	93.7	95.0	96.1	97.3
85°	73.2	77.0	80.8	83.3	84.5	85.8	87.0	88.3
87.5°	69.1	73.0	76.9	79.5	80.6	81.9	83.1	84.4
90°	79.6	84.2	88.7	91.7	93.2	94.6	96.1	97.6
92.5°	78.4	82.4	86.4	89.1	90.4	91.7	93.0	94.3
95°	88.5	92.9	97.3	99.9	100.8	101.7	102.5	103.4
97.5°	95.8	99.9	104.0	106.6	107.9	109.2	110.5	111.8
100°	98.8	103.6	108.4	111.6	112.9	114.3	115.7	117.1
102.5°	98.6	103.9	109.1	112.4	114.0	115.5	117.0	118.5
105°	97.3	102.5	107.7	111.2	113.0	114.8	116.5	118.2
107.5°	106.1	107.0	107.9	109.2	110.9	112.7	114.5	116.2
110°	146.6	130.5	114.5	107.3	109.1	110.8	112.5	114.3





TEST NUMBER: P331479-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.0	204.8	138.7	106.3	107.9	109.5	111.1	112.7
115°	380.0	295.2	210.2	161.3	148.7	136.1	123.4	110.8
117.5°	566.2	547.7	529.1	497.9	454.1	410.1	366.2	322.4
120°	653.2	658.0	662.8	652.9	628.3	603.8	579.2	554.6
122.5°	689.5	693.3	697.1	697.0	692.9	688.8	684.7	680.5
125°	741.3	745.0	748.8	751.4	752.7	754.1	755.5	756.9
127.5°	788.9	793.1	797.3	799.8	800.7	801.6	802.5	803.4
130°	819.2	823.4	827.7	830.1	830.6	831.2	831.6	832.1
132.5°	848.6	852.4	856.2	858.4	859.0	859.5	860.1	860.6
135°	890.5	894.3	898.0	900.1	900.4	900.8	901.2	901.5
137.5°	929.3	932.9	936.4	938.1	938.1	938.1	938.0	938.0
140°	954.6	957.7	960.9	962.2	961.8	961.4	961.0	960.6
142.5°	978.3	981.0	983.7	984.8	984.4	983.8	983.4	982.9
145°	1011.7	1013.6	1015.5	1016.1	1015.7	1015.1	1014.7	1014.1
147.5°	1041.1	1042.1	1043.2	1043.5	1042.9	1042.3	1041.7	1041.2
150°	1059.7	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1076.7	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1099.7	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1119.1	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1130.4	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1140.9	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1164.5	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1170.0	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1174.0	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1178.5	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1179.0	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)