

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332405-830

Luminaire Tested: **S123RDIW-S340D1320U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332405-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1320U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5539.5 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	27	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	0.9
10°-20°	141.5	2.6
20°-30°	203.7	3.7
30°-40°	229.5	4.1
40°-50°	219.5	4.0
50°-60°	179.8	3.2
60°-70°	121.3	2.2
70°-80°	61.0	1.1
80°-90°	20.7	0.4
90°-100°	101.4	1.8
100°-110°	303.4	5.5
110°-120°	516.1	9.3
120°-130°	678.8	12.3
130°-140°	763.0	13.8
140°-150°	750.0	13.5
150°-160°	631.4	11.4
160°-170°	420.3	7.6
170°-180°	147.2	2.7
0°-30°	396.1	7.1
0°-40°	625.5	11.3
0°-60°	1024.8	18.5
0°-90°	1227.9	22.2
90°-120°	920.9	16.6
90°-150°	3112.8	56.2
90°-180°	4312.0	77.8
0°-180°	5539.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	14	29	34	37	6
95°	72	81	90	95	95	81
105°	275	278	288	289	291	295
115°	520	523	521	522	521	514
125°	760	764	762	757	752	678
135°	987	993	993	988	985	760
145°	1197	1199	1203	1202	1197	747
155°	1370	1370	1372	1376	1368	631
165°	1493	1489	1489	1495	1488	421
175°	1553	1548	1548	1554	1546	147
180°	1556	1556	1556	1556	1556	



TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.7	8.4	8.0	7.7	7.4	7.6	8.3	9.0	9.7	10.5	10.6
90°	1.2	4.0	6.7	9.3	12.1	15.2	18.8	22.2	25.8	29.3	30.4
92.5°	29.6	31.4	33.3	35.2	36.9	38.9	40.9	42.9	45.0	46.9	47.8
95°	72.1	74.0	76.0	77.9	79.7	81.8	84.0	86.1	88.3	90.5	91.5
97.5°	128.1	129.5	130.9	132.3	133.7	135.3	136.9	138.4	140.0	141.6	142.8
100°	166.3	167.9	169.5	171.2	172.8	174.3	175.6	177.0	178.3	179.7	180.5
102.5°	210.3	211.2	212.3	213.2	214.1	215.6	217.4	219.1	220.9	222.7	223.6
105°	275.0	275.6	276.2	276.6	277.2	278.7	281.2	283.6	286.1	288.5	288.5
107.5°	350.3	350.7	351.0	351.4	351.7	352.3	353.3	354.3	355.2	356.2	357.1
110°	397.3	397.8	398.4	398.9	399.4	400.0	400.6	401.1	401.6	402.2	403.3



TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.5	446.9	447.1	447.5	447.7	447.8	447.9	448.1	448.2	449.5
115°	519.5	520.4	521.1	522.0	522.8	522.9	522.4	521.9	521.3	520.8	521.0
117.5°	593.4	593.9	594.5	595.0	595.6	595.5	594.7	594.1	593.3	592.7	592.6
120°	639.3	640.9	642.6	644.2	645.8	646.0	644.6	643.3	642.0	640.6	640.3
122.5°	687.3	688.4	689.7	690.9	692.0	692.3	691.5	690.9	690.1	689.5	688.7
125°	760.3	761.2	762.0	762.8	763.6	763.7	763.2	762.7	762.1	761.6	760.5
127.5°	827.8	829.6	831.3	833.0	834.8	835.4	834.8	834.2	833.6	833.0	831.4
130°	872.8	875.0	877.2	879.4	881.6	882.2	881.4	880.6	879.8	878.9	877.9
132.5°	917.8	920.0	922.2	924.4	926.5	927.3	926.7	926.1	925.5	924.9	923.6
135°	986.6	988.2	989.8	991.4	993.1	993.7	993.4	993.2	992.9	992.6	991.6
137.5°	1050.1	1051.4	1052.8	1054.1	1055.6	1056.6	1057.2	1058.0	1058.7	1059.4	1058.2
140°	1094.1	1095.4	1096.8	1098.2	1099.6	1100.3	1100.6	1100.9	1101.2	1101.5	1101.2
142.5°	1134.2	1135.6	1136.9	1138.3	1139.6	1140.6	1141.0	1141.5	1142.0	1142.6	1142.3
145°	1196.7	1197.3	1197.9	1198.4	1198.9	1199.7	1200.4	1201.3	1202.1	1202.9	1202.6
147.5°	1251.5	1252.5	1253.5	1254.5	1255.5	1256.3	1257.1	1257.8	1258.6	1259.3	1259.3
150°	1289.7	1290.2	1290.8	1291.3	1291.8	1292.4	1293.0	1293.5	1294.0	1294.6	1294.6
152.5°	1321.0	1321.7	1322.5	1323.2	1324.0	1324.6	1324.9	1325.2	1325.6	1325.9	1326.3
155°	1370.4	1370.4	1370.4	1370.4	1370.4	1370.6	1370.7	1371.0	1371.3	1371.6	1372.7
157.5°	1412.4	1412.1	1411.7	1411.5	1411.1	1411.1	1411.3	1411.5	1411.7	1411.9	1413.1
160°	1438.8	1438.3	1437.8	1437.2	1436.6	1436.3	1436.3	1436.3	1436.3	1436.3	1437.8
162.5°	1462.3	1461.5	1460.8	1460.0	1459.2	1459.0	1459.2	1459.4	1459.6	1459.8	1461.2
165°	1492.6	1491.8	1491.0	1490.2	1489.4	1488.9	1488.9	1488.9	1488.9	1488.9	1490.5
167.5°	1516.8	1515.7	1514.7	1513.5	1512.5	1512.0	1512.2	1512.5	1512.7	1512.9	1514.6
170°	1530.5	1529.5	1528.3	1527.3	1526.2	1525.6	1525.6	1525.6	1525.6	1525.6	1527.5
172.5°	1541.2	1540.2	1539.1	1538.0	1536.9	1536.3	1536.3	1536.3	1536.3	1536.3	1538.0
175°	1552.6	1551.4	1550.4	1549.3	1548.1	1547.7	1547.7	1547.7	1547.7	1547.7	1549.3
177.5°	1557.2	1556.3	1555.4	1554.5	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1554.5
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2



TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	10.7	10.8	11.0	11.1	11.1	11.1	11.1	11.2
90°	31.5	32.6	33.6	34.5	35.1	35.6	36.1	36.7
92.5°	48.6	49.6	50.4	50.7	50.3	50.0	49.7	49.4
95°	92.7	93.7	94.8	95.4	95.4	95.4	95.4	95.4
97.5°	144.0	145.3	146.6	147.1	147.0	146.9	146.8	146.7
100°	181.3	182.1	182.9	183.6	184.2	184.7	185.3	185.8
102.5°	224.3	225.2	226.0	226.3	226.2	226.1	226.0	225.9
105°	288.5	288.5	288.5	288.8	289.4	289.8	290.4	291.0
107.5°	358.0	358.8	359.7	360.0	359.7	359.3	359.0	358.6
110°	404.4	405.5	406.5	406.8	406.2	405.8	405.2	404.6





TEST NUMBER: P332405-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.7	452.0	453.4	453.9	453.8	453.7	453.6	453.6
115°	521.3	521.6	521.9	521.9	521.6	521.3	521.0	520.8
117.5°	592.6	592.5	592.4	592.0	591.3	590.5	589.7	589.0
120°	640.0	639.8	639.5	639.0	638.6	638.0	637.4	636.9
122.5°	688.1	687.3	686.6	685.9	685.1	684.4	683.6	682.9
125°	759.4	758.4	757.2	756.2	755.1	753.9	752.9	751.8
127.5°	829.9	828.4	826.9	825.5	824.3	823.0	821.8	820.5
130°	876.8	875.7	874.6	873.1	871.2	869.3	867.4	865.5
132.5°	922.3	921.0	919.7	918.3	916.8	915.4	913.9	912.5
135°	990.4	989.4	988.3	987.5	986.9	986.4	985.8	985.3
137.5°	1057.1	1055.9	1054.8	1053.8	1052.7	1051.7	1050.7	1049.6
140°	1100.9	1100.6	1100.3	1099.3	1097.4	1095.4	1093.5	1091.7
142.5°	1142.0	1141.7	1141.4	1140.6	1139.1	1137.6	1136.1	1134.7
145°	1202.3	1202.1	1201.8	1201.2	1200.0	1198.9	1197.9	1196.7
147.5°	1259.3	1259.3	1259.3	1258.6	1257.0	1255.3	1253.7	1252.1
150°	1294.6	1294.6	1294.6	1293.7	1292.1	1290.5	1288.8	1287.2
152.5°	1326.7	1327.2	1327.6	1327.1	1325.7	1324.3	1322.9	1321.4
155°	1373.8	1374.9	1375.9	1375.5	1373.7	1371.8	1369.8	1367.9
157.5°	1414.2	1415.3	1416.5	1416.3	1414.8	1413.2	1411.7	1410.2
160°	1439.1	1440.5	1441.8	1442.0	1440.9	1439.8	1438.7	1437.6
162.5°	1462.5	1464.0	1465.3	1465.1	1463.4	1461.6	1459.9	1458.1
165°	1492.2	1493.8	1495.4	1495.3	1493.5	1491.6	1489.6	1487.7
167.5°	1516.3	1518.0	1519.7	1519.7	1518.0	1516.3	1514.6	1512.9
170°	1529.5	1531.3	1533.2	1533.2	1531.3	1529.5	1527.5	1525.6
172.5°	1539.7	1541.4	1543.1	1543.0	1541.2	1539.2	1537.3	1535.4
175°	1550.9	1552.6	1554.2	1554.0	1552.1	1550.2	1548.3	1546.4
177.5°	1555.9	1557.2	1558.5	1558.4	1556.8	1555.3	1553.8	1552.3
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2

(END OF REPORT)