

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331507-940

Luminaire Tested: **S122DIW-S485D970U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331507-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D970U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5365.4 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	1.5
10°-20°	239.9	4.5
20°-30°	348.2	6.5
30°-40°	367.4	6.8
40°-50°	325.3	6.1
50°-60°	259.6	4.8
60°-70°	176.5	3.3
70°-80°	90.5	1.7
80°-90°	24.7	0.5
90°-100°	39.3	0.7
100°-110°	144.0	2.7
110°-120°	385.0	7.2
120°-130°	635.6	11.8
130°-140°	675.9	12.6
140°-150°	628.3	11.7
150°-160°	505.1	9.4
160°-170°	325.5	6.1
170°-180°	112.0	2.1
0°-30°	670.6	12.5
0°-40°	1038.0	19.3
0°-60°	1623.0	30.2
0°-90°	1914.6	35.7
90°-120°	568.4	10.6
90°-150°	2508.2	46.7
90°-180°	3451.0	64.3
0°-180°	5365.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	20
90°	23	1	23	1	23	11
95°	37	55	37	55	37	34
105°	65	259	65	259	65	67
115°	70	490	70	490	70	175
125°	728	693	728	693	728	630
135°	885	857	885	857	885	682
145°	1010	994	1010	994	1010	631
155°	1096	1095	1096	1095	1096	506
165°	1151	1154	1151	1154	1151	325
175°	1173	1180	1173	1180	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	11.5	11.4	11.7	11.3	11.2	11.3	11.1	10.7	10.8	10.9	10.8
90°	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9	18.0	17.0	15.5
92.5°	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8	20.2	19.8	19.0
95°	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1	34.2	33.3	31.9
97.5°	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0	45.2	44.5	41.4
100°	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6	50.1	48.6	45.4
102.5°	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9	51.9	49.9	46.9
105°	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2	54.0	52.0	49.7
107.5°	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5	70.6	72.8	74.7
110°	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2	130.2	149.1	203.8



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9	307.0	376.1	389.6
115°	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4	438.0	525.8	521.0
117.5°	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8	561.1	582.3	579.1
120°	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1	626.9	624.6	621.2
122.5°	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5	666.1	664.8	661.0
125°	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6	721.3	720.0	716.4
127.5°	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6	771.7	769.7	767.0
130°	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9	803.9	801.8	799.7
132.5°	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4	835.6	833.8	831.7
135°	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3	880.4	878.5	876.7
137.5°	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9	922.1	920.2	918.3
140°	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9	949.2	947.5	945.4
142.5°	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8	974.3	972.7	970.4
145°	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7	1009.3	1008.0	1004.8
147.5°	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0	1040.0	1039.0	1035.8
150°	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7	1058.5	1057.4	1054.4
152.5°	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7	1075.6	1074.4	1071.6
155°	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7	1098.6	1097.4	1095.2
157.5°	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1	1117.8	1116.5	1114.9
160°	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4	1129.3	1128.1	1127.0
162.5°	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9	1139.6	1138.4	1137.4
165°	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1	1150.6
167.5°	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5	1163.1	1161.9	1161.4
170°	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0	1168.7	1167.3	1167.0
172.5°	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0	1172.8	1171.4	1171.0
175°	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5	1177.1	1175.8	1175.5
177.5°	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0	1177.9	1176.9	1176.7
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	10.8	10.5	10.2	10.3	9.2	8.7	7.2	6.1	6.2	6.3	6.2
90°	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9	2.9	5.0	7.1
92.5°	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2	17.0	16.9	16.7
95°	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4	49.1	42.9	36.6
97.5°	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9	92.3	74.7	57.1
100°	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8	124.8	98.9	73.0
102.5°	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8	190.3	184.9	179.3
105°	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0	264.7	270.4	276.1
107.5°	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1	335.7	340.3	344.8
110°	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5	381.5	385.4	389.4



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1	424.6	428.1	431.7
115°	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9	493.1	496.4	499.6
117.5°	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4	555.1	558.7	562.2
120°	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5	599.3	602.1	604.9
122.5°	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6	637.6	640.6	643.5
125°	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7	695.2	697.7	700.1
127.5°	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4	748.1	750.8	753.6
130°	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8	781.9	784.9	787.8
132.5°	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9	815.5	818.1	820.6
135°	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2	860.2	863.3	866.3
137.5°	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0	904.1	906.2	908.4
140°	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3	932.8	934.3	935.9
142.5°	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8	957.2	958.6	959.9
145°	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3	994.2	994.0	993.8
147.5°	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0	1027.2	1026.4	1025.7
150°	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7	1048.4	1047.0	1045.8
152.5°	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2	1066.7	1065.1	1063.7
155°	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9	1093.1	1091.5	1089.8
157.5°	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9	1114.5	1112.9	1111.5
160°	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1127.0	1125.9	1124.7
162.5°	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1	1137.9	1136.8	1135.6
165°	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7	1152.5	1151.4	1150.3
167.5°	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6	1163.4	1162.3	1161.2
170°	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7	1169.6	1168.5	1167.3
172.5°	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8	1173.7	1172.5	1171.4
175°	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1	1178.8	1177.4	1176.2
177.5°	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0	1179.9	1178.8	1177.8
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	6.3	6.4	6.5	6.8	6.9	6.9	6.8	7.0	7.1	6.9	7.0
90°	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9	19.9	20.9	21.5
92.5°	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8	21.2	21.8	22.1
95°	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1	36.1	37.0	37.4
97.5°	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0	46.7	47.5	48.0
100°	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6	53.1	54.7	55.6
102.5°	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9	55.8	57.8	59.0
105°	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2	58.2	60.3	61.7
107.5°	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5	66.4	64.3	63.6
110°	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2	92.3	73.4	64.3



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9	168.9	99.8	65.5
115°	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4	262.7	175.0	124.4
117.5°	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8	518.7	497.5	464.5
120°	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1	631.3	633.6	622.0
122.5°	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5	668.9	670.2	668.4
125°	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6	724.0	725.3	726.2
127.5°	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6	775.5	777.5	778.5
130°	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9	808.1	810.1	811.1
132.5°	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4	839.2	841.0	841.8
135°	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3	884.1	886.0	886.8
137.5°	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9	925.8	927.6	928.3
140°	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9	952.6	954.3	954.7
142.5°	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8	977.4	978.9	979.2
145°	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7	1012.0	1013.3	1013.5
147.5°	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0	1042.0	1042.9	1043.0
150°	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7	1060.8	1061.9	1062.0
152.5°	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7	1077.8	1079.0	1079.0
155°	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7	1100.8	1102.0	1101.8
157.5°	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1	1120.4	1121.7	1121.6
160°	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4	1131.5	1132.7	1132.6
162.5°	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9	1142.2	1143.5	1143.4
165°	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5
167.5°	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5	1165.8	1167.2	1167.0
170°	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0	1171.3	1172.6	1172.4
172.5°	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0	1175.4	1176.7	1176.5
175°	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5	1179.8	1181.2	1180.9
177.5°	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0	1180.0	1181.1	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	7.0	6.9	7.0	6.8	7.0	6.9	7.0	7.0	6.9	7.1	7.0
90°	21.8	22.2	22.6	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9
92.5°	22.3	22.6	22.7	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8
95°	37.2	37.0	36.8	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1
97.5°	48.2	48.4	48.7	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0
100°	55.9	56.4	56.7	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6
102.5°	59.6	60.1	60.6	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9
105°	62.5	63.2	64.0	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2
107.5°	64.4	65.1	65.9	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5
110°	65.0	65.8	66.5	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	66.2	66.8	67.4	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9
115°	110.8	97.1	83.5	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4
117.5°	419.6	374.9	330.1	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8
120°	596.5	570.9	545.3	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1
122.5°	663.4	658.5	653.5	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5
125°	726.8	727.4	727.9	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6
127.5°	778.6	778.7	778.8	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6
130°	810.8	810.7	810.5	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9
132.5°	841.5	841.3	841.2	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4
135°	886.4	886.0	885.6	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3
137.5°	927.6	926.9	926.3	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9
140°	953.8	952.8	951.8	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9
142.5°	978.3	977.3	976.4	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8
145°	1012.5	1011.6	1010.7	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7
147.5°	1042.2	1041.4	1040.6	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0
150°	1061.1	1060.2	1059.2	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7
152.5°	1077.7	1076.5	1075.2	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7
155°	1100.3	1098.8	1097.3	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7
157.5°	1120.1	1118.7	1117.1	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1
160°	1131.2	1129.9	1128.6	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4
162.5°	1141.7	1140.1	1138.4	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9
165°	1155.1	1153.8	1152.4	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8
167.5°	1165.3	1163.6	1161.9	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5
170°	1170.7	1169.0	1167.3	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0
172.5°	1174.8	1173.1	1171.4	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0
175°	1178.9	1177.1	1175.2	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5
177.5°	1179.6	1178.2	1176.9	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	6.8	6.9	6.9	6.8	6.5	6.4	6.3	6.2	6.3	6.2	6.1
90°	18.0	17.0	15.5	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9
92.5°	20.2	19.8	19.0	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2
95°	34.2	33.3	31.9	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4
97.5°	45.2	44.5	41.4	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9
100°	50.1	48.6	45.4	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8
102.5°	51.9	49.9	76.9	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8
105°	54.0	52.0	103.7	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0
107.5°	70.6	72.8	134.7	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1
110°	130.2	149.1	203.8	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	307.0	376.1	389.6	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1
115°	438.0	525.8	521.0	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9
117.5°	561.1	582.3	579.1	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4
120°	626.9	624.6	621.2	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5
122.5°	666.1	664.8	661.0	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6
125°	721.3	720.0	716.4	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7
127.5°	771.7	769.7	767.0	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4
130°	803.9	801.8	799.7	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8
132.5°	835.6	833.8	831.7	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9
135°	880.4	878.5	876.7	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2
137.5°	922.1	920.2	918.3	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0
140°	949.2	947.5	945.4	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3
142.5°	974.3	972.7	970.4	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8
145°	1009.3	1008.0	1004.8	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3
147.5°	1040.0	1039.0	1035.8	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0
150°	1058.5	1057.4	1054.4	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7
152.5°	1075.6	1074.4	1071.6	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2
155°	1098.6	1097.4	1095.2	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9
157.5°	1117.8	1116.5	1114.9	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9
160°	1129.3	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1
162.5°	1139.6	1138.4	1137.4	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1
165°	1152.4	1151.1	1150.6	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7
167.5°	1163.1	1161.9	1161.4	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6
170°	1168.7	1167.3	1167.0	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7
172.5°	1172.8	1171.4	1171.0	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8
175°	1177.1	1175.8	1175.5	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1
177.5°	1177.9	1176.9	1176.7	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.2	8.7	9.2	10.3	10.2	10.5	10.8	10.8	10.9	10.8	10.7
90°	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9
92.5°	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8
95°	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1
97.5°	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0
100°	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6
102.5°	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9
105°	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2
107.5°	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5
110°	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9
115°	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4
117.5°	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8
120°	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1
122.5°	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5
125°	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6
127.5°	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6
130°	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9
132.5°	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4
135°	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3
137.5°	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9
140°	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9
142.5°	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8
145°	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7
147.5°	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0
150°	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7
152.5°	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7
155°	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7
157.5°	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1
160°	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4
162.5°	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9
165°	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8
167.5°	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5
170°	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0
172.5°	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0
175°	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5
177.5°	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	11.1	11.3	11.2	11.3	11.7	11.4	11.5
90°	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	92.3	73.4	64.3	65.0	65.8	66.5	67.3



TEST NUMBER: P331507-940

CATALOG NUMBER: S122DIW-S485D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)