

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332408-830

Luminaire Tested: **S123RDIW-S340D1535U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332408-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1535U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7012.4 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	99	99	99	99	88	88	88	88	65	65	65	45	45	45	26	26	26	18						18														
1	91	87	83	80	80	76	73	71	57	55	53	40	38	37	23	23	22	15						15														
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13						13														
3	75	66	60	54	66	59	53	48	44	40	37	31	29	27	18	17	16	11						11														
4	69	59	51	46	60	52	46	41	39	35	32	27	25	23	16	15	14	9						9														
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8						8														
6	58	47	39	34	51	41	35	30	31	27	24	22	19	17	13	12	11	7						7														
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	12	11	10	6						6														
8	49	38	31	26	43	34	27	23	26	21	18	18	15	13	11	10	9	6						6														
9	46	34	27	23	40	31	25	20	23	19	16	17	14	12	10	9	8	5						5														
10	43	31	25	20	38	28	22	18	21	17	14	15	13	11	10	8	7	5						5														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	0.7
10°-20°	141.5	2.0
20°-30°	203.7	2.9
30°-40°	229.5	3.3
40°-50°	219.5	3.1
50°-60°	179.8	2.6
60°-70°	121.3	1.7
70°-80°	61.0	0.9
80°-90°	21.5	0.3
90°-100°	69.0	1.0
100°-110°	328.6	4.7
110°-120°	789.4	11.3
120°-130°	1005.2	14.3
130°-140°	1074.1	15.3
140°-150°	1004.4	14.3
150°-160°	810.1	11.6
160°-170°	522.9	7.5
170°-180°	180.2	2.6
0°-30°	396.1	5.6
0°-40°	625.5	8.9
0°-60°	1024.8	14.6
0°-90°	1228.6	17.5
90°-120°	1187.0	16.9
90°-150°	4270.6	60.9
90°-180°	5784.0	82.5
0°-180°	7012.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	16	34	39	42	5
95°	86	32	44	53	54	106
105°	420	428	309	73	62	445
115°	788	796	809	822	829	777
125°	1110	1121	1127	1130	1133	991
135°	1382	1391	1396	1400	1396	1064
145°	1595	1604	1608	1610	1611	998
155°	1757	1754	1756	1762	1754	809
165°	1853	1849	1847	1857	1849	523
175°	1897	1890	1891	1900	1890	180
180°	1897	1897	1897	1897	1897	



TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.7	8.5	8.3	8.0	7.8	8.1	8.9	9.7	10.6	11.3	11.5
90°	1.4	4.5	7.6	10.8	13.9	17.5	21.6	25.6	29.8	33.8	35.1
92.5°	26.2	25.4	24.4	23.6	22.7	23.8	26.9	30.0	33.0	36.1	38.1
95°	86.0	73.1	60.3	47.4	34.6	29.9	33.4	36.8	40.2	43.6	45.9
97.5°	172.8	167.0	161.3	155.4	149.7	135.5	113.0	90.5	68.0	45.3	47.9
100°	238.2	244.4	250.6	256.9	263.2	241.9	193.0	144.2	95.4	46.5	49.0
102.5°	312.5	317.1	321.6	326.0	330.5	306.1	252.8	199.4	146.1	92.7	84.9
105°	419.9	423.4	426.8	430.3	433.7	421.3	393.1	365.0	336.8	308.6	253.2
107.5°	533.2	535.9	538.7	541.5	544.2	547.8	552.2	556.8	561.2	565.6	525.0
110°	608.7	611.2	613.7	616.2	618.8	621.7	625.2	628.6	632.1	635.5	625.2



TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	680.9	683.2	685.4	687.7	689.8	692.8	696.2	699.6	703.0	706.5	706.7
115°	787.7	789.6	791.5	793.3	795.2	797.6	800.4	803.1	806.0	808.8	811.9
117.5°	891.1	893.4	895.7	898.1	900.4	902.3	903.7	905.1	906.5	908.0	910.5
120°	955.4	958.2	961.0	963.8	966.7	968.6	969.4	970.3	971.3	972.2	974.8
122.5°	1020.8	1023.0	1025.4	1027.7	1030.0	1031.8	1032.9	1034.2	1035.3	1036.5	1038.3
125°	1110.3	1112.9	1115.4	1117.9	1120.4	1122.3	1123.5	1124.7	1126.1	1127.3	1127.9
127.5°	1197.1	1199.7	1202.2	1204.7	1207.2	1209.2	1210.7	1212.2	1213.7	1215.2	1216.2
130°	1251.2	1253.8	1256.3	1258.8	1261.3	1263.2	1264.4	1265.6	1267.0	1268.2	1269.4
132.5°	1303.2	1305.6	1308.2	1310.6	1313.2	1314.9	1315.9	1316.9	1317.9	1318.9	1320.1
135°	1382.3	1384.2	1386.1	1388.0	1389.9	1391.4	1392.6	1393.9	1395.2	1396.4	1397.3
137.5°	1449.9	1452.4	1454.7	1457.1	1459.4	1461.0	1461.7	1462.4	1463.1	1463.8	1465.3
140°	1495.1	1496.9	1498.8	1500.7	1502.6	1503.9	1504.9	1505.8	1506.7	1507.7	1509.0
142.5°	1536.7	1538.6	1540.5	1542.4	1544.3	1545.7	1546.6	1547.6	1548.5	1549.4	1550.4
145°	1595.1	1597.2	1599.5	1601.7	1603.8	1605.2	1605.9	1606.5	1607.1	1607.8	1608.4
147.5°	1650.0	1651.5	1652.9	1654.4	1655.8	1656.8	1657.5	1658.1	1658.7	1659.3	1660.0
150°	1683.9	1684.8	1685.7	1686.7	1687.6	1688.4	1689.0	1689.7	1690.3	1690.9	1691.5
152.5°	1714.3	1714.8	1715.1	1715.6	1716.1	1716.5	1716.8	1717.2	1717.6	1718.0	1719.1
155°	1757.1	1756.5	1755.9	1755.3	1754.6	1754.4	1754.8	1755.1	1755.4	1755.7	1757.3
157.5°	1790.4	1790.4	1790.3	1790.2	1790.2	1790.0	1789.6	1789.3	1789.0	1788.7	1790.5
160°	1810.7	1810.3	1810.1	1809.8	1809.4	1809.1	1808.8	1808.5	1808.2	1807.9	1809.8
162.5°	1829.9	1829.0	1828.2	1827.4	1826.6	1826.0	1825.7	1825.4	1825.0	1824.8	1826.9
165°	1852.9	1852.0	1851.1	1850.1	1849.2	1848.6	1848.2	1847.9	1847.7	1847.3	1849.8
167.5°	1870.9	1869.7	1868.5	1867.3	1866.0	1865.4	1865.4	1865.4	1865.4	1865.4	1867.8
170°	1881.1	1879.9	1878.6	1877.4	1876.1	1875.5	1875.5	1875.5	1875.5	1875.5	1878.0
172.5°	1887.9	1886.4	1884.9	1883.4	1881.9	1881.2	1881.5	1881.8	1882.0	1882.3	1884.8
175°	1896.6	1895.1	1893.5	1892.0	1890.4	1889.7	1890.1	1890.4	1890.6	1891.0	1893.2
177.5°	1898.8	1897.6	1896.4	1895.2	1893.9	1893.4	1893.7	1893.9	1894.1	1894.4	1896.4
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6



TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	11.7	11.9	12.1	12.2	12.2	12.3	12.3	12.3
90°	36.3	37.6	38.8	39.8	40.4	41.0	41.7	42.2
92.5°	40.1	42.1	44.1	45.2	45.6	46.0	46.4	46.8
95°	48.1	50.2	52.4	53.5	53.5	53.5	53.5	53.5
97.5°	50.4	52.9	55.4	56.8	57.1	57.4	57.8	58.1
100°	51.5	54.0	56.6	58.0	58.2	58.5	58.9	59.2
102.5°	77.2	69.5	61.6	58.1	58.6	59.2	59.8	60.3
105°	197.7	142.3	86.9	59.5	60.1	60.8	61.4	62.0
107.5°	484.3	443.7	403.0	361.8	320.1	278.2	236.5	194.7
110°	614.8	604.5	594.2	566.6	521.8	477.0	432.3	387.5



TEST NUMBER: P332408-830

CATALOG NUMBER: S123RDIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	706.9	707.1	707.3	702.7	693.1	683.7	674.3	664.8
115°	815.1	818.2	821.3	823.5	824.8	826.0	827.3	828.6
117.5°	913.0	915.5	918.0	919.5	919.6	919.9	920.2	920.4
120°	977.3	979.8	982.3	983.5	983.5	983.5	983.5	983.5
122.5°	1040.0	1041.8	1043.6	1044.5	1044.8	1045.0	1045.3	1045.6
125°	1128.5	1129.2	1129.7	1130.4	1131.1	1131.6	1132.3	1132.9
127.5°	1217.2	1218.2	1219.2	1219.4	1218.8	1218.1	1217.5	1216.9
130°	1270.6	1272.0	1273.2	1273.5	1272.9	1272.2	1271.6	1271.0
132.5°	1321.4	1322.7	1323.9	1324.1	1323.2	1322.4	1321.4	1320.6
135°	1398.3	1399.2	1400.1	1400.1	1399.2	1398.3	1397.3	1396.4
137.5°	1466.8	1468.3	1469.8	1470.2	1469.6	1469.0	1468.3	1467.7
140°	1510.2	1511.5	1512.7	1513.1	1512.4	1511.8	1511.2	1510.5
142.5°	1551.4	1552.5	1553.4	1553.5	1552.7	1551.7	1550.9	1550.0
145°	1609.0	1609.7	1610.2	1610.6	1610.6	1610.6	1610.6	1610.6
147.5°	1660.6	1661.2	1661.9	1661.4	1660.0	1658.6	1657.1	1655.7
150°	1692.1	1692.8	1693.4	1693.3	1692.3	1691.4	1690.5	1689.5
152.5°	1720.2	1721.4	1722.5	1722.3	1720.9	1719.4	1718.0	1716.6
155°	1758.9	1760.4	1762.0	1761.8	1759.9	1758.0	1756.1	1754.4
157.5°	1792.4	1794.3	1796.2	1795.9	1793.5	1791.0	1788.6	1786.1
160°	1811.7	1813.5	1815.3	1815.2	1813.0	1810.8	1808.6	1806.5
162.5°	1829.0	1831.2	1833.2	1833.3	1831.5	1829.5	1827.6	1825.6
165°	1852.3	1854.8	1857.4	1857.5	1855.3	1853.1	1850.9	1848.7
167.5°	1870.4	1872.8	1875.4	1875.4	1872.8	1870.4	1867.8	1865.4
170°	1880.5	1883.0	1885.6	1885.6	1883.0	1880.5	1878.0	1875.5
172.5°	1887.3	1889.8	1892.2	1892.2	1889.4	1886.7	1883.9	1881.1
175°	1895.4	1897.5	1899.8	1899.6	1897.1	1894.6	1892.1	1889.6
177.5°	1898.4	1900.4	1902.4	1902.1	1899.6	1897.1	1894.6	1892.2
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6

(END OF REPORT)