

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331543-940

Luminaire Tested: **S122DIW-S675D1240U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331543-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7034.5 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		60	60	60		44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63		53	52	50		40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53		47	45	42		35	34	33	27
3	80	71	64	58	72	64	58	54	53	48	45		42	39	36		32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	38		37	34	31		29	26	25	21
5	67	56	48	42	61	51	44	39	42	37	33		34	30	27		26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29		31	27	24		24	21	19	16
7	57	45	38	32	52	42	35	30	35	29	26		28	24	21		22	19	17	14
8	53	41	34	29	48	38	31	27	31	26	23		26	22	19		20	17	15	13
9	49	38	30	26	45	35	28	24	29	24	21		24	20	17		18	16	14	12
10	46	34	28	23	42	32	26	21	27	22	19		22	18	16		17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.6
10°-20°	327.9	4.7
20°-30°	475.9	6.8
30°-40°	502.2	7.1
40°-50°	444.7	6.3
50°-60°	354.9	5.0
60°-70°	241.2	3.4
70°-80°	123.7	1.8
80°-90°	33.5	0.5
90°-100°	50.3	0.7
100°-110°	184.4	2.6
110°-120°	492.9	7.0
120°-130°	813.7	11.6
130°-140°	865.3	12.3
140°-150°	804.3	11.4
150°-160°	646.7	9.2
160°-170°	416.7	5.9
170°-180°	143.4	2.0
0°-30°	916.7	13.0
0°-40°	1418.9	20.2
0°-60°	2218.4	31.5
0°-90°	2616.8	37.2
90°-120°	727.6	10.3
90°-150°	3210.9	45.6
90°-180°	4418.0	62.8
0°-180°	7034.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	29	1	29	1	29	14
95°	47	71	47	71	47	44
105°	83	332	83	332	83	86
115°	89	627	89	627	89	224
125°	933	887	933	887	933	807
135°	1133	1097	1133	1097	1133	874
145°	1293	1273	1293	1273	1293	808
155°	1403	1402	1403	1402	1403	647
165°	1474	1477	1474	1477	1474	416
175°	1502	1511	1502	1511	1502	143
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	15.3	15.2	15.5	15.1	15.0	15.2	14.9	14.4	14.4	14.5	14.5
90°	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3	23.0	21.8	19.9
92.5°	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6	25.9	25.3	24.3
95°	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9	43.8	42.5	40.8
97.5°	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9	57.9	57.0	53.1
100°	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1	64.1	62.2	58.1
102.5°	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9	66.4	63.9	98.4
105°	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9	69.2	66.5	132.7
107.5°	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7	90.4	93.2	172.5
110°	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4	166.7	190.9	260.9



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6	393.1	481.4	498.8
115°	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5	560.8	673.1	667.0
117.5°	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2	718.3	745.5	741.3
120°	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4	802.5	799.5	795.2
122.5°	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5	852.7	851.0	846.3
125°	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1	923.5	921.8	917.1
127.5°	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3	987.9	985.4	982.0
130°	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8	1029.1	1026.4	1023.8
132.5°	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0	1069.7	1067.5	1064.8
135°	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4	1127.0	1124.6	1122.4
137.5°	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8	1180.4	1178.0	1175.5
140°	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4	1215.1	1213.0	1210.3
142.5°	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2	1247.2	1245.3	1242.2
145°	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8	1292.1	1290.4	1286.3
147.5°	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7	1331.4	1330.1	1326.1
150°	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6	1355.1	1353.7	1349.8
152.5°	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4	1377.0	1375.5	1371.8
155°	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8	1406.4	1405.0	1402.0
157.5°	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7	1431.0	1429.4	1427.4
160°	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2	1445.6	1444.2	1442.8
162.5°	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6	1458.9	1457.3	1456.1
165°	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6	1472.9
167.5°	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8	1489.1	1487.4	1486.7
170°	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8	1496.1	1494.4	1493.9
172.5°	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0	1501.3	1499.6	1499.1
175°	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7	1507.0	1505.3	1504.9
177.5°	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3	1508.0	1506.6	1506.4
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	14.5	14.1	13.7	14.0	12.4	11.9	9.9	8.2	8.4	8.6	8.4
90°	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1	3.7	6.4	9.1
92.5°	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0	21.8	21.6	21.3
95°	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9	62.9	54.9	46.9
97.5°	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7	118.2	95.6	73.1
100°	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1	159.9	126.6	93.5
102.5°	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7	243.6	236.6	229.6
105°	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6	338.9	346.2	353.4
107.5°	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9	429.7	435.6	441.5
110°	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2	488.3	493.4	498.5



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0	543.6	548.0	552.6
115°	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2	631.3	635.4	639.5
117.5°	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0	710.6	715.2	719.8
120°	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6	767.2	770.8	774.5
122.5°	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4	816.3	820.1	823.9
125°	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8	889.9	893.1	896.3
127.5°	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2	957.7	961.2	964.7
130°	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0	1000.9	1004.8	1008.6
132.5°	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6	1043.9	1047.2	1050.5
135°	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3	1101.2	1105.1	1108.9
137.5°	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7	1157.4	1160.1	1162.9
140°	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2	1194.2	1196.1	1198.0
142.5°	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7	1225.4	1227.2	1228.9
145°	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9	1272.7	1272.5	1272.2
147.5°	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9	1315.0	1314.1	1313.1
150°	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9	1342.2	1340.5	1338.7
152.5°	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4	1365.6	1363.6	1361.7
155°	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7	1399.5	1397.3	1395.1
157.5°	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5	1426.6	1424.8	1423.0
160°	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1442.8	1441.3	1439.8
162.5°	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2	1456.7	1455.3	1453.8
165°	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9	1475.5	1474.0	1472.6
167.5°	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9	1489.4	1488.0	1486.6
170°	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8	1497.3	1495.8	1494.4
172.5°	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0	1502.5	1501.1	1499.6
175°	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7	1509.0	1507.3	1505.7
177.5°	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8	1510.5	1509.1	1507.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	8.6	8.6	8.6	9.0	9.1	9.1	9.0	9.2	9.5	9.0	9.2
90°	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3	25.4	26.7	27.6
92.5°	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6	27.2	27.8	28.3
95°	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9	46.2	47.3	47.9
97.5°	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9	59.8	60.8	61.4
100°	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1	67.9	69.9	71.2
102.5°	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9	71.5	74.0	75.6
105°	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9	74.5	77.2	79.0
107.5°	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7	85.0	82.3	81.4
110°	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4	118.2	93.9	82.3



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6	216.2	127.8	83.9
115°	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5	336.4	224.1	159.3
117.5°	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2	664.0	636.9	594.6
120°	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4	808.2	811.2	796.3
122.5°	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5	856.3	858.0	855.7
125°	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1	926.8	928.5	929.7
127.5°	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3	992.8	995.3	996.7
130°	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8	1034.5	1037.1	1038.3
132.5°	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0	1074.2	1076.6	1077.5
135°	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4	1131.8	1134.3	1135.2
137.5°	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8	1185.2	1187.6	1188.3
140°	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4	1219.5	1221.7	1222.2
142.5°	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2	1251.2	1253.2	1253.6
145°	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8	1295.5	1297.2	1297.4
147.5°	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7	1333.9	1335.2	1335.2
150°	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6	1358.1	1359.5	1359.6
152.5°	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4	1379.8	1381.3	1381.3
155°	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8	1409.3	1410.8	1410.5
157.5°	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7	1434.3	1436.0	1435.8
160°	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2	1448.6	1450.0	1449.9
162.5°	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6	1462.2	1463.9	1463.7
165°	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4
167.5°	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8	1492.5	1494.2	1494.0
170°	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8	1499.5	1501.2	1500.9
172.5°	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0	1504.7	1506.4	1506.2
175°	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7	1510.4	1512.1	1511.7
177.5°	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3	1510.6	1512.1	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	9.3	9.0	9.1	8.8	9.1	9.0	9.3	9.2	9.0	9.5	9.2
90°	28.0	28.4	29.0	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3
92.5°	28.5	28.9	29.2	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6
95°	47.6	47.3	47.2	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9
97.5°	61.7	62.1	62.3	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9
100°	71.6	72.1	72.6	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1
102.5°	76.2	77.0	77.7	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9
105°	80.0	81.0	81.9	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9
107.5°	82.4	83.4	84.4	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7
110°	83.3	84.3	85.2	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	84.7	85.5	86.2	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6
115°	141.8	124.4	106.9	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5
117.5°	537.3	479.9	422.6	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2
120°	763.6	730.8	698.1	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4
122.5°	849.4	843.0	836.7	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5
125°	930.4	931.2	931.9	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1
127.5°	996.8	996.9	997.0	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3
130°	1038.0	1037.9	1037.6	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8
132.5°	1077.4	1077.1	1076.8	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0
135°	1134.8	1134.3	1133.8	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4
137.5°	1187.5	1186.7	1185.9	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8
140°	1220.9	1219.8	1218.5	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4
142.5°	1252.4	1251.2	1249.9	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2
145°	1296.2	1295.0	1293.8	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8
147.5°	1334.3	1333.2	1332.2	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7
150°	1358.4	1357.2	1355.9	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6
152.5°	1379.7	1378.0	1376.4	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4
155°	1408.5	1406.7	1404.7	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8
157.5°	1434.0	1432.1	1430.2	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7
160°	1448.2	1446.5	1444.8	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2
162.5°	1461.6	1459.5	1457.4	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6
165°	1478.7	1477.0	1475.3	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0
167.5°	1491.7	1489.6	1487.4	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8
170°	1498.8	1496.6	1494.4	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8
172.5°	1504.0	1501.8	1499.6	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0
175°	1509.3	1506.9	1504.4	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7
177.5°	1510.1	1508.3	1506.6	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	9.0	9.1	9.1	9.0	8.6	8.6	8.6	8.4	8.6	8.4	8.2
90°	23.0	21.8	19.9	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1
92.5°	25.9	25.3	24.3	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0
95°	43.8	42.5	40.8	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9
97.5°	57.9	57.0	53.1	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7
100°	64.1	62.2	58.1	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1
102.5°	66.4	63.9	98.4	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7
105°	69.2	66.5	132.7	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6
107.5°	90.4	93.2	172.5	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9
110°	166.7	190.9	260.9	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	393.1	481.4	498.8	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0
115°	560.8	673.1	667.0	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2
117.5°	718.3	745.5	741.3	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0
120°	802.5	799.5	795.2	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6
122.5°	852.7	851.0	846.3	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4
125°	923.5	921.8	917.1	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8
127.5°	987.9	985.4	982.0	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2
130°	1029.1	1026.4	1023.8	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0
132.5°	1069.7	1067.5	1064.8	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6
135°	1127.0	1124.6	1122.4	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3
137.5°	1180.4	1178.0	1175.5	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7
140°	1215.1	1213.0	1210.3	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2
142.5°	1247.2	1245.3	1242.2	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7
145°	1292.1	1290.4	1286.3	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9
147.5°	1331.4	1330.1	1326.1	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9
150°	1355.1	1353.7	1349.8	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9
152.5°	1377.0	1375.5	1371.8	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4
155°	1406.4	1405.0	1402.0	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7
157.5°	1431.0	1429.4	1427.4	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5
160°	1445.6	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2
162.5°	1458.9	1457.3	1456.1	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2
165°	1475.3	1473.6	1472.9	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9
167.5°	1489.1	1487.4	1486.7	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9
170°	1496.1	1494.4	1493.9	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8
172.5°	1501.3	1499.6	1499.1	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0
175°	1507.0	1505.3	1504.9	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7
177.5°	1508.0	1506.6	1506.4	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.9	11.9	12.4	14.0	13.7	14.1	14.5	14.5	14.5	14.4	14.4
90°	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3
92.5°	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6
95°	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9
97.5°	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9
100°	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1
102.5°	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9
105°	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9
107.5°	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7
110°	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6
115°	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5
117.5°	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2
120°	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4
122.5°	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5
125°	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1
127.5°	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3
130°	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8
132.5°	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0
135°	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4
137.5°	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8
140°	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4
142.5°	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2
145°	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8
147.5°	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7
150°	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6
152.5°	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4
155°	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8
157.5°	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7
160°	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2
162.5°	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6
165°	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0
167.5°	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8
170°	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8
172.5°	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0
175°	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7
177.5°	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	14.9	15.2	15.0	15.1	15.5	15.2	15.3
90°	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331543-940

CATALOG NUMBER: S122DIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)