

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331549-940

Luminaire Tested: **S122DIW-S675D1440U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331549-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7753.7 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot



66% Up

34% Dn



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	79	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.5
10°-20°	327.9	4.2
20°-30°	475.9	6.1
30°-40°	502.2	6.5
40°-50°	444.7	5.7
50°-60°	354.9	4.6
60°-70°	241.2	3.1
70°-80°	123.7	1.6
80°-90°	34.1	0.4
90°-100°	58.5	0.8
100°-110°	214.4	2.8
110°-120°	573.1	7.4
120°-130°	946.0	12.2
130°-140°	1006.1	13.0
140°-150°	935.1	12.1
150°-160°	751.8	9.7
160°-170°	484.5	6.2
170°-180°	166.8	2.2
0°-30°	916.7	11.8
0°-40°	1418.9	18.3
0°-60°	2218.4	28.6
0°-90°	2617.4	33.8
90°-120°	846.0	10.9
90°-150°	3733.2	48.1
90°-180°	5136.0	66.2
0°-180°	7753.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	34	1	34	1	34	16
95°	55	82	55	82	55	51
105°	96	386	96	386	96	100
115°	104	729	104	729	104	260
125°	1084	1031	1084	1031	1084	938
135°	1318	1276	1318	1276	1318	1016
145°	1503	1480	1503	1480	1503	940
155°	1631	1630	1631	1630	1631	753
165°	1713	1717	1713	1717	1713	484
175°	1746	1756	1746	1756	1746	166
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	16.3	16.2	16.5	16.0	15.9	16.1	15.8	15.1	15.2	15.2	15.2
90°	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2	26.8	25.3	23.1
92.5°	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9	30.1	29.4	28.3
95°	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3	50.8	49.5	47.5
97.5°	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5	67.3	66.2	61.6
100°	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8	74.5	72.3	67.5
102.5°	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2	77.2	74.3	114.4
105°	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6	80.4	77.4	154.3
107.5°	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0	105.1	108.3	200.5
110°	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6	193.8	221.9	303.4



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2	457.0	559.8	579.9
115°	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6	652.0	782.5	775.4
117.5°	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6	835.2	866.7	861.8
120°	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4	933.0	929.6	924.5
122.5°	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5	991.5	989.4	983.9
125°	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6	1073.6	1071.7	1066.3
127.5°	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5	1148.6	1145.8	1141.7
130°	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6	1196.5	1193.4	1190.3
132.5°	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3	1243.8	1241.1	1238.0
135°	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1	1310.4	1307.5	1305.0
137.5°	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2	1372.4	1369.7	1366.8
140°	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3	1412.8	1410.2	1407.2
142.5°	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4	1450.1	1447.8	1444.2
145°	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2	1502.3	1500.3	1495.5
147.5°	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4	1547.9	1546.5	1541.8
150°	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3	1575.6	1573.9	1569.3
152.5°	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6	1600.9	1599.2	1594.9
155°	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8	1635.1	1633.4	1630.1
157.5°	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7	1663.8	1661.9	1659.5
160°	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5	1680.8	1679.1	1677.4
162.5°	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2	1696.3	1694.3	1692.9
165°	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3	1712.5
167.5°	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3	1731.3	1729.4	1728.6
170°	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4	1739.5	1737.5	1736.9
172.5°	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5	1745.5	1743.6	1743.0
175°	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1	1752.1	1750.2	1749.6
177.5°	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8	1753.3	1751.7	1751.4
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	15.1	14.6	14.2	14.4	12.7	12.0	10.0	8.3	8.6	8.7	8.6
90°	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2	4.4	7.5	10.6
92.5°	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6	25.3	25.1	24.8
95°	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4	73.1	63.8	54.6
97.5°	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6	137.4	111.2	85.0
100°	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4	185.8	147.2	108.6
102.5°	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4	283.3	275.1	266.9
105°	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6	394.0	402.4	410.9
107.5°	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8	499.6	506.5	513.3
110°	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9	567.8	573.6	579.6



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8	632.0	637.2	642.5
115°	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2	734.1	738.8	743.6
117.5°	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8	826.2	831.5	836.9
120°	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8	892.0	896.2	900.4
122.5°	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6	949.0	953.5	958.0
125°	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1	1034.7	1038.4	1042.1
127.5°	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5	1113.5	1117.6	1121.6
130°	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1	1163.7	1168.1	1172.7
132.5°	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9	1213.7	1217.5	1221.4
135°	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9	1280.3	1284.9	1289.3
137.5°	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6	1345.7	1348.9	1352.0
140°	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2	1388.4	1390.7	1392.9
142.5°	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7	1424.7	1426.7	1428.8
145°	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1	1479.7	1479.4	1479.2
147.5°	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0	1528.9	1527.9	1526.8
150°	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5	1560.5	1558.5	1556.6
152.5°	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8	1587.7	1585.5	1583.2
155°	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7	1627.1	1624.6	1622.0
157.5°	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9	1658.8	1656.6	1654.5
160°	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1677.4	1675.8	1674.1
162.5°	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3	1693.7	1692.0	1690.3
165°	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2	1715.5	1713.8	1712.1
167.5°	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4	1731.7	1730.0	1728.3
170°	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6	1740.9	1739.2	1737.5
172.5°	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6	1747.0	1745.3	1743.6
175°	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5	1754.5	1752.6	1750.6
177.5°	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7	1756.2	1754.6	1753.0
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	8.9	9.1	9.2	9.6	9.7	9.8	9.7	10.0	10.3	9.8	10.1
90°	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2	29.6	31.0	32.0
92.5°	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9	31.7	32.4	32.9
95°	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3	53.7	55.1	55.6
97.5°	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5	69.6	70.7	71.4
100°	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8	79.1	81.3	82.8
102.5°	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2	83.1	86.1	87.9
105°	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6	86.7	89.8	91.8
107.5°	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0	98.8	95.7	94.7
110°	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6	137.4	109.2	95.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2	251.4	148.6	97.6
115°	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6	391.0	260.6	185.1
117.5°	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6	772.0	740.5	691.3
120°	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4	939.8	943.2	925.8
122.5°	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5	995.6	997.6	994.9
125°	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6	1077.5	1079.5	1080.9
127.5°	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5	1154.3	1157.2	1158.8
130°	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6	1202.7	1205.8	1207.2
132.5°	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3	1249.0	1251.7	1252.9
135°	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1	1316.0	1318.8	1319.9
137.5°	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2	1378.0	1380.7	1381.6
140°	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3	1417.9	1420.4	1420.9
142.5°	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4	1454.7	1457.1	1457.5
145°	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2	1506.2	1508.2	1508.5
147.5°	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4	1550.9	1552.4	1552.5
150°	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3	1579.0	1580.6	1580.7
152.5°	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6	1604.3	1606.0	1605.9
155°	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8	1638.5	1640.2	1639.9
157.5°	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7	1667.6	1669.6	1669.4
160°	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5	1684.2	1685.9	1685.8
162.5°	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2	1700.1	1702.0	1701.7
165°	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3
167.5°	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3	1735.3	1737.2	1737.0
170°	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4	1743.4	1745.3	1745.1
172.5°	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5	1749.4	1751.4	1751.1
175°	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1	1756.0	1758.0	1757.7
177.5°	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8	1756.4	1758.0	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	10.2	9.9	10.0	9.7	10.0	9.9	10.2	10.1	9.8	10.3	10.0
90°	32.5	33.1	33.7	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2
92.5°	33.3	33.5	33.9	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9
95°	55.4	55.1	54.8	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3
97.5°	71.8	72.1	72.5	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5
100°	83.3	83.8	84.4	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8
102.5°	88.7	89.4	90.2	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2
105°	93.0	94.2	95.2	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6
107.5°	95.8	96.9	98.1	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0
110°	96.8	97.9	99.1	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	98.5	99.4	100.3	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2
115°	164.9	144.5	124.3	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6
117.5°	624.6	557.9	491.2	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6
120°	887.8	849.7	811.6	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4
122.5°	987.5	980.2	972.8	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5
125°	1081.8	1082.6	1083.5	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6
127.5°	1158.9	1159.0	1159.2	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5
130°	1206.9	1206.7	1206.4	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6
132.5°	1252.6	1252.3	1252.1	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3
135°	1319.4	1318.8	1318.2	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1
137.5°	1380.6	1379.7	1378.8	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2
140°	1419.6	1418.2	1416.8	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3
142.5°	1456.1	1454.6	1453.3	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4
145°	1507.1	1505.7	1504.2	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2
147.5°	1551.3	1550.2	1548.9	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4
150°	1579.4	1578.0	1576.5	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3
152.5°	1604.0	1602.2	1600.4	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6
155°	1637.7	1635.5	1633.2	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8
157.5°	1667.2	1665.0	1662.8	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7
160°	1683.8	1681.8	1679.8	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5
162.5°	1699.3	1696.9	1694.5	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2
165°	1719.3	1717.3	1715.4	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3
167.5°	1734.5	1731.9	1729.4	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3
170°	1742.6	1740.0	1737.5	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4
172.5°	1748.6	1746.1	1743.6	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5
175°	1754.8	1751.9	1749.2	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1
177.5°	1755.7	1753.7	1751.7	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	9.7	9.8	9.7	9.6	9.2	9.1	8.9	8.6	8.7	8.6	8.3
90°	26.8	25.3	23.1	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2
92.5°	30.1	29.4	28.3	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6
95°	50.8	49.5	47.5	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4
97.5°	67.3	66.2	61.6	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6
100°	74.5	72.3	67.5	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4
102.5°	77.2	74.3	114.4	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4
105°	80.4	77.4	154.3	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6
107.5°	105.1	108.3	200.5	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8
110°	193.8	221.9	303.4	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.0	559.8	579.9	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8
115°	652.0	782.5	775.4	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2
117.5°	835.2	866.7	861.8	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8
120°	933.0	929.6	924.5	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8
122.5°	991.5	989.4	983.9	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6
125°	1073.6	1071.7	1066.3	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1
127.5°	1148.6	1145.8	1141.7	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5
130°	1196.5	1193.4	1190.3	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1
132.5°	1243.8	1241.1	1238.0	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9
135°	1310.4	1307.5	1305.0	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9
137.5°	1372.4	1369.7	1366.8	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6
140°	1412.8	1410.2	1407.2	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2
142.5°	1450.1	1447.8	1444.2	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7
145°	1502.3	1500.3	1495.5	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1
147.5°	1547.9	1546.5	1541.8	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0
150°	1575.6	1573.9	1569.3	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5
152.5°	1600.9	1599.2	1594.9	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8
155°	1635.1	1633.4	1630.1	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7
157.5°	1663.8	1661.9	1659.5	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9
160°	1680.8	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1
162.5°	1696.3	1694.3	1692.9	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3
165°	1715.4	1713.3	1712.5	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2
167.5°	1731.3	1729.4	1728.6	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4
170°	1739.5	1737.5	1736.9	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6
172.5°	1745.5	1743.6	1743.0	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6
175°	1752.1	1750.2	1749.6	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5
177.5°	1753.3	1751.7	1751.4	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	10.0	12.0	12.7	14.4	14.2	14.6	15.1	15.2	15.2	15.2	15.1
90°	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2
92.5°	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9
95°	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3
97.5°	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5
100°	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8
102.5°	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2
105°	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6
107.5°	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0
110°	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2
115°	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6
117.5°	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6
120°	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4
122.5°	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5
125°	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6
127.5°	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5
130°	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6
132.5°	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3
135°	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1
137.5°	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2
140°	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3
142.5°	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4
145°	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2
147.5°	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4
150°	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3
152.5°	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6
155°	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8
157.5°	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7
160°	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5
162.5°	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2
165°	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3
167.5°	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3
170°	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4
172.5°	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5
175°	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1
177.5°	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	15.8	16.1	15.9	16.0	16.5	16.2	16.3
90°	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331549-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)