

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332412-830

Luminaire Tested: **S123RDIW-S560D460U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332412-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D460U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3750.9 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54					54			
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46					46			
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39					39			
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33					33			
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	32	29					29			
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25					25			
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22					22			
7	60	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	23	20					20			
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18					18			
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16					16			
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15					15			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9582	9582	9582
5°	9619	9487	9541
10°	9565	9368	9335
15°	9461	9149	9052
20°	9321	8874	8668
25°	9175	8567	8291
30°	8983	8211	7762
35°	8784	7857	7276
40°	8604	7436	6674
45°	8363	7024	6132
50°	8100	6553	5526
55°	7833	6016	4960
60°	7584	5440	4336
65°	7264	4819	3713
70°	6861	4047	2999
75°	6276	3182	2824
80°	5597	2820	2591
85°	4730	2495	2322



TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.2
10°-20°	232.6	6.2
20°-30°	334.9	8.9
30°-40°	377.3	10.1
40°-50°	360.9	9.6
50°-60°	295.6	7.9
60°-70°	199.4	5.3
70°-80°	100.3	2.7
80°-90°	28.1	0.8
90°-100°	20.7	0.6
100°-110°	98.8	2.6
110°-120°	237.2	6.3
120°-130°	302.1	8.1
130°-140°	322.8	8.6
140°-150°	301.8	8.0
150°-160°	243.5	6.5
160°-170°	157.1	4.2
170°-180°	54.2	1.4
0°-30°	651.1	17.4
0°-40°	1028.4	27.4
0°-60°	1684.8	44.9
0°-90°	2012.7	53.7
90°-120°	356.7	9.5
90°-150°	1283.4	34.2
90°-180°	1738.0	46.3
0°-180°	3750.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	890	890	890	890	890	
5°	890	886	878	884	883	84
15°	849	840	821	817	812	239
25°	772	754	721	706	698	355
35°	668	642	598	568	554	418
45°	549	516	461	422	403	424
55°	417	380	321	280	264	374
65°	285	245	189	155	146	282
75°	151	116	76	70	68	161
85°	38	23	20	19	19	43
90°	0	5	10	12	13	3
95°	26	10	13	16	16	32
105°	126	128	93	22	19	134
115°	237	239	243	247	249	234
125°	334	337	339	340	340	298
135°	415	418	420	421	420	320
145°	479	482	483	484	484	300
155°	528	527	528	529	527	243
165°	557	556	555	558	556	157
175°	570	568	568	571	568	54
180°	570	570	570	570	570	



TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	893.2	892.6	892.1	891.6	891.1	890.0	888.5	886.9	885.4	883.9	885.3
5°	890.2	889.5	888.6	887.9	887.0	885.7	883.7	881.8	879.9	878.0	879.4
7.5°	882.0	881.2	880.2	879.4	878.5	876.8	874.4	871.9	869.3	866.9	867.6
10°	875.1	873.9	872.8	871.7	870.6	868.6	865.7	862.8	859.9	857.1	857.1
12.5°	865.3	864.0	862.7	861.5	860.3	857.9	854.3	850.8	847.3	843.8	843.7
15°	849.0	847.3	845.6	843.8	842.1	838.9	834.4	829.9	825.4	821.0	820.1
17.5°	828.7	826.7	824.6	822.6	820.5	816.6	810.9	805.2	799.5	793.8	792.1
20°	813.7	811.2	808.6	806.0	803.4	799.1	793.0	786.9	780.8	774.7	772.6
22.5°	796.9	794.0	791.1	788.1	785.1	780.4	773.9	767.4	761.0	754.5	751.9
25°	772.5	768.5	764.5	760.5	756.5	750.8	743.4	736.0	728.7	721.3	717.9
27.5°	742.9	738.5	734.1	729.6	725.2	718.9	710.7	702.5	694.3	686.1	681.4
30°	722.7	717.9	713.1	708.3	703.5	696.5	687.6	678.6	669.6	660.6	655.2
32.5°	702.5	697.1	691.6	686.2	680.7	673.3	663.7	654.2	644.7	635.2	629.2
35°	668.5	662.8	657.0	651.3	645.5	637.6	627.6	617.7	607.8	597.9	590.9
37.5°	634.2	627.8	621.4	614.9	608.5	600.0	589.4	578.8	568.2	557.5	549.7
40°	612.3	605.2	598.1	591.1	584.0	574.8	563.5	552.0	540.6	529.2	520.8
42.5°	587.4	580.3	573.3	566.3	559.2	549.8	538.0	526.2	514.4	502.7	493.5
45°	549.4	542.2	535.0	527.8	520.6	510.8	498.4	486.1	473.7	461.4	452.2
47.5°	511.4	503.5	495.6	487.7	479.8	469.7	457.2	444.9	432.5	420.2	410.3
50°	483.7	476.2	468.6	461.1	453.6	443.3	430.3	417.4	404.4	391.3	381.4
52.5°	458.9	450.7	442.5	434.3	426.2	415.7	402.7	389.9	377.0	364.2	353.8
55°	417.4	409.4	401.6	393.7	385.9	375.1	361.5	347.9	334.2	320.6	311.2
57.5°	378.9	370.3	361.7	353.2	344.6	333.5	319.8	306.1	292.4	278.7	269.9
60°	352.3	343.6	334.7	325.8	317.1	305.9	292.7	279.4	266.0	252.7	244.0
62.5°	325.7	317.0	308.1	299.3	290.5	279.4	266.1	252.8	239.4	226.1	218.0
65°	285.2	276.4	267.6	258.7	249.9	239.2	226.7	214.2	201.7	189.2	181.3
67.5°	244.6	235.7	226.8	217.8	209.0	198.5	186.4	174.5	162.5	150.4	144.6
70°	218.0	209.3	200.8	192.1	183.4	173.4	162.2	151.0	139.8	128.6	122.9
72.5°	191.4	182.9	174.4	165.9	157.3	148.0	137.8	127.5	117.3	107.2	102.5
75°	150.9	143.2	135.5	127.8	120.1	111.8	103.0	94.2	85.4	76.5	74.9
77.5°	114.0	107.0	100.0	93.0	86.1	79.7	74.1	68.4	62.7	57.0	56.2
80°	90.3	83.7	77.1	70.5	63.9	59.0	55.6	52.2	48.8	45.5	45.0
82.5°	67.8	62.0	56.4	50.7	45.0	41.4	39.8	38.3	36.7	35.1	34.6
85°	38.3	34.8	31.2	27.7	24.1	22.1	21.7	21.2	20.7	20.2	19.9
87.5°	13.9	12.7	11.5	10.3	9.0	8.6	8.8	9.0	9.3	9.5	9.5
90°	0.4	1.3	2.3	3.2	4.1	5.3	6.5	7.7	9.0	10.2	10.6
92.5°	7.9	7.6	7.4	7.1	6.8	7.2	8.1	9.0	9.9	10.8	11.4
95°	25.8	22.0	18.1	14.2	10.4	9.0	10.0	11.0	12.1	13.1	13.8
97.5°	51.9	50.1	48.4	46.8	45.0	40.7	33.9	27.1	20.5	13.7	14.4
100°	71.5	73.4	75.3	77.2	79.1	72.7	58.1	43.4	28.7	13.9	14.7
102.5°	93.9	95.3	96.6	98.0	99.3	92.0	76.0	59.9	43.9	27.9	25.5
105°	126.2	127.2	128.3	129.3	130.4	126.6	118.1	109.7	101.2	92.7	76.1
107.5°	160.2	161.1	161.9	162.7	163.5	164.7	166.0	167.3	168.6	169.9	157.8
110°	182.9	183.7	184.5	185.2	186.0	186.8	187.8	188.9	189.9	191.0	187.8



TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.6	205.3	205.9	206.6	207.4	208.2	209.2	210.3	211.3	212.4	212.4
115°	236.7	237.2	237.8	238.4	238.9	239.7	240.5	241.4	242.2	243.1	244.0
117.5°	267.8	268.5	269.2	269.8	270.6	271.2	271.5	272.0	272.5	272.9	273.6
120°	287.1	287.9	288.8	289.6	290.5	291.1	291.3	291.6	291.9	292.2	292.9
122.5°	306.8	307.5	308.1	308.9	309.5	310.1	310.5	310.8	311.1	311.5	312.0
125°	333.7	334.4	335.2	335.9	336.7	337.2	337.6	338.0	338.4	338.7	338.9
127.5°	359.8	360.5	361.3	362.0	362.8	363.4	363.8	364.3	364.8	365.2	365.5
130°	376.1	376.8	377.6	378.3	379.1	379.7	380.0	380.4	380.8	381.1	381.4
132.5°	391.6	392.4	393.1	393.9	394.6	395.1	395.5	395.8	396.1	396.3	396.7
135°	415.4	415.9	416.5	417.1	417.6	418.1	418.5	418.9	419.2	419.6	419.9
137.5°	435.7	436.5	437.2	437.9	438.6	439.0	439.3	439.5	439.7	439.9	440.4
140°	449.3	449.9	450.4	451.0	451.6	451.9	452.2	452.5	452.8	453.1	453.5
142.5°	461.8	462.4	463.0	463.5	464.1	464.5	464.8	465.1	465.3	465.6	465.9
145°	479.4	480.0	480.7	481.4	482.0	482.4	482.6	482.8	483.0	483.1	483.3
147.5°	495.9	496.3	496.7	497.2	497.6	497.9	498.1	498.3	498.5	498.7	498.9
150°	506.1	506.3	506.6	506.9	507.2	507.4	507.6	507.7	507.9	508.1	508.3
152.5°	515.2	515.3	515.5	515.6	515.8	515.9	515.9	516.0	516.1	516.3	516.6
155°	528.0	527.8	527.6	527.5	527.4	527.3	527.4	527.4	527.5	527.6	528.1
157.5°	538.1	538.0	538.0	538.0	538.0	537.9	537.8	537.7	537.6	537.5	538.1
160°	544.1	544.0	543.9	543.8	543.8	543.7	543.6	543.5	543.4	543.3	543.8
162.5°	549.9	549.7	549.4	549.2	548.9	548.7	548.7	548.6	548.5	548.4	549.0
165°	556.9	556.6	556.3	556.0	555.7	555.5	555.4	555.3	555.3	555.2	555.9
167.5°	562.3	561.9	561.6	561.2	560.8	560.6	560.6	560.6	560.6	560.6	561.4
170°	565.3	565.0	564.6	564.2	563.8	563.6	563.6	563.6	563.6	563.6	564.4
172.5°	567.3	566.9	566.5	566.0	565.5	565.3	565.4	565.5	565.6	565.6	566.4
175°	570.0	569.5	569.0	568.5	568.1	567.9	568.0	568.1	568.2	568.3	568.9
177.5°	570.6	570.2	569.9	569.5	569.1	569.0	569.1	569.1	569.2	569.3	569.9
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	886.7	888.2	889.6	890.1	889.9	889.6	889.4	889.1
5°	880.8	882.3	883.7	884.3	884.0	883.6	883.4	883.0
7.5°	868.5	869.2	870.1	870.2	869.6	869.1	868.6	868.0
10°	857.3	857.5	857.6	857.3	856.6	855.7	855.0	854.1
12.5°	843.6	843.5	843.4	842.8	841.9	840.9	840.1	839.1
15°	819.4	818.5	817.7	816.7	815.6	814.5	813.4	812.3
17.5°	790.4	788.7	786.9	785.3	783.6	781.9	780.2	778.6
20°	770.5	768.5	766.4	764.4	762.4	760.5	758.6	756.7
22.5°	749.3	746.7	744.1	741.9	740.1	738.3	736.5	734.7
25°	714.5	711.1	707.8	705.2	703.5	701.7	699.9	698.1
27.5°	676.7	672.0	667.3	663.6	660.9	658.3	655.5	652.8
30°	649.7	644.2	638.9	634.8	632.3	629.7	627.1	624.5
32.5°	623.3	617.3	611.3	607.0	604.4	601.6	598.9	596.3
35°	584.0	577.1	570.2	565.3	562.4	559.6	556.7	553.7
37.5°	541.9	534.0	526.2	520.6	517.0	513.4	509.8	506.2
40°	512.6	504.2	495.9	489.8	486.2	482.5	478.8	475.0
42.5°	484.5	475.3	466.2	460.0	456.7	453.4	450.1	446.8
45°	443.1	433.9	424.8	418.3	414.4	410.6	406.7	402.8
47.5°	400.3	390.4	380.4	373.7	370.3	366.8	363.4	360.0
50°	371.5	361.5	351.6	344.7	341.0	337.3	333.7	330.0
52.5°	343.6	333.2	322.8	316.0	312.7	309.4	306.1	302.8
55°	302.0	292.7	283.3	277.1	273.9	270.7	267.5	264.3
57.5°	261.1	252.3	243.6	237.8	235.1	232.3	229.6	226.9
60°	235.4	226.7	218.0	212.4	209.6	206.9	204.2	201.4
62.5°	209.8	201.7	193.5	188.0	185.2	182.3	179.5	176.6
65°	173.4	165.6	157.7	152.9	151.2	149.4	147.6	145.8
67.5°	138.7	132.8	127.0	123.1	121.2	119.3	117.4	115.6
70°	117.3	111.7	106.0	102.4	100.6	98.9	97.1	95.3
72.5°	97.9	93.4	88.8	86.1	85.4	84.6	83.9	83.1
75°	73.3	71.7	70.1	69.2	68.8	68.5	68.1	67.9
77.5°	55.3	54.5	53.5	53.0	52.7	52.3	52.0	51.7
80°	44.5	44.0	43.5	43.2	42.9	42.5	42.2	41.8
82.5°	34.1	33.6	33.2	32.9	32.8	32.8	32.7	32.6
85°	19.6	19.2	18.9	18.8	18.8	18.8	18.8	18.8
87.5°	9.4	9.4	9.3	9.2	9.1	9.0	9.0	8.9
90°	10.9	11.3	11.7	12.0	12.2	12.3	12.5	12.7
92.5°	12.1	12.6	13.3	13.6	13.8	13.9	13.9	14.0
95°	14.4	15.1	15.7	16.1	16.1	16.1	16.1	16.1
97.5°	15.2	15.9	16.7	17.1	17.2	17.2	17.3	17.4
100°	15.5	16.2	17.0	17.4	17.5	17.6	17.7	17.8
102.5°	23.2	20.8	18.6	17.4	17.6	17.8	17.9	18.1
105°	59.4	42.8	26.1	17.9	18.1	18.3	18.5	18.7
107.5°	145.5	133.4	121.1	108.8	96.1	83.6	71.1	58.5
110°	184.7	181.6	178.5	170.3	156.8	143.4	129.9	116.5



TEST NUMBER: P332412-830

CATALOG NUMBER: S123RDIW-S560D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.4	212.4	212.5	211.1	208.3	205.5	202.6	199.8
115°	245.0	245.9	246.9	247.5	247.9	248.3	248.6	249.0
117.5°	274.4	275.1	275.9	276.3	276.4	276.4	276.5	276.6
120°	293.7	294.5	295.2	295.6	295.6	295.6	295.6	295.6
122.5°	312.5	313.1	313.6	313.9	314.0	314.1	314.1	314.2
125°	339.1	339.3	339.5	339.7	339.9	340.1	340.3	340.4
127.5°	365.8	366.1	366.4	366.5	366.3	366.1	365.9	365.7
130°	381.8	382.2	382.6	382.7	382.5	382.3	382.1	381.9
132.5°	397.1	397.5	397.8	397.9	397.7	397.4	397.1	396.9
135°	420.2	420.5	420.8	420.8	420.5	420.2	419.9	419.6
137.5°	440.8	441.2	441.7	441.9	441.7	441.5	441.3	441.1
140°	453.8	454.2	454.6	454.7	454.5	454.3	454.1	453.9
142.5°	466.3	466.6	466.8	466.8	466.6	466.4	466.1	465.8
145°	483.5	483.7	483.9	484.0	484.0	484.0	484.0	484.0
147.5°	499.1	499.3	499.5	499.3	498.9	498.4	498.0	497.6
150°	508.5	508.7	508.9	508.9	508.6	508.3	508.0	507.7
152.5°	517.0	517.3	517.6	517.6	517.2	516.7	516.3	515.9
155°	528.6	529.0	529.5	529.4	528.9	528.3	527.7	527.3
157.5°	538.7	539.2	539.8	539.7	538.9	538.3	537.5	536.8
160°	544.4	545.0	545.5	545.5	544.9	544.2	543.6	542.9
162.5°	549.7	550.4	550.9	551.0	550.4	549.8	549.2	548.7
165°	556.7	557.4	558.2	558.2	557.5	556.9	556.3	555.6
167.5°	562.1	562.8	563.5	563.5	562.8	562.1	561.4	560.6
170°	565.1	565.9	566.7	566.7	565.9	565.1	564.4	563.6
172.5°	567.1	567.9	568.6	568.6	567.8	566.9	566.2	565.3
175°	569.6	570.2	570.9	570.9	570.1	569.4	568.6	567.9
177.5°	570.5	571.1	571.7	571.7	570.9	570.1	569.4	568.6
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0

(END OF REPORT)