

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331530-940

Luminaire Tested: **S122DIW-S675D435U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331530-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3749.1 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75	70	68	67	61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	40	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	2.4
10°-20°	250.5	6.7
20°-30°	368.2	9.8
30°-40°	427.7	11.4
40°-50°	427.2	11.4
50°-60°	372.6	9.9
60°-70°	275.5	7.3
70°-80°	156.0	4.2
80°-90°	43.9	1.2
90°-100°	30.3	0.8
100°-110°	94.2	2.5
110°-120°	161.0	4.3
120°-130°	211.8	5.6
130°-140°	237.7	6.3
140°-150°	233.1	6.2
150°-160°	195.5	5.2
160°-170°	129.7	3.5
170°-180°	45.3	1.2
0°-30°	707.7	18.9
0°-40°	1135.4	30.3
0°-60°	1935.1	51.6
0°-90°	2410.5	64.3
90°-120°	285.6	7.6
90°-150°	968.1	25.8
90°-180°	1339.0	35.7
0°-180°	3749.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	0	5	14	13	14	3
95°	21	25	26	26	25	24
105°	87	88	89	90	90	92
115°	162	164	163	163	162	160
125°	235	238	238	236	236	210
135°	304	308	309	309	308	235
145°	369	372	374	375	373	231
155°	422	423	425	426	425	194
165°	459	459	459	462	460	129
175°	478	477	476	478	476	45
180°	479	479	479	479	479	



TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.2	13.1	12.9	12.8	12.8	12.8	12.8	12.8	12.9	13.0	12.5
90°	0.4	1.5	2.6	3.7	4.7	6.2	8.2	10.2	12.1	14.2	14.0
92.5°	7.2	8.0	8.7	9.5	10.3	11.0	11.4	11.9	12.4	12.8	12.8
95°	21.0	21.9	22.8	23.7	24.6	25.1	25.3	25.5	25.7	25.9	25.9
97.5°	38.3	39.1	39.9	40.8	41.6	42.1	42.4	42.8	43.2	43.4	43.4
100°	51.3	52.0	52.7	53.5	54.2	54.7	54.9	55.2	55.5	55.7	55.7
102.5°	64.9	65.5	66.0	66.6	67.1	67.7	67.9	68.3	68.7	69.0	69.1
105°	86.9	87.1	87.4	87.7	87.9	88.2	88.4	88.5	88.7	88.9	89.1
107.5°	109.0	109.4	109.8	110.2	110.6	110.8	110.8	110.8	110.8	110.8	110.8
110°	123.2	123.8	124.3	124.8	125.4	125.6	125.6	125.6	125.6	125.6	125.6



TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.8	139.3	139.8	140.4	140.9	141.2	141.1	141.0	140.9	140.8	140.6
115°	161.6	162.1	162.6	163.2	163.7	163.9	163.7	163.5	163.4	163.2	163.1
117.5°	184.4	185.1	185.8	186.5	187.3	187.3	186.9	186.4	185.8	185.4	185.1
120°	199.6	200.3	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6	199.6
122.5°	213.5	214.4	215.2	216.1	217.0	217.1	216.6	216.1	215.6	215.1	214.9
125°	235.1	235.9	236.7	237.6	238.4	238.6	238.4	238.1	237.8	237.6	237.3
127.5°	256.2	257.3	258.2	259.3	260.3	260.6	260.4	260.0	259.7	259.4	259.0
130°	269.5	270.6	271.8	273.0	274.1	274.6	274.5	274.3	274.1	273.9	273.8
132.5°	284.4	285.3	286.2	287.2	288.1	288.6	288.6	288.7	288.7	288.7	288.4
135°	304.3	305.2	306.2	307.2	308.2	308.7	308.9	309.1	309.2	309.4	309.3
137.5°	325.1	325.9	326.7	327.5	328.3	328.9	329.1	329.4	329.6	329.8	329.8
140°	337.8	338.6	339.4	340.2	341.0	341.6	342.1	342.5	343.0	343.4	343.4
142.5°	350.7	351.5	352.3	353.1	353.9	354.5	354.7	355.1	355.3	355.7	355.8
145°	369.3	369.9	370.5	371.1	371.8	372.4	372.9	373.4	374.0	374.5	374.6
147.5°	385.8	386.6	387.4	388.1	388.9	389.4	389.8	390.1	390.5	390.8	391.0
150°	397.2	397.7	398.2	398.8	399.3	399.8	400.1	400.5	400.8	401.2	401.4
152.5°	407.2	407.7	408.2	408.8	409.3	409.8	410.2	410.6	411.1	411.5	411.9
155°	422.1	422.4	422.7	423.0	423.3	423.6	423.8	424.1	424.4	424.6	425.1
157.5°	435.1	435.2	435.4	435.6	435.8	435.9	436.0	436.2	436.4	436.6	437.2
160°	442.8	443.0	443.2	443.4	443.5	443.6	443.7	443.8	443.9	444.0	444.5
162.5°	449.9	450.0	450.0	450.0	450.0	450.1	450.2	450.3	450.4	450.5	451.0
165°	459.3	459.2	459.1	459.1	459.0	459.0	459.0	459.0	459.0	459.0	459.6
167.5°	467.3	467.0	466.7	466.5	466.2	466.0	466.0	466.0	466.0	466.0	466.6
170°	471.4	471.2	470.9	470.6	470.4	470.2	470.1	470.0	469.9	469.8	470.5
172.5°	474.4	474.1	473.9	473.6	473.3	473.1	473.1	473.0	472.9	472.8	473.4
175°	478.0	477.7	477.4	477.2	476.9	476.6	476.4	476.3	476.1	475.9	476.5
177.5°	479.4	479.2	478.9	478.8	478.5	478.3	478.2	478.0	477.9	477.8	478.2
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	11.9	11.5	11.0	10.6	10.4	10.3	10.2	10.0
90°	13.8	13.6	13.5	13.4	13.5	13.6	13.6	13.7
92.5°	12.9	12.9	13.0	13.0	13.0	13.0	13.1	13.1
95°	25.9	25.9	25.9	25.8	25.6	25.4	25.2	25.1
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4
100°	55.7	55.7	55.7	55.7	55.6	55.6	55.5	55.4
102.5°	69.1	69.2	69.3	69.3	69.2	69.1	69.0	68.9
105°	89.3	89.4	89.6	89.7	89.7	89.7	89.7	89.7
107.5°	110.9	111.0	111.1	110.9	110.5	110.0	109.7	109.2
110°	125.6	125.6	125.6	125.5	125.2	124.9	124.7	124.4



TEST NUMBER: P331530-940

CATALOG NUMBER: S122DIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	140.4	140.2	140.0	139.7	139.6	139.4	139.2	139.0
115°	163.0	162.9	162.8	162.6	162.4	162.1	161.8	161.6
117.5°	184.9	184.7	184.5	184.2	184.0	183.7	183.4	183.2
120°	199.6	199.6	199.6	199.5	199.2	198.9	198.7	198.4
122.5°	214.6	214.5	214.2	214.0	213.8	213.7	213.4	213.2
125°	237.0	236.7	236.5	236.3	236.2	236.1	236.0	235.9
127.5°	258.7	258.4	258.1	257.8	257.4	257.2	256.9	256.6
130°	273.6	273.4	273.2	273.0	272.6	272.2	271.9	271.5
132.5°	288.0	287.6	287.2	286.9	286.6	286.2	286.0	285.7
135°	309.2	309.2	309.1	308.9	308.6	308.4	308.1	307.8
137.5°	329.7	329.6	329.6	329.3	329.0	328.6	328.2	327.9
140°	343.4	343.4	343.4	343.2	342.9	342.5	342.1	341.8
142.5°	355.8	355.9	356.0	355.8	355.4	355.1	354.7	354.4
145°	374.7	374.8	374.9	374.7	374.3	374.0	373.6	373.3
147.5°	391.2	391.5	391.6	391.6	391.2	390.8	390.5	390.2
150°	401.7	402.0	402.3	402.3	402.0	401.7	401.4	401.2
152.5°	412.1	412.5	412.9	412.9	412.5	412.1	411.9	411.5
155°	425.5	426.0	426.4	426.5	426.2	426.0	425.7	425.4
157.5°	437.7	438.4	439.0	439.1	438.6	438.2	437.8	437.4
160°	445.1	445.6	446.1	446.2	445.9	445.5	445.1	444.8
162.5°	451.7	452.3	452.9	453.0	452.5	452.1	451.7	451.3
165°	460.2	460.8	461.5	461.5	461.1	460.7	460.2	459.8
167.5°	467.3	467.9	468.5	468.6	468.1	467.6	467.2	466.7
170°	471.1	471.7	472.3	472.4	471.9	471.4	470.8	470.3
172.5°	474.0	474.7	475.3	475.3	474.7	474.2	473.7	473.1
175°	477.2	477.8	478.4	478.5	478.0	477.4	476.9	476.4
177.5°	478.7	479.0	479.5	479.5	479.0	478.7	478.2	477.8
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8

(END OF REPORT)