

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332197-930

Luminaire Tested: **S123DIW-S1000D1030U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332197-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D1030U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6274.4 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	1.9
10°-20°	343.3	5.5
20°-30°	507.0	8.1
30°-40°	592.3	9.4
40°-50°	595.5	9.5
50°-60°	523.1	8.3
60°-70°	389.7	6.2
70°-80°	222.0	3.5
80°-90°	66.8	1.1
90°-100°	68.5	1.1
100°-110°	205.0	3.3
110°-120°	348.7	5.6
120°-130°	458.7	7.3
130°-140°	515.5	8.2
140°-150°	506.8	8.1
150°-160°	426.6	6.8
160°-170°	284.0	4.5
170°-180°	99.4	1.6
0°-30°	971.9	15.5
0°-40°	1564.1	24.9
0°-60°	2682.6	42.8
0°-90°	3361.2	53.6
90°-120°	622.2	9.9
90°-150°	2103.2	33.5
90°-180°	2913.0	46.4
0°-180°	6274.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	9	20	23	25	6
95°	49	55	61	64	64	55
105°	186	188	195	195	197	199
115°	351	353	352	353	352	347
125°	514	516	515	511	508	458
135°	667	671	671	667	666	513
145°	809	810	813	812	809	505
155°	926	926	927	930	924	426
165°	1008	1006	1006	1010	1005	284
175°	1049	1046	1046	1050	1045	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	23.0	22.8	22.6	22.3	22.3	22.7	22.9	23.2	23.5	23.5
90°	0.8	2.7	4.5	6.4	8.2	10.3	12.6	15.1	17.4	19.8	20.5
92.5°	20.0	21.2	22.5	23.7	24.9	26.3	27.6	29.0	30.3	31.7	32.3
95°	48.8	50.0	51.3	52.6	53.9	55.3	56.7	58.2	59.7	61.1	61.9
97.5°	86.6	87.5	88.5	89.4	90.4	91.4	92.5	93.5	94.6	95.6	96.5
100°	112.3	113.4	114.5	115.6	116.8	117.7	118.7	119.6	120.5	121.4	122.0
102.5°	142.1	142.8	143.4	144.1	144.7	145.6	146.8	148.1	149.3	150.5	151.1
105°	185.9	186.2	186.6	186.9	187.4	188.3	190.0	191.6	193.3	194.9	194.9
107.5°	236.8	236.9	237.2	237.4	237.6	238.1	238.7	239.4	240.0	240.7	241.2
110°	268.5	268.8	269.2	269.5	269.9	270.3	270.7	271.0	271.4	271.7	272.5



TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	301.5	301.7	301.9	302.1	302.4	302.5	302.6	302.6	302.7	302.8	303.7
115°	351.1	351.6	352.1	352.7	353.3	353.4	352.9	352.6	352.2	351.9	352.0
117.5°	401.0	401.3	401.7	402.0	402.4	402.4	401.9	401.4	400.9	400.5	400.4
120°	432.0	433.1	434.2	435.3	436.4	436.5	435.5	434.6	433.7	432.8	432.6
122.5°	464.4	465.2	466.0	466.8	467.6	467.7	467.3	466.8	466.4	465.9	465.4
125°	513.8	514.3	514.9	515.4	516.0	516.1	515.7	515.4	514.9	514.6	513.9
127.5°	559.4	560.5	561.7	562.9	564.0	564.4	564.0	563.6	563.2	562.8	561.8
130°	589.8	591.3	592.7	594.2	595.7	596.1	595.6	595.0	594.4	593.9	593.1
132.5°	620.1	621.6	623.1	624.6	626.1	626.6	626.1	625.7	625.3	624.9	624.0
135°	666.6	667.6	668.8	669.8	671.0	671.4	671.2	671.1	670.9	670.7	669.9
137.5°	709.6	710.5	711.3	712.2	713.2	713.9	714.4	714.9	715.3	715.8	715.0
140°	739.2	740.2	741.1	742.0	742.9	743.5	743.6	743.9	744.0	744.2	744.0
142.5°	766.4	767.3	768.2	769.1	770.1	770.6	770.9	771.3	771.7	772.0	771.8
145°	808.6	809.0	809.3	809.8	810.1	810.6	811.1	811.7	812.2	812.8	812.6
147.5°	845.6	846.3	846.9	847.7	848.3	848.9	849.4	849.9	850.4	850.9	850.9
150°	871.4	871.8	872.1	872.5	872.9	873.3	873.6	874.0	874.3	874.7	874.7
152.5°	892.6	893.1	893.6	894.1	894.6	895.0	895.2	895.4	895.7	895.9	896.2
155°	925.9	925.9	925.9	925.9	925.9	926.0	926.2	926.4	926.6	926.8	927.5
157.5°	954.4	954.1	953.9	953.7	953.5	953.4	953.6	953.7	953.9	954.0	954.8
160°	972.2	971.8	971.4	971.1	970.7	970.5	970.5	970.5	970.5	970.5	971.4
162.5°	988.1	987.6	987.0	986.5	986.0	985.8	985.9	986.1	986.3	986.4	987.3
165°	1008.5	1008.0	1007.5	1006.9	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1
167.5°	1024.9	1024.2	1023.4	1022.7	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4
170°	1034.1	1033.4	1032.7	1031.9	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1
172.5°	1041.4	1040.6	1039.9	1039.2	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3
175°	1049.0	1048.3	1047.6	1046.8	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8
177.5°	1052.1	1051.6	1051.0	1050.4	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	23.4	23.3	23.3	23.3	23.4	23.5	23.6	23.6
90°	21.3	22.0	22.7	23.3	23.6	24.1	24.4	24.8
92.5°	32.9	33.5	34.1	34.2	34.0	33.8	33.6	33.3
95°	62.6	63.3	64.1	64.4	64.4	64.4	64.4	64.4
97.5°	97.3	98.2	99.1	99.4	99.3	99.3	99.2	99.1
100°	122.5	123.1	123.6	124.1	124.4	124.8	125.1	125.6
102.5°	151.6	152.1	152.7	153.0	152.9	152.8	152.7	152.6
105°	194.9	194.9	194.9	195.1	195.5	195.8	196.2	196.6
107.5°	241.9	242.5	243.0	243.2	243.0	242.8	242.6	242.3
110°	273.2	273.9	274.7	274.8	274.5	274.1	273.8	273.4





TEST NUMBER: P332197-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	305.4	306.3	306.7	306.6	306.6	306.6	306.5
115°	352.2	352.5	352.6	352.6	352.5	352.2	352.0	351.9
117.5°	400.4	400.3	400.3	400.0	399.5	399.0	398.4	397.9
120°	432.4	432.3	432.1	431.8	431.5	431.0	430.7	430.3
122.5°	464.9	464.4	464.0	463.4	462.9	462.4	461.9	461.4
125°	513.1	512.4	511.7	510.9	510.2	509.5	508.7	508.0
127.5°	560.8	559.8	558.7	557.7	556.9	556.1	555.2	554.4
130°	592.4	591.7	590.9	590.0	588.6	587.3	586.1	584.8
132.5°	623.2	622.3	621.4	620.5	619.5	618.5	617.5	616.5
135°	669.2	668.5	667.7	667.2	666.8	666.5	666.1	665.8
137.5°	714.3	713.5	712.7	712.0	711.3	710.6	709.9	709.2
140°	743.9	743.6	743.5	742.7	741.4	740.2	738.9	737.6
142.5°	771.6	771.4	771.3	770.6	769.6	768.7	767.7	766.7
145°	812.4	812.2	812.0	811.5	810.8	810.1	809.3	808.6
147.5°	850.9	850.9	850.9	850.4	849.3	848.2	847.1	846.0
150°	874.7	874.7	874.7	874.2	873.1	872.0	870.9	869.8
152.5°	896.4	896.7	897.1	896.7	895.8	894.8	893.8	892.9
155°	928.2	929.0	929.7	929.4	928.1	926.8	925.6	924.3
157.5°	955.5	956.3	957.1	957.0	955.9	955.0	953.9	952.8
160°	972.4	973.3	974.2	974.3	973.5	972.8	972.1	971.3
162.5°	988.2	989.1	990.1	989.9	988.8	987.6	986.4	985.2
165°	1008.3	1009.3	1010.5	1010.4	1009.1	1007.8	1006.5	1005.3
167.5°	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2
170°	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9
172.5°	1040.4	1041.5	1042.7	1042.6	1041.3	1040.0	1038.7	1037.5
175°	1047.9	1049.0	1050.1	1050.0	1048.7	1047.4	1046.2	1044.9
177.5°	1051.2	1052.1	1053.0	1053.0	1051.9	1050.9	1049.9	1048.9
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5

(END OF REPORT)