

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332208-930

Luminaire Tested: **S123DIW-S1000D1535U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332208-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D1535U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8365.7 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	34
2	87	80	74	68	79	73	67	63	60	56	53	48	45	43	37	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	24	21	19	16
7	56	44	37	31	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	1.5
10°-20°	343.3	4.1
20°-30°	507.0	6.1
30°-40°	592.3	7.1
40°-50°	595.5	7.1
50°-60°	523.1	6.3
60°-70°	389.7	4.7
70°-80°	222.0	2.7
80°-90°	68.3	0.8
90°-100°	59.6	0.7
100°-110°	284.3	3.4
110°-120°	682.8	8.2
120°-130°	869.5	10.4
130°-140°	929.1	11.1
140°-150°	868.8	10.4
150°-160°	700.8	8.4
160°-170°	452.3	5.4
170°-180°	155.9	1.9
0°-30°	971.9	11.6
0°-40°	1564.1	18.7
0°-60°	2682.6	32.1
0°-90°	3362.6	40.2
90°-120°	1026.8	12.3
90°-150°	3694.1	44.2
90°-180°	5003.0	59.8
0°-180°	8365.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	14	29	34	36	7
95°	74	28	38	46	46	92
105°	363	370	267	63	54	385
115°	681	689	700	711	717	672
125°	960	970	975	978	980	857
135°	1196	1203	1208	1211	1208	920
145°	1380	1388	1391	1393	1393	863
155°	1520	1518	1519	1524	1518	700
165°	1603	1599	1598	1607	1599	453
175°	1640	1635	1636	1643	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.3	23.2	23.2	23.2	23.2	23.3	23.9	24.4	24.9	25.4	25.4
90°	1.2	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3
92.5°	22.7	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9
95°	74.4	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7
97.5°	149.4	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4
100°	206.0	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4
102.5°	270.4	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5
105°	363.2	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0
107.5°	461.2	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1
110°	526.5	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8



TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	589.0	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3
115°	681.3	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3
117.5°	770.8	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6
120°	826.4	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2
122.5°	883.0	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1
125°	960.4	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7
127.5°	1035.5	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0
130°	1082.3	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0
132.5°	1127.2	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9
135°	1195.7	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7
137.5°	1254.2	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5
140°	1293.2	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3
142.5°	1329.3	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1
145°	1379.7	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2
147.5°	1427.3	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9
150°	1456.5	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1
152.5°	1482.9	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0
155°	1519.9	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0
157.5°	1548.7	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8
160°	1566.3	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5
162.5°	1582.8	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3
165°	1602.8	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1
167.5°	1618.4	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7
170°	1627.2	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5
172.5°	1633.0	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4
175°	1640.5	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6
177.5°	1642.5	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	25.4	25.4	25.4	25.5	25.6	25.8	25.8	25.9
90°	31.4	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	34.7	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	41.6	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	43.6	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	44.5	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	66.8	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	171.0	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	418.9	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	531.8	522.9	514.0	490.1	451.3	412.6	373.9	335.2





TEST NUMBER: P332208-930

CATALOG NUMBER: S123DIW-S1000D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.5	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	705.1	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	789.8	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	845.4	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	899.6	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.2	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1052.9	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1099.1	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1143.0	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1268.8	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1306.4	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.0	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1391.8	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1436.4	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1463.7	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1488.0	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1521.4	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1550.5	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1567.1	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1582.1	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1602.2	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1632.5	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1639.5	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1642.1	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)