

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331538-940

Luminaire Tested: **S122DIW-S675D970U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331538-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D970U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5610.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47					47			
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46					40				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39					34				
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34					30				
4	75	64	57	51	69	60	53	48	51	45	42	42	38	35	34	32	30					26				
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26					23				
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23					20				
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21					18				
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19					16				
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17					15				
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16					14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	2.0
10°-20°	327.9	5.8
20°-30°	475.9	8.5
30°-40°	502.2	9.0
40°-50°	444.7	7.9
50°-60°	354.9	6.3
60°-70°	241.2	4.3
70°-80°	123.7	2.2
80°-90°	34.1	0.6
90°-100°	67.8	1.2
100°-110°	210.6	3.8
110°-120°	360.0	6.4
120°-130°	473.5	8.4
130°-140°	531.4	9.5
140°-150°	521.1	9.3
150°-160°	437.0	7.8
160°-170°	289.9	5.2
170°-180°	101.3	1.8
0°-30°	916.7	16.3
0°-40°	1418.9	25.3
0°-60°	2218.4	39.5
0°-90°	2617.4	46.7
90°-120°	638.5	11.4
90°-150°	2164.4	38.6
90°-180°	2993.0	53.4
0°-180°	5610.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	31	1	31	1	31	15
95°	56	47	56	47	56	62
105°	200	194	200	194	200	211
115°	361	361	361	361	361	357
125°	527	526	527	526	527	470
135°	688	680	688	680	688	530
145°	835	826	835	826	835	521
155°	951	944	951	944	951	438
165°	1028	1027	1028	1027	1028	290
175°	1065	1068	1065	1068	1065	101
180°	1070	1070	1070	1070	1070	



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	15.6	15.6	15.9	15.5	15.4	15.9	15.9	15.6	16.1	16.5	16.0
90°	30.7	30.5	30.3	30.1	29.9	30.0	30.4	30.8	31.2	31.6	27.2
92.5°	29.2	29.2	29.2	29.2	29.1	29.1	29.0	28.9	28.8	28.7	27.6
95°	56.0	56.4	56.8	57.2	57.6	57.8	57.8	57.8	57.8	57.8	57.4
97.5°	97.0	97.0	97.1	97.1	97.2	97.2	97.2	97.2	97.2	97.2	96.4
100°	123.8	123.9	124.1	124.3	124.6	124.7	124.7	124.7	124.7	124.7	124.0
102.5°	154.1	154.3	154.4	154.7	154.9	154.9	154.7	154.6	154.4	154.3	153.5
105°	200.5	200.5	200.5	200.5	200.5	200.3	199.9	199.5	199.1	198.7	198.3
107.5°	244.2	245.1	246.0	247.0	247.9	248.3	248.2	248.0	247.8	247.6	247.6
110°	278.2	278.7	279.4	280.0	280.6	280.9	280.9	280.9	280.9	280.9	280.9



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.7	311.1	311.6	312.0	312.5	312.9	313.4	313.9	314.3	314.9	315.0
115°	361.2	361.9	362.5	363.1	363.6	364.1	364.3	364.4	364.7	364.9	365.2
117.5°	409.5	410.1	410.7	411.3	411.9	412.4	413.0	413.4	413.9	414.4	415.5
120°	443.4	444.1	444.7	445.2	445.9	446.2	446.2	446.2	446.2	446.2	447.8
122.5°	476.7	477.2	477.6	478.0	478.5	478.9	479.4	479.9	480.4	480.8	482.0
125°	527.4	527.6	527.9	528.1	528.2	528.7	529.2	529.9	530.5	531.1	531.6
127.5°	573.7	574.4	575.0	575.6	576.2	576.9	577.7	578.4	579.1	579.9	580.6
130°	606.9	607.7	608.5	609.3	610.1	610.7	611.2	611.5	612.0	612.3	612.8
132.5°	638.7	639.4	640.0	640.7	641.3	642.0	642.9	643.8	644.7	645.6	645.5
135°	688.2	688.8	689.4	690.0	690.6	691.0	691.3	691.4	691.6	691.8	691.4
137.5°	733.0	733.8	734.6	735.4	736.2	736.7	736.9	737.0	737.2	737.4	736.8
140°	764.1	764.9	765.7	766.5	767.3	767.7	767.7	767.7	767.7	767.7	766.7
142.5°	792.3	793.1	793.9	794.7	795.5	795.8	795.7	795.5	795.3	795.1	794.5
145°	834.6	835.4	836.2	837.0	837.8	838.0	837.9	837.7	837.4	837.2	836.1
147.5°	872.3	873.1	873.8	874.6	875.3	875.5	875.0	874.6	874.1	873.7	872.9
150°	896.9	897.4	898.0	898.7	899.3	899.3	898.7	898.0	897.4	896.9	896.1
152.5°	920.0	920.7	921.5	922.3	923.0	923.0	922.3	921.5	920.7	920.0	919.0
155°	951.0	951.6	952.3	952.9	953.4	953.2	952.3	951.3	950.2	949.2	948.6
157.5°	977.8	978.7	979.7	980.7	981.6	981.4	980.1	978.7	977.3	976.0	975.6
160°	994.4	995.2	996.0	996.8	997.6	997.4	996.2	995.0	993.8	992.6	992.4
162.5°	1008.9	1009.8	1010.8	1011.7	1012.7	1012.5	1011.1	1009.8	1008.4	1007.0	1006.8
165°	1027.8	1028.9	1029.8	1030.8	1031.8	1031.6	1030.2	1028.9	1027.4	1026.0	1026.0
167.5°	1043.4	1044.4	1045.4	1046.5	1047.5	1047.3	1046.0	1044.6	1043.1	1041.7	1041.8
170°	1051.3	1052.5	1053.7	1054.9	1056.1	1056.1	1054.6	1053.2	1051.8	1050.4	1050.6
172.5°	1057.8	1059.0	1060.2	1061.4	1062.7	1062.5	1061.1	1059.7	1058.3	1056.9	1057.1
175°	1064.9	1066.0	1067.3	1068.4	1069.7	1069.5	1068.2	1066.8	1065.3	1063.9	1064.3
177.5°	1068.1	1069.1	1070.1	1070.9	1071.9	1071.9	1070.9	1070.1	1069.1	1068.1	1068.4
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	15.5	14.6	13.7	13.7	12.2	11.7	9.8	8.2	8.3	8.5	8.2
90°	22.7	18.4	13.9	10.5	8.1	5.7	3.3	0.9	3.3	5.7	8.1
92.5°	26.7	25.6	24.5	23.2	21.4	19.6	17.8	16.1	17.8	19.6	21.4
95°	57.0	56.6	56.2	55.0	53.0	51.0	49.0	47.0	49.0	51.0	53.0
97.5°	95.7	94.9	94.2	92.8	91.1	89.3	87.6	85.8	87.6	89.3	91.1
100°	123.4	122.8	122.3	121.1	119.5	117.9	116.3	114.7	116.3	117.9	119.5
102.5°	152.8	151.9	151.2	150.2	148.9	147.6	146.3	145.1	146.3	147.6	148.9
105°	197.9	197.5	197.1	196.6	196.0	195.4	194.7	194.2	194.7	195.4	196.0
107.5°	247.6	247.6	247.6	247.2	246.3	245.4	244.6	243.7	244.6	245.4	246.3
110°	280.9	280.9	280.9	280.3	279.1	277.9	276.7	275.4	276.7	277.9	279.1



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	315.1	315.3	315.5	315.0	313.8	312.5	311.4	310.1	311.4	312.5	313.8
115°	365.7	366.0	366.5	366.0	364.9	363.6	362.5	361.2	362.5	363.6	364.9
117.5°	416.6	417.8	418.8	418.7	417.1	415.4	413.8	412.2	413.8	415.4	417.1
120°	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2	447.8	449.4	451.0
122.5°	483.1	484.2	485.4	484.9	483.0	481.1	479.2	477.2	479.2	481.1	483.0
125°	532.3	532.9	533.5	532.9	531.1	529.2	527.4	525.7	527.4	529.2	531.1
127.5°	581.3	582.0	582.7	581.9	579.7	577.4	575.1	572.8	575.1	577.4	579.7
130°	613.1	613.6	613.9	612.9	610.3	607.6	605.0	602.4	605.0	607.6	610.3
132.5°	645.4	645.3	645.2	644.2	642.0	639.9	637.8	635.6	637.8	639.9	642.0
135°	691.0	690.6	690.2	688.9	686.7	684.5	682.3	680.1	682.3	684.5	686.7
137.5°	736.3	735.8	735.3	734.1	732.3	730.5	728.7	726.8	728.7	730.5	732.3
140°	765.7	764.7	763.7	762.2	760.5	758.7	756.9	755.0	756.9	758.7	760.5
142.5°	793.8	793.1	792.5	791.2	789.3	787.6	785.8	784.0	785.8	787.6	789.3
145°	834.8	833.7	832.4	831.2	829.7	828.3	826.9	825.5	826.9	828.3	829.7
147.5°	872.1	871.3	870.5	869.2	867.5	865.9	864.2	862.6	864.2	865.9	867.5
150°	895.3	894.5	893.7	892.6	891.4	890.2	889.0	887.8	889.0	890.2	891.4
152.5°	918.0	917.1	916.1	915.1	913.8	912.7	911.4	910.3	911.4	912.7	913.8
155°	948.1	947.4	946.8	946.2	945.7	945.0	944.4	943.8	944.4	945.0	945.7
157.5°	975.3	974.9	974.6	974.1	973.7	973.3	972.9	972.5	972.9	973.3	973.7
160°	992.2	992.0	991.8	991.5	991.0	990.7	990.2	989.9	990.2	990.7	991.0
162.5°	1006.7	1006.5	1006.2	1006.1	1006.0	1005.9	1005.8	1005.8	1005.8	1005.9	1006.0
165°	1026.0	1026.0	1026.0	1026.1	1026.3	1026.5	1026.7	1026.9	1026.7	1026.5	1026.3
167.5°	1041.8	1041.9	1041.9	1042.2	1042.8	1043.4	1044.0	1044.6	1044.0	1043.4	1042.8
170°	1050.8	1051.0	1051.2	1051.6	1052.2	1052.8	1053.4	1054.0	1053.4	1052.8	1052.2
172.5°	1057.3	1057.5	1057.7	1058.1	1058.7	1059.3	1059.9	1060.5	1059.9	1059.3	1058.7
175°	1064.7	1065.1	1065.5	1066.0	1066.7	1067.3	1067.8	1068.4	1067.8	1067.3	1066.7
177.5°	1068.7	1069.1	1069.3	1069.8	1070.2	1070.8	1071.2	1071.7	1071.2	1070.8	1070.2
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	8.3	8.6	9.1	10.0	10.5	11.1	10.6	10.5	10.4	9.6	9.6
90°	10.5	13.9	18.4	22.7	27.2	31.6	31.2	30.8	30.4	30.0	29.9
92.5°	23.2	24.5	25.6	26.7	27.6	28.7	28.8	28.9	29.0	29.1	29.1
95°	55.0	56.2	56.6	57.0	57.4	57.8	57.8	57.8	57.8	57.8	57.6
97.5°	92.8	94.2	94.9	95.7	96.4	97.2	97.2	97.2	97.2	97.2	97.2
100°	121.1	122.3	122.8	123.4	124.0	124.7	124.7	124.7	124.7	124.7	124.6
102.5°	150.2	151.2	151.9	152.8	153.5	154.3	154.4	154.6	154.7	154.9	154.9
105°	196.6	197.1	197.5	197.9	198.3	198.7	199.1	199.5	199.9	200.3	200.5
107.5°	247.2	247.6	247.6	247.6	247.6	247.6	247.8	248.0	248.2	248.3	247.9
110°	280.3	280.9	280.9	280.9	280.9	280.9	280.9	280.9	280.9	280.9	280.6



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	315.0	315.5	315.3	315.1	315.0	314.9	314.3	313.9	313.4	312.9	312.5
115°	366.0	366.5	366.0	365.7	365.2	364.9	364.7	364.4	364.3	364.1	363.6
117.5°	418.7	418.8	417.8	416.6	415.5	414.4	413.9	413.4	413.0	412.4	411.9
120°	452.6	452.6	451.0	449.4	447.8	446.2	446.2	446.2	446.2	446.2	445.9
122.5°	484.9	485.4	484.2	483.1	482.0	480.8	480.4	479.9	479.4	478.9	478.5
125°	532.9	533.5	532.9	532.3	531.6	531.1	530.5	529.9	529.2	528.7	528.2
127.5°	581.9	582.7	582.0	581.3	580.6	579.9	579.1	578.4	577.7	576.9	576.2
130°	612.9	613.9	613.6	613.1	612.8	612.3	612.0	611.5	611.2	610.7	610.1
132.5°	644.2	645.2	645.3	645.4	645.5	645.6	644.7	643.8	642.9	642.0	641.3
135°	688.9	690.2	690.6	691.0	691.4	691.8	691.6	691.4	691.3	691.0	690.6
137.5°	734.1	735.3	735.8	736.3	736.8	737.4	737.2	737.0	736.9	736.7	736.2
140°	762.2	763.7	764.7	765.7	766.7	767.7	767.7	767.7	767.7	767.7	767.3
142.5°	791.2	792.5	793.1	793.8	794.5	795.1	795.3	795.5	795.7	795.8	795.5
145°	831.2	832.4	833.7	834.8	836.1	837.2	837.4	837.7	837.9	838.0	837.8
147.5°	869.2	870.5	871.3	872.1	872.9	873.7	874.1	874.6	875.0	875.5	875.3
150°	892.6	893.7	894.5	895.3	896.1	896.9	897.4	898.0	898.7	899.3	899.3
152.5°	915.1	916.1	917.1	918.0	919.0	920.0	920.7	921.5	922.3	923.0	923.0
155°	946.2	946.8	947.4	948.1	948.6	949.2	950.2	951.3	952.3	953.2	953.4
157.5°	974.1	974.6	974.9	975.3	975.6	976.0	977.3	978.7	980.1	981.4	981.6
160°	991.5	991.8	992.0	992.2	992.4	992.6	993.8	995.0	996.2	997.4	997.6
162.5°	1006.1	1006.2	1006.5	1006.7	1006.8	1007.0	1008.4	1009.8	1011.1	1012.5	1012.7
165°	1026.1	1026.0	1026.0	1026.0	1026.0	1026.0	1027.4	1028.9	1030.2	1031.6	1031.8
167.5°	1042.2	1041.9	1041.9	1041.8	1041.8	1041.7	1043.1	1044.6	1046.0	1047.3	1047.5
170°	1051.6	1051.2	1051.0	1050.8	1050.6	1050.4	1051.8	1053.2	1054.6	1056.1	1056.1
172.5°	1058.1	1057.7	1057.5	1057.3	1057.1	1056.9	1058.3	1059.7	1061.1	1062.5	1062.7
175°	1066.0	1065.5	1065.1	1064.7	1064.3	1063.9	1065.3	1066.8	1068.2	1069.5	1069.7
177.5°	1069.8	1069.3	1069.1	1068.7	1068.4	1068.1	1069.1	1070.1	1070.9	1071.9	1071.9
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	9.6	9.4	9.4	9.1	9.4	9.4	9.6	9.6	9.6	10.4	10.5
90°	30.1	30.3	30.5	30.7	30.5	30.3	30.1	29.9	30.0	30.4	30.8
92.5°	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.1	29.1	29.0	28.9
95°	57.2	56.8	56.4	56.0	56.4	56.8	57.2	57.6	57.8	57.8	57.8
97.5°	97.1	97.1	97.0	97.0	97.0	97.1	97.1	97.2	97.2	97.2	97.2
100°	124.3	124.1	123.9	123.8	123.9	124.1	124.3	124.6	124.7	124.7	124.7
102.5°	154.7	154.4	154.3	154.1	154.3	154.4	154.7	154.9	154.9	154.7	154.6
105°	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.3	199.9	199.5
107.5°	247.0	246.0	245.1	244.2	245.1	246.0	247.0	247.9	248.3	248.2	248.0
110°	280.0	279.4	278.7	278.2	278.7	279.4	280.0	280.6	280.9	280.9	280.9



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	312.0	311.6	311.1	310.7	311.1	311.6	312.0	312.5	312.9	313.4	313.9
115°	363.1	362.5	361.9	361.2	361.9	362.5	363.1	363.6	364.1	364.3	364.4
117.5°	411.3	410.7	410.1	409.5	410.1	410.7	411.3	411.9	412.4	413.0	413.4
120°	445.2	444.7	444.1	443.4	444.1	444.7	445.2	445.9	446.2	446.2	446.2
122.5°	478.0	477.6	477.2	476.7	477.2	477.6	478.0	478.5	478.9	479.4	479.9
125°	528.1	527.9	527.6	527.4	527.6	527.9	528.1	528.2	528.7	529.2	529.9
127.5°	575.6	575.0	574.4	573.7	574.4	575.0	575.6	576.2	576.9	577.7	578.4
130°	609.3	608.5	607.7	606.9	607.7	608.5	609.3	610.1	610.7	611.2	611.5
132.5°	640.7	640.0	639.4	638.7	639.4	640.0	640.7	641.3	642.0	642.9	643.8
135°	690.0	689.4	688.8	688.2	688.8	689.4	690.0	690.6	691.0	691.3	691.4
137.5°	735.4	734.6	733.8	733.0	733.8	734.6	735.4	736.2	736.7	736.9	737.0
140°	766.5	765.7	764.9	764.1	764.9	765.7	766.5	767.3	767.7	767.7	767.7
142.5°	794.7	793.9	793.1	792.3	793.1	793.9	794.7	795.5	795.8	795.7	795.5
145°	837.0	836.2	835.4	834.6	835.4	836.2	837.0	837.8	838.0	837.9	837.7
147.5°	874.6	873.8	873.1	872.3	873.1	873.8	874.6	875.3	875.5	875.0	874.6
150°	898.7	898.0	897.4	896.9	897.4	898.0	898.7	899.3	899.3	898.7	898.0
152.5°	922.3	921.5	920.7	920.0	920.7	921.5	922.3	923.0	923.0	922.3	921.5
155°	952.9	952.3	951.6	951.0	951.6	952.3	952.9	953.4	953.2	952.3	951.3
157.5°	980.7	979.7	978.7	977.8	978.7	979.7	980.7	981.6	981.4	980.1	978.7
160°	996.8	996.0	995.2	994.4	995.2	996.0	996.8	997.6	997.4	996.2	995.0
162.5°	1011.7	1010.8	1009.8	1008.9	1009.8	1010.8	1011.7	1012.7	1012.5	1011.1	1009.8
165°	1030.8	1029.8	1028.9	1027.8	1028.9	1029.8	1030.8	1031.8	1031.6	1030.2	1028.9
167.5°	1046.5	1045.4	1044.4	1043.4	1044.4	1045.4	1046.5	1047.5	1047.3	1046.0	1044.6
170°	1054.9	1053.7	1052.5	1051.3	1052.5	1053.7	1054.9	1056.1	1056.1	1054.6	1053.2
172.5°	1061.4	1060.2	1059.0	1057.8	1059.0	1060.2	1061.4	1062.7	1062.5	1061.1	1059.7
175°	1068.4	1067.3	1066.0	1064.9	1066.0	1067.3	1068.4	1069.7	1069.5	1068.2	1066.8
177.5°	1070.9	1070.1	1069.1	1068.1	1069.1	1070.1	1070.9	1071.9	1071.9	1070.9	1070.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	10.6	11.1	10.5	10.0	9.1	8.6	8.3	8.2	8.5	8.3	8.2
90°	31.2	31.6	27.2	22.7	18.4	13.9	10.5	8.1	5.7	3.3	0.9
92.5°	28.8	28.7	27.6	26.7	25.6	24.5	23.2	21.4	19.6	17.8	16.1
95°	57.8	57.8	57.4	57.0	56.6	56.2	55.0	53.0	51.0	49.0	47.0
97.5°	97.2	97.2	96.4	95.7	94.9	94.2	92.8	91.1	89.3	87.6	85.8
100°	124.7	124.7	124.0	123.4	122.8	122.3	121.1	119.5	117.9	116.3	114.7
102.5°	154.4	154.3	153.5	152.8	151.9	151.2	150.2	148.9	147.6	146.3	145.1
105°	199.1	198.7	198.3	197.9	197.5	197.1	196.6	196.0	195.4	194.7	194.2
107.5°	247.8	247.6	247.6	247.6	247.6	247.6	247.2	246.3	245.4	244.6	243.7
110°	280.9	280.9	280.9	280.9	280.9	280.9	280.3	279.1	277.9	276.7	275.4



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	314.3	314.9	315.0	315.1	315.3	315.5	315.0	313.8	312.5	311.4	310.1
115°	364.7	364.9	365.2	365.7	366.0	366.5	366.0	364.9	363.6	362.5	361.2
117.5°	413.9	414.4	415.5	416.6	417.8	418.8	418.7	417.1	415.4	413.8	412.2
120°	446.2	446.2	447.8	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2
122.5°	480.4	480.8	482.0	483.1	484.2	485.4	484.9	483.0	481.1	479.2	477.2
125°	530.5	531.1	531.6	532.3	532.9	533.5	532.9	531.1	529.2	527.4	525.7
127.5°	579.1	579.9	580.6	581.3	582.0	582.7	581.9	579.7	577.4	575.1	572.8
130°	612.0	612.3	612.8	613.1	613.6	613.9	612.9	610.3	607.6	605.0	602.4
132.5°	644.7	645.6	645.5	645.4	645.3	645.2	644.2	642.0	639.9	637.8	635.6
135°	691.6	691.8	691.4	691.0	690.6	690.2	688.9	686.7	684.5	682.3	680.1
137.5°	737.2	737.4	736.8	736.3	735.8	735.3	734.1	732.3	730.5	728.7	726.8
140°	767.7	767.7	766.7	765.7	764.7	763.7	762.2	760.5	758.7	756.9	755.0
142.5°	795.3	795.1	794.5	793.8	793.1	792.5	791.2	789.3	787.6	785.8	784.0
145°	837.4	837.2	836.1	834.8	833.7	832.4	831.2	829.7	828.3	826.9	825.5
147.5°	874.1	873.7	872.9	872.1	871.3	870.5	869.2	867.5	865.9	864.2	862.6
150°	897.4	896.9	896.1	895.3	894.5	893.7	892.6	891.4	890.2	889.0	887.8
152.5°	920.7	920.0	919.0	918.0	917.1	916.1	915.1	913.8	912.7	911.4	910.3
155°	950.2	949.2	948.6	948.1	947.4	946.8	946.2	945.7	945.0	944.4	943.8
157.5°	977.3	976.0	975.6	975.3	974.9	974.6	974.1	973.7	973.3	972.9	972.5
160°	993.8	992.6	992.4	992.2	992.0	991.8	991.5	991.0	990.7	990.2	989.9
162.5°	1008.4	1007.0	1006.8	1006.7	1006.5	1006.2	1006.1	1006.0	1005.9	1005.8	1005.8
165°	1027.4	1026.0	1026.0	1026.0	1026.0	1026.0	1026.1	1026.3	1026.5	1026.7	1026.9
167.5°	1043.1	1041.7	1041.8	1041.8	1041.9	1041.9	1042.2	1042.8	1043.4	1044.0	1044.6
170°	1051.8	1050.4	1050.6	1050.8	1051.0	1051.2	1051.6	1052.2	1052.8	1053.4	1054.0
172.5°	1058.3	1056.9	1057.1	1057.3	1057.5	1057.7	1058.1	1058.7	1059.3	1059.9	1060.5
175°	1065.3	1063.9	1064.3	1064.7	1065.1	1065.5	1066.0	1066.7	1067.3	1067.8	1068.4
177.5°	1069.1	1068.1	1068.4	1068.7	1069.1	1069.3	1069.8	1070.2	1070.8	1071.2	1071.7
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.8	11.7	12.2	13.7	13.7	14.6	15.5	16.0	16.5	16.1	15.6
90°	3.3	5.7	8.1	10.5	13.9	18.4	22.7	27.2	31.6	31.2	30.8
92.5°	17.8	19.6	21.4	23.2	24.5	25.6	26.7	27.6	28.7	28.8	28.9
95°	49.0	51.0	53.0	55.0	56.2	56.6	57.0	57.4	57.8	57.8	57.8
97.5°	87.6	89.3	91.1	92.8	94.2	94.9	95.7	96.4	97.2	97.2	97.2
100°	116.3	117.9	119.5	121.1	122.3	122.8	123.4	124.0	124.7	124.7	124.7
102.5°	146.3	147.6	148.9	150.2	151.2	151.9	152.8	153.5	154.3	154.4	154.6
105°	194.7	195.4	196.0	196.6	197.1	197.5	197.9	198.3	198.7	199.1	199.5
107.5°	244.6	245.4	246.3	247.2	247.6	247.6	247.6	247.6	247.6	247.8	248.0
110°	276.7	277.9	279.1	280.3	280.9	280.9	280.9	280.9	280.9	280.9	280.9



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.4	312.5	313.8	315.0	315.5	315.3	315.1	315.0	314.9	314.3	313.9
115°	362.5	363.6	364.9	366.0	366.5	366.0	365.7	365.2	364.9	364.7	364.4
117.5°	413.8	415.4	417.1	418.7	418.8	417.8	416.6	415.5	414.4	413.9	413.4
120°	447.8	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2	446.2	446.2
122.5°	479.2	481.1	483.0	484.9	485.4	484.2	483.1	482.0	480.8	480.4	479.9
125°	527.4	529.2	531.1	532.9	533.5	532.9	532.3	531.6	531.1	530.5	529.9
127.5°	575.1	577.4	579.7	581.9	582.7	582.0	581.3	580.6	579.9	579.1	578.4
130°	605.0	607.6	610.3	612.9	613.9	613.6	613.1	612.8	612.3	612.0	611.5
132.5°	637.8	639.9	642.0	644.2	645.2	645.3	645.4	645.5	645.6	644.7	643.8
135°	682.3	684.5	686.7	688.9	690.2	690.6	691.0	691.4	691.8	691.6	691.4
137.5°	728.7	730.5	732.3	734.1	735.3	735.8	736.3	736.8	737.4	737.2	737.0
140°	756.9	758.7	760.5	762.2	763.7	764.7	765.7	766.7	767.7	767.7	767.7
142.5°	785.8	787.6	789.3	791.2	792.5	793.1	793.8	794.5	795.1	795.3	795.5
145°	826.9	828.3	829.7	831.2	832.4	833.7	834.8	836.1	837.2	837.4	837.7
147.5°	864.2	865.9	867.5	869.2	870.5	871.3	872.1	872.9	873.7	874.1	874.6
150°	889.0	890.2	891.4	892.6	893.7	894.5	895.3	896.1	896.9	897.4	898.0
152.5°	911.4	912.7	913.8	915.1	916.1	917.1	918.0	919.0	920.0	920.7	921.5
155°	944.4	945.0	945.7	946.2	946.8	947.4	948.1	948.6	949.2	950.2	951.3
157.5°	972.9	973.3	973.7	974.1	974.6	974.9	975.3	975.6	976.0	977.3	978.7
160°	990.2	990.7	991.0	991.5	991.8	992.0	992.2	992.4	992.6	993.8	995.0
162.5°	1005.8	1005.9	1006.0	1006.1	1006.2	1006.5	1006.7	1006.8	1007.0	1008.4	1009.8
165°	1026.7	1026.5	1026.3	1026.1	1026.0	1026.0	1026.0	1026.0	1026.0	1027.4	1028.9
167.5°	1044.0	1043.4	1042.8	1042.2	1041.9	1041.9	1041.8	1041.8	1041.7	1043.1	1044.6
170°	1053.4	1052.8	1052.2	1051.6	1051.2	1051.0	1050.8	1050.6	1050.4	1051.8	1053.2
172.5°	1059.9	1059.3	1058.7	1058.1	1057.7	1057.5	1057.3	1057.1	1056.9	1058.3	1059.7
175°	1067.8	1067.3	1066.7	1066.0	1065.5	1065.1	1064.7	1064.3	1063.9	1065.3	1066.8
177.5°	1071.2	1070.8	1070.2	1069.8	1069.3	1069.1	1068.7	1068.4	1068.1	1069.1	1070.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	15.9	15.9	15.4	15.5	15.9	15.6	15.6
90°	30.4	30.0	29.9	30.1	30.3	30.5	30.7
92.5°	29.0	29.1	29.1	29.2	29.2	29.2	29.2
95°	57.8	57.8	57.6	57.2	56.8	56.4	56.0
97.5°	97.2	97.2	97.2	97.1	97.1	97.0	97.0
100°	124.7	124.7	124.6	124.3	124.1	123.9	123.8
102.5°	154.7	154.9	154.9	154.7	154.4	154.3	154.1
105°	199.9	200.3	200.5	200.5	200.5	200.5	200.5
107.5°	248.2	248.3	247.9	247.0	246.0	245.1	244.2
110°	280.9	280.9	280.6	280.0	279.4	278.7	278.2



TEST NUMBER: P331538-940

CATALOG NUMBER: S122DIW-S675D970U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	313.4	312.9	312.5	312.0	311.6	311.1	310.7
115°	364.3	364.1	363.6	363.1	362.5	361.9	361.2
117.5°	413.0	412.4	411.9	411.3	410.7	410.1	409.5
120°	446.2	446.2	445.9	445.2	444.7	444.1	443.4
122.5°	479.4	478.9	478.5	478.0	477.6	477.2	476.7
125°	529.2	528.7	528.2	528.1	527.9	527.6	527.4
127.5°	577.7	576.9	576.2	575.6	575.0	574.4	573.7
130°	611.2	610.7	610.1	609.3	608.5	607.7	606.9
132.5°	642.9	642.0	641.3	640.7	640.0	639.4	638.7
135°	691.3	691.0	690.6	690.0	689.4	688.8	688.2
137.5°	736.9	736.7	736.2	735.4	734.6	733.8	733.0
140°	767.7	767.7	767.3	766.5	765.7	764.9	764.1
142.5°	795.7	795.8	795.5	794.7	793.9	793.1	792.3
145°	837.9	838.0	837.8	837.0	836.2	835.4	834.6
147.5°	875.0	875.5	875.3	874.6	873.8	873.1	872.3
150°	898.7	899.3	899.3	898.7	898.0	897.4	896.9
152.5°	922.3	923.0	923.0	922.3	921.5	920.7	920.0
155°	952.3	953.2	953.4	952.9	952.3	951.6	951.0
157.5°	980.1	981.4	981.6	980.7	979.7	978.7	977.8
160°	996.2	997.4	997.6	996.8	996.0	995.2	994.4
162.5°	1011.1	1012.5	1012.7	1011.7	1010.8	1009.8	1008.9
165°	1030.2	1031.6	1031.8	1030.8	1029.8	1028.9	1027.8
167.5°	1046.0	1047.3	1047.5	1046.5	1045.4	1044.4	1043.4
170°	1054.6	1056.1	1056.1	1054.9	1053.7	1052.5	1051.3
172.5°	1061.1	1062.5	1062.7	1061.4	1060.2	1059.0	1057.8
175°	1068.2	1069.5	1069.7	1068.4	1067.3	1066.0	1064.9
177.5°	1070.9	1071.9	1071.9	1070.9	1070.1	1069.1	1068.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2

(END OF REPORT)