

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332184-930

Luminaire Tested: **S123DIW-S1000D460U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332184-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D460U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4863.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	97	93	90	96	92	89	85	82	80	77	73	71	69	65	63	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	55	52	49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	46	40	36	41	37	33	31
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.6	2.5
10°-20°	343.3	7.1
20°-30°	507.0	10.4
30°-40°	592.3	12.2
40°-50°	595.5	12.2
50°-60°	523.1	10.8
60°-70°	389.7	8.0
70°-80°	222.0	4.6
80°-90°	65.1	1.3
90°-100°	17.9	0.4
100°-110°	85.4	1.8
110°-120°	205.2	4.2
120°-130°	261.3	5.4
130°-140°	279.2	5.7
140°-150°	261.1	5.4
150°-160°	210.6	4.3
160°-170°	135.9	2.8
170°-180°	46.8	1.0
0°-30°	971.9	20.0
0°-40°	1564.1	32.2
0°-60°	2682.6	55.2
0°-90°	3359.4	69.1
90°-120°	308.6	6.3
90°-150°	1110.2	22.8
90°-180°	1504.0	30.9
0°-180°	4863.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	0	4	9	10	11	4
95°	22	8	11	14	14	28
105°	109	111	80	19	16	116
115°	205	207	210	214	215	202
125°	289	291	293	294	294	258
135°	359	362	363	364	363	277
145°	415	417	418	419	419	259
155°	457	456	456	458	456	210
165°	482	481	480	483	481	136
175°	493	491	492	494	491	47
180°	493	493	493	493	493	



TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	22.7	22.3	21.9	21.4	21.2	21.3	21.3	21.3	21.3	21.1
90°	0.3	1.1	2.0	2.8	3.6	4.6	5.6	6.7	7.7	8.8	9.1
92.5°	6.8	6.6	6.4	6.1	5.9	6.2	7.0	7.7	8.6	9.4	9.9
95°	22.3	19.0	15.7	12.3	9.0	7.7	8.6	9.5	10.4	11.3	11.9
97.5°	44.9	43.4	41.9	40.4	38.9	35.2	29.4	23.5	17.7	11.8	12.5
100°	61.9	63.5	65.1	66.8	68.4	62.9	50.2	37.5	24.8	12.1	12.7
102.5°	81.2	82.4	83.6	84.8	85.9	79.6	65.7	51.9	38.0	24.1	22.1
105°	109.2	110.1	111.0	111.9	112.8	109.5	102.2	94.9	87.6	80.2	65.8
107.5°	138.6	139.3	140.1	140.7	141.5	142.4	143.6	144.7	145.9	147.0	136.5
110°	158.2	158.9	159.6	160.2	160.9	161.6	162.5	163.4	164.3	165.2	162.5



TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.0	177.6	178.1	178.7	179.4	180.1	181.0	181.9	182.8	183.7	183.7
115°	204.7	205.2	205.7	206.2	206.7	207.3	208.1	208.8	209.5	210.3	211.1
117.5°	231.6	232.3	232.8	233.4	234.1	234.6	234.9	235.3	235.7	236.0	236.7
120°	248.3	249.1	249.8	250.5	251.3	251.8	252.0	252.3	252.5	252.7	253.4
122.5°	265.4	266.0	266.5	267.2	267.7	268.2	268.6	268.8	269.1	269.5	269.9
125°	288.6	289.3	289.9	290.6	291.2	291.7	292.0	292.4	292.7	293.0	293.2
127.5°	311.2	311.9	312.5	313.2	313.8	314.3	314.7	315.1	315.5	315.9	316.2
130°	325.3	326.0	326.6	327.3	327.9	328.4	328.7	329.1	329.4	329.6	330.0
132.5°	338.8	339.4	340.1	340.7	341.4	341.8	342.1	342.3	342.6	342.8	343.2
135°	359.3	359.8	360.3	360.8	361.3	361.7	362.0	362.3	362.6	363.0	363.2
137.5°	376.9	377.6	378.1	378.8	379.4	379.8	380.0	380.2	380.3	380.5	380.9
140°	388.7	389.1	389.6	390.1	390.6	390.9	391.2	391.4	391.7	391.9	392.2
142.5°	399.5	400.0	400.5	401.0	401.5	401.8	402.0	402.3	402.5	402.8	403.0
145°	414.7	415.2	415.8	416.4	416.9	417.3	417.4	417.6	417.8	417.9	418.1
147.5°	428.9	429.3	429.7	430.1	430.4	430.7	430.9	431.0	431.2	431.4	431.5
150°	437.7	438.0	438.2	438.5	438.7	438.9	439.0	439.2	439.4	439.5	439.7
152.5°	445.6	445.7	445.9	446.0	446.1	446.2	446.3	446.4	446.5	446.6	446.9
155°	456.7	456.6	456.4	456.3	456.2	456.1	456.2	456.2	456.3	456.4	456.8
157.5°	465.5	465.4	465.4	465.4	465.4	465.3	465.2	465.1	465.0	465.0	465.5
160°	470.7	470.6	470.5	470.4	470.3	470.3	470.2	470.1	470.0	469.9	470.4
162.5°	475.6	475.5	475.2	475.1	474.8	474.7	474.6	474.5	474.4	474.3	474.9
165°	481.7	481.4	481.2	480.9	480.7	480.5	480.5	480.4	480.3	480.2	480.9
167.5°	486.4	486.1	485.8	485.4	485.1	484.9	484.9	484.9	484.9	484.9	485.6
170°	489.0	488.7	488.4	488.0	487.7	487.5	487.5	487.5	487.5	487.5	488.2
172.5°	490.7	490.4	490.0	489.6	489.2	489.0	489.1	489.2	489.3	489.3	489.9
175°	493.0	492.6	492.2	491.8	491.4	491.2	491.3	491.4	491.5	491.5	492.1
177.5°	493.6	493.3	492.9	492.6	492.3	492.2	492.3	492.3	492.4	492.4	492.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0



TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	21.0	20.9	20.8	20.7	20.7	20.8	20.8	20.9
90°	9.5	9.8	10.1	10.4	10.5	10.7	10.8	11.0
92.5°	10.4	10.9	11.5	11.7	11.9	12.0	12.1	12.1
95°	12.5	13.0	13.6	13.9	13.9	13.9	13.9	13.9
97.5°	13.1	13.8	14.4	14.8	14.8	14.9	15.0	15.1
100°	13.4	14.0	14.7	15.1	15.2	15.2	15.3	15.4
102.5°	20.1	18.0	16.1	15.1	15.2	15.4	15.5	15.7
105°	51.4	37.0	22.6	15.5	15.7	15.8	16.0	16.1
107.5°	125.9	115.4	104.8	94.1	83.2	72.3	61.5	50.6
110°	159.8	157.1	154.4	147.3	135.7	124.0	112.3	100.8



TEST NUMBER: P332184-930

CATALOG NUMBER: S123DIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	183.8	183.8	183.8	182.6	180.2	177.7	175.3	172.8
115°	211.9	212.7	213.5	214.1	214.4	214.7	215.1	215.4
117.5°	237.3	238.0	238.6	239.0	239.0	239.1	239.2	239.3
120°	254.0	254.7	255.4	255.7	255.7	255.7	255.7	255.7
122.5°	270.4	270.8	271.3	271.5	271.6	271.7	271.7	271.8
125°	293.3	293.5	293.7	293.8	294.0	294.2	294.3	294.5
127.5°	316.4	316.7	316.9	317.0	316.8	316.7	316.5	316.3
130°	330.3	330.6	330.9	331.0	330.8	330.7	330.5	330.4
132.5°	343.5	343.8	344.1	344.2	344.0	343.7	343.5	343.3
135°	363.5	363.7	363.9	363.9	363.7	363.5	363.2	363.0
137.5°	381.3	381.6	382.0	382.2	382.0	381.9	381.7	381.6
140°	392.6	392.9	393.2	393.3	393.1	393.0	392.8	392.6
142.5°	403.3	403.6	403.8	403.8	403.6	403.4	403.2	402.9
145°	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7
147.5°	431.7	431.9	432.0	431.9	431.5	431.1	430.8	430.4
150°	439.9	440.0	440.2	440.2	439.9	439.7	439.4	439.2
152.5°	447.2	447.4	447.8	447.7	447.4	446.9	446.6	446.2
155°	457.2	457.6	458.0	458.0	457.5	457.0	456.5	456.1
157.5°	465.9	466.4	466.9	466.8	466.2	465.6	465.0	464.3
160°	470.9	471.4	471.9	471.9	471.3	470.8	470.2	469.6
162.5°	475.5	476.1	476.5	476.6	476.1	475.6	475.1	474.6
165°	481.5	482.2	482.8	482.8	482.2	481.8	481.2	480.6
167.5°	486.2	486.8	487.5	487.5	486.8	486.2	485.6	484.9
170°	488.9	489.5	490.2	490.2	489.5	488.9	488.2	487.5
172.5°	490.6	491.2	491.9	491.9	491.1	490.4	489.8	489.0
175°	492.7	493.3	493.8	493.8	493.2	492.5	491.9	491.2
177.5°	493.5	494.0	494.6	494.5	493.8	493.2	492.5	491.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0

(END OF REPORT)