

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331583-940

Luminaire Tested: **S122DIW-S865D1440U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331583-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D1440U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8271.4 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77		60	60	60		45	45	45	38
1	95	91	87	84	86	83	79	76	67	65	63		53	51	50		40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52		46	44	42		35	33	32	27
3	79	70	62	57	71	63	57	52	52	47	44		41	38	35		31	29	27	23
4	72	62	54	48	65	56	49	44	46	41	37		36	33	30		28	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32		33	29	26		25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28		30	26	23		23	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24		27	23	20		21	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22		25	21	18		19	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19		23	19	16		17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17		21	17	14		16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.7	1.4
10°-20°	325.6	3.9
20°-30°	478.6	5.8
30°-40°	555.9	6.7
40°-50°	555.3	6.7
50°-60°	484.3	5.9
60°-70°	358.1	4.3
70°-80°	202.8	2.5
80°-90°	58.9	0.7
90°-100°	58.5	0.7
100°-110°	214.4	2.6
110°-120°	573.1	6.9
120°-130°	946.0	11.4
130°-140°	1006.1	12.2
140°-150°	935.1	11.3
150°-160°	751.8	9.1
160°-170°	484.5	5.9
170°-180°	166.8	2.0
0°-30°	919.9	11.1
0°-40°	1475.8	17.8
0°-60°	2515.4	30.4
0°-90°	3135.1	37.9
90°-120°	846.0	10.2
90°-150°	3733.2	45.1
90°-180°	5136.0	62.1
0°-180°	8271.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	1	15	25	32	34	6
95°	82	43	50	55	55	101
105°	386	402	77	91	96	412
115°	729	751	782	223	104	718
125°	1031	1048	1072	1080	1084	919
135°	1276	1296	1308	1319	1318	985
145°	1480	1480	1500	1508	1503	925
155°	1630	1620	1633	1640	1631	751
165°	1717	1710	1713	1721	1713	485
175°	1756	1748	1750	1758	1746	167
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.3	17.5	17.7	17.9	18.1	18.2	18.2	18.3	18.3	18.4	18.0
90°	1.2	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8
92.5°	25.6	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1
95°	82.4	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8
97.5°	163.6	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3
100°	224.4	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5
102.5°	291.4	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2
105°	385.6	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4
107.5°	492.8	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1
110°	561.9	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8



TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.8	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0
115°	729.2	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0
117.5°	820.8	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2
120°	887.8	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0
122.5°	944.6	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5
125°	1031.1	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6
127.5°	1109.5	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6
130°	1159.1	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5
132.5°	1209.9	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8
135°	1275.9	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4
137.5°	1342.6	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4
140°	1386.2	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8
142.5°	1422.7	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1
145°	1480.1	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3
147.5°	1530.0	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9
150°	1562.5	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6
152.5°	1589.8	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9
155°	1629.7	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1
157.5°	1660.9	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8
160°	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8
162.5°	1695.3	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3
165°	1717.2	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4
167.5°	1733.4	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3
170°	1742.6	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5
172.5°	1748.6	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5
175°	1756.5	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1
177.5°	1757.7	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	17.7	17.3	16.9	16.7	16.6	16.5	16.4	16.3
90°	28.2	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	30.9	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	52.3	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	68.5	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	76.8	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	80.2	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	83.6	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	102.0	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	165.6	137.4	109.2	95.7	96.8	97.9	99.1	100.2





TEST NUMBER: P331583-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	354.2	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	521.6	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	803.6	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	936.4	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	993.5	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1075.6	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1151.5	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1199.6	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1246.3	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1313.1	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1375.2	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1415.3	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1452.4	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1504.2	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1549.4	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1577.3	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1602.6	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1636.8	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1665.7	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1682.5	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1698.2	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1733.3	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1741.4	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1747.5	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1754.1	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1754.8	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)