

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331584-940

Luminaire Tested: **S122DIW-S865D1440U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331584-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7591.5 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79		63	63	63		48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64		55	54	52		43	42	41	35
2	87	80	74	69	79	73	68	63	60	56	53		48	46	43		37	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45		43	40	37		33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38		38	34	31		30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33		34	30	27		27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29		31	27	24		24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25		28	24	21		22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22		26	22	19		20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18		22	18	15		17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	1.5
10°-20°	325.6	4.3
20°-30°	478.6	6.3
30°-40°	555.9	7.3
40°-50°	555.3	7.3
50°-60°	484.3	6.4
60°-70°	358.1	4.7
70°-80°	202.8	2.7
80°-90°	60.9	0.8
90°-100°	100.9	1.3
100°-110°	313.5	4.1
110°-120°	535.9	7.1
120°-130°	704.7	9.3
130°-140°	791.0	10.4
140°-150°	775.6	10.2
150°-160°	650.5	8.6
160°-170°	431.5	5.7
170°-180°	150.8	2.0
0°-30°	919.9	12.1
0°-40°	1475.8	19.4
0°-60°	2515.4	33.1
0°-90°	3137.1	41.3
90°-120°	950.3	12.5
90°-150°	3221.6	42.4
90°-180°	4454.0	58.7
0°-180°	7591.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	1	18	47	45	46	6
95°	70	83	86	86	83	80
105°	289	293	296	298	298	305
115°	538	545	543	542	538	532
125°	782	794	790	787	785	699
135°	1012	1026	1030	1028	1024	782
145°	1229	1238	1246	1247	1242	767
155°	1405	1409	1413	1419	1416	646
165°	1528	1527	1527	1536	1530	431
175°	1590	1586	1584	1592	1585	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.3	17.6	17.9	18.2	18.5	19.1	20.0	20.9	21.8	22.6	21.9
90°	1.3	4.9	8.5	12.1	15.7	20.8	27.4	33.9	40.5	47.1	46.5
92.5°	23.9	26.6	29.2	31.8	34.4	36.6	38.1	39.7	41.2	42.7	42.9
95°	69.9	72.9	75.9	78.8	81.9	83.6	84.3	84.8	85.4	86.1	86.1
97.5°	127.7	130.4	133.0	135.6	138.2	140.1	141.2	142.4	143.5	144.6	144.6
100°	170.8	173.1	175.5	177.9	180.3	181.9	182.8	183.7	184.6	185.5	185.5
102.5°	215.9	217.8	219.7	221.6	223.6	225.1	226.2	227.3	228.5	229.6	229.9
105°	289.0	289.9	290.8	291.7	292.6	293.4	294.0	294.5	295.2	295.8	296.3
107.5°	362.7	364.0	365.3	366.7	367.9	368.6	368.6	368.6	368.6	368.6	368.8
110°	410.0	411.8	413.6	415.4	417.1	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.6	463.4	465.2	467.0	468.8	469.6	469.3	469.1	468.9	468.6	467.9
115°	537.7	539.5	541.3	543.1	544.9	545.5	544.9	544.3	543.7	543.1	542.8
117.5°	613.6	615.9	618.3	620.7	623.1	623.5	621.8	620.1	618.4	616.8	616.1
120°	664.1	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	664.1
122.5°	710.3	713.2	716.0	718.9	721.8	722.4	720.8	719.1	717.4	715.7	715.0
125°	782.4	785.1	787.7	790.4	793.2	794.1	793.2	792.3	791.4	790.4	789.5
127.5°	852.6	856.0	859.3	862.8	866.2	867.4	866.3	865.2	864.2	863.1	861.9
130°	896.6	900.5	904.5	908.3	912.2	913.8	913.2	912.7	912.0	911.4	910.9
132.5°	946.1	949.3	952.4	955.6	958.8	960.5	960.6	960.6	960.8	960.9	959.6
135°	1012.3	1015.6	1018.9	1022.1	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5
137.5°	1081.9	1084.6	1087.3	1089.9	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3
140°	1123.8	1126.5	1129.3	1131.9	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6
142.5°	1166.9	1169.6	1172.2	1174.9	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7
145°	1228.7	1230.8	1232.9	1234.9	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4
147.5°	1283.8	1286.3	1288.8	1291.4	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2
150°	1321.4	1323.2	1325.1	1326.9	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8
152.5°	1354.8	1356.6	1358.3	1360.1	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5
155°	1404.8	1405.7	1406.6	1407.5	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3
157.5°	1447.5	1448.1	1448.8	1449.4	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6
160°	1473.4	1474.0	1474.5	1475.2	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2
162.5°	1497.0	1497.2	1497.3	1497.4	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9
165°	1528.5	1528.2	1527.9	1527.6	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2
167.5°	1554.8	1553.9	1553.0	1552.1	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6
170°	1568.8	1567.9	1567.0	1566.1	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5
172.5°	1578.5	1577.6	1576.7	1575.8	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2
175°	1590.3	1589.4	1588.5	1587.6	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7
177.5°	1595.2	1594.5	1593.8	1593.0	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	21.1	20.4	19.6	19.2	19.1	18.9	18.7	18.6
90°	45.8	45.3	44.7	44.5	44.9	45.1	45.4	45.7
92.5°	43.0	43.1	43.2	43.3	43.3	43.4	43.5	43.5
95°	86.1	86.1	86.1	85.7	85.2	84.5	83.9	83.4
97.5°	144.6	144.6	144.6	144.6	144.5	144.5	144.5	144.4
100°	185.5	185.5	185.5	185.4	185.0	184.8	184.5	184.1
102.5°	230.1	230.3	230.6	230.5	230.2	230.0	229.6	229.3
105°	296.9	297.6	298.1	298.5	298.5	298.5	298.5	298.5
107.5°	369.1	369.3	369.5	369.0	367.7	366.2	364.9	363.5
110°	418.1	418.1	418.1	417.6	416.7	415.8	414.9	414.0



TEST NUMBER: P331584-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	467.2	466.5	465.7	465.0	464.4	463.8	463.1	462.4
115°	542.5	542.2	541.9	541.3	540.4	539.5	538.6	537.7
117.5°	615.4	614.7	613.9	613.1	612.2	611.3	610.4	609.5
120°	664.1	664.1	664.1	663.6	662.7	661.8	660.9	660.0
122.5°	714.3	713.5	712.8	712.1	711.5	710.9	710.2	709.5
125°	788.6	787.7	786.8	786.3	786.0	785.7	785.4	785.1
127.5°	860.9	859.8	858.7	857.7	856.8	855.8	854.9	853.9
130°	910.3	909.6	909.0	908.1	907.0	905.8	904.6	903.4
132.5°	958.3	957.0	955.6	954.5	953.6	952.6	951.6	950.7
135°	1029.1	1028.9	1028.6	1028.0	1027.1	1026.2	1025.3	1024.4
137.5°	1097.0	1096.8	1096.5	1095.8	1094.7	1093.4	1092.3	1091.0
140°	1142.6	1142.6	1142.6	1142.1	1140.9	1139.7	1138.4	1137.3
142.5°	1184.0	1184.3	1184.5	1184.0	1182.9	1181.6	1180.4	1179.2
145°	1246.8	1247.1	1247.3	1246.9	1245.7	1244.6	1243.3	1242.2
147.5°	1301.8	1302.4	1303.1	1302.9	1301.7	1300.6	1299.5	1298.3
150°	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9
152.5°	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3
155°	1415.9	1417.4	1418.8	1419.2	1418.3	1417.4	1416.5	1415.6
157.5°	1456.7	1458.7	1460.8	1461.1	1459.6	1458.2	1456.8	1455.4
160°	1481.0	1482.7	1484.5	1484.9	1483.6	1482.5	1481.3	1480.1
162.5°	1503.0	1505.0	1507.0	1507.3	1505.9	1504.5	1503.1	1501.6
165°	1531.3	1533.4	1535.5	1535.8	1534.3	1532.9	1531.3	1529.8
167.5°	1554.7	1556.8	1558.9	1559.2	1557.6	1556.0	1554.5	1552.9
170°	1567.6	1569.7	1571.8	1571.9	1570.1	1568.3	1566.6	1564.8
172.5°	1577.3	1579.4	1581.4	1581.6	1579.8	1578.1	1576.3	1574.5
175°	1587.8	1589.8	1592.0	1592.1	1590.3	1588.5	1586.7	1584.9
177.5°	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0

(END OF REPORT)