

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332232-930

Luminaire Tested: **S123DIW-S1165D1320U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332232-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1320U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8185.4 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	47	47	47		
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40	40	40	40	40	40	40		
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33	33	33	33	33	33	33		
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28	28	28	28	28	28	28		
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24	24	24	24		
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21	21	21	21	21	21	21		
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18	18	18	18	18	18	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16	16	16	16	16	16	16		
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15	15	15	15	15	15	15		
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13	13	13	13		
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12	12	12	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	1.7
10°-20°	396.4	4.8
20°-30°	585.6	7.2
30°-40°	684.0	8.4
40°-50°	687.7	8.4
50°-60°	604.1	7.4
60°-70°	450.0	5.5
70°-80°	256.4	3.1
80°-90°	77.6	0.9
90°-100°	51.3	0.6
100°-110°	244.5	3.0
110°-120°	587.3	7.2
120°-130°	747.9	9.1
130°-140°	799.1	9.8
140°-150°	747.2	9.1
150°-160°	602.7	7.4
160°-170°	389.0	4.8
170°-180°	134.1	1.6
0°-30°	1122.4	13.7
0°-40°	1806.5	22.1
0°-60°	3098.3	37.9
0°-90°	3882.3	47.4
90°-120°	883.1	10.8
90°-150°	3177.3	38.8
90°-180°	4303.0	52.6
0°-180°	8185.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	12	25	29	32	7
95°	64	24	32	40	40	79
105°	312	318	230	54	46	331
115°	586	592	602	612	616	578
125°	826	834	839	841	843	737
135°	1028	1035	1039	1042	1039	791
145°	1187	1194	1196	1198	1198	743
155°	1307	1305	1306	1311	1305	602
165°	1379	1376	1374	1382	1375	389
175°	1411	1406	1407	1413	1406	134
180°	1411	1411	1411	1411	1411	



TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.9	26.7	26.4	26.3	26.0	26.1	26.4	26.8	27.2	27.6	27.6
90°	1.1	3.3	5.7	8.1	10.4	13.0	16.1	19.1	22.1	25.2	26.1
92.5°	19.5	18.8	18.2	17.5	16.9	17.7	20.0	22.3	24.5	26.8	28.3
95°	63.9	54.4	44.8	35.3	25.8	22.3	24.8	27.4	29.9	32.5	34.2
97.5°	128.5	124.3	119.9	115.7	111.4	100.9	84.1	67.3	50.5	33.8	35.6
100°	177.2	181.8	186.5	191.1	195.8	179.9	143.7	107.3	70.9	34.6	36.4
102.5°	232.5	235.9	239.2	242.6	246.0	227.8	188.1	148.4	108.7	69.0	63.2
105°	312.4	315.0	317.6	320.1	322.6	313.5	292.4	271.5	250.5	229.6	188.3
107.5°	396.7	398.8	400.8	402.8	404.9	407.6	410.9	414.2	417.5	420.8	390.5
110°	452.9	454.8	456.6	458.4	460.3	462.5	465.1	467.7	470.3	472.8	465.1



TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.5	508.3	509.9	511.6	513.2	515.4	518.0	520.5	523.1	525.6	525.8
115°	586.0	587.4	588.8	590.2	591.6	593.4	595.4	597.5	599.7	601.8	604.1
117.5°	663.0	664.7	666.4	668.1	669.8	671.2	672.3	673.4	674.5	675.6	677.4
120°	710.8	712.9	714.9	717.1	719.2	720.6	721.2	721.9	722.7	723.3	725.2
122.5°	759.5	761.2	762.9	764.6	766.3	767.6	768.5	769.4	770.3	771.2	772.5
125°	826.1	827.9	829.8	831.7	833.6	834.9	835.8	836.8	837.7	838.7	839.1
127.5°	890.6	892.5	894.4	896.3	898.1	899.6	900.7	901.9	902.9	904.1	904.8
130°	930.9	932.8	934.7	936.5	938.4	939.8	940.7	941.7	942.6	943.5	944.4
132.5°	969.5	971.3	973.2	975.1	977.0	978.3	979.0	979.7	980.5	981.2	982.2
135°	1028.4	1029.8	1031.2	1032.6	1034.0	1035.2	1036.1	1037.1	1038.0	1038.9	1039.6
137.5°	1078.7	1080.5	1082.3	1084.0	1085.8	1087.0	1087.4	1088.0	1088.5	1089.0	1090.1
140°	1112.3	1113.7	1115.1	1116.5	1117.9	1118.9	1119.7	1120.3	1121.0	1121.7	1122.7
142.5°	1143.3	1144.7	1146.1	1147.5	1148.9	1150.0	1150.6	1151.4	1152.0	1152.8	1153.5
145°	1186.7	1188.4	1190.0	1191.6	1193.3	1194.3	1194.7	1195.2	1195.7	1196.1	1196.6
147.5°	1227.6	1228.7	1229.7	1230.8	1231.9	1232.7	1233.1	1233.5	1234.0	1234.5	1235.0
150°	1252.8	1253.4	1254.2	1254.8	1255.6	1256.1	1256.6	1257.0	1257.5	1258.0	1258.5
152.5°	1275.4	1275.7	1276.0	1276.4	1276.7	1277.0	1277.3	1277.6	1277.8	1278.1	1279.0
155°	1307.3	1306.8	1306.4	1305.9	1305.4	1305.3	1305.5	1305.8	1306.0	1306.2	1307.4
157.5°	1332.0	1332.0	1332.0	1331.9	1331.8	1331.7	1331.5	1331.2	1331.0	1330.7	1332.1
160°	1347.1	1346.9	1346.6	1346.4	1346.1	1346.0	1345.7	1345.5	1345.2	1345.0	1346.4
162.5°	1361.4	1360.7	1360.2	1359.5	1358.9	1358.5	1358.3	1358.0	1357.8	1357.6	1359.2
165°	1378.6	1377.9	1377.1	1376.5	1375.7	1375.3	1375.1	1374.8	1374.6	1374.4	1376.2
167.5°	1392.0	1391.1	1390.1	1389.2	1388.2	1387.8	1387.8	1387.8	1387.8	1387.8	1389.7
170°	1399.5	1398.6	1397.7	1396.8	1395.8	1395.3	1395.3	1395.3	1395.3	1395.3	1397.2
172.5°	1404.6	1403.5	1402.3	1401.2	1400.1	1399.6	1399.8	1400.0	1400.2	1400.4	1402.2
175°	1411.0	1409.9	1408.8	1407.5	1406.4	1405.9	1406.1	1406.4	1406.6	1406.9	1408.5
177.5°	1412.8	1411.8	1410.9	1410.0	1409.0	1408.7	1408.8	1409.0	1409.2	1409.4	1410.9
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	27.5	27.5	27.4	27.5	27.6	27.6	27.7	27.8
90°	27.0	28.0	28.9	29.6	30.1	30.5	31.0	31.5
92.5°	29.8	31.3	32.8	33.7	34.0	34.2	34.5	34.8
95°	35.8	37.4	39.1	39.9	39.9	39.9	39.9	39.9
97.5°	37.5	39.4	41.2	42.2	42.5	42.7	43.0	43.2
100°	38.3	40.2	42.1	43.1	43.3	43.5	43.8	44.0
102.5°	57.4	51.6	45.9	43.2	43.6	44.0	44.4	44.8
105°	147.1	105.9	64.7	44.3	44.8	45.2	45.7	46.1
107.5°	360.4	330.1	299.9	269.2	238.1	207.0	175.9	144.9
110°	457.4	449.7	442.1	421.5	388.2	354.9	321.6	288.3



TEST NUMBER: P332232-930

CATALOG NUMBER: S123DIW-S1165D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.9	526.0	526.2	522.8	515.7	508.7	501.7	494.6
115°	606.4	608.7	611.1	612.7	613.6	614.6	615.5	616.4
117.5°	679.3	681.1	683.0	684.0	684.2	684.4	684.6	684.8
120°	727.1	729.0	730.8	731.7	731.7	731.7	731.7	731.7
122.5°	773.8	775.1	776.4	777.1	777.3	777.5	777.7	777.9
125°	839.6	840.1	840.5	841.0	841.5	842.0	842.4	842.9
127.5°	905.6	906.3	907.1	907.2	906.8	906.3	905.8	905.3
130°	945.3	946.3	947.2	947.5	947.0	946.6	946.1	945.6
132.5°	983.1	984.1	985.0	985.1	984.5	983.8	983.2	982.5
135°	1040.3	1041.0	1041.7	1041.7	1041.0	1040.3	1039.6	1038.9
137.5°	1091.3	1092.3	1093.5	1093.8	1093.3	1092.9	1092.4	1091.9
140°	1123.6	1124.5	1125.4	1125.7	1125.2	1124.7	1124.3	1123.8
142.5°	1154.2	1155.0	1155.8	1155.8	1155.1	1154.5	1153.8	1153.2
145°	1197.1	1197.5	1198.0	1198.2	1198.2	1198.2	1198.2	1198.2
147.5°	1235.4	1235.9	1236.4	1236.1	1235.0	1234.0	1232.9	1231.8
150°	1258.9	1259.4	1259.9	1259.7	1259.1	1258.3	1257.7	1256.9
152.5°	1279.8	1280.7	1281.5	1281.4	1280.3	1279.2	1278.1	1277.1
155°	1308.6	1309.7	1310.9	1310.8	1309.4	1308.0	1306.6	1305.2
157.5°	1333.6	1335.0	1336.4	1336.1	1334.3	1332.5	1330.6	1328.9
160°	1347.8	1349.2	1350.6	1350.5	1348.8	1347.2	1345.6	1343.9
162.5°	1360.7	1362.4	1363.9	1364.0	1362.5	1361.1	1359.7	1358.2
165°	1378.1	1380.0	1381.9	1381.9	1380.3	1378.7	1377.0	1375.4
167.5°	1391.6	1393.3	1395.2	1395.2	1393.3	1391.6	1389.7	1387.8
170°	1399.1	1400.9	1402.8	1402.8	1400.9	1399.1	1397.2	1395.3
172.5°	1404.1	1406.0	1407.9	1407.7	1405.7	1403.6	1401.6	1399.5
175°	1410.1	1411.8	1413.4	1413.2	1411.4	1409.6	1407.7	1405.8
177.5°	1412.3	1413.9	1415.4	1415.2	1413.3	1411.4	1409.6	1407.7
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0

(END OF REPORT)