

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331848-940

Luminaire Tested: **S122RDIW-S1005D435U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331848-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4446.3 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	60	57	55	52
3	86	77	70	64	82	73	67	62	66	61	57	60	56	52	53	50	48	44
4	80	69	61	55	75	66	58	53	59	54	49	54	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	24
9	55	43	35	30	52	41	34	29	38	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24380	24380	24380
5°	24473	24076	24209
10°	24287	23682	23481
15°	24008	22980	22318
20°	23622	21978	20874
25°	23225	20838	19475
30°	22676	19669	17682
35°	22141	18398	16109
40°	21602	17081	14286
45°	20970	15602	12638
50°	20321	14109	11017
55°	19657	12504	9464
60°	18887	10811	7857
65°	18010	9085	7156
70°	16966	7482	6581
75°	15689	6818	6138
80°	13845	6100	5588
85°	10893	4798	4798



TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	3.2
10°-20°	388.1	8.7
20°-30°	545.0	12.3
30°-40°	594.3	13.4
40°-50°	546.4	12.3
50°-60°	429.2	9.7
60°-70°	279.8	6.3
70°-80°	144.3	3.2
80°-90°	39.3	0.9
90°-100°	30.3	0.7
100°-110°	94.2	2.1
110°-120°	161.0	3.6
120°-130°	211.8	4.8
130°-140°	237.7	5.3
140°-150°	233.1	5.2
150°-160°	195.5	4.4
160°-170°	129.7	2.9
170°-180°	45.3	1.0
0°-30°	1074.4	24.2
0°-40°	1668.7	37.5
0°-60°	2644.3	59.5
0°-90°	3107.7	69.9
90°-120°	285.6	6.4
90°-150°	968.1	21.8
90°-180°	1339.0	30.1
0°-180°	4446.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1510	1510	1510	1510	1510	
5°	1510	1503	1486	1497	1494	143
15°	1436	1419	1375	1350	1335	404
25°	1304	1257	1170	1116	1093	599
35°	1123	1051	933	850	817	703
45°	918	824	683	590	554	709
55°	698	589	444	365	336	624
65°	471	360	238	194	187	467
75°	252	158	109	100	98	266
85°	59	31	26	26	26	69
90°	0	5	14	13	14	4
95°	21	25	26	26	25	24
105°	87	88	89	90	90	92
115°	162	164	163	163	162	160
125°	235	238	238	236	236	210
135°	304	308	309	309	308	235
145°	369	372	374	375	373	231
155°	422	423	425	426	425	194
165°	459	459	459	462	460	129
175°	478	477	476	478	476	45
180°	479	479	479	479	479	



TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1515.6	1514.3	1513.1	1511.9	1510.6	1508.7	1506.0	1503.4	1500.7	1498.1	1500.5
5°	1510.0	1508.5	1507.0	1505.5	1504.0	1501.3	1497.3	1493.3	1489.4	1485.5	1488.2
7.5°	1494.5	1492.6	1490.8	1488.8	1486.9	1483.7	1479.1	1474.4	1469.9	1465.3	1466.1
10°	1481.4	1479.3	1477.1	1475.0	1472.8	1468.7	1462.7	1456.6	1450.5	1444.5	1443.6
12.5°	1465.0	1462.3	1459.7	1457.1	1454.6	1449.3	1441.5	1433.8	1426.0	1418.3	1416.6
15°	1436.3	1432.9	1429.6	1426.2	1422.9	1416.0	1405.8	1395.4	1385.1	1374.8	1369.0
17.5°	1401.0	1395.9	1390.8	1385.7	1380.6	1371.5	1358.2	1345.0	1331.7	1318.5	1311.6
20°	1374.8	1368.7	1362.6	1356.6	1350.5	1339.9	1324.6	1309.5	1294.3	1279.1	1271.5
22.5°	1346.3	1339.5	1332.8	1326.0	1319.1	1307.2	1290.0	1272.9	1255.8	1238.7	1228.9
25°	1303.7	1294.0	1284.2	1274.5	1264.8	1250.0	1229.9	1209.9	1189.8	1169.7	1157.4
27.5°	1252.3	1241.8	1231.2	1220.7	1210.1	1193.5	1170.9	1148.3	1125.7	1103.1	1088.6
30°	1216.3	1204.7	1193.2	1181.6	1170.1	1152.2	1127.8	1103.6	1079.3	1055.0	1039.5
32.5°	1181.2	1167.8	1154.3	1140.9	1127.3	1108.2	1083.4	1058.6	1033.8	1009.1	991.4
35°	1123.3	1107.9	1092.3	1076.8	1061.4	1040.3	1013.5	986.9	960.1	933.4	914.3
37.5°	1065.4	1048.4	1031.4	1014.3	997.4	974.6	946.1	917.7	889.1	860.7	839.6
40°	1024.9	1006.7	988.5	970.3	952.1	928.2	898.8	869.3	839.8	810.4	788.8
42.5°	983.4	964.2	945.0	925.8	906.6	881.8	851.4	820.9	790.5	760.1	737.8
45°	918.4	898.0	877.6	857.3	837.0	810.8	778.9	747.1	715.2	683.3	661.7
47.5°	854.9	833.4	811.8	790.2	768.7	741.5	708.6	675.6	642.7	609.8	588.4
50°	809.0	787.5	765.9	744.3	722.7	695.3	661.9	628.5	595.0	561.7	540.7
52.5°	764.2	741.6	719.2	696.6	674.0	646.5	613.8	581.1	548.4	515.8	495.5
55°	698.3	674.7	650.9	627.2	603.6	575.3	542.5	509.7	477.0	444.2	425.9
57.5°	630.8	606.5	582.2	557.9	533.6	505.7	474.2	442.6	411.2	379.6	362.9
60°	584.9	560.6	536.3	512.0	487.7	459.9	428.6	397.3	366.0	334.8	319.3
62.5°	540.1	515.8	491.5	467.2	442.9	415.8	386.0	356.1	326.4	296.6	281.8
65°	471.4	446.8	422.3	397.7	373.1	347.1	319.8	292.5	265.1	237.8	227.5
67.5°	405.3	380.9	356.5	332.1	307.6	283.1	258.6	234.0	209.4	184.8	180.0
70°	359.4	335.7	312.0	288.4	264.7	242.4	221.4	200.5	179.5	158.5	155.5
72.5°	315.7	292.9	270.3	247.5	224.8	205.0	188.2	171.4	154.5	137.8	135.2
75°	251.5	230.2	208.9	187.7	166.4	150.6	140.3	130.0	119.7	109.3	107.2
77.5°	188.3	169.7	151.1	132.4	113.7	101.9	96.9	91.9	86.9	82.0	80.8
80°	148.9	133.5	118.0	102.5	87.0	77.8	74.7	71.7	68.7	65.6	64.4
82.5°	112.9	100.8	88.7	76.6	64.6	57.4	55.4	53.3	51.3	49.2	48.5
85°	58.8	52.3	46.0	39.6	33.3	29.6	28.7	27.8	26.8	25.9	25.9
87.5°	17.6	15.9	14.1	12.4	10.7	10.0	10.4	10.8	11.1	11.6	11.3
90°	0.4	1.5	2.6	3.7	4.7	6.2	8.2	10.2	12.1	14.2	14.0
92.5°	7.2	8.0	8.7	9.5	10.3	11.0	11.4	11.9	12.4	12.8	12.8
95°	21.0	21.9	22.8	23.7	24.6	25.1	25.3	25.5	25.7	25.9	25.9
97.5°	38.3	39.1	39.9	40.8	41.6	42.1	42.4	42.8	43.2	43.4	43.4
100°	51.3	52.0	52.7	53.5	54.2	54.7	54.9	55.2	55.5	55.7	55.7
102.5°	64.9	65.5	66.0	66.6	67.1	67.7	67.9	68.3	68.7	69.0	69.1
105°	86.9	87.1	87.4	87.7	87.9	88.2	88.4	88.5	88.7	88.9	89.1
107.5°	109.0	109.4	109.8	110.2	110.6	110.8	110.8	110.8	110.8	110.8	110.8
110°	123.2	123.8	124.3	124.8	125.4	125.6	125.6	125.6	125.6	125.6	125.6



TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.8	139.3	139.8	140.4	140.9	141.2	141.1	141.0	140.9	140.8	140.6
115°	161.6	162.1	162.6	163.2	163.7	163.9	163.7	163.5	163.4	163.2	163.1
117.5°	184.4	185.1	185.8	186.5	187.3	187.3	186.9	186.4	185.8	185.4	185.1
120°	199.6	200.3	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6	199.6
122.5°	213.5	214.4	215.2	216.1	217.0	217.1	216.6	216.1	215.6	215.1	214.9
125°	235.1	235.9	236.7	237.6	238.4	238.6	238.4	238.1	237.8	237.6	237.3
127.5°	256.2	257.3	258.2	259.3	260.3	260.6	260.4	260.0	259.7	259.4	259.0
130°	269.5	270.6	271.8	273.0	274.1	274.6	274.5	274.3	274.1	273.9	273.8
132.5°	284.4	285.3	286.2	287.2	288.1	288.6	288.6	288.7	288.7	288.7	288.4
135°	304.3	305.2	306.2	307.2	308.2	308.7	308.9	309.1	309.2	309.4	309.3
137.5°	325.1	325.9	326.7	327.5	328.3	328.9	329.1	329.4	329.6	329.8	329.8
140°	337.8	338.6	339.4	340.2	341.0	341.6	342.1	342.5	343.0	343.4	343.4
142.5°	350.7	351.5	352.3	353.1	353.9	354.5	354.7	355.1	355.3	355.7	355.8
145°	369.3	369.9	370.5	371.1	371.8	372.4	372.9	373.4	374.0	374.5	374.6
147.5°	385.8	386.6	387.4	388.1	388.9	389.4	389.8	390.1	390.5	390.8	391.0
150°	397.2	397.7	398.2	398.8	399.3	399.8	400.1	400.5	400.8	401.2	401.4
152.5°	407.2	407.7	408.2	408.8	409.3	409.8	410.2	410.6	411.1	411.5	411.9
155°	422.1	422.4	422.7	423.0	423.3	423.6	423.8	424.1	424.4	424.6	425.1
157.5°	435.1	435.2	435.4	435.6	435.8	435.9	436.0	436.2	436.4	436.6	437.2
160°	442.8	443.0	443.2	443.4	443.5	443.6	443.7	443.8	443.9	444.0	444.5
162.5°	449.9	450.0	450.0	450.0	450.0	450.1	450.2	450.3	450.4	450.5	451.0
165°	459.3	459.2	459.1	459.1	459.0	459.0	459.0	459.0	459.0	459.0	459.6
167.5°	467.3	467.0	466.7	466.5	466.2	466.0	466.0	466.0	466.0	466.0	466.6
170°	471.4	471.2	470.9	470.6	470.4	470.2	470.1	470.0	469.9	469.8	470.5
172.5°	474.4	474.1	473.9	473.6	473.3	473.1	473.1	473.0	472.9	472.8	473.4
175°	478.0	477.7	477.4	477.2	476.9	476.6	476.4	476.3	476.1	475.9	476.5
177.5°	479.4	479.2	478.9	478.8	478.5	478.3	478.2	478.0	477.9	477.8	478.2
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1502.9	1505.3	1507.8	1508.7	1508.2	1507.8	1507.3	1506.8
5°	1490.9	1493.7	1496.4	1497.3	1496.4	1495.5	1494.6	1493.7
7.5°	1466.8	1467.6	1468.4	1468.0	1466.4	1464.8	1463.3	1461.7
10°	1442.6	1441.7	1440.8	1439.5	1437.6	1435.8	1434.0	1432.2
12.5°	1415.0	1413.3	1411.7	1409.3	1406.3	1403.3	1400.3	1397.2
15°	1363.2	1357.5	1351.7	1347.3	1344.3	1341.2	1338.2	1335.2
17.5°	1304.8	1297.9	1291.0	1285.0	1279.8	1274.5	1269.3	1264.1
20°	1263.9	1256.3	1248.8	1241.6	1234.9	1228.2	1221.6	1214.9
22.5°	1219.1	1209.3	1199.5	1192.1	1187.2	1182.2	1177.2	1172.2
25°	1144.9	1132.5	1120.0	1111.5	1106.9	1102.3	1097.8	1093.2
27.5°	1074.1	1059.5	1045.0	1034.1	1026.9	1019.7	1012.4	1005.2
30°	1024.0	1008.5	993.0	981.2	973.0	964.8	956.6	948.4
32.5°	973.7	956.1	938.3	925.7	918.0	910.3	902.5	894.8
35°	895.1	876.0	856.8	843.9	837.2	830.5	823.9	817.3
37.5°	818.5	797.5	776.3	762.0	754.4	746.7	739.0	731.4
40°	767.2	745.6	724.2	709.4	701.5	693.6	685.7	677.8
42.5°	715.5	693.2	670.9	655.9	648.3	640.6	633.0	625.4
45°	640.2	618.6	597.0	582.6	575.3	568.0	560.7	553.5
47.5°	566.9	545.5	524.0	510.0	503.4	496.8	490.1	483.5
50°	519.8	498.8	477.9	464.1	457.8	451.4	445.1	438.6
52.5°	475.3	455.0	434.9	421.8	415.9	410.0	404.1	398.2
55°	407.7	389.5	371.2	359.3	353.5	347.7	342.0	336.2
57.5°	346.3	329.5	312.8	302.0	297.2	292.3	287.5	282.6
60°	303.8	288.4	272.9	262.7	257.8	253.0	248.1	243.3
62.5°	267.1	252.3	237.6	228.6	225.8	222.8	219.9	217.0
65°	217.1	206.8	196.4	190.8	189.9	189.0	188.2	187.3
67.5°	175.3	170.6	165.8	162.9	162.0	161.0	160.1	159.1
70°	152.5	149.5	146.4	144.3	143.0	141.8	140.6	139.4
72.5°	132.7	130.1	127.5	125.9	125.2	124.5	123.7	123.0
75°	105.0	103.0	100.9	99.6	99.3	99.0	98.7	98.4
77.5°	79.5	78.4	77.1	76.2	75.8	75.3	74.8	74.4
80°	63.1	62.0	60.7	60.1	60.1	60.1	60.1	60.1
82.5°	47.7	47.0	46.3	45.9	45.9	45.9	45.9	45.9
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	11.1	10.7	10.4	10.3	10.3	10.3	10.3	10.4
90°	13.8	13.6	13.5	13.4	13.5	13.6	13.6	13.7
92.5°	12.9	12.9	13.0	13.0	13.0	13.0	13.1	13.1
95°	25.9	25.9	25.9	25.8	25.6	25.4	25.2	25.1
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4
100°	55.7	55.7	55.7	55.7	55.6	55.6	55.5	55.4
102.5°	69.1	69.2	69.3	69.3	69.2	69.1	69.0	68.9
105°	89.3	89.4	89.6	89.7	89.7	89.7	89.7	89.7
107.5°	110.9	111.0	111.1	110.9	110.5	110.0	109.7	109.2
110°	125.6	125.6	125.6	125.5	125.2	124.9	124.7	124.4



TEST NUMBER: P331848-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	140.4	140.2	140.0	139.7	139.6	139.4	139.2	139.0
115°	163.0	162.9	162.8	162.6	162.4	162.1	161.8	161.6
117.5°	184.9	184.7	184.5	184.2	184.0	183.7	183.4	183.2
120°	199.6	199.6	199.6	199.5	199.2	198.9	198.7	198.4
122.5°	214.6	214.5	214.2	214.0	213.8	213.7	213.4	213.2
125°	237.0	236.7	236.5	236.3	236.2	236.1	236.0	235.9
127.5°	258.7	258.4	258.1	257.8	257.4	257.2	256.9	256.6
130°	273.6	273.4	273.2	273.0	272.6	272.2	271.9	271.5
132.5°	288.0	287.6	287.2	286.9	286.6	286.2	286.0	285.7
135°	309.2	309.2	309.1	308.9	308.6	308.4	308.1	307.8
137.5°	329.7	329.6	329.6	329.3	329.0	328.6	328.2	327.9
140°	343.4	343.4	343.4	343.2	342.9	342.5	342.1	341.8
142.5°	355.8	355.9	356.0	355.8	355.4	355.1	354.7	354.4
145°	374.7	374.8	374.9	374.7	374.3	374.0	373.6	373.3
147.5°	391.2	391.5	391.6	391.6	391.2	390.8	390.5	390.2
150°	401.7	402.0	402.3	402.3	402.0	401.7	401.4	401.2
152.5°	412.1	412.5	412.9	412.9	412.5	412.1	411.9	411.5
155°	425.5	426.0	426.4	426.5	426.2	426.0	425.7	425.4
157.5°	437.7	438.4	439.0	439.1	438.6	438.2	437.8	437.4
160°	445.1	445.6	446.1	446.2	445.9	445.5	445.1	444.8
162.5°	451.7	452.3	452.9	453.0	452.5	452.1	451.7	451.3
165°	460.2	460.8	461.5	461.5	461.1	460.7	460.2	459.8
167.5°	467.3	467.9	468.5	468.6	468.1	467.6	467.2	466.7
170°	471.1	471.7	472.3	472.4	471.9	471.4	470.8	470.3
172.5°	474.0	474.7	475.3	475.3	474.7	474.2	473.7	473.1
175°	477.2	477.8	478.4	478.5	478.0	477.4	476.9	476.4
177.5°	478.7	479.0	479.5	479.5	479.0	478.7	478.2	477.8
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8

(END OF REPORT)