

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332112-930

Luminaire Tested: **S123DIW-S340D1320U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332112-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1320U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5456.7 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21				
1	91	87	83	80	81	77	74	71	59	57	55	42	41	39	26	25	25	18				
2	83	76	70	65	73	67	63	58	51	48	45	37	35	33	23	22	21	15				
3	76	67	60	54	67	59	53	49	45	41	38	32	30	28	20	19	18	13				
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15	11				
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13	9				
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12	8				
7	54	42	34	29	47	37	31	26	29	24	21	21	18	16	13	12	10	7				
8	50	38	31	25	44	34	27	23	26	22	18	19	16	14	12	10	9	6				
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	9	8	6				
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	10	9	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	0.8
10°-20°	117.5	2.2
20°-30°	173.6	3.2
30°-40°	202.8	3.7
40°-50°	203.9	3.7
50°-60°	179.1	3.3
60°-70°	133.4	2.4
70°-80°	76.0	1.4
80°-90°	25.8	0.5
90°-100°	51.3	0.9
100°-110°	244.5	4.5
110°-120°	587.3	10.8
120°-130°	747.9	13.7
130°-140°	799.1	14.6
140°-150°	747.2	13.7
150°-160°	602.7	11.0
160°-170°	389.0	7.1
170°-180°	134.1	2.5
0°-30°	332.7	6.1
0°-40°	535.5	9.8
0°-60°	918.4	16.8
0°-90°	1153.6	21.1
90°-120°	883.1	16.2
90°-150°	3177.3	58.2
90°-180°	4303.0	78.9
0°-180°	5456.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	1	12	25	29	32	4
95°	64	24	32	40	40	79
105°	312	318	230	54	46	331
115°	586	592	602	612	616	578
125°	826	834	839	841	843	737
135°	1028	1035	1039	1042	1039	791
145°	1187	1194	1196	1198	1198	743
155°	1307	1305	1306	1311	1305	602
165°	1379	1376	1374	1382	1375	389
175°	1411	1406	1407	1413	1406	134
180°	1411	1411	1411	1411	1411	



TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.1	8.4	8.6	8.9	9.1	9.5	10.1	10.7	11.2	11.7	11.8
90°	1.1	3.3	5.7	8.1	10.4	13.0	16.1	19.1	22.1	25.2	26.1
92.5°	19.5	18.8	18.2	17.5	16.9	17.7	20.0	22.3	24.5	26.8	28.3
95°	63.9	54.4	44.8	35.3	25.8	22.3	24.8	27.4	29.9	32.5	34.2
97.5°	128.5	124.3	119.9	115.7	111.4	100.9	84.1	67.3	50.5	33.8	35.6
100°	177.2	181.8	186.5	191.1	195.8	179.9	143.7	107.3	70.9	34.6	36.4
102.5°	232.5	235.9	239.2	242.6	246.0	227.8	188.1	148.4	108.7	69.0	63.2
105°	312.4	315.0	317.6	320.1	322.6	313.5	292.4	271.5	250.5	229.6	188.3
107.5°	396.7	398.8	400.8	402.8	404.9	407.6	410.9	414.2	417.5	420.8	390.5
110°	452.9	454.8	456.6	458.4	460.3	462.5	465.1	467.7	470.3	472.8	465.1



TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.5	508.3	509.9	511.6	513.2	515.4	518.0	520.5	523.1	525.6	525.8
115°	586.0	587.4	588.8	590.2	591.6	593.4	595.4	597.5	599.7	601.8	604.1
117.5°	663.0	664.7	666.4	668.1	669.8	671.2	672.3	673.4	674.5	675.6	677.4
120°	710.8	712.9	714.9	717.1	719.2	720.6	721.2	721.9	722.7	723.3	725.2
122.5°	759.5	761.2	762.9	764.6	766.3	767.6	768.5	769.4	770.3	771.2	772.5
125°	826.1	827.9	829.8	831.7	833.6	834.9	835.8	836.8	837.7	838.7	839.1
127.5°	890.6	892.5	894.4	896.3	898.1	899.6	900.7	901.9	902.9	904.1	904.8
130°	930.9	932.8	934.7	936.5	938.4	939.8	940.7	941.7	942.6	943.5	944.4
132.5°	969.5	971.3	973.2	975.1	977.0	978.3	979.0	979.7	980.5	981.2	982.2
135°	1028.4	1029.8	1031.2	1032.6	1034.0	1035.2	1036.1	1037.1	1038.0	1038.9	1039.6
137.5°	1078.7	1080.5	1082.3	1084.0	1085.8	1087.0	1087.4	1088.0	1088.5	1089.0	1090.1
140°	1112.3	1113.7	1115.1	1116.5	1117.9	1118.9	1119.7	1120.3	1121.0	1121.7	1122.7
142.5°	1143.3	1144.7	1146.1	1147.5	1148.9	1150.0	1150.6	1151.4	1152.0	1152.8	1153.5
145°	1186.7	1188.4	1190.0	1191.6	1193.3	1194.3	1194.7	1195.2	1195.7	1196.1	1196.6
147.5°	1227.6	1228.7	1229.7	1230.8	1231.9	1232.7	1233.1	1233.5	1234.0	1234.5	1235.0
150°	1252.8	1253.4	1254.2	1254.8	1255.6	1256.1	1256.6	1257.0	1257.5	1258.0	1258.5
152.5°	1275.4	1275.7	1276.0	1276.4	1276.7	1277.0	1277.3	1277.6	1277.8	1278.1	1279.0
155°	1307.3	1306.8	1306.4	1305.9	1305.4	1305.3	1305.5	1305.8	1306.0	1306.2	1307.4
157.5°	1332.0	1332.0	1332.0	1331.9	1331.8	1331.7	1331.5	1331.2	1331.0	1330.7	1332.1
160°	1347.1	1346.9	1346.6	1346.4	1346.1	1346.0	1345.7	1345.5	1345.2	1345.0	1346.4
162.5°	1361.4	1360.7	1360.2	1359.5	1358.9	1358.5	1358.3	1358.0	1357.8	1357.6	1359.2
165°	1378.6	1377.9	1377.1	1376.5	1375.7	1375.3	1375.1	1374.8	1374.6	1374.4	1376.2
167.5°	1392.0	1391.1	1390.1	1389.2	1388.2	1387.8	1387.8	1387.8	1387.8	1387.8	1389.7
170°	1399.5	1398.6	1397.7	1396.8	1395.8	1395.3	1395.3	1395.3	1395.3	1395.3	1397.2
172.5°	1404.6	1403.5	1402.3	1401.2	1400.1	1399.6	1399.8	1400.0	1400.2	1400.4	1402.2
175°	1411.0	1409.9	1408.8	1407.5	1406.4	1405.9	1406.1	1406.4	1406.6	1406.9	1408.5
177.5°	1412.8	1411.8	1410.9	1410.0	1409.0	1408.7	1408.8	1409.0	1409.2	1409.4	1410.9
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	12.0	12.1	12.2	12.3	12.4	12.5	12.6	12.6
90°	27.0	28.0	28.9	29.6	30.1	30.5	31.0	31.5
92.5°	29.8	31.3	32.8	33.7	34.0	34.2	34.5	34.8
95°	35.8	37.4	39.1	39.9	39.9	39.9	39.9	39.9
97.5°	37.5	39.4	41.2	42.2	42.5	42.7	43.0	43.2
100°	38.3	40.2	42.1	43.1	43.3	43.5	43.8	44.0
102.5°	57.4	51.6	45.9	43.2	43.6	44.0	44.4	44.8
105°	147.1	105.9	64.7	44.3	44.8	45.2	45.7	46.1
107.5°	360.4	330.1	299.9	269.2	238.1	207.0	175.9	144.9
110°	457.4	449.7	442.1	421.5	388.2	354.9	321.6	288.3



TEST NUMBER: P332112-930

CATALOG NUMBER: S123DIW-S340D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.9	526.0	526.2	522.8	515.7	508.7	501.7	494.6
115°	606.4	608.7	611.1	612.7	613.6	614.6	615.5	616.4
117.5°	679.3	681.1	683.0	684.0	684.2	684.4	684.6	684.8
120°	727.1	729.0	730.8	731.7	731.7	731.7	731.7	731.7
122.5°	773.8	775.1	776.4	777.1	777.3	777.5	777.7	777.9
125°	839.6	840.1	840.5	841.0	841.5	842.0	842.4	842.9
127.5°	905.6	906.3	907.1	907.2	906.8	906.3	905.8	905.3
130°	945.3	946.3	947.2	947.5	947.0	946.6	946.1	945.6
132.5°	983.1	984.1	985.0	985.1	984.5	983.8	983.2	982.5
135°	1040.3	1041.0	1041.7	1041.7	1041.0	1040.3	1039.6	1038.9
137.5°	1091.3	1092.3	1093.5	1093.8	1093.3	1092.9	1092.4	1091.9
140°	1123.6	1124.5	1125.4	1125.7	1125.2	1124.7	1124.3	1123.8
142.5°	1154.2	1155.0	1155.8	1155.8	1155.1	1154.5	1153.8	1153.2
145°	1197.1	1197.5	1198.0	1198.2	1198.2	1198.2	1198.2	1198.2
147.5°	1235.4	1235.9	1236.4	1236.1	1235.0	1234.0	1232.9	1231.8
150°	1258.9	1259.4	1259.9	1259.7	1259.1	1258.3	1257.7	1256.9
152.5°	1279.8	1280.7	1281.5	1281.4	1280.3	1279.2	1278.1	1277.1
155°	1308.6	1309.7	1310.9	1310.8	1309.4	1308.0	1306.6	1305.2
157.5°	1333.6	1335.0	1336.4	1336.1	1334.3	1332.5	1330.6	1328.9
160°	1347.8	1349.2	1350.6	1350.5	1348.8	1347.2	1345.6	1343.9
162.5°	1360.7	1362.4	1363.9	1364.0	1362.5	1361.1	1359.7	1358.2
165°	1378.1	1380.0	1381.9	1381.9	1380.3	1378.7	1377.0	1375.4
167.5°	1391.6	1393.3	1395.2	1395.2	1393.3	1391.6	1389.7	1387.8
170°	1399.1	1400.9	1402.8	1402.8	1400.9	1399.1	1397.2	1395.3
172.5°	1404.1	1406.0	1407.9	1407.7	1405.7	1403.6	1401.6	1399.5
175°	1410.1	1411.8	1413.4	1413.2	1411.4	1409.6	1407.7	1405.8
177.5°	1412.3	1413.9	1415.4	1415.2	1413.3	1411.4	1409.6	1407.7
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0

(END OF REPORT)