

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331850-940

Luminaire Tested: **S122RDIW-S1005D710U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331850-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D710U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5594.4 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	90	95	91	88	85	80	77	75	69	68	66	60	59	58	53
2	93	86	80	75	87	81	76	71	71	67	64	62	59	57	54	52	50	46
3	85	77	70	64	80	72	66	61	64	59	55	56	52	49	49	46	44	40
4	79	69	61	55	74	65	58	53	57	52	48	51	47	43	44	41	39	36
5	73	62	54	48	68	58	51	46	52	46	42	46	42	38	40	37	35	32
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31	28
7	63	51	43	38	59	48	41	36	43	38	34	39	34	31	34	31	28	26
8	59	47	39	34	55	44	38	33	40	34	30	36	31	28	32	28	26	23
9	55	43	36	31	51	41	34	30	37	31	28	33	29	26	30	26	23	21
10	51	40	33	28	48	38	31	27	34	29	25	31	27	23	28	24	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	31752	31752	31752	31752
5°	35462	31951	28329	31951
10°	39346	31727	24556	31727
15°	41279	31263	19348	31263
20°	35787	30574	16744	30574
25°	23469	29630	14949	29630
30°	15797	28486	13530	28486
35°	12796	27045	12203	27045
40°	11377	25478	11291	25478
45°	10298	23640	10079	23640
50°	9372	21815	9339	21815
55°	8811	19792	8695	19792
60°	7369	17938	7282	17938
65°	6212	16290	7049	16290
70°	5740	14549	6647	14549
75°	5371	12664	6138	12664
80°	4956	10423	5467	10423
85°	4557	8225	4798	8225



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.4	3.3
10°-20°	519.5	9.3
20°-30°	669.4	12.0
30°-40°	636.1	11.4
40°-50°	544.9	9.7
50°-60°	415.0	7.4
60°-70°	262.3	4.7
70°-80°	131.0	2.3
80°-90°	37.2	0.7
90°-100°	49.7	0.9
100°-110°	154.3	2.8
110°-120°	263.8	4.7
120°-130°	346.9	6.2
130°-140°	389.3	7.0
140°-150°	381.7	6.8
150°-160°	320.2	5.7
160°-170°	212.4	3.8
170°-180°	74.2	1.3
0°-30°	1375.3	24.6
0°-40°	2011.4	36.0
0°-60°	2971.3	53.1
0°-90°	3401.9	60.8
90°-120°	467.8	8.4
90°-150°	1585.7	28.3
90°-180°	2193.0	39.2
0°-180°	5594.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1967	1967	1967	1967	1967	
5°	2188	1971	1748	1971	2188	216
15°	2470	1870	1158	1870	2470	666
25°	1317	1663	839	1663	1317	625
35°	649	1372	619	1372	649	415
45°	451	1035	441	1035	451	349
55°	313	703	309	703	313	275
65°	163	426	184	426	163	166
75°	86	203	98	203	86	91
85°	25	44	26	44	25	27
90°	22	1	22	1	22	11
95°	41	34	41	34	41	46
105°	147	142	147	142	147	155
115°	265	265	265	265	265	261
125°	386	385	386	385	386	345
135°	504	498	504	498	504	388
145°	611	605	611	605	611	382
155°	697	691	697	691	697	321
165°	753	752	753	752	753	212
175°	780	783	780	783	780	74
180°	784	784	784	784	784	



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2046.4	2048.1	2049.7	2045.9	2045.9	2042.6	2035.5	2030.0	2014.7	2012.5	2012.5
5°	2188.0	2186.7	2189.3	2180.5	2168.2	2165.4	2152.5	2135.4	2117.6	2097.8	2093.7
7.5°	2328.8	2326.7	2321.2	2319.8	2310.3	2289.6	2268.8	2246.5	2217.0	2188.2	2173.6
10°	2399.9	2422.4	2408.7	2384.8	2389.6	2357.5	2340.4	2311.0	2286.4	2243.4	2233.8
12.5°	2469.8	2478.7	2474.3	2460.8	2454.6	2432.3	2409.2	2383.7	2338.3	2299.6	2266.0
15°	2469.5	2482.5	2485.9	2481.8	2485.3	2483.9	2471.6	2450.4	2410.7	2368.4	2331.5
17.5°	2287.2	2296.2	2318.6	2333.8	2353.0	2393.4	2413.3	2421.2	2415.3	2391.1	2365.1
20°	2082.8	2067.7	2130.6	2162.8	2190.0	2258.3	2317.1	2339.7	2375.9	2375.3	2368.4
22.5°	1793.1	1796.6	1856.2	1894.4	1974.2	2042.5	2109.4	2194.3	2264.4	2310.7	2337.8
25°	1317.4	1343.5	1402.8	1454.8	1543.6	1670.7	1786.2	1920.1	2046.6	2146.3	2241.3
27.5°	989.4	991.4	1038.5	1086.5	1139.2	1243.4	1388.8	1548.7	1728.9	1877.7	2048.7
30°	847.3	843.2	863.0	892.4	937.5	1018.2	1127.5	1284.7	1464.4	1688.5	1888.0
32.5°	746.7	747.0	761.9	783.6	821.1	875.5	950.4	1078.0	1247.9	1468.2	1702.2
35°	649.2	648.5	659.4	675.1	690.8	725.7	776.9	843.9	960.7	1166.4	1405.6
37.5°	579.2	582.2	587.5	597.4	614.7	634.1	664.9	709.8	793.1	914.7	1115.7
40°	539.8	541.2	548.7	556.9	567.1	582.2	607.4	643.7	704.5	801.6	948.4
42.5°	503.7	505.2	510.4	518.1	526.2	541.2	562.1	593.4	642.7	718.5	839.6
45°	451.0	451.0	455.8	459.2	468.1	481.7	498.8	524.8	558.9	615.0	695.6
47.5°	401.5	401.6	404.8	410.7	416.3	427.0	443.7	464.9	489.8	533.2	602.0
50°	373.1	373.8	375.9	380.6	384.1	393.6	406.6	425.0	451.0	484.5	541.9
52.5°	350.2	349.7	352.3	354.4	356.7	363.6	373.3	389.5	412.7	441.8	489.4
55°	313.0	310.2	314.3	317.7	319.8	322.5	328.0	338.2	358.0	382.6	418.2
57.5°	266.5	265.4	268.3	271.4	277.9	285.3	289.9	296.4	306.7	324.3	359.5
60°	228.2	228.2	234.3	236.4	244.0	253.5	263.1	268.6	278.8	290.4	316.4
62.5°	194.3	194.9	197.8	199.8	204.0	215.8	229.2	241.2	250.9	262.0	279.2
65°	162.6	164.0	164.0	165.3	168.1	170.9	176.3	185.8	203.0	218.6	231.7
67.5°	138.0	138.5	138.8	140.2	140.9	143.9	146.1	150.3	154.3	169.2	185.3
70°	121.6	123.7	123.0	124.4	125.0	126.4	129.1	131.2	137.3	140.8	150.3
72.5°	106.3	107.8	107.7	108.5	110.3	110.6	112.7	114.8	118.8	121.6	126.8
75°	86.1	85.4	86.1	87.5	88.2	88.8	88.8	91.6	93.6	96.3	99.8
77.5°	66.4	67.1	67.0	67.1	67.2	68.5	68.3	69.6	71.6	72.9	74.6
80°	53.3	53.9	53.3	53.9	54.7	55.4	54.7	55.4	57.4	58.8	58.8
82.5°	41.3	41.4	41.8	42.0	42.1	42.3	43.2	43.3	44.9	44.6	45.1
85°	24.6	23.9	23.9	23.9	24.6	25.3	24.6	24.6	25.3	25.3	25.3
87.5°	13.3	13.7	13.7	13.7	13.6	13.7	13.7	14.4	13.9	14.4	13.3
90°	22.5	22.4	22.2	22.0	21.9	22.0	22.3	22.6	22.8	23.2	19.9
92.5°	21.4	21.4	21.4	21.3	21.3	21.3	21.2	21.1	21.1	21.0	20.2
95°	41.0	41.3	41.6	41.9	42.2	42.4	42.4	42.4	42.4	42.4	42.1
97.5°	71.1	71.1	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	70.6
100°	90.7	90.8	91.0	91.1	91.2	91.3	91.3	91.3	91.3	91.3	90.9
102.5°	112.9	113.1	113.2	113.3	113.5	113.5	113.3	113.2	113.2	113.0	112.4
105°	146.9	146.9	146.9	146.9	146.9	146.8	146.4	146.2	145.9	145.6	145.3
107.5°	179.0	179.6	180.3	180.9	181.6	181.9	181.8	181.6	181.6	181.5	181.5
110°	203.8	204.2	204.6	205.1	205.5	205.8	205.8	205.8	205.8	205.8	205.8



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.7	227.9	228.3	228.6	228.9	229.3	229.6	230.0	230.3	230.7	230.8
115°	264.7	265.1	265.6	266.0	266.4	266.7	266.9	267.1	267.2	267.3	267.6
117.5°	300.0	300.4	300.9	301.3	301.8	302.2	302.6	302.9	303.3	303.6	304.4
120°	324.9	325.3	325.7	326.2	326.6	326.9	326.9	326.9	326.9	326.9	328.1
122.5°	349.3	349.6	349.9	350.2	350.5	350.9	351.2	351.6	352.0	352.3	353.1
125°	386.5	386.6	386.7	386.9	387.0	387.3	387.7	388.2	388.6	389.1	389.5
127.5°	420.4	420.8	421.2	421.7	422.2	422.7	423.2	423.7	424.3	424.8	425.3
130°	444.7	445.2	445.9	446.4	447.0	447.5	447.7	448.1	448.4	448.6	448.9
132.5°	468.0	468.4	468.9	469.4	469.8	470.4	471.0	471.7	472.3	473.0	473.0
135°	504.2	504.6	505.1	505.5	506.0	506.3	506.4	506.6	506.7	506.8	506.6
137.5°	537.0	537.6	538.2	538.8	539.4	539.8	539.8	539.9	540.1	540.2	539.8
140°	559.8	560.4	561.0	561.6	562.1	562.4	562.4	562.4	562.4	562.4	561.7
142.5°	580.4	581.0	581.6	582.2	582.8	583.0	582.9	582.8	582.6	582.6	582.0
145°	611.4	612.0	612.6	613.1	613.8	613.9	613.9	613.7	613.5	613.4	612.5
147.5°	639.1	639.6	640.2	640.8	641.3	641.4	641.1	640.8	640.4	640.2	639.5
150°	657.1	657.5	657.9	658.4	658.8	658.8	658.4	657.9	657.5	657.1	656.5
152.5°	674.0	674.6	675.1	675.6	676.3	676.3	675.6	675.1	674.6	674.0	673.3
155°	696.8	697.2	697.7	698.1	698.6	698.4	697.7	696.9	696.2	695.4	695.0
157.5°	716.3	717.0	717.7	718.5	719.2	719.0	718.0	717.0	716.0	715.1	714.8
160°	728.5	729.2	729.7	730.3	730.8	730.8	729.9	729.0	728.1	727.2	727.0
162.5°	739.1	739.9	740.6	741.2	741.9	741.8	740.8	739.8	738.8	737.8	737.6
165°	753.0	753.8	754.5	755.2	756.0	755.8	754.7	753.8	752.7	751.7	751.7
167.5°	764.4	765.2	765.9	766.7	767.4	767.3	766.2	765.3	764.2	763.2	763.2
170°	770.2	771.1	772.0	772.8	773.7	773.6	772.7	771.6	770.6	769.5	769.7
172.5°	775.0	775.9	776.8	777.7	778.5	778.5	777.4	776.4	775.3	774.3	774.5
175°	780.2	781.0	781.9	782.7	783.6	783.6	782.6	781.5	780.5	779.4	779.8
177.5°	782.5	783.2	783.9	784.6	785.3	785.3	784.6	783.9	783.2	782.5	782.7
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2013.7	2009.2	2005.5	1995.6	1990.7	1979.7	1978.1	1977.5	1963.4	1949.6	1945.8
5°	2082.8	2071.8	2055.5	2036.3	2016.5	1996.0	1982.4	1971.4	1944.0	1918.1	1903.1
7.5°	2152.5	2129.0	2100.7	2064.5	2034.3	2000.4	1975.2	1952.7	1913.9	1876.7	1851.6
10°	2204.4	2166.1	2128.5	2078.7	2039.7	2001.4	1966.0	1935.2	1891.4	1842.3	1807.4
12.5°	2236.7	2194.6	2142.8	2094.0	2043.5	1994.9	1947.3	1907.8	1856.5	1805.6	1764.2
15°	2280.3	2235.2	2172.3	2102.6	2037.6	1974.2	1919.5	1870.3	1803.3	1742.5	1691.9
17.5°	2316.0	2253.9	2186.4	2105.8	2030.6	1949.8	1879.5	1816.6	1742.0	1668.7	1609.1
20°	2327.4	2265.9	2188.0	2107.4	2018.6	1923.6	1847.7	1779.4	1699.4	1619.4	1551.1
22.5°	2320.3	2272.4	2185.9	2089.4	1998.3	1899.0	1813.3	1734.0	1645.3	1563.7	1484.4
25°	2272.1	2255.7	2173.6	2068.4	1964.5	1849.1	1750.0	1663.2	1562.1	1474.6	1388.5
27.5°	2159.5	2194.9	2144.1	2032.0	1916.6	1792.8	1681.4	1582.6	1477.7	1379.2	1293.4
30°	2051.4	2132.6	2110.8	2006.9	1877.8	1756.1	1631.1	1527.9	1415.9	1314.7	1230.0
32.5°	1903.2	2037.6	2058.9	1971.9	1838.4	1704.8	1573.7	1471.1	1354.1	1247.5	1164.9
35°	1667.3	1868.2	1960.4	1905.1	1771.2	1627.0	1491.7	1372.1	1254.5	1149.3	1067.4
37.5°	1385.9	1659.6	1813.3	1817.2	1694.3	1544.4	1397.0	1278.3	1158.0	1054.6	966.0
40°	1203.4	1499.9	1700.1	1744.5	1640.7	1478.7	1329.7	1208.8	1091.3	990.2	888.3
42.5°	1039.4	1334.8	1580.9	1658.1	1575.7	1414.8	1265.2	1138.8	1024.6	928.9	824.9
45°	840.5	1098.8	1370.0	1508.1	1462.3	1313.3	1155.5	1035.3	927.9	845.3	745.5
47.5°	709.0	891.1	1153.6	1340.2	1339.4	1203.5	1048.2	933.0	833.5	756.0	675.3
50°	634.1	792.6	1014.8	1226.5	1244.3	1130.2	982.6	868.5	775.6	694.3	629.4
52.5°	566.9	697.5	897.2	1100.3	1150.8	1052.0	908.8	803.4	713.3	638.5	582.9
55°	479.0	580.1	731.8	921.8	998.4	928.6	801.6	703.1	630.0	567.1	519.3
57.5°	405.2	481.1	602.8	755.7	844.9	801.0	696.2	616.3	553.7	496.8	459.1
60°	358.7	420.9	524.1	651.9	750.3	719.5	630.0	555.5	502.2	453.1	417.5
62.5°	315.0	368.5	456.9	560.6	650.8	638.1	565.0	502.5	455.8	411.0	380.8
65°	253.5	292.5	361.5	442.8	515.2	521.4	468.8	426.4	384.7	349.2	322.5
67.5°	201.9	227.3	275.9	344.4	398.7	418.0	385.9	353.6	320.5	293.0	269.9
70°	170.1	190.6	226.1	281.5	331.4	351.9	333.5	308.2	279.5	256.9	237.1
72.5°	137.9	157.8	184.0	224.7	267.4	289.6	283.2	265.0	241.7	223.0	204.3
75°	103.9	110.0	127.8	155.2	188.6	207.8	212.5	203.0	184.5	170.1	159.2
77.5°	76.8	80.5	89.0	103.3	125.2	142.2	149.3	148.1	135.5	127.1	116.8
80°	61.5	63.6	67.7	73.8	90.2	107.3	112.1	112.1	103.2	99.8	89.5
82.5°	46.7	48.2	50.7	54.1	61.8	76.7	82.0	83.1	77.5	72.9	64.9
85°	26.7	25.9	27.4	29.4	30.8	34.9	43.1	44.4	43.1	37.5	35.5
87.5°	12.7	12.6	11.9	10.9	11.1	11.2	13.6	16.0	14.2	12.8	12.1
90°	16.7	13.5	10.3	7.8	6.0	4.2	2.4	0.6	2.4	4.2	6.0
92.5°	19.5	18.7	18.0	16.9	15.7	14.4	13.1	11.8	13.1	14.4	15.7
95°	41.7	41.5	41.2	40.3	38.8	37.4	35.8	34.4	35.8	37.4	38.8
97.5°	70.1	69.6	68.9	68.0	66.7	65.5	64.1	62.9	64.1	65.5	66.7
100°	90.4	90.0	89.5	88.7	87.6	86.4	85.2	84.0	85.2	86.4	87.6
102.5°	111.9	111.4	110.8	110.0	109.1	108.2	107.2	106.3	107.2	108.2	109.1
105°	145.0	144.7	144.4	144.0	143.6	143.1	142.7	142.2	142.7	143.1	143.6
107.5°	181.5	181.5	181.5	181.1	180.5	179.9	179.1	178.5	179.1	179.9	180.5
110°	205.8	205.8	205.8	205.4	204.5	203.6	202.7	201.8	202.7	203.6	204.5





TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	230.9	231.0	231.1	230.8	229.9	229.0	228.1	227.2	228.1	229.0	229.9
115°	267.9	268.2	268.5	268.2	267.3	266.4	265.6	264.7	265.6	266.4	267.3
117.5°	305.2	306.0	306.8	306.7	305.5	304.3	303.2	302.0	303.2	304.3	305.5
120°	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	328.1	329.2	330.4
122.5°	353.9	354.7	355.6	355.3	353.8	352.5	351.1	349.6	351.1	352.5	353.8
125°	389.9	390.4	390.8	390.4	389.1	387.7	386.5	385.1	386.5	387.7	389.1
127.5°	425.9	426.4	427.0	426.3	424.6	423.0	421.3	419.6	421.3	423.0	424.6
130°	449.2	449.5	449.8	449.0	447.1	445.1	443.3	441.3	443.3	445.1	447.1
132.5°	472.9	472.8	472.8	471.9	470.4	468.9	467.3	465.7	467.3	468.9	470.4
135°	506.3	506.0	505.7	504.7	503.1	501.5	499.9	498.3	499.9	501.5	503.1
137.5°	539.5	539.0	538.7	537.8	536.5	535.2	533.9	532.5	533.9	535.2	536.5
140°	561.0	560.3	559.5	558.5	557.1	555.8	554.5	553.2	554.5	555.8	557.1
142.5°	581.6	581.0	580.6	579.6	578.4	577.0	575.7	574.4	575.7	577.0	578.4
145°	611.6	610.7	609.8	608.9	607.9	606.8	605.8	604.8	605.8	606.8	607.9
147.5°	638.9	638.4	637.8	636.9	635.6	634.4	633.1	632.0	633.1	634.4	635.6
150°	655.9	655.3	654.7	654.0	653.1	652.2	651.3	650.4	651.3	652.2	653.1
152.5°	672.6	671.9	671.2	670.4	669.5	668.6	667.7	666.8	667.7	668.6	669.5
155°	694.6	694.1	693.7	693.2	692.8	692.3	691.9	691.4	691.9	692.3	692.8
157.5°	714.5	714.3	714.0	713.7	713.4	713.1	712.8	712.5	712.8	713.1	713.4
160°	726.9	726.7	726.7	726.4	726.1	725.8	725.5	725.2	725.5	725.8	726.1
162.5°	737.5	737.4	737.2	737.1	737.0	737.0	736.9	736.8	736.9	737.0	737.0
165°	751.7	751.7	751.7	751.8	751.9	752.1	752.2	752.3	752.2	752.1	751.9
167.5°	763.2	763.3	763.3	763.6	764.0	764.5	764.9	765.4	764.9	764.5	764.0
170°	769.8	770.0	770.2	770.4	770.9	771.3	771.8	772.2	771.8	771.3	770.9
172.5°	774.6	774.7	774.9	775.2	775.6	776.1	776.5	776.9	776.5	776.1	775.6
175°	780.1	780.3	780.7	781.0	781.5	781.9	782.4	782.7	782.4	781.9	781.5
177.5°	783.0	783.2	783.5	783.7	784.1	784.4	784.8	785.2	784.8	784.4	784.1
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1938.8	1934.9	1927.8	1916.8	1910.3	1898.8	1891.1	1895.5	1896.7	1895.5	1894.4
5°	1886.7	1872.3	1852.5	1833.4	1815.6	1796.4	1785.6	1780.7	1771.2	1765.7	1763.0
7.5°	1823.6	1798.9	1770.9	1737.6	1709.2	1679.6	1664.5	1656.9	1637.4	1626.7	1617.4
10°	1776.6	1737.7	1709.7	1666.0	1639.3	1600.4	1573.7	1574.4	1547.7	1532.7	1521.8
12.5°	1724.7	1681.9	1635.3	1596.0	1559.0	1527.7	1495.5	1482.6	1454.3	1439.8	1410.2
15°	1638.6	1588.8	1539.5	1486.2	1448.7	1400.2	1353.7	1297.0	1251.2	1211.6	1200.6
17.5°	1544.6	1482.8	1433.5	1370.9	1306.5	1224.9	1171.1	1138.2	1110.5	1089.7	1074.1
20°	1480.1	1417.2	1364.6	1270.3	1183.5	1128.2	1088.5	1063.3	1034.6	1012.0	999.7
22.5°	1412.3	1346.7	1275.0	1169.7	1102.1	1057.7	1022.3	993.3	973.8	956.3	945.0
25°	1316.1	1244.3	1126.1	1053.6	999.0	952.5	927.9	910.2	889.7	865.8	854.9
27.5°	1214.4	1100.3	1015.4	961.5	909.4	879.1	857.0	830.5	812.2	801.4	790.1
30°	1138.4	1024.3	958.1	899.3	862.4	828.8	802.9	787.9	770.1	751.6	744.1
32.5°	1053.6	962.5	899.0	850.1	812.6	784.1	763.6	739.2	726.4	715.1	699.3
35°	948.4	879.4	821.4	781.8	746.2	723.0	699.0	684.7	661.5	651.9	645.8
37.5°	859.3	799.5	756.2	714.3	686.2	660.5	645.9	623.0	613.0	599.7	586.7
40°	809.0	750.3	708.6	674.4	643.0	623.8	605.4	587.0	571.9	565.8	550.1
42.5°	757.7	709.8	668.2	630.7	609.7	589.4	566.1	552.5	537.0	527.0	517.3
45°	686.7	644.4	608.9	578.1	554.8	533.7	518.6	496.1	487.2	467.4	459.2
47.5°	624.5	585.1	551.2	521.9	499.3	485.4	463.4	445.8	431.6	419.5	408.9
50°	580.1	547.3	514.5	488.6	468.1	448.3	425.7	416.8	394.9	388.8	382.6
52.5°	539.7	508.5	478.5	453.1	432.6	413.3	393.4	381.8	367.1	361.0	356.4
55°	483.1	453.1	424.4	401.8	381.3	361.5	349.2	334.8	328.0	323.2	317.7
57.5°	426.2	399.2	377.2	354.4	333.8	318.0	303.8	295.2	288.1	281.8	275.3
60°	390.2	364.2	344.4	323.2	302.0	289.0	278.1	267.9	259.7	250.1	247.4
62.5°	351.9	329.2	311.0	290.4	272.0	260.1	249.7	240.0	230.2	216.2	212.4
65°	299.3	281.5	262.4	245.3	228.9	217.3	202.2	191.4	187.3	185.8	185.2
67.5°	251.7	235.0	218.6	201.0	186.1	175.3	167.7	166.0	163.2	162.4	160.4
70°	220.1	204.3	187.9	171.5	157.2	155.2	152.4	149.6	146.2	144.9	143.5
72.5°	191.6	175.3	158.9	145.8	139.6	137.1	134.4	131.6	129.3	128.0	127.1
75°	147.0	131.9	120.9	116.2	112.7	110.7	106.6	104.5	103.2	101.1	100.4
77.5°	105.8	97.3	92.3	89.3	85.7	83.5	81.1	79.1	77.7	77.2	76.2
80°	80.6	76.5	73.1	69.0	67.7	64.9	64.2	62.2	62.9	60.8	60.8
82.5°	62.6	57.4	54.6	52.6	51.3	49.0	48.4	47.4	47.5	46.0	46.0
85°	32.1	30.8	29.4	28.0	28.0	25.9	26.7	25.9	25.9	24.6	23.9
87.5°	11.9	11.9	11.4	12.1	12.8	12.8	12.8	12.1	12.1	12.0	11.5
90°	7.8	10.3	13.5	16.7	19.9	23.2	22.8	22.6	22.3	22.0	21.9
92.5°	16.9	18.0	18.7	19.5	20.2	21.0	21.1	21.1	21.2	21.3	21.3
95°	40.3	41.2	41.5	41.7	42.1	42.4	42.4	42.4	42.4	42.4	42.2
97.5°	68.0	68.9	69.6	70.1	70.6	71.2	71.2	71.2	71.2	71.2	71.2
100°	88.7	89.5	90.0	90.4	90.9	91.3	91.3	91.3	91.3	91.3	91.2
102.5°	110.0	110.8	111.4	111.9	112.4	113.0	113.2	113.2	113.3	113.5	113.5
105°	144.0	144.4	144.7	145.0	145.3	145.6	145.9	146.2	146.4	146.8	146.9
107.5°	181.1	181.5	181.5	181.5	181.5	181.5	181.6	181.6	181.8	181.9	181.6
110°	205.4	205.8	205.8	205.8	205.8	205.8	205.8	205.8	205.8	205.8	205.5



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.8	231.1	231.0	230.9	230.8	230.7	230.3	230.0	229.6	229.3	228.9
115°	268.2	268.5	268.2	267.9	267.6	267.3	267.2	267.1	266.9	266.7	266.4
117.5°	306.7	306.8	306.0	305.2	304.4	303.6	303.3	302.9	302.6	302.2	301.8
120°	331.5	331.5	330.4	329.2	328.1	326.9	326.9	326.9	326.9	326.9	326.6
122.5°	355.3	355.6	354.7	353.9	353.1	352.3	352.0	351.6	351.2	350.9	350.5
125°	390.4	390.8	390.4	389.9	389.5	389.1	388.6	388.2	387.7	387.3	387.0
127.5°	426.3	427.0	426.4	425.9	425.3	424.8	424.3	423.7	423.2	422.7	422.2
130°	449.0	449.8	449.5	449.2	448.9	448.6	448.4	448.1	447.7	447.5	447.0
132.5°	471.9	472.8	472.8	472.9	473.0	473.0	472.3	471.7	471.0	470.4	469.8
135°	504.7	505.7	506.0	506.3	506.6	506.8	506.7	506.6	506.4	506.3	506.0
137.5°	537.8	538.7	539.0	539.5	539.8	540.2	540.1	539.9	539.8	539.8	539.4
140°	558.5	559.5	560.3	561.0	561.7	562.4	562.4	562.4	562.4	562.4	562.1
142.5°	579.6	580.6	581.0	581.6	582.0	582.6	582.6	582.8	582.9	583.0	582.8
145°	608.9	609.8	610.7	611.6	612.5	613.4	613.5	613.7	613.9	613.9	613.8
147.5°	636.9	637.8	638.4	638.9	639.5	640.2	640.4	640.8	641.1	641.4	641.3
150°	654.0	654.7	655.3	655.9	656.5	657.1	657.5	657.9	658.4	658.8	658.8
152.5°	670.4	671.2	671.9	672.6	673.3	674.0	674.6	675.1	675.6	676.3	676.3
155°	693.2	693.7	694.1	694.6	695.0	695.4	696.2	696.9	697.7	698.4	698.6
157.5°	713.7	714.0	714.3	714.5	714.8	715.1	716.0	717.0	718.0	719.0	719.2
160°	726.4	726.7	726.7	726.9	727.0	727.2	728.1	729.0	729.9	730.8	730.8
162.5°	737.1	737.2	737.4	737.5	737.6	737.8	738.8	739.8	740.8	741.8	741.9
165°	751.8	751.7	751.7	751.7	751.7	751.7	752.7	753.8	754.7	755.8	756.0
167.5°	763.6	763.3	763.3	763.2	763.2	763.2	764.2	765.3	766.2	767.3	767.4
170°	770.4	770.2	770.0	769.8	769.7	769.5	770.6	771.6	772.7	773.6	773.7
172.5°	775.2	774.9	774.7	774.6	774.5	774.3	775.3	776.4	777.4	778.5	778.5
175°	781.0	780.7	780.3	780.1	779.8	779.4	780.5	781.5	782.6	783.6	783.6
177.5°	783.7	783.5	783.2	783.0	782.7	782.5	783.2	783.9	784.6	785.3	785.3
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1888.5	1889.5	1887.9	1889.0	1887.9	1889.5	1888.5	1894.4	1895.5	1896.7	1895.5
5°	1759.5	1751.3	1750.0	1747.9	1750.0	1751.3	1759.5	1763.0	1765.7	1771.2	1780.7
7.5°	1605.7	1604.5	1601.1	1596.3	1601.1	1604.5	1605.7	1617.4	1626.7	1637.4	1656.9
10°	1506.7	1503.3	1502.6	1497.8	1502.6	1503.3	1506.7	1521.8	1532.7	1547.7	1574.4
12.5°	1390.8	1368.9	1366.5	1354.6	1366.5	1368.9	1390.8	1410.2	1439.8	1454.3	1482.6
15°	1184.2	1180.1	1166.4	1157.5	1166.4	1180.1	1184.2	1200.6	1211.6	1251.2	1297.0
17.5°	1066.1	1052.8	1048.5	1046.6	1048.5	1052.8	1066.1	1074.1	1089.7	1110.5	1138.2
20°	990.2	977.9	975.8	974.5	975.8	977.9	990.2	999.7	1012.0	1034.6	1063.3
22.5°	937.6	924.8	919.4	915.3	919.4	924.8	937.6	945.0	956.3	973.8	993.3
25°	848.0	843.2	840.5	839.1	840.5	843.2	848.0	854.9	865.8	889.7	910.2
27.5°	777.9	767.4	765.4	761.8	765.4	767.4	777.9	790.1	801.4	812.2	830.5
30°	738.0	734.6	729.8	725.7	729.8	734.6	738.0	744.1	751.6	770.1	787.9
32.5°	691.0	688.1	683.9	682.0	683.9	688.1	691.0	699.3	715.1	726.4	739.2
35°	638.9	629.4	625.3	619.1	625.3	629.4	638.9	645.8	651.9	661.5	684.7
37.5°	583.8	578.8	573.0	575.1	573.0	578.8	583.8	586.7	599.7	613.0	623.0
40°	541.2	537.8	536.5	535.7	536.5	537.8	541.2	550.1	565.8	571.9	587.0
42.5°	507.3	497.8	494.3	494.2	494.3	497.8	507.3	517.3	527.0	537.0	552.5
45°	455.8	446.9	440.8	441.4	440.8	446.9	455.8	459.2	467.4	487.2	496.1
47.5°	403.1	402.8	399.0	400.1	399.0	402.8	403.1	408.9	419.5	431.6	445.8
50°	377.9	373.8	371.0	371.8	371.0	373.8	377.9	382.6	388.8	394.9	416.8
52.5°	353.8	350.3	348.1	351.0	348.1	350.3	353.8	356.4	361.0	367.1	381.8
55°	314.3	310.2	309.5	308.9	309.5	310.2	314.3	317.7	323.2	328.0	334.8
57.5°	270.2	267.4	263.3	261.5	263.3	267.4	270.2	275.3	281.8	288.1	295.2
60°	238.4	233.0	226.1	225.5	226.1	233.0	238.4	247.4	250.1	259.7	267.9
62.5°	209.5	208.4	207.1	206.9	207.1	208.4	209.5	212.4	216.2	230.2	240.0
65°	183.8	183.2	183.8	184.5	183.8	183.2	183.8	185.2	185.8	187.3	191.4
67.5°	160.2	158.9	157.7	158.3	157.7	158.9	160.2	160.4	162.4	163.2	166.0
70°	142.1	141.4	140.8	140.8	140.8	141.4	142.1	143.5	144.9	146.2	149.6
72.5°	124.7	124.5	123.9	123.2	123.9	124.5	124.7	127.1	128.0	129.3	131.6
75°	99.8	98.4	98.4	98.4	98.4	98.4	99.8	100.4	101.1	103.2	104.5
77.5°	76.0	75.3	74.6	74.1	74.6	75.3	76.0	76.2	77.2	77.7	79.1
80°	60.1	59.5	58.8	58.8	58.8	59.5	60.1	60.8	60.8	62.9	62.2
82.5°	45.9	45.2	45.1	44.6	45.1	45.2	45.9	46.0	46.0	47.5	47.4
85°	24.6	25.3	24.6	25.9	24.6	25.3	24.6	23.9	24.6	25.9	25.9
87.5°	11.5	11.0	11.6	11.1	11.6	11.0	11.5	11.5	12.0	12.1	12.1
90°	22.0	22.2	22.4	22.5	22.4	22.2	22.0	21.9	22.0	22.3	22.6
92.5°	21.3	21.4	21.4	21.4	21.4	21.4	21.3	21.3	21.3	21.2	21.1
95°	41.9	41.6	41.3	41.0	41.3	41.6	41.9	42.2	42.4	42.4	42.4
97.5°	71.2	71.2	71.1	71.1	71.1	71.2	71.2	71.2	71.2	71.2	71.2
100°	91.1	91.0	90.8	90.7	90.8	91.0	91.1	91.2	91.3	91.3	91.3
102.5°	113.3	113.2	113.1	112.9	113.1	113.2	113.3	113.5	113.5	113.3	113.2
105°	146.9	146.9	146.9	146.9	146.9	146.9	146.9	146.9	146.8	146.4	146.2
107.5°	180.9	180.3	179.6	179.0	179.6	180.3	180.9	181.6	181.9	181.8	181.6
110°	205.1	204.6	204.2	203.8	204.2	204.6	205.1	205.5	205.8	205.8	205.8



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	228.6	228.3	227.9	227.7	227.9	228.3	228.6	228.9	229.3	229.6	230.0
115°	266.0	265.6	265.1	264.7	265.1	265.6	266.0	266.4	266.7	266.9	267.1
117.5°	301.3	300.9	300.4	300.0	300.4	300.9	301.3	301.8	302.2	302.6	302.9
120°	326.2	325.7	325.3	324.9	325.3	325.7	326.2	326.6	326.9	326.9	326.9
122.5°	350.2	349.9	349.6	349.3	349.6	349.9	350.2	350.5	350.9	351.2	351.6
125°	386.9	386.7	386.6	386.5	386.6	386.7	386.9	387.0	387.3	387.7	388.2
127.5°	421.7	421.2	420.8	420.4	420.8	421.2	421.7	422.2	422.7	423.2	423.7
130°	446.4	445.9	445.2	444.7	445.2	445.9	446.4	447.0	447.5	447.7	448.1
132.5°	469.4	468.9	468.4	468.0	468.4	468.9	469.4	469.8	470.4	471.0	471.7
135°	505.5	505.1	504.6	504.2	504.6	505.1	505.5	506.0	506.3	506.4	506.6
137.5°	538.8	538.2	537.6	537.0	537.6	538.2	538.8	539.4	539.8	539.8	539.9
140°	561.6	561.0	560.4	559.8	560.4	561.0	561.6	562.1	562.4	562.4	562.4
142.5°	582.2	581.6	581.0	580.4	581.0	581.6	582.2	582.8	583.0	582.9	582.8
145°	613.1	612.6	612.0	611.4	612.0	612.6	613.1	613.8	613.9	613.9	613.7
147.5°	640.8	640.2	639.6	639.1	639.6	640.2	640.8	641.3	641.4	641.1	640.8
150°	658.4	657.9	657.5	657.1	657.5	657.9	658.4	658.8	658.8	658.4	657.9
152.5°	675.6	675.1	674.6	674.0	674.6	675.1	675.6	676.3	676.3	675.6	675.1
155°	698.1	697.7	697.2	696.8	697.2	697.7	698.1	698.6	698.4	697.7	696.9
157.5°	718.5	717.7	717.0	716.3	717.0	717.7	718.5	719.2	719.0	718.0	717.0
160°	730.3	729.7	729.2	728.5	729.2	729.7	730.3	730.8	730.8	729.9	729.0
162.5°	741.2	740.6	739.9	739.1	739.9	740.6	741.2	741.9	741.8	740.8	739.8
165°	755.2	754.5	753.8	753.0	753.8	754.5	755.2	756.0	755.8	754.7	753.8
167.5°	766.7	765.9	765.2	764.4	765.2	765.9	766.7	767.4	767.3	766.2	765.3
170°	772.8	772.0	771.1	770.2	771.1	772.0	772.8	773.7	773.6	772.7	771.6
172.5°	777.7	776.8	775.9	775.0	775.9	776.8	777.7	778.5	778.5	777.4	776.4
175°	782.7	781.9	781.0	780.2	781.0	781.9	782.7	783.6	783.6	782.6	781.5
177.5°	784.6	783.9	783.2	782.5	783.2	783.9	784.6	785.3	785.3	784.6	783.9
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1891.1	1898.8	1910.3	1916.8	1927.8	1934.9	1938.8	1945.8	1949.6	1963.4	1977.5
5°	1785.6	1796.4	1815.6	1833.4	1852.5	1872.3	1886.7	1903.1	1918.1	1944.0	1971.4
7.5°	1664.5	1679.6	1709.2	1737.6	1770.9	1798.9	1823.6	1851.6	1876.7	1913.9	1952.7
10°	1573.7	1600.4	1639.3	1666.0	1709.7	1737.7	1776.6	1807.4	1842.3	1891.4	1935.2
12.5°	1495.5	1527.7	1559.0	1596.0	1635.3	1681.9	1724.7	1764.2	1805.6	1856.5	1907.8
15°	1353.7	1400.2	1448.7	1486.2	1539.5	1588.8	1638.6	1691.9	1742.5	1803.3	1870.3
17.5°	1171.1	1224.9	1306.5	1370.9	1433.5	1482.8	1544.6	1609.1	1668.7	1742.0	1816.6
20°	1088.5	1128.2	1183.5	1270.3	1364.6	1417.2	1480.1	1551.1	1619.4	1699.4	1779.4
22.5°	1022.3	1057.7	1102.1	1169.7	1275.0	1346.7	1412.3	1484.4	1563.7	1645.3	1734.0
25°	927.9	952.5	999.0	1053.6	1126.1	1244.3	1316.1	1388.5	1474.6	1562.1	1663.2
27.5°	857.0	879.1	909.4	961.5	1015.4	1100.3	1214.4	1293.4	1379.2	1477.7	1582.6
30°	802.9	828.8	862.4	899.3	958.1	1024.3	1138.4	1230.0	1314.7	1415.9	1527.9
32.5°	763.6	784.1	812.6	850.1	899.0	962.5	1053.6	1164.9	1247.5	1354.1	1471.1
35°	699.0	723.0	746.2	781.8	821.4	879.4	948.4	1067.4	1149.3	1254.5	1372.1
37.5°	645.9	660.5	686.2	714.3	756.2	799.5	859.3	966.0	1054.6	1158.0	1278.3
40°	605.4	623.8	643.0	674.4	708.6	750.3	809.0	888.3	990.2	1091.3	1208.8
42.5°	566.1	589.4	609.7	630.7	668.2	709.8	757.7	824.9	928.9	1024.6	1138.8
45°	518.6	533.7	554.8	578.1	608.9	644.4	686.7	745.5	845.3	927.9	1035.3
47.5°	463.4	485.4	499.3	521.9	551.2	585.1	624.5	675.3	756.0	833.5	933.0
50°	425.7	448.3	468.1	488.6	514.5	547.3	580.1	629.4	694.3	775.6	868.5
52.5°	393.4	413.3	432.6	453.1	478.5	508.5	539.7	582.9	638.5	713.3	803.4
55°	349.2	361.5	381.3	401.8	424.4	453.1	483.1	519.3	567.1	630.0	703.1
57.5°	303.8	318.0	333.8	354.4	377.2	399.2	426.2	459.1	496.8	553.7	616.3
60°	278.1	289.0	302.0	323.2	344.4	364.2	390.2	417.5	453.1	502.2	555.5
62.5°	249.7	260.1	272.0	290.4	311.0	329.2	351.9	380.8	411.0	455.8	502.5
65°	202.2	217.3	228.9	245.3	262.4	281.5	299.3	322.5	349.2	384.7	426.4
67.5°	167.7	175.3	186.1	201.0	218.6	235.0	251.7	269.9	293.0	320.5	353.6
70°	152.4	155.2	157.2	171.5	187.9	204.3	220.1	237.1	256.9	279.5	308.2
72.5°	134.4	137.1	139.6	145.8	158.9	175.3	191.6	204.3	223.0	241.7	265.0
75°	106.6	110.7	112.7	116.2	120.9	131.9	147.0	159.2	170.1	184.5	203.0
77.5°	81.1	83.5	85.7	89.3	92.3	97.3	105.8	116.8	127.1	135.5	148.1
80°	64.2	64.9	67.7	69.0	73.1	76.5	80.6	89.5	99.8	103.2	112.1
82.5°	48.4	49.0	51.3	52.6	54.6	57.4	62.6	64.9	72.9	77.5	83.1
85°	26.7	25.9	28.0	28.0	29.4	30.8	32.1	35.5	37.5	43.1	44.4
87.5°	12.8	12.8	12.8	12.1	11.4	11.9	11.9	12.1	12.8	14.2	16.0
90°	22.8	23.2	19.9	16.7	13.5	10.3	7.8	6.0	4.2	2.4	0.6
92.5°	21.1	21.0	20.2	19.5	18.7	18.0	16.9	15.7	14.4	13.1	11.8
95°	42.4	42.4	42.1	41.7	41.5	41.2	40.3	38.8	37.4	35.8	34.4
97.5°	71.2	71.2	70.6	70.1	69.6	68.9	68.0	66.7	65.5	64.1	62.9
100°	91.3	91.3	90.9	90.4	90.0	89.5	88.7	87.6	86.4	85.2	84.0
102.5°	113.2	113.0	112.4	111.9	111.4	110.8	110.0	109.1	108.2	107.2	106.3
105°	145.9	145.6	145.3	145.0	144.7	144.4	144.0	143.6	143.1	142.7	142.2
107.5°	181.6	181.5	181.5	181.5	181.5	181.5	181.1	180.5	179.9	179.1	178.5
110°	205.8	205.8	205.8	205.8	205.8	205.8	205.4	204.5	203.6	202.7	201.8



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	230.3	230.7	230.8	230.9	231.0	231.1	230.8	229.9	229.0	228.1	227.2
115°	267.2	267.3	267.6	267.9	268.2	268.5	268.2	267.3	266.4	265.6	264.7
117.5°	303.3	303.6	304.4	305.2	306.0	306.8	306.7	305.5	304.3	303.2	302.0
120°	326.9	326.9	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9
122.5°	352.0	352.3	353.1	353.9	354.7	355.6	355.3	353.8	352.5	351.1	349.6
125°	388.6	389.1	389.5	389.9	390.4	390.8	390.4	389.1	387.7	386.5	385.1
127.5°	424.3	424.8	425.3	425.9	426.4	427.0	426.3	424.6	423.0	421.3	419.6
130°	448.4	448.6	448.9	449.2	449.5	449.8	449.0	447.1	445.1	443.3	441.3
132.5°	472.3	473.0	473.0	472.9	472.8	472.8	471.9	470.4	468.9	467.3	465.7
135°	506.7	506.8	506.6	506.3	506.0	505.7	504.7	503.1	501.5	499.9	498.3
137.5°	540.1	540.2	539.8	539.5	539.0	538.7	537.8	536.5	535.2	533.9	532.5
140°	562.4	562.4	561.7	561.0	560.3	559.5	558.5	557.1	555.8	554.5	553.2
142.5°	582.6	582.6	582.0	581.6	581.0	580.6	579.6	578.4	577.0	575.7	574.4
145°	613.5	613.4	612.5	611.6	610.7	609.8	608.9	607.9	606.8	605.8	604.8
147.5°	640.4	640.2	639.5	638.9	638.4	637.8	636.9	635.6	634.4	633.1	632.0
150°	657.5	657.1	656.5	655.9	655.3	654.7	654.0	653.1	652.2	651.3	650.4
152.5°	674.6	674.0	673.3	672.6	671.9	671.2	670.4	669.5	668.6	667.7	666.8
155°	696.2	695.4	695.0	694.6	694.1	693.7	693.2	692.8	692.3	691.9	691.4
157.5°	716.0	715.1	714.8	714.5	714.3	714.0	713.7	713.4	713.1	712.8	712.5
160°	728.1	727.2	727.0	726.9	726.7	726.7	726.4	726.1	725.8	725.5	725.2
162.5°	738.8	737.8	737.6	737.5	737.4	737.2	737.1	737.0	737.0	736.9	736.8
165°	752.7	751.7	751.7	751.7	751.7	751.7	751.8	751.9	752.1	752.2	752.3
167.5°	764.2	763.2	763.2	763.2	763.3	763.3	763.6	764.0	764.5	764.9	765.4
170°	770.6	769.5	769.7	769.8	770.0	770.2	770.4	770.9	771.3	771.8	772.2
172.5°	775.3	774.3	774.5	774.6	774.7	774.9	775.2	775.6	776.1	776.5	776.9
175°	780.5	779.4	779.8	780.1	780.3	780.7	781.0	781.5	781.9	782.4	782.7
177.5°	783.2	782.5	782.7	783.0	783.2	783.5	783.7	784.1	784.4	784.8	785.2
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1978.1	1979.7	1990.7	1995.6	2005.5	2009.2	2013.7	2012.5	2012.5	2014.7	2030.0
5°	1982.4	1996.0	2016.5	2036.3	2055.5	2071.8	2082.8	2093.7	2097.8	2117.6	2135.4
7.5°	1975.2	2000.4	2034.3	2064.5	2100.7	2129.0	2152.5	2173.6	2188.2	2217.0	2246.5
10°	1966.0	2001.4	2039.7	2078.7	2128.5	2166.1	2204.4	2233.8	2243.4	2286.4	2311.0
12.5°	1947.3	1994.9	2043.5	2094.0	2142.8	2194.6	2236.7	2266.0	2299.6	2338.3	2383.7
15°	1919.5	1974.2	2037.6	2102.6	2172.3	2235.2	2280.3	2331.5	2368.4	2410.7	2450.4
17.5°	1879.5	1949.8	2030.6	2105.8	2186.4	2253.9	2316.0	2365.1	2391.1	2415.3	2421.2
20°	1847.7	1923.6	2018.6	2107.4	2188.0	2265.9	2327.4	2368.4	2375.3	2375.9	2339.7
22.5°	1813.3	1899.0	1998.3	2089.4	2185.9	2272.4	2320.3	2337.8	2310.7	2264.4	2194.3
25°	1750.0	1849.1	1964.5	2068.4	2173.6	2255.7	2272.1	2241.3	2146.3	2046.6	1920.1
27.5°	1681.4	1792.8	1916.6	2032.0	2144.1	2194.9	2159.5	2048.7	1877.7	1728.9	1548.7
30°	1631.1	1756.1	1877.8	2006.9	2110.8	2132.6	2051.4	1888.0	1688.5	1464.4	1284.7
32.5°	1573.7	1704.8	1838.4	1971.9	2058.9	2037.6	1903.2	1702.2	1468.2	1247.9	1078.0
35°	1491.7	1627.0	1771.2	1905.1	1960.4	1868.2	1667.3	1405.6	1166.4	960.7	843.9
37.5°	1397.0	1544.4	1694.3	1817.2	1813.3	1659.6	1385.9	1115.7	914.7	793.1	709.8
40°	1329.7	1478.7	1640.7	1744.5	1700.1	1499.9	1203.4	948.4	801.6	704.5	643.7
42.5°	1265.2	1414.8	1575.7	1658.1	1580.9	1334.8	1039.4	839.6	718.5	642.7	593.4
45°	1155.5	1313.3	1462.3	1508.1	1370.0	1098.8	840.5	695.6	615.0	558.9	524.8
47.5°	1048.2	1203.5	1339.4	1340.2	1153.6	891.1	709.0	602.0	533.2	489.8	464.9
50°	982.6	1130.2	1244.3	1226.5	1014.8	792.6	634.1	541.9	484.5	451.0	425.0
52.5°	908.8	1052.0	1150.8	1100.3	897.2	697.5	566.9	489.4	441.8	412.7	389.5
55°	801.6	928.6	998.4	921.8	731.8	580.1	479.0	418.2	382.6	358.0	338.2
57.5°	696.2	801.0	844.9	755.7	602.8	481.1	405.2	359.5	324.3	306.7	296.4
60°	630.0	719.5	750.3	651.9	524.1	420.9	358.7	316.4	290.4	278.8	268.6
62.5°	565.0	638.1	650.8	560.6	456.9	368.5	315.0	279.2	262.0	250.9	241.2
65°	468.8	521.4	515.2	442.8	361.5	292.5	253.5	231.7	218.6	203.0	185.8
67.5°	385.9	418.0	398.7	344.4	275.9	227.3	201.9	185.3	169.2	154.3	150.3
70°	333.5	351.9	331.4	281.5	226.1	190.6	170.1	150.3	140.8	137.3	131.2
72.5°	283.2	289.6	267.4	224.7	184.0	157.8	137.9	126.8	121.6	118.8	114.8
75°	212.5	207.8	188.6	155.2	127.8	110.0	103.9	99.8	96.3	93.6	91.6
77.5°	149.3	142.2	125.2	103.3	89.0	80.5	76.8	74.6	72.9	71.6	69.6
80°	112.1	107.3	90.2	73.8	67.7	63.6	61.5	58.8	58.8	57.4	55.4
82.5°	82.0	76.7	61.8	54.1	50.7	48.2	46.7	45.1	44.6	44.9	43.3
85°	43.1	34.9	30.8	29.4	27.4	25.9	26.7	25.3	25.3	25.3	24.6
87.5°	13.6	11.2	11.1	10.9	11.9	12.6	12.7	13.3	14.4	13.9	14.4
90°	2.4	4.2	6.0	7.8	10.3	13.5	16.7	19.9	23.2	22.8	22.6
92.5°	13.1	14.4	15.7	16.9	18.0	18.7	19.5	20.2	21.0	21.1	21.1
95°	35.8	37.4	38.8	40.3	41.2	41.5	41.7	42.1	42.4	42.4	42.4
97.5°	64.1	65.5	66.7	68.0	68.9	69.6	70.1	70.6	71.2	71.2	71.2
100°	85.2	86.4	87.6	88.7	89.5	90.0	90.4	90.9	91.3	91.3	91.3
102.5°	107.2	108.2	109.1	110.0	110.8	111.4	111.9	112.4	113.0	113.2	113.2
105°	142.7	143.1	143.6	144.0	144.4	144.7	145.0	145.3	145.6	145.9	146.2
107.5°	179.1	179.9	180.5	181.1	181.5	181.5	181.5	181.5	181.5	181.6	181.6
110°	202.7	203.6	204.5	205.4	205.8	205.8	205.8	205.8	205.8	205.8	205.8





TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	228.1	229.0	229.9	230.8	231.1	231.0	230.9	230.8	230.7	230.3	230.0
115°	265.6	266.4	267.3	268.2	268.5	268.2	267.9	267.6	267.3	267.2	267.1
117.5°	303.2	304.3	305.5	306.7	306.8	306.0	305.2	304.4	303.6	303.3	302.9
120°	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	326.9	326.9
122.5°	351.1	352.5	353.8	355.3	355.6	354.7	353.9	353.1	352.3	352.0	351.6
125°	386.5	387.7	389.1	390.4	390.8	390.4	389.9	389.5	389.1	388.6	388.2
127.5°	421.3	423.0	424.6	426.3	427.0	426.4	425.9	425.3	424.8	424.3	423.7
130°	443.3	445.1	447.1	449.0	449.8	449.5	449.2	448.9	448.6	448.4	448.1
132.5°	467.3	468.9	470.4	471.9	472.8	472.8	472.9	473.0	473.0	472.3	471.7
135°	499.9	501.5	503.1	504.7	505.7	506.0	506.3	506.6	506.8	506.7	506.6
137.5°	533.9	535.2	536.5	537.8	538.7	539.0	539.5	539.8	540.2	540.1	539.9
140°	554.5	555.8	557.1	558.5	559.5	560.3	561.0	561.7	562.4	562.4	562.4
142.5°	575.7	577.0	578.4	579.6	580.6	581.0	581.6	582.0	582.6	582.6	582.8
145°	605.8	606.8	607.9	608.9	609.8	610.7	611.6	612.5	613.4	613.5	613.7
147.5°	633.1	634.4	635.6	636.9	637.8	638.4	638.9	639.5	640.2	640.4	640.8
150°	651.3	652.2	653.1	654.0	654.7	655.3	655.9	656.5	657.1	657.5	657.9
152.5°	667.7	668.6	669.5	670.4	671.2	671.9	672.6	673.3	674.0	674.6	675.1
155°	691.9	692.3	692.8	693.2	693.7	694.1	694.6	695.0	695.4	696.2	696.9
157.5°	712.8	713.1	713.4	713.7	714.0	714.3	714.5	714.8	715.1	716.0	717.0
160°	725.5	725.8	726.1	726.4	726.7	726.7	726.9	727.0	727.2	728.1	729.0
162.5°	736.9	737.0	737.0	737.1	737.2	737.4	737.5	737.6	737.8	738.8	739.8
165°	752.2	752.1	751.9	751.8	751.7	751.7	751.7	751.7	751.7	752.7	753.8
167.5°	764.9	764.5	764.0	763.6	763.3	763.3	763.2	763.2	763.2	764.2	765.3
170°	771.8	771.3	770.9	770.4	770.2	770.0	769.8	769.7	769.5	770.6	771.6
172.5°	776.5	776.1	775.6	775.2	774.9	774.7	774.6	774.5	774.3	775.3	776.4
175°	782.4	781.9	781.5	781.0	780.7	780.3	780.1	779.8	779.4	780.5	781.5
177.5°	784.8	784.4	784.1	783.7	783.5	783.2	783.0	782.7	782.5	783.2	783.9
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2035.5	2042.6	2045.9	2045.9	2049.7	2048.1	2046.4
5°	2152.5	2165.4	2168.2	2180.5	2189.3	2186.7	2188.0
7.5°	2268.8	2289.6	2310.3	2319.8	2321.2	2326.7	2328.8
10°	2340.4	2357.5	2389.6	2384.8	2408.7	2422.4	2399.9
12.5°	2409.2	2432.3	2454.6	2460.8	2474.3	2478.7	2469.8
15°	2471.6	2483.9	2485.3	2481.8	2485.9	2482.5	2469.5
17.5°	2413.3	2393.4	2353.0	2333.8	2318.6	2296.2	2287.2
20°	2317.1	2258.3	2190.0	2162.8	2130.6	2067.7	2082.8
22.5°	2109.4	2042.5	1974.2	1894.4	1856.2	1796.6	1793.1
25°	1786.2	1670.7	1543.6	1454.8	1402.8	1343.5	1317.4
27.5°	1388.8	1243.4	1139.2	1086.5	1038.5	991.4	989.4
30°	1127.5	1018.2	937.5	892.4	863.0	843.2	847.3
32.5°	950.4	875.5	821.1	783.6	761.9	747.0	746.7
35°	776.9	725.7	690.8	675.1	659.4	648.5	649.2
37.5°	664.9	634.1	614.7	597.4	587.5	582.2	579.2
40°	607.4	582.2	567.1	556.9	548.7	541.2	539.8
42.5°	562.1	541.2	526.2	518.1	510.4	505.2	503.7
45°	498.8	481.7	468.1	459.2	455.8	451.0	451.0
47.5°	443.7	427.0	416.3	410.7	404.8	401.6	401.5
50°	406.6	393.6	384.1	380.6	375.9	373.8	373.1
52.5°	373.3	363.6	356.7	354.4	352.3	349.7	350.2
55°	328.0	322.5	319.8	317.7	314.3	310.2	313.0
57.5°	289.9	285.3	277.9	271.4	268.3	265.4	266.5
60°	263.1	253.5	244.0	236.4	234.3	228.2	228.2
62.5°	229.2	215.8	204.0	199.8	197.8	194.9	194.3
65°	176.3	170.9	168.1	165.3	164.0	164.0	162.6
67.5°	146.1	143.9	140.9	140.2	138.8	138.5	138.0
70°	129.1	126.4	125.0	124.4	123.0	123.7	121.6
72.5°	112.7	110.6	110.3	108.5	107.7	107.8	106.3
75°	88.8	88.8	88.2	87.5	86.1	85.4	86.1
77.5°	68.3	68.5	67.2	67.1	67.0	67.1	66.4
80°	54.7	55.4	54.7	53.9	53.3	53.9	53.3
82.5°	43.2	42.3	42.1	42.0	41.8	41.4	41.3
85°	24.6	25.3	24.6	23.9	23.9	23.9	24.6
87.5°	13.7	13.7	13.6	13.7	13.7	13.7	13.3
90°	22.3	22.0	21.9	22.0	22.2	22.4	22.5
92.5°	21.2	21.3	21.3	21.3	21.4	21.4	21.4
95°	42.4	42.4	42.2	41.9	41.6	41.3	41.0
97.5°	71.2	71.2	71.2	71.2	71.2	71.1	71.1
100°	91.3	91.3	91.2	91.1	91.0	90.8	90.7
102.5°	113.3	113.5	113.5	113.3	113.2	113.1	112.9
105°	146.4	146.8	146.9	146.9	146.9	146.9	146.9
107.5°	181.8	181.9	181.6	180.9	180.3	179.6	179.0
110°	205.8	205.8	205.5	205.1	204.6	204.2	203.8



TEST NUMBER: P331850-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	229.6	229.3	228.9	228.6	228.3	227.9	227.7
115°	266.9	266.7	266.4	266.0	265.6	265.1	264.7
117.5°	302.6	302.2	301.8	301.3	300.9	300.4	300.0
120°	326.9	326.9	326.6	326.2	325.7	325.3	324.9
122.5°	351.2	350.9	350.5	350.2	349.9	349.6	349.3
125°	387.7	387.3	387.0	386.9	386.7	386.6	386.5
127.5°	423.2	422.7	422.2	421.7	421.2	420.8	420.4
130°	447.7	447.5	447.0	446.4	445.9	445.2	444.7
132.5°	471.0	470.4	469.8	469.4	468.9	468.4	468.0
135°	506.4	506.3	506.0	505.5	505.1	504.6	504.2
137.5°	539.8	539.8	539.4	538.8	538.2	537.6	537.0
140°	562.4	562.4	562.1	561.6	561.0	560.4	559.8
142.5°	582.9	583.0	582.8	582.2	581.6	581.0	580.4
145°	613.9	613.9	613.8	613.1	612.6	612.0	611.4
147.5°	641.1	641.4	641.3	640.8	640.2	639.6	639.1
150°	658.4	658.8	658.8	658.4	657.9	657.5	657.1
152.5°	675.6	676.3	676.3	675.6	675.1	674.6	674.0
155°	697.7	698.4	698.6	698.1	697.7	697.2	696.8
157.5°	718.0	719.0	719.2	718.5	717.7	717.0	716.3
160°	729.9	730.8	730.8	730.3	729.7	729.2	728.5
162.5°	740.8	741.8	741.9	741.2	740.6	739.9	739.1
165°	754.7	755.8	756.0	755.2	754.5	753.8	753.0
167.5°	766.2	767.3	767.4	766.7	765.9	765.2	764.4
170°	772.7	773.6	773.7	772.8	772.0	771.1	770.2
172.5°	777.4	778.5	778.5	777.7	776.8	775.9	775.0
175°	782.6	783.6	783.6	782.7	781.9	781.0	780.2
177.5°	784.6	785.3	785.3	784.6	783.9	783.2	782.5
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1

(END OF REPORT)