

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332095-930

Luminaire Tested: **S123DIW-S340D460U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332095-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D460U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2454.2 lumens  
Efficiency: N/A  
Efficacy: 106.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45				39	
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38				33	
3	81	71	64	58	74	66	59	54	55	50	46	46	42	39	37	34	32				28	
4	74	63	55	49	67	58	51	46	49	44	40	41	37	33	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24				21	
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	27	24	21				18	
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19				16	
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17				14	
9	50	37	30	25	46	35	28	24	30	24	21	25	21	18	21	17	15				13	
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14				12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.6	1.7
10°-20°	117.5	4.8
20°-30°	173.6	7.1
30°-40°	202.8	8.3
40°-50°	203.9	8.3
50°-60°	179.1	7.3
60°-70°	133.4	5.4
70°-80°	76.0	3.1
80°-90°	23.2	0.9
90°-100°	30.6	1.2
100°-110°	91.7	3.7
110°-120°	156.0	6.4
120°-130°	205.2	8.4
130°-140°	230.6	9.4
140°-150°	226.7	9.2
150°-160°	190.8	7.8
160°-170°	127.0	5.2
170°-180°	44.5	1.8
0°-30°	332.7	13.6
0°-40°	535.5	21.8
0°-60°	918.4	37.4
0°-90°	1151.0	46.9
90°-120°	278.3	11.3
90°-150°	940.8	38.3
90°-180°	1303.0	53.1
0°-180°	2454.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	0	4	9	10	11	2
95°	22	24	27	29	29	24
105°	83	84	87	87	88	89
115°	157	158	157	158	157	155
125°	230	231	230	229	227	205
135°	298	300	300	299	298	230
145°	362	362	364	363	362	226
155°	414	414	415	416	413	191
165°	451	450	450	452	450	127
175°	469	468	468	470	467	45
180°	470	470	470	470	470	



TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.0	7.9	7.9	7.8	7.8	7.9	8.0	8.2	8.3	8.5	8.5
90°	0.4	1.2	2.0	2.9	3.7	4.6	5.6	6.8	7.8	8.9	9.2
92.5°	9.0	9.5	10.0	10.6	11.2	11.7	12.4	13.0	13.6	14.2	14.4
95°	21.8	22.3	22.9	23.6	24.1	24.7	25.4	26.0	26.7	27.3	27.6
97.5°	38.7	39.1	39.5	40.0	40.4	40.8	41.3	41.8	42.3	42.8	43.1
100°	50.2	50.7	51.2	51.7	52.2	52.7	53.1	53.5	53.9	54.3	54.5
102.5°	63.5	63.8	64.2	64.4	64.7	65.1	65.7	66.2	66.8	67.3	67.6
105°	83.2	83.3	83.5	83.6	83.8	84.2	85.0	85.7	86.4	87.2	87.2
107.5°	105.9	106.0	106.1	106.2	106.3	106.5	106.8	107.0	107.4	107.7	107.9
110°	120.1	120.3	120.4	120.6	120.7	120.9	121.1	121.2	121.4	121.6	121.9



TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.9	134.9	135.1	135.2	135.3	135.3	135.3	135.4	135.4	135.4	135.8
115°	157.0	157.3	157.5	157.8	158.0	158.1	157.9	157.8	157.6	157.4	157.5
117.5°	179.4	179.5	179.7	179.9	180.0	179.9	179.8	179.5	179.4	179.1	179.1
120°	193.2	193.7	194.2	194.7	195.2	195.3	194.9	194.4	194.0	193.6	193.6
122.5°	207.7	208.1	208.5	208.8	209.1	209.2	209.0	208.8	208.6	208.4	208.1
125°	229.8	230.1	230.3	230.6	230.8	230.8	230.6	230.5	230.3	230.2	229.8
127.5°	250.2	250.7	251.3	251.8	252.3	252.5	252.3	252.1	251.9	251.8	251.3
130°	263.8	264.5	265.1	265.8	266.4	266.6	266.4	266.1	265.9	265.6	265.3
132.5°	277.4	278.0	278.8	279.4	280.1	280.3	280.1	279.9	279.7	279.6	279.2
135°	298.2	298.6	299.1	299.6	300.1	300.4	300.3	300.2	300.1	300.0	299.7
137.5°	317.4	317.8	318.2	318.6	319.0	319.4	319.5	319.8	320.0	320.2	319.8
140°	330.7	331.1	331.5	331.9	332.3	332.6	332.6	332.7	332.8	332.9	332.8
142.5°	342.8	343.2	343.6	344.1	344.5	344.7	344.9	345.0	345.2	345.3	345.2
145°	361.7	361.9	362.1	362.2	362.4	362.6	362.8	363.1	363.3	363.5	363.5
147.5°	378.3	378.5	378.9	379.1	379.4	379.7	379.9	380.2	380.4	380.7	380.7
150°	389.8	390.0	390.1	390.3	390.4	390.6	390.8	390.9	391.1	391.3	391.3
152.5°	399.3	399.5	399.7	399.9	400.1	400.3	400.4	400.6	400.6	400.7	400.9
155°	414.2	414.2	414.2	414.2	414.2	414.3	414.3	414.4	414.5	414.6	414.9
157.5°	426.9	426.8	426.7	426.6	426.5	426.5	426.6	426.6	426.6	426.7	427.1
160°	434.9	434.7	434.6	434.4	434.2	434.1	434.1	434.1	434.1	434.1	434.6
162.5°	442.0	441.7	441.5	441.2	441.1	441.0	441.0	441.1	441.2	441.2	441.6
165°	451.1	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.5
167.5°	458.4	458.1	457.8	457.5	457.1	457.0	457.1	457.1	457.2	457.2	457.8
170°	462.6	462.3	461.9	461.6	461.3	461.1	461.1	461.1	461.1	461.1	461.7
172.5°	465.9	465.5	465.2	464.9	464.5	464.3	464.3	464.3	464.3	464.3	464.9
175°	469.2	468.9	468.6	468.2	467.9	467.7	467.7	467.7	467.7	467.7	468.2
177.5°	470.7	470.3	470.1	469.9	469.6	469.4	469.4	469.4	469.4	469.4	469.9
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3



TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	8.5	8.5	8.5	8.5	8.5	8.6	8.6	8.6
90°	9.5	9.9	10.2	10.4	10.6	10.8	10.9	11.1
92.5°	14.7	15.0	15.2	15.3	15.2	15.1	15.0	14.9
95°	28.0	28.3	28.6	28.8	28.8	28.8	28.8	28.8
97.5°	43.5	43.9	44.3	44.4	44.4	44.4	44.4	44.4
100°	54.8	55.0	55.3	55.5	55.7	55.8	56.0	56.2
102.5°	67.8	68.1	68.3	68.4	68.4	68.3	68.3	68.2
105°	87.2	87.2	87.2	87.2	87.5	87.6	87.8	88.0
107.5°	108.2	108.4	108.7	108.8	108.7	108.6	108.5	108.4
110°	122.2	122.5	122.9	122.9	122.8	122.6	122.5	122.3





TEST NUMBER: P332095-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	136.2	136.6	137.1	137.2	137.1	137.1	137.1	137.1
115°	157.6	157.7	157.8	157.8	157.7	157.6	157.5	157.4
117.5°	179.1	179.0	179.0	179.0	178.7	178.5	178.2	178.0
120°	193.5	193.4	193.3	193.1	193.0	192.8	192.7	192.5
122.5°	208.0	207.7	207.5	207.3	207.1	206.8	206.6	206.4
125°	229.5	229.2	228.9	228.5	228.2	227.9	227.6	227.2
127.5°	250.9	250.4	249.9	249.5	249.2	248.7	248.3	248.0
130°	265.0	264.6	264.3	263.9	263.3	262.8	262.2	261.5
132.5°	278.8	278.3	277.9	277.5	277.1	276.6	276.2	275.7
135°	299.4	299.1	298.7	298.5	298.3	298.2	298.0	297.8
137.5°	319.5	319.2	318.8	318.5	318.1	317.9	317.6	317.2
140°	332.7	332.6	332.6	332.2	331.7	331.1	330.5	330.0
142.5°	345.1	345.0	345.0	344.7	344.3	343.8	343.4	342.9
145°	363.4	363.3	363.2	363.1	362.7	362.4	362.1	361.7
147.5°	380.7	380.7	380.7	380.4	379.9	379.4	378.9	378.4
150°	391.3	391.3	391.3	391.0	390.5	390.0	389.6	389.1
152.5°	401.0	401.1	401.3	401.1	400.7	400.2	399.8	399.4
155°	415.2	415.6	415.9	415.7	415.2	414.6	414.0	413.4
157.5°	427.5	427.8	428.1	428.0	427.6	427.1	426.6	426.2
160°	435.0	435.4	435.8	435.8	435.5	435.1	434.8	434.5
162.5°	442.1	442.5	442.9	442.8	442.3	441.7	441.2	440.7
165°	451.0	451.5	452.0	451.9	451.3	450.8	450.2	449.6
167.5°	458.3	458.8	459.3	459.3	458.8	458.3	457.8	457.2
170°	462.3	462.8	463.4	463.4	462.8	462.3	461.7	461.1
172.5°	465.4	465.9	466.4	466.4	465.8	465.2	464.6	464.1
175°	468.7	469.2	469.7	469.7	469.1	468.6	468.0	467.4
177.5°	470.3	470.7	471.0	471.0	470.5	470.1	469.6	469.1
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3

(END OF REPORT)