

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332101-930

Luminaire Tested: **S123DIW-S340D755U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332101-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3286.3 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332101-930
CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332101-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P332101-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.3
10°-20°	117.5	3.6
20°-30°	173.6	5.3
30°-40°	202.8	6.2
40°-50°	203.9	6.2
50°-60°	179.1	5.4
60°-70°	133.4	4.1
70°-80°	76.0	2.3
80°-90°	24.1	0.7
90°-100°	50.2	1.5
100°-110°	150.2	4.6
110°-120°	255.5	7.8
120°-130°	336.1	10.2
130°-140°	377.7	11.5
140°-150°	371.3	11.3
150°-160°	312.6	9.5
160°-170°	208.1	6.3
170°-180°	72.9	2.2
0°-30°	332.7	10.1
0°-40°	535.5	16.3
0°-60°	918.4	27.9
0°-90°	1151.9	35.1
90°-120°	455.9	13.9
90°-150°	1540.9	46.9
90°-180°	2134.0	64.9
0°-180°	3286.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	1	7	14	17	18	3
95°	36	40	45	47	47	40
105°	136	138	143	143	144	146
115°	257	259	258	258	258	254
125°	376	378	377	375	372	336
135°	488	492	491	489	488	376
145°	592	594	596	595	592	370
155°	678	678	679	681	677	312
165°	739	737	737	740	736	208
175°	768	766	766	769	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332101-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.0	8.1	8.2	8.2	8.3	8.5	8.7	9.0	9.3	9.6	9.6
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1
92.5°	14.7	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6
95°	35.7	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3
97.5°	63.4	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7
100°	82.3	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4
102.5°	104.1	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6
105°	136.2	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8
107.5°	173.4	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8
110°	196.7	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7



TEST NUMBER: P332101-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.9	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5
115°	257.2	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0
117.5°	293.8	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3
120°	316.5	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0
122.5°	340.2	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0
125°	376.4	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5
127.5°	409.8	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6
130°	432.1	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6
132.5°	454.4	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2
135°	488.4	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8
137.5°	519.8	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8
140°	541.6	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.5	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4
145°	592.5	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3
147.5°	619.5	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5
150°	638.5	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8
152.5°	654.0	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6
155°	678.4	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6
157.5°	699.2	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5
160°	712.2	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8
162.5°	723.9	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3
165°	738.9	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8
167.5°	750.9	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7
170°	757.7	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2
172.5°	763.0	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4
175°	768.5	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0
177.5°	770.9	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332101-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	9.7	9.7	9.8	9.8	9.9	9.9	9.9	10.0
90°	15.6	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.1	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	45.8	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.3	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	89.8	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.0	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.2	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.2	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332101-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	223.1	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.8	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.6	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.9	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.8	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	434.1	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	456.6	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	490.3	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	523.3	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.3	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.2	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	656.8	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.0	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.1	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	712.4	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.0	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	738.7	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	762.2	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	767.8	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.2	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)