

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331783-940

Luminaire Tested: **S122RDIW-S290D1440U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331783-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1440U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6061.2 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	99	99	99	99	87	87	87	87	64	64	64	43	43	43	24	24	24	15																				
1	90	86	82	79	79	76	73	70	56	54	52	38	37	36	22	21	21	13																				
2	82	75	70	65	72	66	62	58	49	46	44	34	32	30	19	18	18	11																				
3	75	66	59	54	65	58	53	48	43	40	37	30	28	26	17	16	15	10																				
4	68	58	51	46	60	52	45	41	39	34	31	27	24	22	15	14	13	8																				
5	63	52	44	39	55	46	40	35	34	30	27	24	21	19	14	12	11	7																				
6	58	46	39	33	50	41	35	30	31	27	23	21	19	17	13	11	10	7																				
7	53	42	34	29	47	37	31	26	28	24	20	19	17	15	11	10	9	6																				
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	10	9	8	5																				
9	46	34	27	22	40	30	24	20	23	19	16	16	13	12	10	8	7	5																				
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	0.7
10°-20°	115.0	1.9
20°-30°	161.6	2.7
30°-40°	176.2	2.9
40°-50°	162.0	2.7
50°-60°	127.2	2.1
60°-70°	82.9	1.4
70°-80°	42.8	0.7
80°-90°	15.4	0.3
90°-100°	58.5	1.0
100°-110°	214.4	3.5
110°-120°	573.1	9.5
120°-130°	946.0	15.6
130°-140°	1006.1	16.6
140°-150°	935.1	15.4
150°-160°	751.8	12.4
160°-170°	484.5	8.0
170°-180°	166.8	2.8
0°-30°	318.5	5.3
0°-40°	494.7	8.2
0°-60°	783.8	12.9
0°-90°	924.9	15.3
90°-120°	846.0	14.0
90°-150°	3733.2	61.6
90°-180°	5136.0	84.7
0°-180°	6061.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	1	15	25	32	34	5
95°	82	43	50	55	55	101
105°	386	402	77	91	96	412
115°	729	751	782	223	104	718
125°	1031	1048	1072	1080	1084	919
135°	1276	1296	1308	1319	1318	985
145°	1480	1480	1500	1508	1503	925
155°	1630	1620	1633	1640	1631	751
165°	1717	1710	1713	1721	1713	485
175°	1756	1748	1750	1758	1746	167
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.4	5.4	5.5	5.5	5.6	5.9	6.3	6.8	7.2	7.7	7.8
90°	1.2	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8
92.5°	25.6	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1
95°	82.4	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8
97.5°	163.6	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3
100°	224.4	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5
102.5°	291.4	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2
105°	385.6	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4
107.5°	492.8	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1
110°	561.9	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8



TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.8	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0
115°	729.2	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0
117.5°	820.8	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2
120°	887.8	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0
122.5°	944.6	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5
125°	1031.1	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6
127.5°	1109.5	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6
130°	1159.1	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5
132.5°	1209.9	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8
135°	1275.9	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4
137.5°	1342.6	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4
140°	1386.2	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8
142.5°	1422.7	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1
145°	1480.1	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3
147.5°	1530.0	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9
150°	1562.5	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6
152.5°	1589.8	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9
155°	1629.7	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1
157.5°	1660.9	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8
160°	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8
162.5°	1695.3	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3
165°	1717.2	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4
167.5°	1733.4	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3
170°	1742.6	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5
172.5°	1748.6	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5
175°	1756.5	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1
177.5°	1757.7	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	8.1	8.3	8.5	8.6	8.7	8.9	9.0	9.1
90°	28.2	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	30.9	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	52.3	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	68.5	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	76.8	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	80.2	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	83.6	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	102.0	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	165.6	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331783-940

CATALOG NUMBER: S122RDIW-S290D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	354.2	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	521.6	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	803.6	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	936.4	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	993.5	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1075.6	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1151.5	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1199.6	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1246.3	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1313.1	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1375.2	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1415.3	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1452.4	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1504.2	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1549.4	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1577.3	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1602.6	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1636.8	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1665.7	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1682.5	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1698.2	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1733.3	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1741.4	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1747.5	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1754.1	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1754.8	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)