

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331771-940

Luminaire Tested: **S122RDIW-S290D710U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331771-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3450.9 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				
2	85	78	72	67	75	70	65	61	55	51	48	41	38	37	28	26	25	20				
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17				
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	20	19	15				
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12				
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.2
10°-20°	115.0	3.3
20°-30°	161.6	4.7
30°-40°	176.2	5.1
40°-50°	162.0	4.7
50°-60°	127.2	3.7
60°-70°	82.9	2.4
70°-80°	42.8	1.2
80°-90°	13.2	0.4
90°-100°	28.8	0.8
100°-110°	105.5	3.1
110°-120°	282.1	8.2
120°-130°	465.6	13.5
130°-140°	495.2	14.4
140°-150°	460.3	13.3
150°-160°	370.1	10.7
160°-170°	238.5	6.9
170°-180°	82.1	2.4
0°-30°	318.5	9.2
0°-40°	494.7	14.3
0°-60°	783.8	22.7
0°-90°	922.7	26.7
90°-120°	416.4	12.1
90°-150°	1837.6	53.2
90°-180°	2528.0	73.3
0°-180°	3450.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	1	7	12	16	17	3
95°	41	21	24	27	27	50
105°	190	198	38	45	47	203
115°	359	370	385	110	51	353
125°	508	516	527	532	534	452
135°	628	638	644	649	649	485
145°	728	728	738	742	740	455
155°	802	797	804	807	803	369
165°	845	842	843	847	843	239
175°	865	860	862	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.4	5.1	4.7	4.5	4.2	4.2	4.5	4.6	4.9	5.1	5.2
90°	0.6	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2
92.5°	12.6	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8
95°	40.6	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1
97.5°	80.5	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2
100°	110.5	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6
102.5°	143.5	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0
105°	189.8	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6
107.5°	242.5	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7
110°	276.5	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4



TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.5	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0
115°	358.9	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9
117.5°	404.0	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1
120°	436.9	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2
122.5°	464.9	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0
125°	507.5	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4
127.5°	546.1	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3
130°	570.5	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0
132.5°	595.6	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2
135°	628.0	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0
137.5°	660.8	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6
140°	682.3	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4
142.5°	700.3	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8
145°	728.5	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5
147.5°	753.0	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0
150°	769.1	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5
152.5°	782.6	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0
155°	802.2	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9
157.5°	817.5	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9
160°	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3
162.5°	834.5	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9
165°	845.3	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4
167.5°	853.2	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2
170°	857.7	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2
172.5°	860.7	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2
175°	864.6	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5
177.5°	865.2	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	5.3	5.3	5.4	5.4	5.4	5.5	5.6	5.6
90°	13.9	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.2	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	25.8	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	33.7	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	37.8	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	39.5	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	41.1	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	50.2	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	81.5	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331771-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	174.3	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	256.7	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	395.6	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	460.9	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	489.0	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	529.4	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	566.8	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	590.5	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	613.5	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	646.4	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	676.9	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	696.7	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	714.9	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	740.4	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	762.7	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	776.3	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	788.8	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	805.7	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	819.9	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	828.1	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	835.9	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	853.2	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	857.2	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	860.1	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	863.4	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	863.8	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)