

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332162-930

Luminaire Tested: **S123DIW-S775D1030U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332162-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1030U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6023.3 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.4
10°-20°	278.3	4.6
20°-30°	467.0	7.8
30°-40°	528.8	8.8
40°-50°	474.2	7.9
50°-60°	382.7	6.4
60°-70°	266.7	4.4
70°-80°	140.2	2.3
80°-90°	37.4	0.6
90°-100°	40.1	0.7
100°-110°	191.0	3.2
110°-120°	458.8	7.6
120°-130°	584.2	9.7
130°-140°	624.2	10.4
140°-150°	583.7	9.7
150°-160°	470.8	7.8
160°-170°	303.9	5.0
170°-180°	104.7	1.7
0°-30°	832.1	13.8
0°-40°	1360.9	22.6
0°-60°	2217.8	36.8
0°-90°	2662.0	44.2
90°-120°	689.8	11.5
90°-150°	2481.9	41.2
90°-180°	3361.0	55.8
0°-180°	6023.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	24	1	24	1	24	13
95°	31	50	31	50	31	26
105°	36	244	36	244	36	82
115°	482	458	482	458	482	445
125°	658	645	658	645	658	588
135°	812	803	812	803	812	626
145°	936	927	936	927	936	584
155°	1020	1021	1020	1021	1020	470
165°	1074	1077	1074	1077	1074	303
175°	1098	1102	1098	1102	1098	105
180°	1102	1102	1102	1102	1102	



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	15.2	14.4	14.7	14.9	14.5	14.8	14.9	15.2	15.3	15.6	15.4
90°	24.5	24.2	23.8	23.5	23.1	22.6	21.9	21.1	20.4	19.6	17.3
92.5°	27.1	27.0	26.7	26.5	26.3	25.6	24.5	23.3	22.1	21.0	19.2
95°	31.1	31.1	31.1	31.1	31.1	30.5	29.2	28.0	26.7	25.4	23.4
97.5°	33.8	33.6	33.3	33.2	33.0	32.2	30.7	29.3	27.8	26.3	23.9
100°	34.4	34.2	34.0	33.8	33.7	32.9	31.4	29.9	28.5	27.0	25.4
102.5°	35.1	34.7	34.4	34.1	33.8	33.8	32.9	31.4	29.9	28.5	27.0
105°	36.0	35.6	35.3	35.0	34.6	34.6	33.7	32.9	31.4	29.9	28.5
107.5°	113.2	137.5	161.8	186.0	210.3	234.2	257.9	281.4	305.1	328.7	326.1
110°	225.2	251.2	277.2	303.3	329.3	345.3	351.3	357.3	363.3	369.3	367.3



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.4	391.8	397.4	402.8	408.3	411.0	410.9	410.8	410.7	410.6	408.6
115°	481.5	480.8	480.0	479.3	478.6	477.4	475.5	473.7	471.9	470.0	468.4
117.5°	534.9	534.8	534.6	534.4	534.3	533.5	532.1	530.6	529.1	527.7	526.8
120°	571.6	571.6	571.6	571.6	571.6	570.9	569.4	567.9	566.5	565.0	564.5
122.5°	607.6	607.5	607.3	607.2	607.1	606.4	605.4	604.4	603.4	602.3	601.7
125°	658.4	658.0	657.6	657.3	657.0	656.6	656.2	655.8	655.5	655.1	654.4
127.5°	707.2	707.6	707.9	708.3	708.7	708.6	707.9	707.4	706.8	706.2	705.3
130°	738.7	739.0	739.4	739.7	740.1	739.9	739.2	738.5	737.8	737.0	736.3
132.5°	767.4	768.0	768.5	769.0	769.5	769.4	768.7	767.9	767.2	766.5	765.9
135°	811.5	812.0	812.6	813.2	813.7	813.7	813.2	812.6	812.0	811.5	810.8
137.5°	853.0	853.3	853.7	854.0	854.4	854.2	853.3	852.4	851.5	850.7	850.3
140°	877.8	878.2	878.6	879.0	879.3	879.1	878.4	877.7	876.9	876.2	875.6
142.5°	900.7	901.3	901.8	902.3	902.8	902.8	902.2	901.6	901.1	900.4	899.9
145°	936.0	936.0	936.0	936.0	936.0	935.8	935.5	935.1	934.7	934.3	934.0
147.5°	962.2	963.0	963.8	964.7	965.6	965.8	965.4	965.1	964.7	964.3	963.9
150°	981.9	982.4	982.9	983.5	984.1	984.1	983.7	983.4	983.0	982.7	982.3
152.5°	997.6	998.4	999.2	1000.0	1000.9	1001.0	1000.4	999.7	999.1	998.4	998.2
155°	1019.5	1020.6	1021.7	1022.8	1023.9	1024.0	1023.0	1022.1	1021.2	1020.3	1020.2
157.5°	1038.0	1039.4	1040.9	1042.3	1043.7	1043.8	1042.8	1041.7	1040.6	1039.5	1039.7
160°	1049.8	1051.1	1052.4	1053.6	1054.9	1055.0	1053.9	1052.8	1051.7	1050.7	1050.8
162.5°	1060.9	1062.1	1063.2	1064.4	1065.4	1065.4	1064.2	1062.9	1061.7	1060.5	1060.6
165°	1074.4	1075.6	1076.9	1078.2	1079.5	1079.4	1077.9	1076.4	1075.1	1073.6	1073.7
167.5°	1084.0	1085.5	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0	1084.0
170°	1090.0	1091.4	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0	1090.0
172.5°	1093.2	1094.8	1096.4	1098.0	1099.6	1099.7	1098.2	1096.8	1095.4	1093.9	1093.7
175°	1098.1	1099.6	1101.1	1102.5	1104.0	1104.1	1102.8	1101.5	1100.2	1098.9	1098.8
177.5°	1099.6	1101.1	1102.5	1104.0	1105.5	1105.5	1104.4	1103.3	1102.1	1100.9	1100.7
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	15.7	15.5	14.0	12.2	11.2	9.8	9.4	8.4	8.1	8.4	8.4
90°	14.9	12.6	10.2	8.1	6.3	4.5	2.6	0.8	2.6	4.5	6.3
92.5°	17.4	15.7	13.9	13.2	13.7	14.2	14.8	15.2	14.8	14.2	13.7
95°	21.4	19.4	17.4	20.1	27.6	35.1	42.5	50.0	42.5	35.1	27.6
97.5°	52.6	65.7	78.8	87.0	90.3	93.7	97.0	100.4	97.0	93.7	90.3
100°	83.8	112.2	140.6	153.0	149.3	145.7	142.0	138.4	142.0	145.7	149.3
102.5°	115.9	146.9	177.9	192.1	189.5	186.9	184.3	181.6	184.3	186.9	189.5
105°	212.1	228.4	244.8	252.0	250.1	248.0	246.1	244.0	246.1	248.0	250.1
107.5°	323.5	321.0	318.4	316.3	314.7	313.1	311.4	309.9	311.4	313.1	314.7
110°	365.3	363.3	361.3	359.5	358.2	356.7	355.2	353.8	355.2	356.7	358.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	406.6	404.6	402.6	401.0	399.7	398.3	397.0	395.7	397.0	398.3	399.7
115°	466.8	465.1	463.5	462.1	461.1	459.9	458.9	457.8	458.9	459.9	461.1
117.5°	526.0	525.2	524.3	523.3	521.9	520.6	519.2	517.9	519.2	520.6	521.9
120°	563.9	563.4	562.9	561.7	560.1	558.5	556.8	555.2	556.8	558.5	560.1
122.5°	601.0	600.3	599.6	598.6	597.2	595.9	594.5	593.2	594.5	595.9	597.2
125°	653.6	652.9	652.2	651.1	649.6	648.2	646.8	645.3	646.8	648.2	649.6
127.5°	704.5	703.6	702.7	701.6	700.1	698.6	697.2	695.7	697.2	698.6	700.1
130°	735.6	734.8	734.1	733.0	731.6	730.1	728.6	727.2	728.6	730.1	731.6
132.5°	765.3	764.8	764.2	763.1	761.7	760.2	758.8	757.3	758.8	760.2	761.7
135°	810.1	809.3	808.6	807.7	806.6	805.5	804.5	803.3	804.5	805.5	806.6
137.5°	849.9	849.5	849.1	848.2	846.8	845.4	844.0	842.6	844.0	845.4	846.8
140°	875.1	874.6	874.0	873.2	872.1	871.1	869.9	868.9	869.9	871.1	872.1
142.5°	899.4	898.8	898.3	897.5	896.3	895.3	894.1	893.1	894.1	895.3	896.3
145°	933.6	933.3	932.9	932.1	930.8	929.5	928.2	927.0	928.2	929.5	930.8
147.5°	963.6	963.2	962.9	962.3	961.4	960.6	959.8	959.0	959.8	960.6	961.4
150°	981.9	981.5	981.2	980.7	980.2	979.7	979.1	978.6	979.1	979.7	980.2
152.5°	997.9	997.8	997.5	997.3	997.0	996.8	996.5	996.3	996.5	996.8	997.0
155°	1019.9	1019.8	1019.6	1019.7	1020.1	1020.4	1020.8	1021.2	1020.8	1020.4	1020.1
157.5°	1039.8	1040.1	1040.2	1040.3	1040.4	1040.4	1040.5	1040.5	1040.5	1040.4	1040.4
160°	1051.0	1051.2	1051.3	1051.6	1051.7	1051.9	1052.1	1052.3	1052.1	1051.9	1051.7
162.5°	1060.9	1061.0	1061.2	1061.5	1062.0	1062.5	1062.9	1063.4	1062.9	1062.5	1062.0
165°	1073.9	1074.1	1074.3	1074.6	1075.2	1075.8	1076.3	1076.8	1076.3	1075.8	1075.2
167.5°	1084.0	1084.0	1084.0	1084.4	1085.2	1085.9	1086.6	1087.3	1086.6	1085.9	1085.2
170°	1090.0	1090.0	1090.0	1090.3	1091.0	1091.8	1092.5	1093.2	1092.5	1091.8	1091.0
172.5°	1093.6	1093.4	1093.3	1093.6	1094.5	1095.4	1096.3	1097.1	1096.3	1095.4	1094.5
175°	1098.6	1098.4	1098.2	1098.6	1099.5	1100.4	1101.3	1102.2	1101.3	1100.4	1099.5
177.5°	1100.7	1100.5	1100.3	1100.7	1101.4	1102.1	1102.8	1103.5	1102.8	1102.1	1101.4
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	8.5	9.2	9.4	10.2	10.3	11.1	11.3	10.7	10.8	12.0	10.8
90°	8.1	10.2	12.6	14.9	17.3	19.6	20.4	21.1	21.9	22.6	23.1
92.5°	13.2	13.9	15.7	17.4	19.2	21.0	22.1	23.3	24.5	25.6	26.3
95°	20.1	17.4	19.4	21.4	23.4	25.4	26.7	28.0	29.2	30.5	31.1
97.5°	87.0	78.8	65.7	52.6	39.5	26.3	27.8	29.3	30.7	32.2	33.0
100°	153.0	140.6	112.2	83.8	55.4	27.0	28.5	29.9	31.4	32.9	33.7
102.5°	192.1	177.9	146.9	115.9	84.9	53.9	49.4	44.8	40.4	35.8	33.8
105°	252.0	244.8	228.4	212.1	195.8	179.4	147.2	115.0	82.7	50.5	34.6
107.5°	316.3	318.4	321.0	323.5	326.1	328.7	305.1	281.4	257.9	234.2	210.3
110°	359.5	361.3	363.3	365.3	367.3	369.3	363.3	357.3	351.3	345.3	329.3



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	401.0	402.6	404.6	406.6	408.6	410.6	410.7	410.8	410.9	411.0	408.3
115°	462.1	463.5	465.1	466.8	468.4	470.0	471.9	473.7	475.5	477.4	478.6
117.5°	523.3	524.3	525.2	526.0	526.8	527.7	529.1	530.6	532.1	533.5	534.3
120°	561.7	562.9	563.4	563.9	564.5	565.0	566.5	567.9	569.4	570.9	571.6
122.5°	598.6	599.6	600.3	601.0	601.7	602.3	603.4	604.4	605.4	606.4	607.1
125°	651.1	652.2	652.9	653.6	654.4	655.1	655.5	655.8	656.2	656.6	657.0
127.5°	701.6	702.7	703.6	704.5	705.3	706.2	706.8	707.4	707.9	708.6	708.7
130°	733.0	734.1	734.8	735.6	736.3	737.0	737.8	738.5	739.2	739.9	740.1
132.5°	763.1	764.2	764.8	765.3	765.9	766.5	767.2	767.9	768.7	769.4	769.5
135°	807.7	808.6	809.3	810.1	810.8	811.5	812.0	812.6	813.2	813.7	813.7
137.5°	848.2	849.1	849.5	849.9	850.3	850.7	851.5	852.4	853.3	854.2	854.4
140°	873.2	874.0	874.6	875.1	875.6	876.2	876.9	877.7	878.4	879.1	879.3
142.5°	897.5	898.3	898.8	899.4	899.9	900.4	901.1	901.6	902.2	902.8	902.8
145°	932.1	932.9	933.3	933.6	934.0	934.3	934.7	935.1	935.5	935.8	936.0
147.5°	962.3	962.9	963.2	963.6	963.9	964.3	964.7	965.1	965.4	965.8	965.6
150°	980.7	981.2	981.5	981.9	982.3	982.7	983.0	983.4	983.7	984.1	984.1
152.5°	997.3	997.5	997.8	997.9	998.2	998.4	999.1	999.7	1000.4	1001.0	1000.9
155°	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2	1022.1	1023.0	1024.0	1023.9
157.5°	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6	1041.7	1042.8	1043.8	1043.7
160°	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7	1052.8	1053.9	1055.0	1054.9
162.5°	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7	1062.9	1064.2	1065.4	1065.4
165°	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1	1076.4	1077.9	1079.4	1079.5
167.5°	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5	1087.0	1088.4	1089.9	1089.9
170°	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4	1092.8	1094.3	1095.8	1095.8
172.5°	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4	1096.8	1098.2	1099.7	1099.6
175°	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2	1101.5	1102.8	1104.1	1104.0
177.5°	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1	1103.3	1104.4	1105.5	1105.5
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	10.8	10.9	10.7	10.4	10.7	10.9	10.8	10.8	12.0	10.8	10.7
90°	23.5	23.8	24.2	24.5	24.2	23.8	23.5	23.1	22.6	21.9	21.1
92.5°	26.5	26.7	27.0	27.1	27.0	26.7	26.5	26.3	25.6	24.5	23.3
95°	31.1	31.1	31.1	31.1	31.1	31.1	31.1	31.1	30.5	29.2	28.0
97.5°	33.2	33.3	33.6	33.8	33.6	33.3	33.2	33.0	32.2	30.7	29.3
100°	33.8	34.0	34.2	34.4	34.2	34.0	33.8	33.7	32.9	31.4	29.9
102.5°	34.1	34.4	34.7	35.1	34.7	34.4	34.1	33.8	35.8	40.4	44.8
105°	35.0	35.3	35.6	36.0	35.6	35.3	35.0	34.6	50.5	82.7	115.0
107.5°	186.0	161.8	137.5	113.2	137.5	161.8	186.0	210.3	234.2	257.9	281.4
110°	303.3	277.2	251.2	225.2	251.2	277.2	303.3	329.3	345.3	351.3	357.3



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	402.8	397.4	391.8	386.4	391.8	397.4	402.8	408.3	411.0	410.9	410.8
115°	479.3	480.0	480.8	481.5	480.8	480.0	479.3	478.6	477.4	475.5	473.7
117.5°	534.4	534.6	534.8	534.9	534.8	534.6	534.4	534.3	533.5	532.1	530.6
120°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	570.9	569.4	567.9
122.5°	607.2	607.3	607.5	607.6	607.5	607.3	607.2	607.1	606.4	605.4	604.4
125°	657.3	657.6	658.0	658.4	658.0	657.6	657.3	657.0	656.6	656.2	655.8
127.5°	708.3	707.9	707.6	707.2	707.6	707.9	708.3	708.7	708.6	707.9	707.4
130°	739.7	739.4	739.0	738.7	739.0	739.4	739.7	740.1	739.9	739.2	738.5
132.5°	769.0	768.5	768.0	767.4	768.0	768.5	769.0	769.5	769.4	768.7	767.9
135°	813.2	812.6	812.0	811.5	812.0	812.6	813.2	813.7	813.7	813.2	812.6
137.5°	854.0	853.7	853.3	853.0	853.3	853.7	854.0	854.4	854.2	853.3	852.4
140°	879.0	878.6	878.2	877.8	878.2	878.6	879.0	879.3	879.1	878.4	877.7
142.5°	902.3	901.8	901.3	900.7	901.3	901.8	902.3	902.8	902.8	902.2	901.6
145°	936.0	936.0	936.0	936.0	936.0	936.0	936.0	936.0	935.8	935.5	935.1
147.5°	964.7	963.8	963.0	962.2	963.0	963.8	964.7	965.6	965.8	965.4	965.1
150°	983.5	982.9	982.4	981.9	982.4	982.9	983.5	984.1	984.1	983.7	983.4
152.5°	1000.0	999.2	998.4	997.6	998.4	999.2	1000.0	1000.9	1001.0	1000.4	999.7
155°	1022.8	1021.7	1020.6	1019.5	1020.6	1021.7	1022.8	1023.9	1024.0	1023.0	1022.1
157.5°	1042.3	1040.9	1039.4	1038.0	1039.4	1040.9	1042.3	1043.7	1043.8	1042.8	1041.7
160°	1053.6	1052.4	1051.1	1049.8	1051.1	1052.4	1053.6	1054.9	1055.0	1053.9	1052.8
162.5°	1064.4	1063.2	1062.1	1060.9	1062.1	1063.2	1064.4	1065.4	1065.4	1064.2	1062.9
165°	1078.2	1076.9	1075.6	1074.4	1075.6	1076.9	1078.2	1079.5	1079.4	1077.9	1076.4
167.5°	1088.4	1087.0	1085.5	1084.0	1085.5	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0
170°	1094.3	1092.8	1091.4	1090.0	1091.4	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8
172.5°	1098.0	1096.4	1094.8	1093.2	1094.8	1096.4	1098.0	1099.6	1099.7	1098.2	1096.8
175°	1102.5	1101.1	1099.6	1098.1	1099.6	1101.1	1102.5	1104.0	1104.1	1102.8	1101.5
177.5°	1104.0	1102.5	1101.1	1099.6	1101.1	1102.5	1104.0	1105.5	1105.5	1104.4	1103.3
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	11.3	11.1	10.3	10.2	9.4	9.2	8.5	8.4	8.4	8.1	8.4
90°	20.4	19.6	17.3	14.9	12.6	10.2	8.1	6.3	4.5	2.6	0.8
92.5°	22.1	21.0	19.2	17.4	15.7	13.9	13.2	13.7	14.2	14.8	15.2
95°	26.7	25.4	23.4	21.4	19.4	17.4	20.1	27.6	35.1	42.5	50.0
97.5°	27.8	26.3	39.5	52.6	65.7	78.8	87.0	90.3	93.7	97.0	100.4
100°	28.5	27.0	55.4	83.8	112.2	140.6	153.0	149.3	145.7	142.0	138.4
102.5°	49.4	53.9	84.9	115.9	146.9	177.9	192.1	189.5	186.9	184.3	181.6
105°	147.2	179.4	195.8	212.1	228.4	244.8	252.0	250.1	248.0	246.1	244.0
107.5°	305.1	328.7	326.1	323.5	321.0	318.4	316.3	314.7	313.1	311.4	309.9
110°	363.3	369.3	367.3	365.3	363.3	361.3	359.5	358.2	356.7	355.2	353.8



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	410.7	410.6	408.6	406.6	404.6	402.6	401.0	399.7	398.3	397.0	395.7
115°	471.9	470.0	468.4	466.8	465.1	463.5	462.1	461.1	459.9	458.9	457.8
117.5°	529.1	527.7	526.8	526.0	525.2	524.3	523.3	521.9	520.6	519.2	517.9
120°	566.5	565.0	564.5	563.9	563.4	562.9	561.7	560.1	558.5	556.8	555.2
122.5°	603.4	602.3	601.7	601.0	600.3	599.6	598.6	597.2	595.9	594.5	593.2
125°	655.5	655.1	654.4	653.6	652.9	652.2	651.1	649.6	648.2	646.8	645.3
127.5°	706.8	706.2	705.3	704.5	703.6	702.7	701.6	700.1	698.6	697.2	695.7
130°	737.8	737.0	736.3	735.6	734.8	734.1	733.0	731.6	730.1	728.6	727.2
132.5°	767.2	766.5	765.9	765.3	764.8	764.2	763.1	761.7	760.2	758.8	757.3
135°	812.0	811.5	810.8	810.1	809.3	808.6	807.7	806.6	805.5	804.5	803.3
137.5°	851.5	850.7	850.3	849.9	849.5	849.1	848.2	846.8	845.4	844.0	842.6
140°	876.9	876.2	875.6	875.1	874.6	874.0	873.2	872.1	871.1	869.9	868.9
142.5°	901.1	900.4	899.9	899.4	898.8	898.3	897.5	896.3	895.3	894.1	893.1
145°	934.7	934.3	934.0	933.6	933.3	932.9	932.1	930.8	929.5	928.2	927.0
147.5°	964.7	964.3	963.9	963.6	963.2	962.9	962.3	961.4	960.6	959.8	959.0
150°	983.0	982.7	982.3	981.9	981.5	981.2	980.7	980.2	979.7	979.1	978.6
152.5°	999.1	998.4	998.2	997.9	997.8	997.5	997.3	997.0	996.8	996.5	996.3
155°	1021.2	1020.3	1020.2	1019.9	1019.8	1019.6	1019.7	1020.1	1020.4	1020.8	1021.2
157.5°	1040.6	1039.5	1039.7	1039.8	1040.1	1040.2	1040.3	1040.4	1040.4	1040.5	1040.5
160°	1051.7	1050.7	1050.8	1051.0	1051.2	1051.3	1051.6	1051.7	1051.9	1052.1	1052.3
162.5°	1061.7	1060.5	1060.6	1060.9	1061.0	1061.2	1061.5	1062.0	1062.5	1062.9	1063.4
165°	1075.1	1073.6	1073.7	1073.9	1074.1	1074.3	1074.6	1075.2	1075.8	1076.3	1076.8
167.5°	1085.5	1084.0	1084.0	1084.0	1084.0	1084.0	1084.4	1085.2	1085.9	1086.6	1087.3
170°	1091.4	1090.0	1090.0	1090.0	1090.0	1090.0	1090.3	1091.0	1091.8	1092.5	1093.2
172.5°	1095.4	1093.9	1093.7	1093.6	1093.4	1093.3	1093.6	1094.5	1095.4	1096.3	1097.1
175°	1100.2	1098.9	1098.8	1098.6	1098.4	1098.2	1098.6	1099.5	1100.4	1101.3	1102.2
177.5°	1102.1	1100.9	1100.7	1100.7	1100.5	1100.3	1100.7	1101.4	1102.1	1102.8	1103.5
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.4	9.8	11.2	12.2	14.0	15.5	15.7	15.4	15.6	15.3	15.2
90°	2.6	4.5	6.3	8.1	10.2	12.6	14.9	17.3	19.6	20.4	21.1
92.5°	14.8	14.2	13.7	13.2	13.9	15.7	17.4	19.2	21.0	22.1	23.3
95°	42.5	35.1	27.6	20.1	17.4	19.4	21.4	23.4	25.4	26.7	28.0
97.5°	97.0	93.7	90.3	87.0	78.8	65.7	52.6	39.5	26.3	27.8	29.3
100°	142.0	145.7	149.3	153.0	140.6	112.2	83.8	55.4	27.0	28.5	29.9
102.5°	184.3	186.9	189.5	192.1	177.9	146.9	115.9	84.9	53.9	49.4	44.8
105°	246.1	248.0	250.1	252.0	244.8	228.4	212.1	195.8	179.4	147.2	115.0
107.5°	311.4	313.1	314.7	316.3	318.4	321.0	323.5	326.1	328.7	305.1	281.4
110°	355.2	356.7	358.2	359.5	361.3	363.3	365.3	367.3	369.3	363.3	357.3



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	397.0	398.3	399.7	401.0	402.6	404.6	406.6	408.6	410.6	410.7	410.8
115°	458.9	459.9	461.1	462.1	463.5	465.1	466.8	468.4	470.0	471.9	473.7
117.5°	519.2	520.6	521.9	523.3	524.3	525.2	526.0	526.8	527.7	529.1	530.6
120°	556.8	558.5	560.1	561.7	562.9	563.4	563.9	564.5	565.0	566.5	567.9
122.5°	594.5	595.9	597.2	598.6	599.6	600.3	601.0	601.7	602.3	603.4	604.4
125°	646.8	648.2	649.6	651.1	652.2	652.9	653.6	654.4	655.1	655.5	655.8
127.5°	697.2	698.6	700.1	701.6	702.7	703.6	704.5	705.3	706.2	706.8	707.4
130°	728.6	730.1	731.6	733.0	734.1	734.8	735.6	736.3	737.0	737.8	738.5
132.5°	758.8	760.2	761.7	763.1	764.2	764.8	765.3	765.9	766.5	767.2	767.9
135°	804.5	805.5	806.6	807.7	808.6	809.3	810.1	810.8	811.5	812.0	812.6
137.5°	844.0	845.4	846.8	848.2	849.1	849.5	849.9	850.3	850.7	851.5	852.4
140°	869.9	871.1	872.1	873.2	874.0	874.6	875.1	875.6	876.2	876.9	877.7
142.5°	894.1	895.3	896.3	897.5	898.3	898.8	899.4	899.9	900.4	901.1	901.6
145°	928.2	929.5	930.8	932.1	932.9	933.3	933.6	934.0	934.3	934.7	935.1
147.5°	959.8	960.6	961.4	962.3	962.9	963.2	963.6	963.9	964.3	964.7	965.1
150°	979.1	979.7	980.2	980.7	981.2	981.5	981.9	982.3	982.7	983.0	983.4
152.5°	996.5	996.8	997.0	997.3	997.5	997.8	997.9	998.2	998.4	999.1	999.7
155°	1020.8	1020.4	1020.1	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2	1022.1
157.5°	1040.5	1040.4	1040.4	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6	1041.7
160°	1052.1	1051.9	1051.7	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7	1052.8
162.5°	1062.9	1062.5	1062.0	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7	1062.9
165°	1076.3	1075.8	1075.2	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1	1076.4
167.5°	1086.6	1085.9	1085.2	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5	1087.0
170°	1092.5	1091.8	1091.0	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4	1092.8
172.5°	1096.3	1095.4	1094.5	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4	1096.8
175°	1101.3	1100.4	1099.5	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2	1101.5
177.5°	1102.8	1102.1	1101.4	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1	1103.3
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	14.9	14.8	14.5	14.9	14.7	14.4	15.2
90°	21.9	22.6	23.1	23.5	23.8	24.2	24.5
92.5°	24.5	25.6	26.3	26.5	26.7	27.0	27.1
95°	29.2	30.5	31.1	31.1	31.1	31.1	31.1
97.5°	30.7	32.2	33.0	33.2	33.3	33.6	33.8
100°	31.4	32.9	33.7	33.8	34.0	34.2	34.4
102.5°	40.4	35.8	33.8	34.1	34.4	34.7	35.1
105°	82.7	50.5	34.6	35.0	35.3	35.6	36.0
107.5°	257.9	234.2	210.3	186.0	161.8	137.5	113.2
110°	351.3	345.3	329.3	303.3	277.2	251.2	225.2



TEST NUMBER: P332162-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	410.9	411.0	408.3	402.8	397.4	391.8	386.4
115°	475.5	477.4	478.6	479.3	480.0	480.8	481.5
117.5°	532.1	533.5	534.3	534.4	534.6	534.8	534.9
120°	569.4	570.9	571.6	571.6	571.6	571.6	571.6
122.5°	605.4	606.4	607.1	607.2	607.3	607.5	607.6
125°	656.2	656.6	657.0	657.3	657.6	658.0	658.4
127.5°	707.9	708.6	708.7	708.3	707.9	707.6	707.2
130°	739.2	739.9	740.1	739.7	739.4	739.0	738.7
132.5°	768.7	769.4	769.5	769.0	768.5	768.0	767.4
135°	813.2	813.7	813.7	813.2	812.6	812.0	811.5
137.5°	853.3	854.2	854.4	854.0	853.7	853.3	853.0
140°	878.4	879.1	879.3	879.0	878.6	878.2	877.8
142.5°	902.2	902.8	902.8	902.3	901.8	901.3	900.7
145°	935.5	935.8	936.0	936.0	936.0	936.0	936.0
147.5°	965.4	965.8	965.6	964.7	963.8	963.0	962.2
150°	983.7	984.1	984.1	983.5	982.9	982.4	981.9
152.5°	1000.4	1001.0	1000.9	1000.0	999.2	998.4	997.6
155°	1023.0	1024.0	1023.9	1022.8	1021.7	1020.6	1019.5
157.5°	1042.8	1043.8	1043.7	1042.3	1040.9	1039.4	1038.0
160°	1053.9	1055.0	1054.9	1053.6	1052.4	1051.1	1049.8
162.5°	1064.2	1065.4	1065.4	1064.4	1063.2	1062.1	1060.9
165°	1077.9	1079.4	1079.5	1078.2	1076.9	1075.6	1074.4
167.5°	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0
170°	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0
172.5°	1098.2	1099.7	1099.6	1098.0	1096.4	1094.8	1093.2
175°	1102.8	1104.1	1104.0	1102.5	1101.1	1099.6	1098.1
177.5°	1104.4	1105.5	1105.5	1104.0	1102.5	1101.1	1099.6
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2

(END OF REPORT)