

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331775-940

Luminaire Tested: **S122RDIW-S290D970U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331775-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D970U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4374.3 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	26	26	25	18
2	83	77	71	66	74	68	63	59	52	49	46	37	35	34	23	22	22	16
3	76	67	61	55	67	60	54	50	46	42	39	33	31	29	21	20	19	13
4	70	60	52	47	61	53	47	42	41	37	33	29	27	25	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	29	26	24	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.9	1.0
10°-20°	115.0	2.6
20°-30°	161.6	3.7
30°-40°	176.2	4.0
40°-50°	162.0	3.7
50°-60°	127.2	2.9
60°-70°	82.9	1.9
70°-80°	42.8	1.0
80°-90°	14.0	0.3
90°-100°	39.3	0.9
100°-110°	144.0	3.3
110°-120°	385.0	8.8
120°-130°	635.6	14.5
130°-140°	675.9	15.5
140°-150°	628.3	14.4
150°-160°	505.1	11.5
160°-170°	325.5	7.4
170°-180°	112.0	2.6
0°-30°	318.5	7.3
0°-40°	494.7	11.3
0°-60°	783.8	17.9
0°-90°	923.5	21.1
90°-120°	568.4	13.0
90°-150°	2508.2	57.3
90°-180°	3451.0	78.9
0°-180°	4374.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	1	10	17	21	23	3
95°	55	29	33	37	37	68
105°	259	270	52	61	65	277
115°	490	505	526	150	70	482
125°	693	704	720	726	728	617
135°	857	870	878	886	885	662
145°	994	994	1008	1013	1010	622
155°	1095	1088	1097	1102	1096	504
165°	1154	1149	1151	1156	1151	326
175°	1180	1175	1176	1181	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.4	5.2	5.0	4.9	4.7	4.8	5.1	5.4	5.7	6.0	6.2
90°	0.9	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0
92.5°	17.2	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2
95°	55.4	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2
97.5°	109.9	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2
100°	150.8	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1
102.5°	195.8	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9
105°	259.0	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0
107.5°	331.1	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6
110°	377.5	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2



TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.1	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0
115°	489.9	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0
117.5°	551.4	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1
120°	596.5	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9
122.5°	634.6	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1
125°	692.7	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3
127.5°	745.4	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7
130°	778.8	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9
132.5°	812.9	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6
135°	857.2	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4
137.5°	902.0	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1
140°	931.3	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2
142.5°	955.8	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3
145°	994.3	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3
147.5°	1028.0	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0
150°	1049.7	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5
152.5°	1068.2	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6
155°	1094.9	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6
157.5°	1115.9	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8
160°	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3
162.5°	1139.1	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6
165°	1153.7	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4
167.5°	1164.6	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1
170°	1170.7	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7
172.5°	1174.8	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8
175°	1180.1	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1
177.5°	1181.0	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	6.2	6.3	6.5	6.6	6.6	6.7	6.8	6.9
90°	18.9	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	20.8	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	35.1	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.0	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	51.6	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	53.9	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	56.2	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	68.5	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	111.2	92.3	73.4	64.3	65.0	65.8	66.5	67.3





TEST NUMBER: P331775-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.9	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	350.4	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	539.8	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	629.1	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	667.5	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	722.6	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	773.6	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	805.9	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	837.4	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	882.3	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	923.9	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	950.9	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	975.8	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1010.7	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1041.0	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1059.7	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1076.7	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1099.7	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1119.1	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1130.4	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1140.9	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1164.5	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1170.0	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1174.0	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1178.5	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1179.0	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)