

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331792-940

Luminaire Tested: **S122RDIW-S485D710U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331792-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3709.2 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	1.9
10°-20°	189.1	5.1
20°-30°	265.6	7.2
30°-40°	289.6	7.8
40°-50°	266.3	7.2
50°-60°	209.1	5.6
60°-70°	136.4	3.7
70°-80°	70.3	1.9
80°-90°	21.4	0.6
90°-100°	49.7	1.3
100°-110°	154.3	4.2
110°-120°	263.8	7.1
120°-130°	346.9	9.4
130°-140°	389.3	10.5
140°-150°	381.7	10.3
150°-160°	320.2	8.6
160°-170°	212.4	5.7
170°-180°	74.2	2.0
0°-30°	523.6	14.1
0°-40°	813.2	21.9
0°-60°	1288.6	34.7
0°-90°	1516.7	40.9
90°-120°	467.8	12.6
90°-150°	1585.7	42.8
90°-180°	2193.0	59.1
0°-180°	3709.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	9	23	22	22	3
95°	34	41	42	42	41	39
105°	142	144	146	147	147	150
115°	265	268	267	267	265	262
125°	385	391	389	387	386	344
135°	498	505	507	506	504	385
145°	605	609	613	614	611	378
155°	691	693	695	698	697	318
165°	752	752	752	756	753	212
175°	783	781	779	784	780	74
180°	784	784	784	784	784	



TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	8.0	7.5	6.9	6.2	6.3	7.0	7.6	8.2	8.9	8.7
90°	0.6	2.4	4.2	6.0	7.8	10.3	13.5	16.7	19.9	23.2	22.8
92.5°	11.8	13.1	14.4	15.7	16.9	18.0	18.7	19.5	20.2	21.0	21.1
95°	34.4	35.8	37.4	38.8	40.3	41.2	41.5	41.7	42.1	42.4	42.4
97.5°	62.9	64.1	65.5	66.7	68.0	68.9	69.6	70.1	70.6	71.2	71.2
100°	84.0	85.2	86.4	87.6	88.7	89.5	90.0	90.4	90.9	91.3	91.3
102.5°	106.3	107.2	108.2	109.1	110.0	110.8	111.4	111.9	112.4	113.0	113.2
105°	142.2	142.7	143.1	143.6	144.0	144.4	144.7	145.0	145.3	145.6	145.9
107.5°	178.5	179.1	179.9	180.5	181.1	181.5	181.5	181.5	181.5	181.5	181.6
110°	201.8	202.7	203.6	204.5	205.4	205.8	205.8	205.8	205.8	205.8	205.8



TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.2	228.1	229.0	229.9	230.8	231.1	231.0	230.9	230.8	230.7	230.3
115°	264.7	265.6	266.4	267.3	268.2	268.5	268.2	267.9	267.6	267.3	267.2
117.5°	302.0	303.2	304.3	305.5	306.7	306.8	306.0	305.2	304.4	303.6	303.3
120°	326.9	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	326.9
122.5°	349.6	351.1	352.5	353.8	355.3	355.6	354.7	353.9	353.1	352.3	352.0
125°	385.1	386.5	387.7	389.1	390.4	390.8	390.4	389.9	389.5	389.1	388.6
127.5°	419.6	421.3	423.0	424.6	426.3	427.0	426.4	425.9	425.3	424.8	424.3
130°	441.3	443.3	445.1	447.1	449.0	449.8	449.5	449.2	448.9	448.6	448.4
132.5°	465.7	467.3	468.9	470.4	471.9	472.8	472.8	472.9	473.0	473.0	472.3
135°	498.3	499.9	501.5	503.1	504.7	505.7	506.0	506.3	506.6	506.8	506.7
137.5°	532.5	533.9	535.2	536.5	537.8	538.7	539.0	539.5	539.8	540.2	540.1
140°	553.2	554.5	555.8	557.1	558.5	559.5	560.3	561.0	561.7	562.4	562.4
142.5°	574.4	575.7	577.0	578.4	579.6	580.6	581.0	581.6	582.0	582.6	582.6
145°	604.8	605.8	606.8	607.9	608.9	609.8	610.7	611.6	612.5	613.4	613.5
147.5°	632.0	633.1	634.4	635.6	636.9	637.8	638.4	638.9	639.5	640.2	640.4
150°	650.4	651.3	652.2	653.1	654.0	654.7	655.3	655.9	656.5	657.1	657.5
152.5°	666.8	667.7	668.6	669.5	670.4	671.2	671.9	672.6	673.3	674.0	674.6
155°	691.4	691.9	692.3	692.8	693.2	693.7	694.1	694.6	695.0	695.4	696.2
157.5°	712.5	712.8	713.1	713.4	713.7	714.0	714.3	714.5	714.8	715.1	716.0
160°	725.2	725.5	725.8	726.1	726.4	726.7	726.7	726.9	727.0	727.2	728.1
162.5°	736.8	736.9	737.0	737.0	737.1	737.2	737.4	737.5	737.6	737.8	738.8
165°	752.3	752.2	752.1	751.9	751.8	751.7	751.7	751.7	751.7	751.7	752.7
167.5°	765.4	764.9	764.5	764.0	763.6	763.3	763.3	763.2	763.2	763.2	764.2
170°	772.2	771.8	771.3	770.9	770.4	770.2	770.0	769.8	769.7	769.5	770.6
172.5°	776.9	776.5	776.1	775.6	775.2	774.9	774.7	774.6	774.5	774.3	775.3
175°	782.7	782.4	781.9	781.5	781.0	780.7	780.3	780.1	779.8	779.4	780.5
177.5°	785.2	784.8	784.4	784.1	783.7	783.5	783.2	783.0	782.7	782.5	783.2
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	8.6	8.4	8.2	8.1	8.1	8.2	8.2	8.2
90°	22.6	22.3	22.0	21.9	22.0	22.2	22.4	22.5
92.5°	21.1	21.2	21.3	21.3	21.3	21.4	21.4	21.4
95°	42.4	42.4	42.4	42.2	41.9	41.6	41.3	41.0
97.5°	71.2	71.2	71.2	71.2	71.2	71.2	71.1	71.1
100°	91.3	91.3	91.3	91.2	91.1	91.0	90.8	90.7
102.5°	113.2	113.3	113.5	113.5	113.3	113.2	113.1	112.9
105°	146.2	146.4	146.8	146.9	146.9	146.9	146.9	146.9
107.5°	181.6	181.8	181.9	181.6	180.9	180.3	179.6	179.0
110°	205.8	205.8	205.8	205.5	205.1	204.6	204.2	203.8



TEST NUMBER: P331792-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.0	229.6	229.3	228.9	228.6	228.3	227.9	227.7
115°	267.1	266.9	266.7	266.4	266.0	265.6	265.1	264.7
117.5°	302.9	302.6	302.2	301.8	301.3	300.9	300.4	300.0
120°	326.9	326.9	326.9	326.6	326.2	325.7	325.3	324.9
122.5°	351.6	351.2	350.9	350.5	350.2	349.9	349.6	349.3
125°	388.2	387.7	387.3	387.0	386.9	386.7	386.6	386.5
127.5°	423.7	423.2	422.7	422.2	421.7	421.2	420.8	420.4
130°	448.1	447.7	447.5	447.0	446.4	445.9	445.2	444.7
132.5°	471.7	471.0	470.4	469.8	469.4	468.9	468.4	468.0
135°	506.6	506.4	506.3	506.0	505.5	505.1	504.6	504.2
137.5°	539.9	539.8	539.8	539.4	538.8	538.2	537.6	537.0
140°	562.4	562.4	562.4	562.1	561.6	561.0	560.4	559.8
142.5°	582.8	582.9	583.0	582.8	582.2	581.6	581.0	580.4
145°	613.7	613.9	613.9	613.8	613.1	612.6	612.0	611.4
147.5°	640.8	641.1	641.4	641.3	640.8	640.2	639.6	639.1
150°	657.9	658.4	658.8	658.8	658.4	657.9	657.5	657.1
152.5°	675.1	675.6	676.3	676.3	675.6	675.1	674.6	674.0
155°	696.9	697.7	698.4	698.6	698.1	697.7	697.2	696.8
157.5°	717.0	718.0	719.0	719.2	718.5	717.7	717.0	716.3
160°	729.0	729.9	730.8	730.8	730.3	729.7	729.2	728.5
162.5°	739.8	740.8	741.8	741.9	741.2	740.6	739.9	739.1
165°	753.8	754.7	755.8	756.0	755.2	754.5	753.8	753.0
167.5°	765.3	766.2	767.3	767.4	766.7	765.9	765.2	764.4
170°	771.6	772.7	773.6	773.7	772.8	772.0	771.1	770.2
172.5°	776.4	777.4	778.5	778.5	777.7	776.8	775.9	775.0
175°	781.5	782.6	783.6	783.6	782.7	781.9	781.0	780.2
177.5°	783.9	784.6	785.3	785.3	784.6	783.9	783.2	782.5
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1

(END OF REPORT)