

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332155-930

Luminaire Tested: **S123DIW-S775D460U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332155-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D460U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3888.0 lumens  
Efficiency: N/A  
Efficacy: 103.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20						20								20		
RC	80					70						30								10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	111	111	111	111		105	105	105	105		92	92	92		81	81	81		71	71	71	66
1	101	97	93	89		95	91	88	85		81	78	76		72	70	68		63	61	60	56
2	92	85	78	73		87	80	74	69		71	67	63		63	59	57		55	53	51	47
3	84	74	67	61		79	70	64	58		63	57	53		56	51	48		49	46	43	40
4	77	66	58	51		72	62	55	49		56	50	45		50	45	41		44	40	37	34
5	71	59	50	44		66	56	48	42		50	44	39		44	39	36		39	35	32	29
6	65	53	44	38		61	50	43	37		45	39	34		40	35	31		36	32	28	26
7	60	48	40	34		57	45	38	33		41	35	30		37	32	28		33	28	25	23
8	56	43	36	30		53	41	34	29		37	31	27		34	28	25		30	26	23	20
9	52	40	32	27		49	38	31	26		34	28	24		31	26	22		28	24	20	18
10	49	37	29	24		46	35	28	23		32	26	22		29	24	20		26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.5	2.4
10°-20°	264.1	6.8
20°-30°	390.1	10.0
30°-40°	455.7	11.7
40°-50°	458.1	11.8
50°-60°	402.4	10.3
60°-70°	299.8	7.7
70°-80°	170.8	4.4
80°-90°	50.4	1.3
90°-100°	30.6	0.8
100°-110°	91.7	2.4
110°-120°	156.0	4.0
120°-130°	205.2	5.3
130°-140°	230.6	5.9
140°-150°	226.7	5.8
150°-160°	190.8	4.9
160°-170°	127.0	3.3
170°-180°	44.5	1.1
0°-30°	747.7	19.2
0°-40°	1203.3	30.9
0°-60°	2063.8	53.1
0°-90°	2584.9	66.5
90°-120°	278.3	7.2
90°-150°	940.8	24.2
90°-180°	1303.0	33.5
0°-180°	3888.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	0	4	9	10	11	4
95°	22	24	27	29	29	24
105°	83	84	87	87	88	89
115°	157	158	157	158	157	155
125°	230	231	230	229	227	205
135°	298	300	300	299	298	230
145°	362	362	364	363	362	226
155°	414	414	415	416	413	191
165°	451	450	450	452	450	127
175°	469	468	468	470	467	45
180°	470	470	470	470	470	



TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.5	17.3	17.0	16.6	16.6	16.6	16.7	16.7	16.8	16.7
90°	0.4	1.2	2.0	2.9	3.7	4.6	5.6	6.8	7.8	8.9	9.2
92.5°	9.0	9.5	10.0	10.6	11.2	11.7	12.4	13.0	13.6	14.2	14.4
95°	21.8	22.3	22.9	23.6	24.1	24.7	25.4	26.0	26.7	27.3	27.6
97.5°	38.7	39.1	39.5	40.0	40.4	40.8	41.3	41.8	42.3	42.8	43.1
100°	50.2	50.7	51.2	51.7	52.2	52.7	53.1	53.5	53.9	54.3	54.5
102.5°	63.5	63.8	64.2	64.4	64.7	65.1	65.7	66.2	66.8	67.3	67.6
105°	83.2	83.3	83.5	83.6	83.8	84.2	85.0	85.7	86.4	87.2	87.2
107.5°	105.9	106.0	106.1	106.2	106.3	106.5	106.8	107.0	107.4	107.7	107.9
110°	120.1	120.3	120.4	120.6	120.7	120.9	121.1	121.2	121.4	121.6	121.9



TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.9	134.9	135.1	135.2	135.3	135.3	135.3	135.4	135.4	135.4	135.8
115°	157.0	157.3	157.5	157.8	158.0	158.1	157.9	157.8	157.6	157.4	157.5
117.5°	179.4	179.5	179.7	179.9	180.0	179.9	179.8	179.5	179.4	179.1	179.1
120°	193.2	193.7	194.2	194.7	195.2	195.3	194.9	194.4	194.0	193.6	193.6
122.5°	207.7	208.1	208.5	208.8	209.1	209.2	209.0	208.8	208.6	208.4	208.1
125°	229.8	230.1	230.3	230.6	230.8	230.8	230.6	230.5	230.3	230.2	229.8
127.5°	250.2	250.7	251.3	251.8	252.3	252.5	252.3	252.1	251.9	251.8	251.3
130°	263.8	264.5	265.1	265.8	266.4	266.6	266.4	266.1	265.9	265.6	265.3
132.5°	277.4	278.0	278.8	279.4	280.1	280.3	280.1	279.9	279.7	279.6	279.2
135°	298.2	298.6	299.1	299.6	300.1	300.4	300.3	300.2	300.1	300.0	299.7
137.5°	317.4	317.8	318.2	318.6	319.0	319.4	319.5	319.8	320.0	320.2	319.8
140°	330.7	331.1	331.5	331.9	332.3	332.6	332.6	332.7	332.8	332.9	332.8
142.5°	342.8	343.2	343.6	344.1	344.5	344.7	344.9	345.0	345.2	345.3	345.2
145°	361.7	361.9	362.1	362.2	362.4	362.6	362.8	363.1	363.3	363.5	363.5
147.5°	378.3	378.5	378.9	379.1	379.4	379.7	379.9	380.2	380.4	380.7	380.7
150°	389.8	390.0	390.1	390.3	390.4	390.6	390.8	390.9	391.1	391.3	391.3
152.5°	399.3	399.5	399.7	399.9	400.1	400.3	400.4	400.6	400.6	400.7	400.9
155°	414.2	414.2	414.2	414.2	414.2	414.3	414.3	414.4	414.5	414.6	414.9
157.5°	426.9	426.8	426.7	426.6	426.5	426.5	426.6	426.6	426.6	426.7	427.1
160°	434.9	434.7	434.6	434.4	434.2	434.1	434.1	434.1	434.1	434.1	434.6
162.5°	442.0	441.7	441.5	441.2	441.1	441.0	441.0	441.1	441.2	441.2	441.6
165°	451.1	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.5
167.5°	458.4	458.1	457.8	457.5	457.1	457.0	457.1	457.1	457.2	457.2	457.8
170°	462.6	462.3	461.9	461.6	461.3	461.1	461.1	461.1	461.1	461.1	461.7
172.5°	465.9	465.5	465.2	464.9	464.5	464.3	464.3	464.3	464.3	464.3	464.9
175°	469.2	468.9	468.6	468.2	467.9	467.7	467.7	467.7	467.7	467.7	468.2
177.5°	470.7	470.3	470.1	469.9	469.6	469.4	469.4	469.4	469.4	469.4	469.9
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3



TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	16.6	16.6	16.5	16.4	16.5	16.5	16.6	16.6
90°	9.5	9.9	10.2	10.4	10.6	10.8	10.9	11.1
92.5°	14.7	15.0	15.2	15.3	15.2	15.1	15.0	14.9
95°	28.0	28.3	28.6	28.8	28.8	28.8	28.8	28.8
97.5°	43.5	43.9	44.3	44.4	44.4	44.4	44.4	44.4
100°	54.8	55.0	55.3	55.5	55.7	55.8	56.0	56.2
102.5°	67.8	68.1	68.3	68.4	68.4	68.3	68.3	68.2
105°	87.2	87.2	87.2	87.2	87.5	87.6	87.8	88.0
107.5°	108.2	108.4	108.7	108.8	108.7	108.6	108.5	108.4
110°	122.2	122.5	122.9	122.9	122.8	122.6	122.5	122.3





TEST NUMBER: P332155-930

CATALOG NUMBER: S123DIW-S775D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	136.2	136.6	137.1	137.2	137.1	137.1	137.1	137.1
115°	157.6	157.7	157.8	157.8	157.7	157.6	157.5	157.4
117.5°	179.1	179.0	179.0	179.0	178.7	178.5	178.2	178.0
120°	193.5	193.4	193.3	193.1	193.0	192.8	192.7	192.5
122.5°	208.0	207.7	207.5	207.3	207.1	206.8	206.6	206.4
125°	229.5	229.2	228.9	228.5	228.2	227.9	227.6	227.2
127.5°	250.9	250.4	249.9	249.5	249.2	248.7	248.3	248.0
130°	265.0	264.6	264.3	263.9	263.3	262.8	262.2	261.5
132.5°	278.8	278.3	277.9	277.5	277.1	276.6	276.2	275.7
135°	299.4	299.1	298.7	298.5	298.3	298.2	298.0	297.8
137.5°	319.5	319.2	318.8	318.5	318.1	317.9	317.6	317.2
140°	332.7	332.6	332.6	332.2	331.7	331.1	330.5	330.0
142.5°	345.1	345.0	345.0	344.7	344.3	343.8	343.4	342.9
145°	363.4	363.3	363.2	363.1	362.7	362.4	362.1	361.7
147.5°	380.7	380.7	380.7	380.4	379.9	379.4	378.9	378.4
150°	391.3	391.3	391.3	391.0	390.5	390.0	389.6	389.1
152.5°	401.0	401.1	401.3	401.1	400.7	400.2	399.8	399.4
155°	415.2	415.6	415.9	415.7	415.2	414.6	414.0	413.4
157.5°	427.5	427.8	428.1	428.0	427.6	427.1	426.6	426.2
160°	435.0	435.4	435.8	435.8	435.5	435.1	434.8	434.5
162.5°	442.1	442.5	442.9	442.8	442.3	441.7	441.2	440.7
165°	451.0	451.5	452.0	451.9	451.3	450.8	450.2	449.6
167.5°	458.3	458.8	459.3	459.3	458.8	458.3	457.8	457.2
170°	462.3	462.8	463.4	463.4	462.8	462.3	461.7	461.1
172.5°	465.4	465.9	466.4	466.4	465.8	465.2	464.6	464.1
175°	468.7	469.2	469.7	469.7	469.1	468.6	468.0	467.4
177.5°	470.3	470.7	471.0	471.0	470.5	470.1	469.6	469.1
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3

(END OF REPORT)